

Wall Mount Adapters

Desktop

5W to 10W	12W	18W	24W	36W	36W to 60W	65W to 70W	85W to 90W	100W to 160W	200W	250W	300W
<p>VFR05</p> <ul style="list-style-type: none"> • 5W • 55.1 x 37.0 x 42.9mm • Level VI & CoC Tier 2 • LPS approved • Changeable input plugs 	<p>ACM12</p> <ul style="list-style-type: none"> • 12W • 76.0 x 30.3 x 48.2mm • Level VI & CoC Tier 2 • 2 x MOPP • Optional white case 	<p>AMF18</p> <ul style="list-style-type: none"> • 18W • 90.5 x 33.5 x 58.5mm • Home healthcare approval • 2 x MOPP • Optional white case 	<p>AMF24</p> <ul style="list-style-type: none"> • 24W • 90.5 x 33.5 x 58.5mm • Home healthcare approval • 2 x MOPP • Optional white case 	<p>AMF36</p> <ul style="list-style-type: none"> • 36W • 90.5 x 33.5 x 58.5mm • Home healthcare approval • 2 x MOPP • Optional white case 	<p>AKM36</p> <ul style="list-style-type: none"> • 36W • 108.0 x 50.0 x 33.8mm • Level VI & CoC Tier 2 • 2 x MOPP • Optional white case 	<p>AKM65</p> <ul style="list-style-type: none"> • 65W • 125.0 x 62.3 x 34.0mm • Home healthcare approval • 2 x MOPP • Optional white case 	<p>ALM85</p> <ul style="list-style-type: none"> • 85W • 116.3 x 52.4 x 31.3mm • Level VI & CoC Tier 2 • 2 x MOPP • IP32 rating 	<p>AEJ100</p> <ul style="list-style-type: none"> • 100W • 141.0 x 58.0 x 39.5mm • Level VI & CoC Tier 2 • 65°C operation • Active PFC 	<p>AQM200</p> <ul style="list-style-type: none"> • 200W • 166.5 x 54.2 x 33.0mm • Home healthcare approval • IP22 rating • Class I & II 	<p>AQM250</p> <ul style="list-style-type: none"> • 250W • 173.0 x 67.0 x 32.0mm • Home healthcare approval • IP22 rating • Class I & II 	<p>AQM300</p> <ul style="list-style-type: none"> • 300W • 183.0 x 85.0 x 35.0mm • Home healthcare approval • IP22 rating • Class I & II
<p>VFL05</p> <ul style="list-style-type: none"> • 5W • 55.1 x 24.1 x 35.5mm • Level VI & CoC Tier 2 • LPS approved • Low cost 	<p>VEL12</p> <ul style="list-style-type: none"> • 12W • 76.0 x 29.5 x 39.4mm • Level VI & CoC Tier 2 • LPS approved • Low cost 	<p>ACM18</p> <ul style="list-style-type: none"> • 18W • 88.0 x 30.0 x 49.5mm • Level VI & CoC Tier 2 • 2 x MOPP • Optional white case 	<p>ACM24</p> <ul style="list-style-type: none"> • 24W • 88.0 x 30.0 x 57.0mm • Level VI & CoC Tier 2 • 2 x MOPP • Optional white case 	<p>ACM36</p> <ul style="list-style-type: none"> • 36W • 96.7 x 33.0 x 59.5mm • Level VI & CoC Tier 2 • 2 x MOPP • Optional white case 	<p>AEK40</p> <ul style="list-style-type: none"> • 40W • 107.0 x 47.0 x 30.1mm • Level VI & CoC Tier 2 • 5V to 48V outputs • Class I 	<p>ALM65</p> <ul style="list-style-type: none"> • 65W • 116.3 x 52.4 x 31.3mm • Level VI • 2 x MOPP • Class I & II 	<p>VES90</p> <ul style="list-style-type: none"> • 90W • 139.0 x 58.0 x 31.0mm • Level VI & CoC Tier 2 • CCC qualified • Low cost 	<p>ALM120</p> <ul style="list-style-type: none"> • 120W • 140.0 x 71.0 x 22.0mm • Level VI & CoC Tier 2 • CCC qualified • 2 x MOPP 	<p>ALM200</p> <ul style="list-style-type: none"> • 200W • 209.0 x 82.0 x 43.0mm • Home healthcare approval • IP32 rating • Class I & II 	<p>AHM250</p> <ul style="list-style-type: none"> • 250W • 223.0 x 88.5 x 38.6mm • Level V • IP22 rating • Low profile 	<p>VES300</p> <ul style="list-style-type: none"> • 300W • 197.4 x 88.9 x 39.0mm • Level VI & CoC Tier 2 • CCC qualified • Low cost
<p>ACM06</p> <ul style="list-style-type: none"> • 6W • 73.5 x 30.7 x 42.5mm • Level VI & CoC Tier 2 • 2 x MOPP • Optional white case 	<p>VER12</p> <ul style="list-style-type: none"> • 12W • 76.5 x 41.0 x 37.6mm • Level VI & CoC Tier 2 • LPS approved • Changeable input plugs 	<p>VEL18</p> <ul style="list-style-type: none"> • 18W • 90.0 x 34.0 x 47.5mm • Level VI & CoC Tier 2 • LPS approved • Low cost 	<p>VEL24</p> <ul style="list-style-type: none"> • 24W • 90.0 x 34.0 x 47.5mm • Level VI & CoC Tier 2 • LPS approved • Low cost 	<p>VEL36</p> <ul style="list-style-type: none"> • 36W • 94.0 x 35.0 x 46.6mm • Level VI & CoC Tier 2 • LPS approved • Low cost 	<p>VEC40</p> <ul style="list-style-type: none"> • 40W • 116.3 x 52.4 x 31.3mm • Level VI & CoC Tier 2 • CCC qualified • LPS approved 	<p>VEC65</p> <ul style="list-style-type: none"> • 65W • 116.3 x 52.4 x 31.3mm • Level VI & CoC Tier 2 • CCC qualified • LPS approved 	<p>AKM90</p> <ul style="list-style-type: none"> • 90W • 125.0 x 62.3 x 34.0mm • Level VI & CoC Tier 2, EU2019/1782 • 2 x MOPP • Class I & II 	<p>VES120</p> <ul style="list-style-type: none"> • 120W • 168.0 x 71.0 x 37.5mm • Level VI & CoC Tier 2 • CCC qualified • Low cost 			
<p>VEU10</p> <ul style="list-style-type: none"> • 2.1A USB A socket • 50.8 x 37.0 x 22.0mm • Level VI & CoC Tier 2 • Low cost • Class II 			<p>VER24</p> <ul style="list-style-type: none"> • 24W • 90.5 x 42.0 x 42.7mm • Level VI & CoC Tier 2 • LPS approved • Changeable input plugs 	<p>VER36</p> <ul style="list-style-type: none"> • 36W • 94.5 x 47.0 x 43.9mm • Level VI & CoC Tier 2 • LPS approved • Low cost 	<p>AKM45</p> <ul style="list-style-type: none"> • 45W • 122.4 x 51.4 x 31.5mm • Home healthcare approval • 2 x MOPP • Optional white case 	<p>AEJ70</p> <ul style="list-style-type: none"> • 70W • 120.0 x 52.0 x 31.0mm • Level VI & CoC Tier 2 • 65°C operation • Class I 	<p>AJM90</p> <ul style="list-style-type: none"> • 90W • 140.0 x 71.0 x 22.0mm • Level VI • Slim profile • Class II 	<p>ALM150</p> <ul style="list-style-type: none"> • 150W • 186.0 x 72.0 x 38.0mm • Home healthcare approval • IP32 rating • Class I & II 			
					<p>VEC50</p> <ul style="list-style-type: none"> • 50W • 116.3 x 52.4 x 31.3mm • Level VI & CoC Tier 2 • CCC Qualified • LPS approved 				<p>AEJ160</p> <ul style="list-style-type: none"> • 160W • 150.0 x 70.0 x 38.0mm • Level VI & CoC Tier 2 • 65°C operation • Active PFC 		
					<p>AEK60</p> <ul style="list-style-type: none"> • 60W • 118.0 x 47.0 x 30.1mm • Level VI & CoC Tier 2 • <0.15W standby power • Class I 						