

Wall Mount Adapters

Desktop

6W to 10W	12W	18W	24W	36W	36W to 60W	65W to 70W	85W to 90W	100W to 160W	200W	250W	300W
<p>ACM06</p> <ul style="list-style-type: none"> • 6W • 2.89" x 1.67" x 1.21" • Level VI & CoC Tier 2 • 2 x MOPP • Optional White Case 	<p>ACM12</p> <ul style="list-style-type: none"> • 12W • 2.99" x 1.19" x 1.91" • Level VI & CoC Tier 2 • 2 x MOPP • Optional White Case 	<p>AMF18</p> <ul style="list-style-type: none"> • 18W • 3.56" x 1.32" x 2.30" • Home Healthcare Approval • 2 x MOPP • Optional White Case 	<p>AMF24</p> <ul style="list-style-type: none"> • 24W • 3.56" x 1.32" x 2.30" • Home Healthcare Approval • 2 x MOPP • Optional White Case 	<p>AMF36</p> <ul style="list-style-type: none"> • 36W • 3.56" x 1.32" x 2.30" • Home Healthcare Approval • 2 x MOPP • Optional White Case 	<p>AKM36</p> <ul style="list-style-type: none"> • 36W • 4.25" x 1.97" x 1.33" • Level VI & CoC Tier 2 • 2 x MOPP • Optional White Case 	<p>AKM65</p> <ul style="list-style-type: none"> • 65W • 4.92" x 2.45" x 1.34" • Home Healthcare Approval • 2 x MOPP • Optional White Case 	<p>ALM85</p> <ul style="list-style-type: none"> • 85W • 5.31" x 2.44" x 1.45" • Level VI & CoC Tier 2 • 2 x MOPP • IP32 Rating 	<p>AEJ100</p> <ul style="list-style-type: none"> • 100W • 5.59" x 2.28" x 1.48" • Level VI & CoC Tier 2 • 65°C Operation • Active PFC 	<p>AQM200</p> <ul style="list-style-type: none"> • 200W • 6.56" x 1.30" x 2.13" • Home Healthcare Approval • IP22 Rating • Class I & II 	<p>AQM250</p> <ul style="list-style-type: none"> • 250W • 6.80" x 1.26" x 2.64" • Home Healthcare Approval • IP22 Rating • Class I & II 	<p>AQM300</p> <ul style="list-style-type: none"> • 300W • 7.20" x 1.38" x 3.35" • Home Healthcare Approval • IP22 Rating • Class I & II
<p>VEU10</p> <ul style="list-style-type: none"> • 2.1A USB A Socket • 1.45" x 0.86" x 2.0" • Level VI & CoC Tier 2 • Low Cost • Class II 	<p>VEL12</p> <ul style="list-style-type: none"> • 12W • 2.99" x 1.16" x 1.55" • Level VI & CoC Tier 2 • LPS Approved • Low Cost 	<p>ACM18</p> <ul style="list-style-type: none"> • 18W • 3.46" x 1.18" x 1.95" • Level VI & CoC Tier 2 • 2 x MOPP • Optional White Case 	<p>ACM24</p> <ul style="list-style-type: none"> • 24W • 3.46" x 1.18" x 2.24" • Level VI & CoC Tier 2 • 2 x MOPP • Optional White Case 	<p>ACM36</p> <ul style="list-style-type: none"> • 36W • 3.81" x 1.30" x 2.34" • Level VI & CoC Tier 2 • 2 x MOPP • Optional White Case 	<p>AEK40</p> <ul style="list-style-type: none"> • 40W • 4.21" x 1.85" x 1.19" • Level VI & CoC Tier 2 • 5V to 48V Outputs • Class I 	<p>ALM65</p> <ul style="list-style-type: none"> • 65W • 4.94" x 2.19" x 1.32" • Level VI • 2 x MOPP • Class I & II 	<p>VES90</p> <ul style="list-style-type: none"> • 90W • 5.47" x 2.28" x 1.22" • Level VI & CoC Tier 2 • CCC Qualified • Low Cost 	<p>ALM120</p> <ul style="list-style-type: none"> • 120W • 6.61" x 2.80" x 1.48" • Level VI & CoC Tier 2 • CCC Qualified • 2 x MOPP 	<p>ALM200</p> <ul style="list-style-type: none"> • 200W • 8.23" x 3.32" x 1.69" • Home Healthcare Approval • IP32 Rating • Class I & II 	<p>AHM250</p> <ul style="list-style-type: none"> • 250W • 8.80" x 3.48" x 1.46" • Level V • IP22 Rating • Low Profile 	<p>VES300</p> <ul style="list-style-type: none"> • 300W • 7.77" x 3.50" x 1.53" • Level VI & CoC Tier 2 • CCC Qualified • Low Cost
	<p>VER12</p> <ul style="list-style-type: none"> • 12W • 3.01" x 1.61" x 1.48" • Level VI & CoC Tier 2 • LPS Approved • Changeable Input Plugs 	<p>VEL18</p> <ul style="list-style-type: none"> • 18W • 3.54" x 1.34" x 1.87" • Level VI & CoC Tier 2 • LPS Approved • Low Cost 	<p>VEL24</p> <ul style="list-style-type: none"> • 24W • 3.54" x 1.34" x 1.87" • Level VI & CoC Tier 2 • LPS Approved • Low Cost 	<p>VEL36</p> <ul style="list-style-type: none"> • 36W • 3.70" x 1.38" x 1.83" • Level VI & CoC Tier 2 • LPS Approved • Low Cost 	<p>VEC40</p> <ul style="list-style-type: none"> • 40W • 4.58" x 2.06" x 1.23" • Level VI & CoC Tier 2 • CCC Qualified • LPS Approved 	<p>VEC65</p> <ul style="list-style-type: none"> • 65W • 4.58" x 2.06" x 1.23" • Level VI & CoC Tier 2 • CCC Qualified • LPS Approved 	<p>AKM90</p> <ul style="list-style-type: none"> • 90W • 5.96" x 2.36" x 1.46" • CoC Tier 2, EU2019/1782 • 2 x MOPP • Class I & II 	<p>VES120</p> <ul style="list-style-type: none"> • 120W • 6.61" x 2.80" x 1.48" • Level VI & CoC Tier 2 • CCC Qualified • Low Cost 			
			<p>VER24</p> <ul style="list-style-type: none"> • 24W • 3.54" x 1.69" x 1.68" • Level VI & CoC Tier 2 • LPS Approved • Changeable Input Plugs 	<p>VER36</p> <ul style="list-style-type: none"> • 36W • 3.72" x 1.85" x 1.71" • Level VI & CoC Tier 2 • LPS Approved • Low Cost 	<p>AKM45</p> <ul style="list-style-type: none"> • 45W • 4.82" x 2.02" x 1.24" • Home Healthcare Approval • 2 x MOPP • Optional White Case 	<p>AEJ70</p> <ul style="list-style-type: none"> • 70W • 4.72" x 2.05" x 1.22" • Level VI & CoC Tier 2 • 65°C Operation • Class I 	<p>AJM90</p> <ul style="list-style-type: none"> • 90W • 5.51" x 2.80" x 0.87" • Level VI • Slim Profile • Class II 	<p>ALM150</p> <ul style="list-style-type: none"> • 150W • 7.32" x 2.84" x 1.49" • Home Healthcare Approval • IP32 Rating • Class I & II 			
					<p>VEC50</p> <ul style="list-style-type: none"> • 50W • 4.58" x 2.06" x 1.23" • Level VI & CoC Tier 2 • CCC Qualified • LPS Approved 			<p>AEJ160</p> <ul style="list-style-type: none"> • 160W • 5.91" x 2.76" x 1.50" • Level VI & CoC Tier 2 • 65°C Operation • Active PFC 			
					<p>AEK60</p> <ul style="list-style-type: none"> • 60W • 4.65" x 1.85" x 1.19" • Level VI & CoC Tier 2 • <0.15W Standby Power • Class I 						