

PTC 2016~2021出貨到Avnet含有REACH SVHC清單
PTC 2016~2021 shipped to Avnet contains REACH SVHC list

料碼(P/No.):	物質名稱 Substance Name	化學文摘號碼 CAS No.	歐洲委員會號碼 EC No.	Substance Location	Concentration (ppm)	Concentration (g)
PC0802LRS-AWA-B-Q	2-(2H-benzotriazol-2-yl)-4,6-ditertpentylphenol (UV-328)	25973-55-1	247-384-8	Down polarizer	6390	0.00490113
	Lead oxide (lead monoxide)	1317-36-8	215-267-0	Resistor	2608.96	0.000168641
PC1602LRS-CWA-H-Q	Lead oxide (lead monoxide)	1317-36-8	215-267-0	Resistor	2608.96	0.000192733
PC1602LRS-FWA-B-Q	2-(2H-benzotriazol-2-yl)-4,6-ditertpentylphenol (UV-328)	25973-55-1	247-384-8	Down polarizer	6390	0.00764244
	Lead oxide (lead monoxide)	1317-36-8	215-267-0	Resistor	2608.96	0.000192733
PC1602LRU-CWA-H-Q	Lead oxide (lead monoxide)	1317-36-8	215-267-0	Resistor	2608.96	0.000192733
PC1602LRU-DWA-B-Q	2-(2H-benzotriazol-2-yl)-4,6-ditertpentylphenol (UV-328)	25973-55-1	247-384-8	Down polarizer	6390	0.00764244
	Lead oxide (lead monoxide)	1317-36-8	215-267-0	Resistor	2608.96	0.000192733
PC1602LRU-FWA-K03Q	Lead oxide (lead monoxide)	1317-36-8	215-267-0	Resistor	2608.96	0.000216825
PC1602LRU-KWA-BY5Q	Lead oxide (lead monoxide)	1317-36-8	215-267-0	Resistor	2608.96	0.00014455
PC2004LRU-CWA-B-Q	Lead oxide (lead monoxide)	1317-36-8	215-267-0	Resistor	2608.96	0.000112533
PC2004LRS-AWA-B-Q	Lead oxide (lead monoxide)	1317-36-8	215-267-0	Resistor	2608.96	0.000192733
PC2402LRU-AWA-B-Q	2-(2H-benzotriazol-2-yl)-4,6-ditertpentylphenol (UV-328)	25973-55-1	247-384-8	Down polarizer	8140	0.015873
	Lead oxide (lead monoxide)	1317-36-8	215-267-0	Resistor	2608.96	0.000168641
PC2402LRU-LWA-B-Q	Lead oxide (lead monoxide)	1317-36-8	215-267-0	Resistor	2608.96	0.000168641
PC4002LRS-BWA-B-Q	Lead oxide (lead monoxide)	1317-36-8	215-267-0	Resistor	2608.96	0.000192733
PC4002LRU-BWA-B-Q	Lead oxide (lead monoxide)	1317-36-8	215-267-0	Resistor	2608.96	0.000192733
PE12864LRF-027-B-Q	2-(2H-benzotriazol-2-yl)-4,6-ditertpentylphenol (UV-328)	25973-55-1	247-384-8	Down polarizer	8140	0.010042318
PG12864WYF-JCNHY4Q	Lead oxide (lead monoxide)	1317-36-8	215-267-0	Resistor	2608.96	0.000135709
PG240128LRUATBHY2Q	Lead oxide (lead monoxide)	1317-36-8	215-267-0	Resistor	2608.96	0.00032418
PG24064LRF-EGAHP5Q	2-(2H-benzotriazol-2-yl)-4,6-ditertpentylphenol (UV-328)	25973-55-1	247-384-8	Down polarizer	8140	0.05322746
	Lead oxide (lead monoxide)	1317-36-8	215-267-0	Resistor	2608.96	0.000200059
PG24064WRF-EGAH16Q	2-(2H-benzotriazol-2-yl)-4,6-ditertpentylphenol (UV-328)	25973-55-1	247-384-8	Down polarizer	8140	0.05322746
	Lead oxide (lead monoxide)	1317-36-8	215-267-0	Resistor	2608.96	0.000212562
PG320240WRFHBAHS1Q	Lead oxide (lead monoxide)	1317-36-8	215-267-0	Resistor	2608.96	0.000161632
PH102600T009-IBA02	Lead oxide (lead monoxide)	1317-36-8	215-267-0	Resistor	2608.96	5.13356E-05
PH102600T009-IBC03	Lead oxide (lead monoxide)	1317-36-8	215-267-0	Resistor	2608.96	5.13356E-05
PH102600T009-IBC04	Lead oxide (lead monoxide)	1317-36-8	215-267-0	Resistor	2608.96	5.13356E-05
PH102600T009-IBC07	Lead oxide (lead monoxide)	1317-36-8	215-267-0	Resistor	2608.96	0.000164099
PH128800T004-ZZR01	Lead oxide (lead monoxide)	1317-36-8	215-267-0	Resistor	2608.96	0.000467724
PH320240T-006-I57Q	Lead oxide (lead monoxide)	1317-36-8	215-267-0	Resistor	2608.96	3.65583E-05
PH320240T-006-I-Q	Lead oxide (lead monoxide)	1317-36-8	215-267-0	Resistor	2608.96	3.65583E-05

PTC 2016~2021出貨到Avnet含有REACH SVHC清單
 PTC 2016~2021 shipped to Avnet contains REACH SVHC list

料碼(P/No.):	物質名稱 Substance Name	化學文摘號碼 CAS No.	歐洲委員會號碼 EC No.	Substance Location	Concentration (ppm)	Concentration (g)
PH320240T-009-IC1Q	Lead oxide (lead monoxide)	1317-36-8	215-267-0	Resistor	2608.96	0.000250074
PH320240T-023-I03Q	Lead oxide (lead monoxide)	1317-36-8	215-267-0	Resistor	2608.96	1.71119E-05
PH320240T023-IHA03	Lead oxide (lead monoxide)	1317-36-8	215-267-0	Resistor	2608.96	5.70396E-06
PH480272T-005-I01Q	Lead oxide (lead monoxide)	1317-36-8	215-267-0	Resistor	2608.96	4.56316E-05
PH480272T-005-I10Q	Lead oxide (lead monoxide)	1317-36-8	215-267-0	Resistor	2608.96	5.78787E-05
PH480272T-005-I11Q	Lead oxide (lead monoxide)	1317-36-8	215-267-0	Resistor	2608.96	4.56316E-05
PH480272T005-IAB05	Lead oxide (lead monoxide)	1317-36-8	215-267-0	Backlight current limit	2608.96	0.00248457
PH480272T005-IAC01	Lead oxide (lead monoxide)	1317-36-8	215-267-0	Backlight current limit	2608.96	0.00248457
PH480272T009-IHB	Lead oxide (lead monoxide)	1317-36-8	215-267-0	Resistor	2608.96	5.83393E-05
PH720128T003-ZBC02	Lead oxide (lead monoxide)	1317-36-8	215-267-0	Backlight current limit	2608.96	1.94464E-05
PH800480T013-IHC08	Lead oxide (lead monoxide)	1317-36-8	215-267-0	Resistor	2608.96	0.000317389
PH800480T013-IHF19	Lead oxide (lead monoxide)	1317-36-8	215-267-0	Resistor	2608.96	0.000125487
PH800480T013-IHC23	Lead	7439-92-1	231-100-4	Variable Resistance	1873.54	0.000072
	Lead oxide (lead monoxide)	1317-36-8	215-267-0	Resistor	2608.96	0.000394102