

# TLF35584QWS2 NEW

- [Overview](#)
- [Parametrics](#)
- [Order](#)
- [Support](#)

Parametric	TLF35584QWS2
Comments	Buck/Boost PreReg; 3linear PostRegs ( $\mu$ C, RefLDO, TRX); 2 tracker; StBy-LDO; ISO26262-compliant; Safety Features
V <sub>Q</sub> (multiple)	3.3V/5.0V, 5.0V, 5.0V
I <sub>q</sub>	70.0 $\mu$ A
Regulator Type	DC/DC->BuckBoost
Tolerance	2%
Watchdog	Window-WD & Functional-WD
Protect	Y
Reset	yes
Inhibit	Y
Operating Temperature <b>min max</b>	-40.0°C 150.0°C
Mounting	SMT

Follow us



© 1999 - 2017 Infineon Technologies AG, 苏ICP备15016286号

[Usage of this website is subject to our Usage Terms](#) > [Imprint](#) > [Contact](#) > [Privacy Policy](#) > [Glossary](#)

[Switch to Mobile Version](#)

This site uses cookies. By accepting cookies you can optimize your browsing experience. Please read our [Privacy Policy](#) for more information.

OK