



/ LEAD-TIME GUIDE  
JULY 2024

## POWER

Product	Lead-time: weeks	Lead-time: prognosis
AC-DC PSU general purpose	20 - 48	=
AC-DC PSU medical	20 - 48	=
AC-DC PSU DIN rail	20 - 48	=
Rectifiers & front-end PSU	22 - 48	=
AC-DC external-adaptors	20 - 48	=
AC-DC railway	20 - 48	=
AC-DC LED drivers general	20 - 48	=
AC-DC LED drivers special	20 - 48	=
DC-DC miniature	12 - 36	=
DC-DC industrial & bricks	12 - 48	=
DC-DC panel mount	12 - 48	=
DC-DC LED drivers	12 - 48	=

## FILTER & MAGNETICS

Product	Average lead-time	Lead-time: prognosis
Active filter	10	=
EMI filter	10	=
Power line filter	10	=
SAW filter	14 - 38	=
Ceramic filter	10	=
EMI/RFI filter	10	=
RF filter	10	=
Common mode chokes	10 - 30	↑
Ferrite chip beads	10 - 12	=
Ferrite core	12 - 42	=
Inductor leaded	10 - 14+	=
Wireless charging coils	16 - 18	=
Inductor surface mount	8 - 80	↑

## ELECTROMECHANICAL

Product	Lead-time: weeks	Lead-time: prognosis
Switches	10 - allocation	=
Relays general purpose	35 - allocation	19 - allocation
Relays automotive/telecom	35 - allocation	19 - allocation
Fans	19 - 52	=
Heatsinks	8 - 12	=
Sensors	10 - allocation	=

## CONNECTORS

Product	Average lead-time	Lead-time: prognosis
Cable flat	13	=
Backplanes DIN 41612; 2MM; high speed; power signal;	14	↑
I/O connectors	14	=
Memory card reader	14	=
Sockets DIP/SIP; PLCC/PGA/BGA; SIMM/IMM/Holtite	19	=
Non-solderable terminals/fastons	9	=
Circular military	21	↑
Circular industrial	17	=
Circular medical	17	=
Rectangular military	21	↑
Rectangular industrial	17	=
Rectangular medical	15	=
RF coaxial	15	=
Board to board	15	=
Wire to board/wire to wire	15	=
Automotive	19	↑
Power - connector systems	19	=

## PASSIVE

Product	Lead-time: weeks	Lead-time: prognosis
Ceramic capacitors single layer	10 - 24	=
Ceramic capacitors leaded multilayer	20 - 30	=
Ceramic capacitors multilayer SMD	8 - 20+	↓
Ceramic capacitors multilayer high CV	8 - 20+	↓
Ceramic capacitors safety caps	16 - 30	=
Ceramic capacitors trimmer caps	16 - 30	=
Ceramic capacitors automotive	8 - 20+	↓
Aluminium electrolytic capacitors leaded	8 - 26+	↓
Aluminium electrolytic capacitors SMD	8 - 26+	↓
Aluminium electrolytic capacitors snap-in & large can	8 - 26+	↓
Film capacitors leaded	8 - 16+	↓
Film capacitors SMD	8 - 16+	↓
Film capacitors suppression	8 - 26+	↓
Polymer capacitors	8 - 26+	↓
Tantalum capacitors leaded	8 - 16	↓
Tantalum capacitors SMD	8 - 16	↓
Resistor SMD	16 - 20+	=
Resistor MELF/Metal film	14 - 20+	=
Resistor NLR	18 - 20	↑
Resistor Potentiometer	16 - 20	=
Resistor Trimmer	14 - 16	=
Resistor Varistor	14 - 22	↑
Resistor Wirewound	16 - 18	=
Resistor Networks/Arrays	18 - 20	=
Circuit protection - fuses	8 - 26+	=
Circuit protection - resettable devices	8 - 26+	=
Circuit protection - thermistors	8 - 26+	=
Circuit protection - varistors	8 - 26+	=
Antennas	12 - 30+	=
Frequency control crystals/ oscillators	12 - 30+	=
Frequency control resonators	8 - 14	=
Electromagnetic piezo buzzers, sounders and transducers	8 - 14	=

## AUSTRIA

Avnet EMG Elektronische Bauelemente GmbH  
Grünbergstraße 15/1/4.OG,  
A-1120 Wien  
Phone: +43 (0)1 86642-0  
Fax: +43 (0)1 86642-250  
wien@avnet-abacus.eu

## BELGIUM

De Kleetlaan 3  
BE-1831 Diegem  
Phone: +32 2 227 2000  
diegem@avnet-abacus.eu

## BULGARIA

48, Sitnyakovo Boulevard  
Unit 1006, Floor 10,  
BG-1505 Sofia  
Phone: +359 896 135 069  
bulgaria@avnet-abacus.eu

## CROATIA

c/o Avnet Abacus Slovenia  
Dunajska Cesta 167  
SI-1000 Ljubljana  
Phone: +386 (0)1 560 97 54  
Fax: +386 (0)1 560 98 78  
croatia@avnet-abacus.eu

## CZECH REPUBLIC

Amazon Court Karolinska 661/4  
CZ-18600 Prague  
Phone: +420 234 091 011  
Fax: +420 234 091 010  
praha@avnet-abacus.eu

## DENMARK

Knudlundvej 24, DK-8653 Them  
Phone: +45 86 84 84 84  
Fax: +45 86 84 82 44  
them@avnet-abacus.eu

Lyskær 9, DK-2730 Herlev  
Phone: +45 86 84 84 84  
Fax: +45 43 29 37 00  
herlev@avnet-abacus.eu

## EGYPT

c/o Avnet Abacus Turkey  
Tatlısu Mahallesi Pakdil  
Sokak No: 7 Kat: 2  
TR-34774 Umraniye Istanbul Turkiye  
Phone: +90 216 52 88 370  
Fax: +90 216 52 88 377  
egypt@avnet-abacus.eu

## ESTONIA

Suur-Jõe 63, Pärnu,  
EE-80042 Pärnu Maakond  
Phone: +372 56637737  
paernu@avnet-abacus.eu

## FINLAND

Klovinpellontie 1-3  
Tower 1, Floor 6  
FI-02180 Espoo  
Phone: +35 820 749 9220  
Fax: +35 820 749 9240  
espoo@avnet-abacus.eu

## FRANCE

Le Copernic  
12, rue Jean Bart  
FR-91300 Massy  
Phone: +33 (0) 1 6447 2929  
Fax: +33 (0) 1 6447 9150  
paris@avnet-abacus.eu

8 chemin de la Terrasse  
Bat D 1er étage  
FR-31500 Toulouse  
Phone: +33 (0) 5 6247 4787  
Fax: +33 (0) 5 6247 4761  
toulouse@avnet-abacus.eu

16 C Rue de Jouanet  
FR-35700 Rennes  
Phone: +33 (0) 2 9983 7720  
Fax: +33 (0) 2 9983 4829  
rennes@avnet-abacus.eu

2 avenue Tony Garnier, 3rd floor  
FR-69007 Lyon  
Phone: +33 (0) 4 7877 1370  
Fax: +33 (0) 4 7877 1391  
lyon@avnet-abacus.eu

## GERMANY

Kaiserin-Augusta-Allee 14  
DE-10553 Berlin  
Phone: +49 (0) 30 790 997 0  
Fax: +49 (0) 30 790 997 51  
berlin@avnet-abacus.eu

Industriestr. 16  
DE-76297 Stutensee  
Phone: +49 (0) 7249 910 149  
Fax: +49 (0) 7249 910 177  
stutensee@avnet-abacus.eu

Rhenus-Platz 2  
D-59439 Holzwickede/Dortmund  
Phone: +49 (0) 2301 2959 27  
Fax: +49 (0) 2301 2959 29  
dortmund@avnet-abacus.eu

Ursula-de-Boor-Str. 45  
22419 Hamburg  
Phone: +49 (0) 40 608 23 59 0  
Fax: +49 (0) 40 608 23 59 20  
hamburg@avnet-abacus.eu

Im Technologiepark 2-8  
DE-85586 Poing  
Phone: +49 (0) 8121 775 400  
bayern@avnet.eu

Lina-Ammon-Str. 19 b  
DE-90471 Nuernberg  
Phone: +49 (0) 911 244 25 0  
Fax: +49 (0) 911 244 25 25  
bayern@avnet.eu

Neue Ramtelstr. 4  
DE-71229 Leonberg  
Phone: +49 (0) 7152 3009 70  
Fax: +49 (0) 7152 3009 96  
stuttgart@avnet-abacus.eu

Rotenburger Str. 20  
D-30659 Hannover  
Phone: +49 (0) 511 336517 10  
hannover@avnet-abacus.eu

## GREECE

c/o Abacus Avnet Serbia  
Milentija Popovića 5B,  
Floors 6-8  
Belgrade RS-11070  
Phone: +381 11 4022302  
Fax: +381 11 4049900  
belgrade@avnet-abacus.eu

## HUNGARY

c/o Avnet Abacus Slovakia  
GreenPoint Offices,  
Blok F Turcianska 2  
SK-82109 Bratislava  
Phone: +421 232 242 608  
Fax: +421 2 32 1111 40  
budapest@avnet-abacus.eu

## IRELAND

c/o Avnet Abacus Bolton  
Oceanic Building  
Waters Meeting Road  
Bolton BL1 8SW  
Phone: +44 (0)1204 547190  
Fax: +44 (0)1204 547171  
bolton@avnet.eu

## ISRAEL

1 Habrosh Street  
Bney Dror IL-4581500  
Phone: +972 9 778 0280  
Fax: +972 3 760 0794  
israel@avnet-abacus.eu

## ITALY

Via Manzoni 44  
IT-20095 Cusano Milanino/Milano  
Phone: +39 02 660 921  
Fax: +39 02 66092 332  
milano@avnet-abacus.eu

Viale dell'industria 23  
IT-35129 Padova  
Phone: +39 049 7800 381  
Fax: +39 049 7730 36  
padova@avnet-abacus.eu

Via Scaglia Est. 31/33  
IT-41126 Modena  
Phone: +39 059 34891  
Fax: +39 059 344 993  
modena@avnet-abacus.eu

Via Panciatici 40/11  
IT-50127 Firenze  
Phone: +39 055 436 1928  
Fax: +39 055 428 8810  
firenze@avnet-abacus.eu

Viale Luca Gaurico 9/11  
IT-00143 Roma  
Phone: +39 02 660 921  
rome@avnet-abacus.eu

## LATVIA

c/o Avnet Abacus Poland  
Plac Solny 16  
PL-50-062 Wroclaw  
Phone: +48 71 34 205 99  
Fax: +48 71 34 229 10  
latvia@avnet-abacus.eu

## LITHUANIA

c/o Avnet Abacus Poland  
Plac Solny 16  
PL-50-062 Wroclaw  
Phone: +48 71 34 205 99  
Fax: +48 71 34 229 10  
lithuania@avnet-abacus.eu

## NETHERLANDS

Stadionstraat 2, 6th floor  
NL-4815 NG Breda  
Phone: +31 (0) 76 57 22 300  
Fax: +31 (0) 76 57 22 303  
breda@avnet-abacus.eu

## NORWAY

Olaf Helsetsvæi 6,  
NO-0694 Oslo  
Phone: +47 (0) 94 89 53 73  
oslo@avnet-abacus.eu

## POLAND

Plac Solny 16  
PL-50-062 Wroclaw  
Phone: +48 71 34 205 99  
Fax: +48 71 34 229 10  
wroclaw@avnet-abacus.eu

## PORTUGAL

Tower Plaza, Rot. Eng. Edgar  
Cardoso, 23,Piso 14, Sala E  
PT-4400-676 Vila Nova de Gaia  
Phone: +351 223 779502  
Fax: +351 223 779503  
portugal@avnet-abacus.eu

## ROMANIA

SkyTower Building, 12th floor,  
Calea Floreasca 246C,  
RO-014476 Bucharest  
Phone: +4021 528 16 90  
romania@avnet-abacus.eu

## SERBIA

Milentija Popovića 5B, Floors 6-8  
Belgrade RS-11070  
Phone: +381 11 4022302  
Fax: +381 11 4049900  
belgrade@avnet-abacus.eu

## SLOVAKIA

GreenPoint Offices,  
Blok F Turcianska 2  
SK-82109, Bratislava  
Phone: +421 232 242 608  
Fax: +421 2 32 1111 40  
slovakia@avnet-abacus.eu

## SLOVENIA

Dunajska Cesta 167  
SI-1000 Ljubljana  
Phone: +386 (0)1 560 97 60  
Fax: +386 (0)1 560 98 78  
ljubljana@avnet-abacus.eu

## SOUTH AFRICA

Block 13, Pinewood Office Park  
33 Riley Road Woodmead,  
ZA-2191 Sandton, Johannesburg  
Phone: +27 (0)10 447 0180  
avnet-abacus-sales-southafrica@avnet.eu

## SPAIN

NyN Tower, C/Tarragona  
149-157, Floor 19  
ES-08014 Barcelona  
Phone: +34 (0) 93 327 85 50  
Fax: +34 (0) 93 425 05 44  
barcelona@avnet-abacus.eu

Avenida Madariaga 1  
Floor 3  
ES-48014 Bilbao  
Phone: +34 (0) 94 457 00 44  
Fax: +34 (0) 94 456 88 55  
bilbao@avnet-abacus.eu

Ronda de Poniente  
(pq Empresarial Euronova),  
4 - 2ª PLANTA, tres Cantos,  
28760, Madrid  
madrid@avnet-abacus.eu

## SWEDEN

Avnet Nortec AB  
Hemvärnsgatan 9  
SE-171 54 Solna  
Phone: +46 (0)8587 462 00  
Fax: +46 (0)8587 460 01  
stockholm@avnet-abacus.eu

Smörhålevägen 3  
SE-43442 Kungsbacka  
Phone: +46 (0)8 58746 200  
Fax: +46 (0)300 140 15  
gothenburg@avnet-abacus.eu

## SWITZERLAND

Bernstrasse 394  
CH-8953 Dietikon  
Phone: +41 (0)43 322 49 90  
Fax: +41 (0)43 322 49 99  
zurich@avnet-abacus.eu

## TURKEY

Tatlısu Mahallesi Pakdil  
Sokak No: 7 Kat: 2  
TR-34774 Umraniye Istanbul Turkiye  
Phone: +90 216 52 88 370  
Fax: +90 216 52 88 377  
istanbul@avnet-abacus.eu

## UK

Building 5, Waltham Park  
White Waltham  
Maidenhead Berkshire SL6 3TN  
Phone: +44 (0)1628 512900  
Fax: +44 (0)1628 512999  
maidenhead@avnet.eu

## UKRAINE

c/o Avnet Abacus Poland  
Plac Solny 16  
PL-50-062 Wroclaw  
Phone: +48 71 34 205 99  
Fax: +48 71 34 229 10  
ukraine@avnet-abacus.eu