

No: OER-220624-5511
Date: June 28, 2022

To: Avnet

Reply sheet for REACH SVHC on our product or parts

OMRON RELAY & DEVICES Corporation
Dep. Quality Environment Group.
Name: Deputy Group Manager, Fumiaki Tanaka (Person in charge : Rieko Hara)

We are pleased to inform you of the situation of SVHC in the REACH regulation ((EC)No 1907/2006) on our products or parts (including attached accessories, packaging materials) at the time of shipment from our factory, based on our collectable data.

- The following information is/are for 1 substances of SVHC which were published in Jun. 2022.
- The column of "SVHC Contained/Not contained" indicates the following state:
 "Contained": The content of SVHC exceeds 0.1wt%
 "Not contained": The content of SVHC is 0.1wt% or less than 0.1wt%
- The data of "CAS No.", "Substance name", "Content rate(wt%)", "Content quantity(mg)" are indicated only when the content of SVHC exceeds 0.1wt%.

- Note -

No.	Product type name	SVHC Contained/ Not contained	CAS No.	Substance name	Content rate (wt%)	Content quantity (mg)
1	G3VM-2FL	Not contained				
2	G3VM-353D	Not contained				
3	G3VM-353E	Not contained				
4	G3VM-353A	Not contained				
5	G3VM-353B	Not contained				
6	G3VM-354C	Not contained				
7	G3VM-601BY	Not contained				
8	G3VM-601EY	Not contained				
9	G3VM-354F	Not contained				
10	G3VM-601EY(TR)	Not contained				
11	G3VM-401E(TR)	Not contained				
12	G3VM-401BY	Not contained				
13	G3VM-401EY	Not contained				
14	G3VM-21GR1	Not contained				
15	G3VM-41GR4	Not contained				
16	G3VM-41GR6	Not contained				
17	G3VM-41GR6(TR)	Not contained				
18	G3VM-353G	Not contained				
19	G3VM-21GR	Not contained				
20	G3VM-41GR5	Not contained				
21	G3VM-351A	Not contained				
22	G3VM-351D	Not contained				
23	G3VM-351D(TR)	Not contained				
24	G3VM-351B	Not contained				
25	G3VM-351E	Not contained				
26	G3VM-351E(TR)	Not contained				
27	G3VM-352C	Not contained				
28	G3VM-352F	Not contained				
29	G3VM-352F(TR)	Not contained				
30	G3VM-21LR1	Not contained				
31	G3VM-355CR	Not contained				
32	G3VM-355FR	Not contained				
33	G3VM-355JR	Not contained				
34	G3VM-355JR(TR)	Not contained				
35	G3VM-401G	Not contained				
36	G3VM-401G(TR)	Not contained				
37	G3VM-402J	Not contained				
38	G3VM-402J(TR)	Not contained				
39	G3VM-401A	Not contained				
40	G3VM-401D	Not contained				
41	G3VM-402F	Not contained				
42	G3VM-61H1	Not contained				
43	G3VM-62J1	Not contained				
44	G3VM-62J1(TR)	Not contained				
45	G3VM-352J	Not contained				
46	G3VM-61A1	Not contained				

47	G3VM-61D1	Not contained				
48	G3VM-61D1(TR)	Not contained				
49	G3VM-62C1	Not contained				
50	G3VM-62F1	Not contained				
51	G3VM-62F1(TR)	Not contained				
52	G3VM-81HR(TR)	Not contained				
53	G3VM-81G1	Not contained				
54	G3VM-61B1	Not contained				
55	G3VM-61E1	Not contained				
56	G3VM-61E1(TR)	Not contained				
57	G3VM-351H	Not contained				
58	G3VM-41LR5(TR05)	Not contained				
59	G3VM-41LR4(TR05)	Not contained				
60	G3VM-401H	Not contained				
61	G3VM-202J1	Not contained				
62	G3VM-61BR	Not contained				
63	G3VM-61ER	Not contained				
64	G3VM-351GL	Not contained				
65	G3VM-351GL(TR)	Not contained				
66	G3VM-21LR10(TR05)	Not contained				
67	G3VM-21LR10	Not contained				
68	G3VM-41LR10(TR05)	Not contained				
69	G3VM-41GR8	Not contained				
70	G3VM-402F(TR)#S	Not contained				
71	G3VM-401EY(TR2)	Not contained				
72	G3VM-61G2	Not contained				
73	G3VM-61G2(TR)	Not contained				
74	G3VM-201G1	Not contained				
75	G3VM-201G1(TR)	Not contained				
76	G3VM-351G1	Not contained				
77	G3VM-41HR	Not contained				
78	G3VM-41HR(TR)	Not contained				
79	G3VM-61HR	Not contained				
80	G3VM-101HR	Not contained				
81	G3VM-61PR(TR05)	Not contained				
82	G3VM-21DR	Not contained				
83	G3VM-61AR	Not contained				
84	G3VM-61DR	Not contained				
85	G3VM-101DR	Not contained				
86	G3VM-21ER(TR)	Not contained				
87	G3VM-41ER	Not contained				
88	G3VM-61BR1	Not contained				
89	G3VM-61ER1	Not contained				
90	G3VM-101ER	Not contained				
91	G3VM-21PR11(TR05)	Not contained				
92	G3VM-51PR(TR05)	Not contained				
93	G3VM-61G3	Not contained				
94	G3VM-61G3(TR)	Not contained				
95	G3VM-401G1	Not contained				
96	G3VM-41AY1	Not contained				
97	G3VM-41DY1	Not contained				
98	G3VM-41DY1(TR05)	Not contained				
99	G3VM-201DY1	Not contained				
100	G3VM-351DY1(TR05)	Not contained				
101	G3VM-601DY1	Not contained				
102	G3VM-41PR5(TR05)	Not contained				
103	G3VM-101PR(TR05)	Not contained				
104	G3VM-61VY1	Not contained				
105	G3VM-61VY1(TR)	Not contained				
106	G3VM-61GR2	Not contained				
107	G3VM-61GR2(TR05)	Not contained				
108	G3VM-61HR1	Not contained				
109	G3VM-63G	Not contained				
110	G3VM-63G(TR05)	Not contained				
111	G3VM-61CR1	Not contained				
112	G3VM-61FR1	Not contained				
113	G3VM-61FR1(TR05)	Not contained				
114	G3VM-401FR	Not contained				
115	G3VM-61VY2	Not contained				
116	G3VM-61VY2(TR05)	Not contained				
117	G3VM-351VY	Not contained				
118	G3VM-351VY(TR05)	Not contained				
119	G3VM-61VY2(TR)	Not contained				

120	G3VM-351VY(TR)	Not contained				
121	G3VM-101FR	Not contained				
122	G3VM-61VY3	Not contained				
123	G3VM-61VY3(TR05)	Not contained				
124	G3VM-61VY3(TR)	Not contained				
125	G3VM-61VR	Not contained				
126	G3VM-61VR(TR05)	Not contained				
127	G3VM-401VY	Not contained				
128	G3VM-61BR2	Not contained				
129	G3VM-61ER2	Not contained				
130	G3VM-61ER2(TR05)	Not contained				
131	G3VM-101HR2	Not contained				
132	G3VM-31AR	Not contained				
133	G3VM-31DR	Not contained				
134	G3VM-31DR(TR05)	Not contained				
135	G3VM-31BR	Not contained				
136	G3VM-31ER	Not contained				
137	G3VM-31ER(TR05)	Not contained				
138	G3VM-61AR1	Not contained				
139	G3VM-61DR1	Not contained				
140	G3VM-61DR1(TR05)	Not contained				
141	G3VM-101AR1	Not contained				
142	G3VM-101DR1	Not contained				
143	G3VM-101DR1(TR05)	Not contained				
144	G3VM-201AR	Not contained				
145	G3VM-201DR	Not contained				
146	G3VM-201DR(TR05)	Not contained				
147	G3VM-101BR1	Not contained				
148	G3VM-101ER1	Not contained				
149	G3VM-101ER1(TR05)	Not contained				
150	G3VM-31HR1	Not contained				
151	G3VM-31HR1(TR05)	Not contained				
152	G3VM-61HR2	Not contained				
153	G3VM-61HR2(TR05)	Not contained				
154	G3VM-101HR1	Not contained				
155	G3VM-21UR11	Contained	SG039	Hexahydromethylphthalic anhydride	7.5	0.45
156	G3VM-21UR11(TR05)	Contained	SG039	Hexahydromethylphthalic anhydride	7.5	0.45
157	G3VM-41UR10(TR05)	Contained	SG039	Hexahydromethylphthalic anhydride	7.5	0.45
158	G3VM-61UR(TR05)	Contained	SG039	Hexahydromethylphthalic anhydride	7.5	0.45
159	G3VM-81UR(TR05)	Contained	SG039	Hexahydromethylphthalic anhydride	7.5	0.45
160	G3VM-101UR(TR05)	Contained	SG039	Hexahydromethylphthalic anhydride	7.5	0.45
161	G3VM-21UR10(TR05)	Contained	SG039	Hexahydromethylphthalic anhydride	7.5	0.45
162	G3VM-101QR1(TR05)	Contained	SG039	Hexahydromethylphthalic anhydride	7.5	0.45
163	G3VM-31QVH(TR05)	Contained	SG039	Hexahydromethylphthalic anhydride	7.5	0.37
164	G3VM-31QVL(TR05)	Contained	SG039	Hexahydromethylphthalic anhydride	7.5	0.37
165	G3VM-61QV2H(TR05)	Contained	SG039	Hexahydromethylphthalic anhydride	7.5	0.37
166	G3VM-61QV2L(TR05)	Contained	SG039	Hexahydromethylphthalic anhydride	7.5	0.37
167	G3VM-61QVH(TR05)	Contained	SG039	Hexahydromethylphthalic anhydride	7.5	0.37
168	G3VM-21UV11(TR05)	Contained	SG039	Hexahydromethylphthalic anhydride	7.5	0.45
169	G3VM-51UV(TR05)	Contained	SG039	Hexahydromethylphthalic anhydride	7.5	0.45
170	G3VM-61UV(TR05)	Contained	SG039	Hexahydromethylphthalic anhydride	7.5	0.45
171	G3VM-21MT(TR01)	Not contained	80-05-7	4,4'-isopropylidenediphenol	0.1	0.011
172	G3VM-21MT(TR05)	Not contained	80-05-7	4,4'-isopropylidenediphenol	0.1	0.011
173	G3VM-31WR(TR05)	Contained	SG039	Hexahydromethylphthalic anhydride	7.5	0.87
174	G3VM-61WR(TR05)	Contained	SG039	Hexahydromethylphthalic anhydride	7.5	0.87
175	G3VM-101WR(TR05)	Contained	SG039	Hexahydromethylphthalic anhydride	7.5	0.87
176	G3VM-61MT(TR01)	Not contained	80-05-7	4,4'-isopropylidenediphenol	0.1	0.011
177	G3VM-61MT(TR05)	Not contained	80-05-7	4,4'-isopropylidenediphenol	0.1	0.011
178	G3VM-101MT(TR01)	Not contained	80-05-7	4,4'-isopropylidenediphenol	0.1	0.011
179	G3VM-101MT(TR05)	Not contained	80-05-7	4,4'-isopropylidenediphenol	0.1	0.011
180	G3VM-201WR(TR05)	Contained	SG039	Hexahydromethylphthalic anhydride	7.5	0.87
181	G6A-234P-ST-US DC5	Not contained				
182	G6A-234P-ST-US DC12	Not contained				
183	G6A-234P-ST-US DC24	Not contained				
184	G6A-234P-ST-US DC48	Not contained				
185	G6A-274P-ST-US DC5	Not contained				
186	G6A-274P-ST-US DC12	Not contained				
187	G6A-274P-ST-US DC24	Not contained				
188	G6A-234P DC4.5	Not contained				
189	G6A-274P-ST40-US DC48	Not contained				
190	G6A-2-H DC12	Not contained				
191	G6AK-274P DC5	Not contained				
192	G6AK-274P DC24	Not contained				

193	G6AK-234P DC5	Not contained				
194	G6AK-234P DC12	Not contained				
195	G6AK-234P DC24	Not contained				
196	G6AU-274P-ST-US DC12	Not contained				
197	G6AU-274P-ST-US DC24	Not contained				
198	G6AK-234P-ST-US DC5	Not contained				
199	G6AK-234P-ST-US DC12	Not contained				
200	G6AK-234P-ST-US DC24	Not contained				
201	G6AK-274P-ST-US DC5	Not contained				
202	G6AU-234P-ST-US DC5	Not contained				
203	G6AU-274P-ST-US DC5	Not contained				
204	G6AK-274P-ST-US DC12	Not contained				
205	G6AK-274P-ST-US DC24	Not contained				
206	G6AK-274P-ST40-US DC5	Not contained				
207	G6B-1114P-US DC5	Not contained				
208	G6B-1114P-US DC12	Not contained				
209	G6B-1114P-US DC24	Not contained				
210	G6B-1114P-FD-US DC24	Not contained				
211	G6B-1174P-US DC5	Not contained				
212	G6B-1174P-US DC12	Not contained				
213	G6B-1174P-US DC24	Not contained				
214	G6B-1174P-FD-US DC5	Not contained				
215	G6B-1174P-FD-US DC12	Not contained				
216	G6B-1174P-FD-US DC24	Not contained				
217	G6B-1114P-US-SV DC5	Not contained				
218	G6B-1114P-US-SV DC24	Not contained				
219	G6B-1177P-ND-US DC24	Not contained				
220	G6B-1114P-1-US DC12	Not contained				
221	G6B-1114P-US-SV DC6	Not contained				
222	G6BK-1114P-US DC3	Not contained				
223	G6BK-1114P-US DC5	Not contained				
224	G6BK-1114P-US DC12	Not contained				
225	G6BK-1114P-US DC24	Not contained				
226	G6BU-1114P-US DC5	Not contained				
227	G6BU-1114P-US DC12	Not contained				
228	G6BU-1114P-US DC24	Not contained				
229	G6BK-1114P-1-US DC3	Not contained				
230	G6C-2114P-US DC24	Not contained				
231	G6C-2117P-US DC24	Not contained				
232	G6C-1117P-US DC24	Not contained				
233	G6C-1114P-US DC24	Not contained				
234	G6C-2114P-US DC12	Not contained				
235	G6C-1114P-US DC12	Not contained				
236	G6C-2117P-US DC12	Not contained				
237	G6C-1117P-US DC12	Not contained				
238	G6C-1117P-US DC5	Not contained				
239	G6C-1114P-US DC5	Not contained				
240	G6C-2114P-US DC5	Not contained				
241	G6C-2117P-US DC5	Not contained				
242	G6C-1117P-US DC6	Not contained				
243	G6C-2114P-US DC3	Not contained				
244	G6C-2114P-US-U DC12	Not contained				
245	G6C-2114P-US DC9	Not contained				
246	G6CU-1117P-US DC3	Not contained				
247	G6CU-1117P-US DC5	Not contained				
248	G6CU-1114P-US DC3	Not contained				
249	G6CU-2117P-US DC3	Not contained				
250	G6CU-2117P-US DC24	Not contained				
251	G6CU-2114P-US DC3	Not contained				
252	G6CU-2114P-US DC5	Not contained				
253	G6CU-2114P-US DC12	Not contained				
254	G6CK-1117P-US DC12	Not contained				
255	G6CK-1117P-US DC24	Not contained				
256	G6CK-1114P-US DC3	Not contained				
257	G6CK-1114P-US DC5	Not contained				
258	G6CK-1114P-US DC12	Not contained				
259	G6CK-1114P-US DC24	Not contained				
260	G6CK-2117P-US DC12	Not contained				
261	G6CK-2117P-US DC24	Not contained				
262	G6CK-2114P-US DC5	Not contained				
263	G6CK-2114P-US DC12	Not contained				
264	G6CK-2114P-US DC24	Not contained				
265	G6CK-2114P-US-360 DC5	Not contained				

266	G6DN-1A DC4.5	Not contained				
267	G6DN-1A DC5	Not contained				
268	G6DN-1A DC12	Not contained				
269	G6DN-1A DC24	Not contained				
270	G6DN-1A-L DC5	Not contained				
271	G6DN-1A-L DC12	Not contained				
272	G6DN-1A-L DC24	Not contained				
273	G6E-134P-US DC24	Not contained				
274	G6E-134P-US DC5	Not contained				
275	G6E-134P-US DC12	Not contained				
276	G6E-134P-US DC6	Not contained				
277	G6E-134P-ST-US DC5	Not contained				
278	G6E-134P-ST-US DC24	Not contained				
279	G6E-134P-ST-US DC12	Not contained				
280	G6E-134P-ST-US DC48	Not contained				
281	G6E-134P-US DC3	Not contained				
282	G6E-134PL-ST-US DC12	Not contained				
283	G6E-134PL-ST-US DC5	Not contained				
284	G6EU-134P-ST-US DC5	Not contained				
285	G6EU-134P-US DC12	Not contained				
286	G6EK-134P-US DC5	Not contained				
287	G6EK-134P-US DC12	Not contained				
288	G6EK-134P-US DC24	Not contained				
289	G6K-2P DC12	Not contained				
290	G6K-2P DC3	Not contained				
291	G6K-2P DC5	Not contained				
292	G6K-2P DC24	Not contained				
293	G6K-2P-Y DC3	Not contained				
294	G6K-2P-Y DC5	Not contained				
295	G6K-2P-Y DC12	Not contained				
296	G6KU-2F-Y DC4.5	Not contained				
297	G6KU-2F-Y DC12	Not contained				
298	G6KU-2P-Y DC5	Not contained				
299	G6KU-2P-Y DC12	Not contained				
300	G6KU-2P-Y DC24	Not contained				
301	G6KU-2F-Y-TR DC3	Not contained				
302	G6KU-2F-Y-TR DC4.5	Not contained				
303	G6K-2F DC3	Not contained				
304	G6K-2F DC5	Not contained				
305	G6K-2F DC12	Not contained				
306	G6K-2F DC24	Not contained				
307	G6K-2F-TR DC3	Not contained				
308	G6K-2F-TR DC5	Not contained				
309	G6K-2F-TR DC12	Not contained				
310	G6K-2F-TR DC24	Not contained				
311	G6K-2F-Y DC3	Not contained				
312	G6K-2F-Y DC24	Not contained				
313	G6K-2F-RF DC3	Not contained				
314	G6K-2F-RF DC4.5	Not contained				
315	G6K-2F-RF DC5	Not contained				
316	G6K-2F-RF DC9	Not contained				
317	G6K-2F-RF DC12	Not contained				
318	G6KU-2F-RF DC3	Not contained				
319	G6KU-2F-RF DC4.5	Not contained				
320	G6KU-2F-RF DC5	Not contained				
321	G6KU-2F-RF-TR09 DC4.5	Not contained				
322	G6K-2F-RF-TR03 DC3	Not contained				
323	G6K-2F-RF-TR03 DC4.5	Not contained				
324	G6K-2F-RF-TR03 DC5	Not contained				
325	G6KU-2F-RF-TR03 DC3	Not contained				
326	G6KU-2F-RF-TR03 DC4.5	Not contained				
327	G6K-2F-RF-S DC3	Not contained				
328	G6K-2F-RF-S DC5	Not contained				
329	G6K-2F-RF-S DC12	Not contained				
330	G6K-2F-RF-S DC24	Not contained				
331	G6KU-2F-RF-S DC5	Not contained				
332	G6KU-2F-RF-S-TR03 DC5	Not contained				
333	G6KU-2F-RF-S-TR09 DC5	Not contained				
334	G6K-2F-RF-T DC4.5	Not contained				
335	G6K-2F-RF-T DC24	Not contained				
336	G6KU-2F-RF-T DC5	Not contained				
337	G6K-2F-RF-T-TR03 DC5	Not contained				
338	G6KU-2G-Y-TR DC4.5	Not contained				

339	G6KU-2G-Y-TR DC5	Not contained				
340	G6K-2G DC3	Not contained				
341	G6K-2G DC5	Not contained				
342	G6K-2G DC12	Not contained				
343	G6K-2G DC24	Not contained				
344	G6K-2G-TR DC3	Not contained				
345	G6K-2G-TR DC5	Not contained				
346	G6K-2G-Y DC5	Not contained				
347	G6K-2G-Y-TR DC4.5	Not contained				
348	G6K-2G-Y-TR DC5	Not contained				
349	G6K-2G-Y-TR DC24	Not contained				
350	G6K-2P-RF DC5	Not contained				
351	P6B-04P FOR G6B	Not contained				
352	P6B-C2	Not contained				
353	P6B-26P	Not contained				
354	P6C-06P FOR G6C	Not contained				
355	P6D-04P	Not contained				
356	P7LF-D	Not contained				
357	P7LF-06	Not contained				
358	P7LF-06D	Not contained				
359	R99-07(E KANAGU) FOR G7L	Not contained				