



/ LEAD-TIME GUIDE SEPTEMBER 2026

POWER

Product	Lead-time: weeks	Lead-time: prognosis
AC-DC PSU general purpose	33	↑
AC-DC PSU medical	32	↑
AC-DC PSU DIN rail	33	↑
Rectifiers & front-end PSU	33	↑
AC-DC external-adaptors	25	↑
AC-DC railway	33	↑
AC-DC LED drivers general	47	=
AC-DC LED drivers special	47	=
DC-DC miniature	28	=
DC-DC industrial & bricks	28	=
DC-DC panel mount	28	=

FILTER & MAGNETICS

Product	Lead-time: weeks	Lead-time: prognosis
Active filter	53	=
EMI filter	53	=
Power line filter	29	=
SAW filter	20	↓
Ceramic filter	20	↓
EMI/RFI filter	53	=
RF filter	20	↓
Common mode chokes	21	↓
Ferrite chip beads	21	=
Inductor leaded	22	=
Wireless charging coils	30	=
Inductor surface mount	19	=

ELECTROMECHANICAL

Product	Lead-time: weeks	Lead-time: prognosis
Switches	21	=
Relays general purpose	59	=
Relays automotive/telecom	63	=
Fans	22	↑
Heatsinks	12	=

CONNECTORS

Product	Lead-time: weeks	Lead-time: prognosis
Cable flat	25	↑
Backplanes DIN 41612; 2MM; high speed; power signal;	31	=
I/O connectors	20	=
Memory card reader	38	=
Sockets DIP/SIP; PLCC/PGA/BGA; SIMM/IMM/Holtite	26	=
Non-solderable terminals/fastons	30	=
Circular military	21	=
Circular industrial	17	=
Circular medical	12	=
Rectangular military	27	↓
Rectangular industrial	28	=
Rectangular medical	28	=
RF coaxial	19	=
Board to board	12	=
Wire to board/wire to wire	19	=
Automotive	21	=
Power - connector systems	14	=

PASSIVE

Product	Lead-time: weeks	Lead-time: prognosis
Ceramic capacitors single layer	23	↑
Ceramic capacitors leaded multilayer	23	↑
Ceramic capacitors multilayer SMD	26	=
Ceramic capacitors multilayer high CV	25	↑
Ceramic capacitors automotive	26	=
Aluminium electrolytic capacitors leaded	29	↑
Aluminium electrolytic capacitors SMD	29	=
Aluminium electrolytic capacitors snap-in & large can	27	↑
Film capacitors leaded	23	=
Film capacitors SMD	26	↑
Film capacitors suppression	26	=
Polymer capacitors	42	=
Tantalum capacitors leaded	29	=
Tantalum capacitors SMD	29	↑
Resistor Metal Film SMD Thick Film	31	=
Resistor Metal Film SMD Thin Film	26	↑
Resistor Metal Film MELF	15	=

Product	Lead-time: weeks	Lead-time: prognosis
Resistor Metal Film SMD Low Ohmic	22	=
Resistor Networks & Arrays	22	=
Resistor Metal Film & Oxide Leaded	17	=
Resistor Ceramic Leaded	20	=
Resistor Carbon Film Leaded	14	↓
Resistor Wirewound	23	↑
Trimmer SMD	16	=
Trimmer Leaded	17	↑
Potentiometer	17	=
Varistor SMD	22	↑
Varistor Leaded	21	↑
Circuit protection - fuses	15	=
Circuit protection - resettable devices	17	=
Frequency control crystals / oscillators	50	=
Frequency control resonators	14	=
Electromagnetic piezo buzzers, sounders and transducers	16	=
Antennas	30	=

SENSORS

Product	Lead-time: weeks	Lead-time: prognosis
Air, gases & humidity	14	=
Light, Photodiodes, PIR	28	=
Liquid level & Flow	54	↓
Magnetic ICs, Current	25	↓
Microphones	16	=
Position, Motion	23	=
Pressure	28	↑
Thermal	25	=

AUSTRIA

Avnet EMG Elektronische
Bauelemente GmbH
Grünbergstraße 15/1/4. OG,
A-1120 Vienna
Phone: +43 (0)1 86642-0
Fax: +43 (0)1 86642-250
wien@avnet-abacus.eu

BELGIUM

De Kleetlaan 3
BE-1831 Diegem
Phone: +32 2 227 2000
diegem@avnet-abacus.eu

BULGARIA

48, Sitnyakovo Boulevard
Unit 1006, Floor 10,
BG-1505 Sofia
Phone: +359 896 135 069
bulgaria@avnet-abacus.eu

CROATIA

c/o Avnet Abacus Slovenia
Dunajska Cesta 167
SI-1000 Ljubljana
Phone: +386 (0)1 560 97 54
Fax: +386 (0)1 560 98 78
croatia@avnet-abacus.eu

CZECH REPUBLIC

Amazon Court Karolinska 661/4
CZ-18600 Prague
Phone: +420 234 091 011
Fax: +420 234 091 010
praha@avnet-abacus.eu

DENMARK

Knudlundvej 24, DK-8653 Them
Phone: +45 86 84 84 84
Fax: +45 86 84 82 44
them@avnet-abacus.eu

Marielundvej 41, 2. Sal,
DK-2730 Herlev
Phone: +45 86 84 84 84
Fax: +45 43 29 37 00
herlev@avnet-abacus.eu

EGYPT

c/o Avnet Abacus Turkey
Tatlısu Mahallesi Pakdil
Sokak No: 7 Kat: 2
TR-34774 Umraniye Istanbul Türkiye
Phone: +90 216 52 88 370
Fax: +90 216 52 88 377
egypt@avnet-abacus.eu

ESTONIA

Suur-Jõe 63, Pärnu,
EE-80042 Pärnu Maakond
Phone: +372 56637737
paernu@avnet-abacus.eu

FINLAND

Klovinpellontie 1-3
Tower 1, Floor 6
FI-02180 Espoo
Phone: +35 820 749 9220
Fax: +35 820 749 9240
espoo@avnet-abacus.eu

FRANCE

Le Copernic
12, rue Jean Bart
FR-91300 Massy
Phone: +33 (0) 1 6447 2929
Fax: +33 (0) 1 6447 9150
paris@avnet-abacus.eu

6, rue Ariane
Bâtiment 3
FR-31520 Ramonville Saint Agne
toulouse@avnet-abacus.eu

16 C Rue de Jouanet
FR-35700 Rennes
Phone: +33 (0) 2 9983 7720
Fax: +33 (0) 2 9983 4829
rennes@avnet-abacus.eu

Parc Club du Moulin à Vent
Bat 10, 33 rue du Dr. G Lévy
FR-69693, Vénissieux Cedex, Lyon
lyon@avnet-abacus.eu

GERMANY

AVNET EMG GMBH
Kaiserin-Augusta-Allee 14
DE-10553 Berlin
Phone: +49 (0) 30 790 997 0
Fax: +49 (0) 30 790 997 51
berlin@avnet-abacus.eu

Industriestr. 16
DE-76297 Stutensee
Phone: +49 (0) 7249 910 149
Fax: +49 (0) 7249 910 177
stutensee@avnet-abacus.eu

Rhenus-Platz 2
D-59439 Holzwickede/Dortmund
Phone: +49 (0) 2301 2959 0
Fax: +49 (0) 2301 2959 29
dortmund@avnet-abacus.eu

Ursula-de-Boor-Str. 45
22419 Hamburg
Phone: +49 (0) 40 608 23 59 0
Fax: +49 (0) 40 608 23 59 20
hamburg@avnet-abacus.eu

Im Technologiepark 2-8
DE-85586 Poing
Phone: +49 (0) 8121 775 400
bayern@avnet.eu

Lina-Ammon-Str. 19 b
DE-90471 Nuernberg
Phone: +49 (0) 911 244 250
Fax: +49 (0) 911 244 25 25
bayern@avnet.eu

Neue Ramtelstr. 4
DE-71229 Leonberg
Phone: +49 (0) 7152 3009 70
Fax: +49 (0) 7152 3009 96
stuttgart@avnet-abacus.eu

Rotenburger Str. 20
DE-30659 Hannover
Phone: +49 (0) 5132 5099 0
hannover@avnet-abacus.eu

Otto-von-Guericke-Ring 13-15
DE-65205, Wiesbaden
wiesbaden@avnet-abacus.eu

GREECE

c/o Abacus Avnet Serbia
Milentija Popovića 5B,
Floors 6-8
Belgrade RS-11070
Phone: +381 11 4022302
Fax: +381 11 4049900
belgrade@avnet-abacus.eu

HUNGARY

c/o Avnet Abacus Slovakia
GreenPoint Offices,
Blok F Turcianska 2
SK-82109 Bratislava
Phone: +421 232 242 608
Fax: +421 2 32 1111 40
budapest@avnet-abacus.eu

IRELAND

c/o Avnet Abacus Bolton
Deakins Business Park
Blackburn Road, Egerton
Bolton BL7 9RP
+44 (0)1204 936400
abacus.bolton@avnet-abacus.eu

ISRAEL

1 Habrosh Street
Bney Dror IL-4581500
Phone: +972 9 778 0280
Fax: +972 3 760 0794
israel@avnet-abacus.eu

ITALY

Via Manzoni 44
IT-20095 Cusano Milanino/Milano
Phone: +39 02 660 921
Fax: +39 02 66092 332
milano@avnet-abacus.eu

Viale dell'industria 23
IT-35129 Padova
Phone: +39 049 7800 381
Fax: +39 049 7730 36
padova@avnet-abacus.eu

Via Scaglia Est. 31/33
IT-41126 Modena
Phone: +39 059 34891
Fax: +39 059 344 993
modena@avnet-abacus.eu

Via Panciatichi 40/11
IT-50127 Firenze
Phone: +39 055 436 1928
Fax: +39 055 428 8810
firenze@avnet-abacus.eu

Via Tiburtina, 652/A
C/O Urban Places
IT-00159 Roma
Phone: +39 02 660 921
rome@avnet-abacus.eu

LATVIA

c/o Avnet Abacus Poland
Plac Solny 16
PL-50-062 Wroclaw
Phone: +48 71 34 205 99
Fax: +48 71 34 229 10
latvia@avnet-abacus.eu

LITHUANIA

c/o Avnet Abacus Poland
Plac Solny 16
PL-50-062 Wroclaw
Phone: +48 71 34 205 99
Fax: +48 71 34 229 10
lithuania@avnet-abacus.eu

NETHERLANDS

Stadionstraat 2, 6th floor
NL-4815 NG Breda
Phone: +31 (0) 76 57 22 300
Fax: +31 (0) 76 57 22 303
breda@avnet-abacus.eu

NORWAY

Olaf Helsetsvet 6,
NO-0694 Oslo
Phone: +47 (0) 94 89 53 73
oslo@avnet-abacus.eu

POLAND

Plac Solny 16
PL-50-062 Wroclaw
Phone: +48 71 34 205 99
Fax: +48 71 34 229 10
wroclaw@avnet-abacus.eu

PORTUGAL

Tower Plaza, Rot. Eng. Edgar
Cardoso, 23,Piso 14, Sala E
PT-4400-676 Vila Nova de Gaia
Phone: +351 223 779502
Fax: +351 223 779503
portugal@avnet-abacus.eu

ROMANIA

SkyTower Building, 12th floor,
Calea Floreasca 246C,
RO-014476 Bucharest
Phone: +4021 528 16 90
romania@avnet-abacus.eu

SERBIA

Milentija Popovića 5B, Floors 6-8
Belgrade RS-11070
Phone: +381 11 4022302
Fax: +381 11 4049900
belgrade@avnet-abacus.eu

SLOVAKIA

GreenPoint Offices,
Blok F Turcianska 2
SK-82109, Bratislava
Phone: +421 232 242 608
Fax: +421 2 32 1111 40
slovakia@avnet-abacus.eu

SLOVENIA

Dunajska Cesta 167
SI-1000 Ljubljana
Phone: +386 (0)1 560 97 60
Fax: +386 (0)1 560 98 78
ljubljana@avnet-abacus.eu

SOUTH AFRICA

Block 13, Pinewood Office Park
33 Riley Road Woodmead,
ZA-2191 Sandton, Johannesburg
Phone: +27 (0)10 447 0180
avnet-abacus-sales-southafrica@avnet.eu

SPAIN

NyN Tower, C/Tarragona
149-157. Floor 19
ES-08014 Barcelona
Phone: +34 (0) 93 327 85 50
Fax: +34 (0) 93 425 05 44
barcelona@avnet-abacus.eu

Avenida Madariaga 1
Floor 3
ES-48014 Bilbao
Phone: +34 (0) 94 457 00 44
Fax: +34 (0) 94 456 88 55
bilbao@avnet-abacus.eu

Ronda de Poniente
(pq Empresarial Euronova),
4 - 2ª Planta, tres Cantos,
28760, Madrid
madrid@avnet-abacus.eu

SWEDEN

Avnet Nortec AB
Hemvärnsgatan 9
SE-171 54 Solna
Phone: +46 (0)8587 462 00
Fax: +46 (0)8587 460 01
stockholm@avnet-abacus.eu

Smörhålevägen 3
SE-43442 Kungsbacka
Phone: +46 (0)8 58746 200
Fax: +46 (0)300 140 15
gothenburg@avnet-abacus.eu

SWITZERLAND

Bernstrasse 394
CH-8953 Dietikon
Phone: +41 (0)43 322 49 90
Fax: +41 (0)43 322 49 99
zurich@avnet-abacus.eu

TURKEY

Tatlısu Mahallesi Pakdil
Sokak No: 7 Kat: 2
TR-34774 Umraniye Istanbul Türkiye
Phone: +90 216 52 88 370
Fax: +90 216 52 88 377
istanbul@avnet-abacus.eu

UK

Building 5, Waltham Park
White Waltham
Maidenhead Berkshire SL6 3TN
Phone: +44 (0)1628 512900
Fax: +44 (0)1628 512999
abacus.maidenhead@avnet-abacus.eu

Deakins Business Park
Blackburn Road, Egerton
Bolton BL7 9RP
+44 (0)1204 936400
abacus.bolton@avnet-abacus.eu

UKRAINE

c/o Avnet Abacus Poland
Plac Solny 16
PL-50-062 Wroclaw
Phone: +48 71 34 205 99
Fax: +48 71 34 229 10
ukraine@avnet-abacus.eu