

Product brief

XMC7000 Industrial Microcontrollers



The XMC7000 is the latest entry in Infineon's industrial microcontroller portfolio, equipped with peripherals such as CAN-FD, TCPWM and Gb Ethernet, which increase flexibility and offer added value. The XMC7000 architecture is built on a low-power 40-nm process technology and the MCUs offer best-in-class compute performance addressing high-end industrial applications.

The XMC7000 offers both single and dual-core Arm® Cortex®-M7 options, supported by a Arm® Cortex®-M0+ enabling designers to optimize their end products to meet the dynamic and demanding business conditions of industrial applications. The advanced peripheral set and robust security features make it attractive to customers, who need a high-quality MCU platform. The MCU is able to operate in harsh environments with a temperature range of -40°C to 125°C, and it is ideal for power critical applications based on its low-power modes, which go down to 8µA. The flexible XMC7000 comes in four package/pin types with 17 part number variants to meet many design requirements.

The XMC7000 family comes in 2 series: XMC7100 and XMC7200, and it is available in TQFP and LFBGA packages scaling from 100 to 272 pins. The XMC7200 integrates Gigabit Ethernet, providing real-time ethernet communications and reliable connectivity for always on applications. The XMC7000 family is ideal for motor control, digital power conversion and I/O applications.

Key XMC™ 7000 family features



- Best-in-class performance, enabling task distribution
- XMC7000 delivers real-time control to meet even the most demanding industrial applications
- The advanced TCPWM is ideal for sophisticated motor control applications
- High-quality platform that operates in harsh environments -40°C to 125°C
- Broad offering of core, memory and package combinations for design flexibility

Key applications

Industrial Drives & Robotics	General purpose drives (GPD), Servo Drives, Medium Voltage Drives (MVD), Sensor nodes, Service robots, Industrial robots
EV-charging	AC or DC charging, Wallbox, Charging cable, Fast charging station, Inductive chargers, Power supply
Electric Two-Wheeler	Battery management system
PLC	Programmable Logic Control (PLC), I/O Modules

Silicon	Description
XMC7100-F100K1088AA	Single Core Arm® Cortex® M7 (+Arm® Cortex®-M0+), TQFP 100pins, 1MB Flash
XMC7100-F100K2112AA	Single Core Arm® Cortex® M7 (+Arm® Cortex®-M0+), TQFP 100pins, 2MB Flash
XMC7100-F100K4160AA	Single Core Arm® Cortex® M7 (+Arm® Cortex®-M0+), TQFP 100pins, 4MB Flash
XMC7100D-F100K2112AA	Dual Core Arm® Cortex® M7 (+Arm® Cortex®-M0+), TQFP 100pins, 2MB Flash
XMC7100D-F100K4160AA	Dual Core Arm® Cortex® M7 (+Arm® Cortex®-M0+), TQFP 100pins, 4MB Flash
XMC7100-F144K2112AA	Single Core Arm® Cortex® M7(+ Arm® Cortex®-M0+), TQFP 144pins, 2MB Flash
XMC7100-F144K4160AA	Single Core Arm® Cortex® M7(+ Arm® Cortex®-M0+), TQFP 144pins, 4MB Flash
XMC7100D-F144K2112AA	Dual Core Arm® Cortex® M7 (+Arm® Cortex®-M0+), TQFP 144pins, 2MB Flash
XMC7100D-F144K4160AA	Dual Core Arm® Cortex® M7 (+Arm® Cortex®-M0+), TQFP 144pins, 4MB Flash
XMC7100-F176K4160AA	Single Core Arm® Cortex® M7(+ Arm® Cortex®-M0+), TQFP 176pins, 4MB Flash
XMC7100D-F176K4160AA	Dual Core Arm® Cortex® M7 (+Arm® Cortex®-M0+), TQFP 176pins, 4MB Flash
XMC7100-E272K4160AA	Single Core Arm® Cortex® M7(+ Arm® Cortex®-M0+), LBGGA 272pins, 4MB Flash
XMC7100D-E272K4160AA	Dual Core Arm® Cortex® M7(+ Arm® Cortex®-M0+), LFBGA 272pins, 4MB Flash
XMC7200-F176K8384AA	Single Core Arm® Cortex® M7 (+Arm® Cortex®-M0+), TQFP 176pins, 8MB Flash
XMC7200D-F176K8384AA	Dual Core Arm® Cortex® M7 (+Arm® Cortex®-M0+), TQFP 176pins, 8MB Flash
XMC7200-E272K8384AA	Single Core Arm® Cortex® M7 (+Arm® Cortex®-M0+), LFBGA 272pins, 8MB Flash
XMC7200D-E272K8384AA	Dual Core Arm® Cortex® M7 (+Arm® Cortex®-M0+), LFBGA 272pins, 8MB Flash

Block diagrams:



Published by
Infineon Technologies AG
81726 Munich, Germany

©2021 Infineon Technologies AG.
All Rights Reserved.

Please note!

This Document is for information purposes only and any information given herein shall in no event be regarded as a warranty, guarantee or description of any functionality, conditions and/or quality of our products or any suitability for a particular purpose. With regard to the technical specifications of our products, we kindly ask you to refer to the relevant product data sheets provided by us. Our customers and their technical departments are required to evaluate the suitability of our products for the intended application.

We reserve the right to change this document and/or the information given herein at any time.

Additional information

For further information on technologies, our products, the application of our products, delivery terms and conditions and/or prices, please contact your nearest Infineon Technologies office (www.infineon.com).

Warnings

Due to technical requirements, our products may contain dangerous substances. For information on the types in question, please contact your nearest Infineon Technologies office.

Except as otherwise explicitly approved by us in a written document signed by authorized representatives of Infineon Technologies, our products may not be used in any life-endangering applications, including but not limited to medical, nuclear, military, life-critical or any other applications where a failure of the product or any consequences of the use thereof can result in personal injury.