


ABC180 Series

Ultra Low Profile Open Frame Power Supplies

The ABC180 Series of ultra low profile open frame power supplies feature a wide universal AC input range of 80 – 264 VAC, offering up to 180 W of output power with 13 CFM, or up to 120 W with convection cooling in a compact footprint, with a variety of isolated single output voltages.

The high efficiency and high power density of the ABC family ensures minimal power loss in end-use equipment, thereby facilitating higher reliability, easier thermal management and meets regulatory approvals for environmentally-friendly end products.

These power supplies are ideal for broad range of telecom, datacom, industrial equipment and other applications.



Key Features & Benefits

- 4 x 2 x 0.75 Inches Form factor
- 180 Watts with Forced Air Cooling
- Efficiencies up to 92%
- -40 to 70°C degree operating temperature
- 12 V / 0.5 A Fan Output, Thermal Shut-Down feature
- 3.37 million Hours, Telcordia -SR332-issue 3 MTBF
- Standby Power < 0.5W

Applications

- Instrumentation
- Lighting
- Industrial Applications
- Applied Computing
- Renewable Energy
- Test and Measurement
- Robotics
- Wireless Communication



bel POWER
SOLUTIONS &
PROTECTION

a bel group

belpowersolutions.com

1. MODEL SELECTION

MODEL NUMBER	CONNECTOR	VOLTAGE	MAX. LOAD (CONVECTION) 112.5 W @ 50°C	MAX. LOAD (CONVECTION) 120 W @ 40°C	MAX. LOAD (13 CFM)	MIN. LOAD	RIPPLE & NOISE ¹
ABC180-1T12L	Screw Terminal	12 V	9.37 A	10 A	15 A	0.0 A	2%
ABC180-1012L	Molex Connector						
ABC180-1T15L	Screw Terminal	15 V	7.5 A	8 A	12 A	0.0 A	2%
ABC180-1015L	Molex Connector						
ABC180-1T24L	Screw Terminal	24 V	4.68 A	5 A	7.5 A	0.0 A	1%
ABC180-1024L	Molex Connector						
ABC180-1T30L	Screw Terminal	30 V	3.75 A	4 A	6 A	0.0 A	1%
ABC180-1030L	Molex Connector						
ABC180-1T48L	Screw Terminal	48 V	2.34 A	2.5 A	3.75 A	0.0 A	1%
ABC180-1048L	Molex Connector						
ABC180-1T58L	Screw Terminal	58 V	1.94 A	2.07 A	3.1 A	0.0 A	1%
ABC180-1058L	Molex Connector						
COVER-180-XBC	metal cover kit accessory						

¹ Ripple is peak to peak with 20 MHz bandwidth and 10 μ F (Tantalum capacitor) in parallel with a 0.1 μ F capacitor at rated line voltage and load ranges.

2. INPUT SPECIFICATIONS

Specifications are for nominal input voltage, 25°C unless otherwise stated.

PARAMETER	DESCRIPTION / CONDITION	SPECIFICATION
Input Voltage	Universal (Derate from 100% at 100 VAC to 77% at 80 VAC)	80-264 VAC / 390 VDC
Input Frequency		47-63 Hz
Input Current	115 VAC: 230 VAC:	2.2 A max. 1.1 A max.
No Load Power	Typical for ABC180-1XXX Typical for ABC180-1XXX-PGPF	< 0.5 W < 0.85 W
Inrush Current	115 VAC: 230 VAC: 264 VAC:	25 A 45 A 75 A
Leakage Current	Typical (N.A. For Class II Option- without input Earth pin) Touch current	300 μ A < 100 μ A
Power Factor	115 VAC: 230 VAC:	> 0.95 0.90
Switching Frequency	PFC PWM	70 to 130 kHz 50 to 80 kHz

3. OUTPUT SPECIFICATIONS

PARAMETER	DESCRIPTION / CONDITION	SPECIFICATION
Output Power ²	With 13 CFM forced air cooling With natural convection cooling at 100 to 264 VAC	180 W up to 120 W
Efficiency (typical @ 230 VAC full load)	48 V, 58 V: 24 V, 30 V: 12 V, 15 V:	92% 90% 88%
Hold-up Time	At 180 W: At 120 W:	10 ms 16 ms
Line Regulation		+/-0.5%
Load Regulation		+/-1%
Transient Response	25% step load change, at 0.1 A/uS slew rate, 50% duty cycle, 50 Hz = 4%	recovery time < 5 ms
Voltage Adjustment		+/-3%
Rise Time	Typical	55 ms
Set Point Tolerance ³		+/-1%
Over Current Protection		> 110%
Over Voltage Protection		110 to 140%
Short Circuit Protection	Hiccup mode	

² Combined output power of main output, fan supply shall not exceed max. Power rating.

³ Fan supply output voltage tolerance including set point accuracy, line and load regulation is +/-10% and Ripple and noise is less than 10%.

4. ENVIRONMENTAL SPECIFICATIONS

PARAMETER	DESCRIPTION / CONDITION	SPECIFICATION
Operating Temperature	Startup guaranteed with spec. deviation	-40 to +70°C -40 to 0°C
Storage Temperature		-40 to +85°C
Relative Humidity	Non-condensing	5% to 95%
Altitude	Operating: Non-operating:	16,000 ft 40,000 ft.
MTBF	Telcordia -SR332-issue 3	3.37 million hours

5. EMC SPECIFICATIONS

PARAMETER	DESCRIPTION / CONDITION	SPECIFICATION
Conducted Emissions	EN55022-B, CISPR22-B, FCC PART15 – B	
Static Discharge	EN61000-4-2:	Level-3
RF Field Susceptibility	EN61000-4-3:	Level-3
Fast Transients/Bursts	EN61000-4-4:	Level-3
Radiated Emissions	Radiated: Radiated with external core: (King core K5B RC 25x12x15-M in input cable (5 turns))	Level A Level B
Surge Susceptibility	EN61000-4-5:	Level-3
Harmonic Current	EN61000-3-2:	Class D



Asia-Pacific
+86 755 298 85888

Europe, Middle East
+353 61 225 977

North America
+1 408 785 5200

6. SAFETY SPECIFICATIONS

PARAMETER	DESCRIPTION / CONDITION	SPECIFICATION
Isolation Voltage	Input to Output: (for ITE applications) Input to GND: (Not Applicable For Class II Option)	3000 VAC 1500 VAC
Safety Standard(s)	Approved to the latest edition of the following standards: CSA/UL60950-1, EN60950-1 and IEC60950-1. Class1 SELV	
Agency Approvals	Nemko, UL, C-UL	
CE mark	Complies with LVD Directive	


7. CONNECTOR & PIN DESCRIPTION

CONNECTOR	PIN	DESCRIPTION / CONDITION	MANUFACTURER / PN
AC Input Connector	J1	Pin 1 AC Line Pin 2 Not Fitted Pin 3 AC Neutral	Molex: 26-60-4030 Mating: 09-50-3031; Pins: 08-50-0106
DC Output Connector	J2	Pin 1, 2, 3 V1 +VE Pin 4, 5, 6 V1 -VE	Option 1 (Screw Terminal): Molex: 39357 Series or equivalent Option 2 (Molex Connector): Molex: 26-60-4060 Mating: 09-50-3061; Pins: 08-50-0106
Aux (Fan) Output	J3	Pin 1 FAN +VE Pin 2 FAN -VE	AMP: 640456-2 Mating: 640440-2
Signal Output ⁴	J4	Pin 1 Vs Pin 2 PGPF Pin 3 GDN	AMP :640456-3 Mating: 640440-3


⁴ For PGPF Signal Output Connector option please contact factory.

8. MECHANICAL SPECIFICATIONS

PARAMETER	DESCRIPTION / CONDITION
Weight	approx. 200 g
Dimensions	101.6 x 50.8 x 19.05 mm (4 x 2 x 0.75 inches)
Cooling	180 W with 13 CFM forced air cooling (refer to Mechanical Drawing) Up to 120 W with natural convection cooling (refer to Derating Curve)




Mechanical Drawing – Option 1 without PGPF




Mechanical Drawing – Option 2 without PGPF

NOTES: In case the PCB is mounted in a metal enclosure, using metal hardware ensure the following:

- 1 Stand off, used to mount PCB has OD of 5.4 mm max.
- 2 Screws, used to fix PCB on stand off, have head dia of 6.0 mm max.
- 3 Washer, if used, to have dia of 6.5 mm max.



Mechanical Drawing – Option 1 with PGPF





Mechanical Drawing – Option 2 with PGPF

NOTES: In case the PCB is mounted in a metal enclosure, using metal hardware ensure the following:

- 1 Stand off, used to mount PCB has OD of 5.4 mm max.
- 2 Screws, used to fix PCB on stand off, have head dia of 6.0 mm max.
- 3 Washer, if used, to have dia of 6.5 mm max.

DERATING CURVES



For more information on these products consult: tech.support@psbel.com

NUCLEAR AND MEDICAL APPLICATIONS - Products are not designed or intended for use as critical components in life support systems, equipment used in hazardous environments, or nuclear control systems.

TECHNICAL REVISIONS - The appearance of products, including safety agency certifications pictured on labels, may change depending on the date manufactured. Specifications are subject to change without notice.



Asia-Pacific
+86 755 298 85888

Europe, Middle East
+353 61 225 977

North America
+1 408 785 5200