



RAYCHEM CAT 6A CABLE

10 Gb/s ETHERNET IN A SMALLER, MORE RUGGED CABLE FOR
HARSH MILITARY AND AEROSPACE ENVIRONMENTS

RAYCHEM CAT 6A CABLE

Smaller, More Rugged Cable for Harsh Environments



Achieve 10 Gb/s speeds while saving space and helping to meet the demands of harsh military and aerospace environments. Raychem Cat 6a cables are fully shielded four-pair cables meeting the electrical requirements of ANSI/TIA-568-C.2 for Category 6a cable.

The cable's FEP insulation and jacket allow a reduced-diameter cable, when compared to standard commercial Cat 6a cables, while stranded conductors provide high flexibility in routing.

Engineered to Perform

The cable is highly engineered to provide excellent 10G signal integrity and performance stability over a temperature range as wide as -55°C to +200°C.

The cable comes in two wire gauges: the industry-standard 24 AWG and a smaller 26 AWG as required in certain military and aerospace applications.

High Speed, High Compatibility

Compared to commonly used tape-wrapped cables, Raychem Cat 6a cables are easier to terminate. Plus the cable is compatible with common high-speed aerospace and military connectors. This compatibility includes TE's high-performance 10 Gb/s CeeLok FAS-T and CeeLok FAS-X connectors.

HIGH PERFORMANCE

- Excellent signal integrity at 10 Gb/s
- Stable performance in extreme conditions
- Support full 100 m links

COMPACT AND RUGGED

- Ruggedized to survive in harsh environments
- Reduced size and weight

EASY TO USE

- Easier to terminate compared to tape-wrapped designs
- Flexible with tight bend radius for easier routing

COMPATIBLE

- Fit most high-speed aerospace connectors, including TE's CeeLok FAS-T and CeeLok FAS-X connectors

APPLICATIONS

- Military and Commercial Aerospace
- In-Flight Entertainment Systems
- Flight Control
- Avionics
- Cabin Management Systems
- Military Ground Vehicles
- Formula 1 Motorsport

TE Components . . . TE Technology . . . TE Know-how . . .

AMP | Agastat | CII | Hartman | Kilovac | Microdot | Nanonics | Polamco | Raychem | Rochester | DEUTSCH
SEACON Phoenix | L.L. Rowe | Phoenix Optix | AFP | SEACON

Get your product to market faster with a smarter, better solution.



Specifications

MATERIALS

- **Conductors:**
 24 AWG: Stranded silver-coated copper alloy
 26 AWG: Stranded silver-coated high-strength copper alloy
- **Dielectric:** FEP
- **Core Wrap:** PTFE (26 AWG cables only)
- **Shielding:**
 200°C Rated Cables: Silver-coated copper braid an aluminum/polyimide foil wrap
 150°C Rated Cables: Tin-coated copper braid an aluminum/polyester foil wrap
- **Jacket:** FEP, in colors per MIL-STD-681 or laser-markable white

ELECTRICAL


- **Standard Impedance (Nom):** 100 ohms
- **Attenuation (Max.) at 500 MHz:**
 24 AWG: 54.4 ohms/100 m
 26 AWG: 67.9 ohms/100 m
- **Mutual Capacitance (Max.) at 1 kHz:** 5.6 nF/100 m
- **DC Resistance (Nom.) at 20°C:** 43.9 ohms/1000 ft.
- **Velocity of Propagation (Nom.):** 70%

ENVIRONMENTAL/MECHANICAL

- **Temperature Range:** -55°C to 150°C or 200°C
- **Bend Radius (Min.):**
 24 AWG: 1.0 in.
 26 AWG: 0.75 in.

STANDARDS/SPECIFICATIONS

- **Ethernet Cable:** ANSI/TIA-568-C.2 and IEEE 801.3
- **Environmental Testing:** WC 27500/AS6070
- **Smoke and toxicity:**
 Boeing and Airbus ABD0031 standards
 FAR Part 25, Appendix F, Part 1
- **TE Product Specification:** 1200/1400



Part Numbers

Temperature (Max.)	Conductor Size	Jacket OD, Nom.	Part No.
150°C	24 AWG	0.292	C6A-24C444-814
	26 AWG	0.237	C6A-26C444-814
200°C	24 AWG	0.290	C6A-24C444-B24
	26 AWG	0.235	C6A-26C444-B24

LET'S CONNECT

We make it easy to connect with our experts and are ready to provide all the support you need. Just call your local support number or visit www.te.com/industrial to chat with a Product Information Specialist.

Technical Support

te.com/support-center

North America	+1 800 522 6752	Asia Pacific	+86 400 820 6015
North America (Toll)	+1 717 986 7777	Japan	044 844 8180
EMEA/South Africa	+800 0440 5100	Australia	+61 2 9554 2695
EMEA (Toll)	+31 73 624 6999	New Zealand	+64 (0) 9 634 4580
India (Toll-Free)	+800 440 5100		

te.com/cat6a

CeeLok FAS-T, CeeLok FAS-X, Raychem, TE, TE Connectivity and the TE connectivity (logo) are trademarks of the TE Connectivity Ltd. family of companies. Boeing, Airbus, Formula 1, and other products, logos, and company names mentioned herein may be trademarks of their respective owners.

While TE Connectivity (TE) has made every reasonable effort to ensure the accuracy of the information herein, nothing herein constitutes any guarantee that such information is error-free, or any other representation, warranty or guarantee that the information is accurate, correct, reliable or current. The TE entity issuing this publication reserves the right to make any adjustments to the information contained herein at any time without notice. All implied warranties regarding the information contained herein, including, but not limited to, any implied warranties of merchantability or fitness for a particular purpose are expressly disclaimed. The dimensions herein are for reference purposes only and are subject to change without notice. Specifications are subject to change without notice.

Consult TE for the latest dimensions and design specifications.

© 2016 TE Connectivity Ltd. family of companies. All Rights Reserved.

1-1773889-1 09/16 Original