


NEW PRODUCT INFORMATION**NEW DOME LENS SMD-LED IN 0805 PACKAGE
KPTD-2012 SERIES****Features**

- 2.0 mm x 1,25 mm x 1,05 mm
- Low power consumption
- Package: 3000 pcs / reel
- Moisture sensitivity level: 3
- RoHS compliant

Applications

- Backlight
- Status Indicator
- Home and smart appliances
- Wearable and portable devices
- Healthcare applications

Part number	Dom. wavelength	Lens type	lv (mcd) @ 20mA		Viewing angle
			min.	typ.	
KPTD-2012SURCK	630 nm	water-clear	300	550	40°
KPTD-2012SECK	601 nm	water-clear	300	750	40°
KPTD-2012SECK-J3-PRV	625 nm	water-clear	1000	2000	40°
KPTD-2012CGCK	570 nm	water-clear	120	350	40°
KPTD-2012SYCK	590 nm	water-clear	400	870	40°
KPTD-2012SYCK-J3-PRV	590 nm	water-clear	1000	2000	40°
KPTD-2012QBC-D	465 nm	water-clear	120	400	30°
KPTD-2012VBC-D	470 nm	water-clear	300	600	30°
KPTD-2012ZGCK	525 nm	water-clear	1600	2500	30°

Luminous intensity value is traceable to the CIE 120-2007 compliant national standards

Head office in Germany:

Lindenau 7 / Gewerbegebiet
D-47661 Issum
Tel. +49 (2835) 4446-0
Fax +49 (2835) 4446-29
info@kingbright-europe.de

Branch office in France:

33 rue Benoit Malon
F-92150 SURESNES
Tel. +33 01.71.12.61.28
Fax +33 01.71.12.61.36
info@kingbright-europe.fr