



ND1K0.520.2FW.B.007

Nickel sensor with wires

For medium temperatures

Benefits & Characteristics

- Excellent long-term stability
- Connections remain in shape
- Easy interchangeability
- Simple linearization
- Vibration and temperature shock resistant


Illustration¹⁾



Technical Data

Operating temperature range:	-60 °C to +200 °C	
Nominal resistance:	1000 Ω at 0 °C	
Characteristics curve:	6180 ppm/K (Nickel ND)	
Long-term stability:	< 0.1 % at 1000 h at maximal operating temperature	
Tolerance class (dependent on temperature range):	T > 0 °C 0.4 + 0.007 x t	IST AG reference B
Connection:	Ni/Au-flat wire, 0.2 x 0.4 mm (solderable, weldable, crimpable), 7 mm long	
Dimensions:	5.0 x 2.0 x 0.65 / 1.3	
Tolerance (chip):	L ±0.2 mm, W ±0.2 mm, H ±0.1 mm, H2 ±0.3 mm	

Product Photo





Order Information

Description:

ND1K0.520.2FW.B.007

Item number:

103172

Former main reference:

020.00348



Application Note

RTD Nickel Sensor

General Information

In many sectors, temperature measurement is one of the most important physically defined parameter to determine product quality, security and reliability. Temperature sensors are produced with different technologies to fit specific application requirements. To this end, IST AG has concentrated the development, manufacturing processes and materials to produce high-end thin-film temperature sensors. This know-how, partially derived from the semiconductor industry, allows IST AG to manufacture sensors in very small dimensions. Thin-film temperature sensors exhibit a very short response time due to their low thermal mass. The technologies and processes of IST AG thin-film sensors combines the positive attributes of traditional wire-wound nickel sensors - accuracy, long-term stability, repeatability and interchangeability within a wide temperature range. The advantages of thin-film mass-production create an optimal price/performance-ratio.

Construction

The temperature sensor consists of a photolithographically structured nickel meander on a ceramic substrate. The resistivity is laser-trimmed and precisely adjusted to the final value. The resistive structure is covered with a polymer or glass passivation layer protecting the sensor against mechanical damages. The welded wires are covered with an additional fixation layer.

Nominal Value and Temperature Coefficient

The nominal value of the sensor is the defined value of the sensor resistance at 0 °C. The temperature coefficient α (TCR) is defined as:

$$\alpha = \quad \quad \quad [K^{-1}] \text{ according to the DIN 43760 (formerly) numerical value of } 0.00618 \text{ K}^{-1}.$$

Generally, the value is defined in ppm/K.

R_0 = resistance value in Ω at 0 °C
 R_{100} = resistance value in Ω at +100 °C

Long-term Stability

The change in ohmic value after 1,000 h at maximum operating temperature amounts to less than 0.1 %.

Temperature Characteristic Curve¹⁾

The characteristic curve is defined with a polynomial:

$$R(T) = R_0 (1 + A * T + B * T^2 + C * T^3 + D * T^4 + E * T^5 + F * T^6)$$

	Nickel ND (6180 ppm/K)	Nickel NL (5000 ppm/K)	Nickel NJ (6370 ppm/K)	Nickel NA (6720 ppm/K)
A	$5.485 * 10^{-3} [^{\circ}C^{-1}]$	$4.427 * 10^{-3} [^{\circ}C^{-1}]$	$5.64742 * 10^{-3} [^{\circ}C^{-1}]$	$5.88025 * 10^{-3} [^{\circ}C^{-1}]$
B	$6.65 * 10^{-6} [^{\circ}C^{-2}]$	$5.172 * 10^{-6} [^{\circ}C^{-2}]$	$6.69504 * 10^{-6} [^{\circ}C^{-2}]$	$8.28385 * 10^{-6} [^{\circ}C^{-2}]$
C	0	$5.585 * 10^{-9} [^{\circ}C^{-3}]$	$5.68816 * 10^{-9} [^{\circ}C^{-3}]$	0
D	$2.805 * 10^{-11} [^{\circ}C^{-4}]$	0	0	$7.67175 * 10^{-12} [^{\circ}C^{-4}]$
E	0	0	0	0
F	$-2 * 10^{-17} [^{\circ}C^{-6}]$	0	0	$-1.5 * 10^{-16} [^{\circ}C^{-6}]$

R_0 = resistance value in Ω at 0°C

T = temperature at ITS 90


¹⁾ customer-specific characteristic curve (e.g. Balco) available



Tolerance classes formerly DIN 43760

Class	± limit deviations in °C		IST AG reference
	T < 0 °C	T > 0 °C	
1/2 DIN 43760	$0.2 + 0.014 \times T $	$0.2 + 0.0035 \times T $	A
DIN 43760	$0.4 + 0.028 \times T $	$0.4 + 0.007 \times T $	B

|T| is the numerical value of the temperature in °C without taking leading signs into account. The tolerances are only guaranteed up to +260 °C.



Applied Current

The current applied is highly dependent on the application and leads to self-heating effects and temperature measuring errors is $\Delta T = P/E$ (see self-heating). Depending on the thermal transfer from the sensor into the application, the current can be increased. There is no bottom current limit for nickel thin-film sensors.

Recommended current supplies:

100 Ω	500 Ω	1000 Ω	2000 Ω	10000 Ω
1 mA	0.5 mA	0.3 mA	0.2 mA	0.1 mA

Self-heating

To measure the resistance, electric current must run through the element. The current generates heat energy, resulting in errors of measurement. To minimize the error, caused by self-heating, the current should be kept as low as possible. Temperature error $\Delta T = P/E = R \times I^2/E$.

E = the self-heating coefficient in mW/K, R = resistance in kΩ, I = measured current in mA, P = Power in mW

Response Time

The response time is defined as the time in seconds the sensor needs to detect the change in temperature. $t_{0.63}$ describes the time in seconds the sensor needs to measure 63 % of the temperature change. The response time is depending on the sensor dimensions, the thermal contact resistance and the surrounding medium.



Dimensions number	Sensor size L x W x H / H2 in mm	Response time in seconds						Self-heating			
		Water (v = 0.4 m/s)			Air (v = 1 m/s)			Water (v = 0 m/s)		Air (v = 0 m/s)	
		t _{0.5}	t _{0.63}	t _{0.9}	t _{0.5}	t _{0.63}	t _{0.9}	E in mW/K	ΔT in [mK] ¹⁾	E in mW/K	E in mW/K
232	2	0.09	0.12	0.33	2.7	3.6	7.5	40	2.3	4	22.5
232	2.3 x 2.0 x 0.65/1.3	0.15	0.2	0.55	4.5	6	12	40	2.3	4	22.5
325	3.0 x 2.5 x 0.65/1.3	0.25	0.3	0.7	5.5	7.5	16	90	1	8	11.3
516	5.0 x 1.6 x 0.65/1.3	0.25	0.3	0.7	5.5	7.5	16	80	1.1	7	12.9
520	5.0 x 2.0 x 0.65/1.3	0.25	0.3	0.75	6	8.5	18	80	1.1	7	12.9
525	5.0 x 2.5 x 0.65/1.3	0.33	0.4	0.85	6.5	9	19	90	1	8	11.3
102	10.0 x 2.0 x 0.65/1.3	0.33	0.4	0.85	7.5	10.5	20	140	0.6	10	9
538	5.0 x 3.8 x 0.65/1.3	0.35	0.5	0.9	7.5	10	20	140	0.6	10	9
505	5.0 x 5.0 x 0.65/1.3	0.4	0.5	1.1	8	11	21	150	0.6	11	0.6
SMD 1206	3.2 x 1.6 x 0.4	0.15	0.25	0.45	3.5	4.2	10	55	1.8	7	14.3
SMD 0805	2.0 x 1.2 x 0.4	0.1	0.12	0.33	2.5	3	8	38	2.6	4	25

1) Self-heating [mK] was measured for Ni1000 with 0.3 mA measurement current at 0 °C

L: Sensor length (without connections)

H: Sensor height (without connections)

W: Sensor width

H2: Sensor height (incl. connections and strain relief)

The values in the table are for informative purposes only. Based on the assembly method and the different measurement conditions, self-heating and response time can vary.

Operating Conditions

The sensors are designed and developed to have a high performance and robustness. However, the sensor must be tested, in the application, by the customer, to ensure durability and performance. IST AG cannot be held liable for any application failures.

It is recommended to protect the sensor from direct contact to the environment, to avoid aggressive media and high humidity atmospheres. The sensor should not be in direct contact with liquids.

Dimensions Tolerances

Sensor width (W) ±0.2 mm
Sensor length (L) ±0.2 mm
Sensor height (H2) ±0.2 mm

Sensor height (H) ±0.1 mm
Wire length ±1.0 mm (5 mm to 30 mm)
Wire length > 30 mm, tolerances on request

Storage

Nickel thin-film sensors must not be exposed to etching, corrosive or damp environments. Humidity above 70% rH and direct exposure to sunlight should be avoided. Additional storage precautions apply to specific sensors.

In ideal circumstances, the following parameters apply:

Temp. range:

10 °C to 30 °C

Humidity:

50 +/- 10 % rH

Storage:

Neutral environment, no direct exposure to sunlight

Additional storage precautions:

Silver plated and silver wire should be packaged in an airtight wrapping to avoid tarnishing.



Innovative Sensor Technology IST AG, Stegrütistrasse 14, 9642 Ebnat-Kappel, Switzerland
Phone: +41 71 992 01 00 | Fax: +41 71 992 01 99 | Email: info@ist-ag.com | www.ist-ag.com

All mechanical dimensions are valid at 25 °C ambient temperature, if not differently indicated • All data except the mechanical dimensions only have information purposes and are not to be understood as assured characteristics • Technical changes without previous announcement as well as mistakes reserved • The information on this data sheet was examined carefully and will be accepted as correct; No liability in case of mistakes • Load with extreme values during a longer period can affect the reliability • The material contained herein may not be reproduced, adapted, merged, translated, stored, or used without the prior written consent of the copyright owner • Typing errors and mistakes reserved • Product specifications are subject to change without notice • All rights reserved