



# / LEAD-TIME GUIDE JULY 2025

**POWER**

| Product                    | Lead-time: weeks | Lead-time: prognosis |
|----------------------------|------------------|----------------------|
| AC-DC PSU general purpose  | 20 - 48          | =                    |
| AC-DC PSU medical          | 20 - 48          | =                    |
| AC-DC PSU DIN rail         | 20 - 48          | =                    |
| Rectifiers & front-end PSU | 22 - 48          | =                    |
| AC-DC external-adaptors    | 20 - 48          | =                    |
| AC-DC railway              | 20 - 48          | =                    |
| AC-DC LED drivers general  | 20 - 48          | =                    |
| AC-DC LED drivers special  | 20 - 48          | =                    |
| DC-DC miniature            | 12 - 36          | =                    |
| DC-DC industrial & bricks  | 12 - 48          | =                    |
| DC-DC panel mount          | 12 - 48          | =                    |
| DC-DC LED drivers          | 12 - 48          | =                    |

**FILTER & MAGNETICS**

| Product                 | Average lead-time | Lead-time: prognosis |
|-------------------------|-------------------|----------------------|
| Active filter           | 10                | =                    |
| EMI filter              | 10                | =                    |
| Power line filter       | 10                | =                    |
| SAW filter              | 14 - 38           | =                    |
| Ceramic filter          | 10                | =                    |
| EMI/RFI filter          | 10                | =                    |
| RF filter               | 10                | =                    |
| Common mode chokes      | 10 - 30           | ↑                    |
| Ferrite chip beads      | 10 - 12           | =                    |
| Ferrite core            | 12 - 42           | =                    |
| Inductor leaded         | 10 - 14+          | =                    |
| Wireless charging coils | 16 - 18           | =                    |
| Inductor surface mount  | 8 - 80            | ↑                    |

**ELECTROMECHANICAL**

| Product                   | Lead-time: weeks | Lead-time: prognosis |
|---------------------------|------------------|----------------------|
| Switches                  | 10 - allocation  | =                    |
| Relays general purpose    | 35 - allocation  | =                    |
| Relays automotive/telecom | 35 - allocation  | =                    |
| Fans                      | 19 - 52          | =                    |
| Heatsinks                 | 8 - 12           | =                    |
| Sensors                   | 10 - 48          | ↓                    |

**CONNECTORS**

| Product                                              | Average lead-time | Lead-time: prognosis |
|------------------------------------------------------|-------------------|----------------------|
| Cable flat                                           | 13                | ↑                    |
| Backplanes DIN 41612; 2MM; high speed; power signal; | 16                | ↑                    |
| I/O connectors                                       | 14                | ↑                    |
| Memory card reader                                   | 14                | =                    |
| Sockets DIP/SIP; PLCC/PGA/BGA; SIMM/IMM/Holtite      | 19                | =                    |
| Non-solderable terminals/fastons                     | 9                 | =                    |
| Circular military                                    | 21                | ↑                    |
| Circular industrial                                  | 17                | ↑                    |
| Circular medical                                     | 17                | ↑                    |
| Rectangular military                                 | 21                | ↑                    |
| Rectangular industrial                               | 17                | =                    |
| Rectangular medical                                  | 15                | =                    |
| RF coaxial                                           | 15                | ↑                    |
| Board to board                                       | 15                | ↑                    |
| Wire to board/wire to wire                           | 15                | =                    |
| Automotive                                           | 19                | ↑                    |
| Power - connector systems                            | 19                | =                    |

## PASSIVE

| Product                                               | Lead-time:<br>weeks | Lead-time:<br>prognosis |
|-------------------------------------------------------|---------------------|-------------------------|
| Ceramic capacitors single layer                       | 10 - 24             | =                       |
| Ceramic capacitors leaded multilayer                  | 20 - 30             | =                       |
| Ceramic capacitors multilayer SMD                     | 8 - 20+             | =                       |
| Ceramic capacitors multilayer high CV                 | 8 - 20+             | =                       |
| Ceramic capacitors safety caps                        | 16 - 30             | =                       |
| Ceramic capacitors trimmer caps                       | 16 - 30             | =                       |
| Ceramic capacitors automotive                         | 8 - 20+             | =                       |
| Aluminium electrolytic capacitors leaded              | 8 - 26+             | ↓                       |
| Aluminium electrolytic capacitors SMD                 | 8 - 26+             | ↓                       |
| Aluminium electrolytic capacitors snap-in & large can | 8 - 26+             | ↓                       |
| Film capacitors leaded                                | 8 - 26+             | ↓                       |
| Film capacitors SMD                                   | 8 - 26+             | ↓                       |
| Film capacitors suppression                           | 8 - 26+             | ↓                       |
| Polymer capacitors                                    | 8 - 26+             | ↑                       |
| Tantalum capacitors leaded                            | 8 - 16              | =                       |
| Tantalum capacitors SMD                               | 8 - 16              | =                       |
| Resistor Metal Film SMD Thick Film                    | 10 - 20             | =                       |
| Resistor Metal Film SMD Thin Film                     | 10 - 20             | =                       |
| Resistor Metal Film MELF                              | 11 - 12             | =                       |
| Resistor Metal Film SMD Low Ohmic                     | 10 - 20             | =                       |
| Resistor Networks & Arrays                            | 9 - 28              | =                       |
| Resistor Metal Film & Oxide Leaded                    | 7 - 16              | =                       |
| Resistor Ceramic Leaded                               | 14 - 19             | =                       |
| Resistor Carbon Film Leaded                           | 10 - 20             | =                       |
| Resistor Wirewound                                    | 10 - 25             | =                       |
| Thermistor NTC                                        | 12 - 26             | =                       |
| Thermistor PTC                                        | 12 - 26             | =                       |

| Product                                                 | Lead-time:<br>weeks | Lead-time:<br>prognosis |
|---------------------------------------------------------|---------------------|-------------------------|
| Trimmer SMD                                             | 7 - 21              | =                       |
| Trimmer Leaded                                          | 7 - 19              | =                       |
| Potentiometer                                           | 14 - 32             | =                       |
| Varistor SMD                                            | 11 - 26             | =                       |
| Varistor Leaded                                         | 12 - 25             | =                       |
| Circuit protection - fuses                              | 8 - 26+             | =                       |
| Circuit protection - resettable devices                 | 8 - 26+             | =                       |
| Circuit protection - thermistors                        | 8 - 26+             | =                       |
| Circuit protection - varistors                          | 8 - 26+             | =                       |
| Frequency control crystals/ oscillators                 | 12 - 30+            | =                       |
| Frequency control resonators                            | 8 - 14              | =                       |
| Electromagnetic piezo buzzers, sounders and transducers | 8 - 14              | =                       |
| Antennas                                                | 8 - 24              | =                       |
| Wireless modules                                        | 16-32               | =                       |

## AUSTRIA

Avnet EMG Elektronische  
Bauelemente GmbH  
Grünbergstraße 15/1/4.OG,  
A-1120 Wien  
Phone: +43 (0)1 86642-0  
Fax: +43 (0)1 86642-250  
wien@avnet-abacus.eu

## BELGIUM

De Kleetlaan 3  
BE-1831 Diegem  
Phone: +32 2 227 2000  
diegem@avnet-abacus.eu

## BULGARIA

48, Sitnyakovo Boulevard  
Unit 1006, Floor 10,  
BG-1505 Sofia  
Phone: +359 896 135 069  
bulgaria@avnet-abacus.eu

## CROATIA

c/o Avnet Abacus Slovenia  
Dunajska Cesta 167  
SI-1000 Ljubljana  
Phone: +386 (0)1 560 97 54  
Fax: +386 (0)1 560 98 78  
croatia@avnet-abacus.eu

## CZECH REPUBLIC

Amazon Court Karolinska 661/4  
CZ-18600 Prague  
Phone: +420 234 091 011  
Fax: +420 234 091 010  
praha@avnet-abacus.eu

## DENMARK

Knudlundvej 24, DK-8653 Them  
Phone: +45 86 84 84 84  
Fax: +45 86 84 82 44  
them@avnet-abacus.eu

Lyskær 9, DK-2730 Herlev  
Phone: +45 86 84 84 84  
Fax: +45 43 29 37 00  
herlev@avnet-abacus.eu

## EGYPT

c/o Avnet Abacus Turkey  
Tatlısu Mahallesi Pakdil  
Sokak No: 7 Kat: 2  
TR-34774 Umraniye Istanbul Turkiye  
Phone: +90 216 52 88 370  
Fax: +90 216 52 88 377  
egypt@avnet-abacus.eu

## ESTONIA

Suur-Jõe 63, Pärnu,  
EE-80042 Pärnu Maakond  
Phone: +372 56637737  
paernu@avnet-abacus.eu

## FINLAND

Klovinpellontie 1-3  
Tower 1, Floor 6  
FI-02180 Espoo  
Phone: +35 820 749 9220  
Fax: +35 820 749 9240  
espoo@avnet-abacus.eu

## FRANCE

Le Copernic  
12, rue Jean Bart  
FR-91300 Massy  
Phone: +33 (0) 1 6447 2929  
Fax: +33 (0) 1 6447 9150  
paris@avnet-abacus.eu

8 chemin de la Terrasse  
Bat D 1er étage  
FR-31500 Toulouse  
Phone: +33 (0) 5 6247 4787  
Fax: +33 (0) 5 6247 4761  
toulouse@avnet-abacus.eu

16 C Rue de Jouanet  
FR-35700 Rennes  
Phone: +33 (0) 2 9983 7720  
Fax: +33 (0) 2 9983 4829  
rennes@avnet-abacus.eu

2 avenue Tony Garnier, 3rd floor  
FR-69007 Lyon  
Phone: +33 (0) 4 7877 1370  
Fax: +33 (0) 4 7877 1391  
lyon@avnet-abacus.eu

## GERMANY

Kaiserin-Augusta-Allee 14  
DE-10553 Berlin  
Phone: +49 (0) 30 790 997 0  
Fax: +49 (0) 30 790 997 51  
berlin@avnet-abacus.eu

Industriestr. 16  
DE-76297 Stutensee  
Phone: +49 (0) 7249 910 149  
Fax: +49 (0) 7249 910 177  
stutensee@avnet-abacus.eu

Rhenus-Platz 2  
D-59439 Holzwickede/Dortmund  
Phone: +49 (0) 2301 2959 27  
Fax: +49 (0) 2301 2959 29  
dortmund@avnet-abacus.eu

Ursula-de-Boor-Str. 45  
22419 Hamburg  
Phone: +49 (0) 40 608 23 59 0  
Fax: +49 (0) 40 608 23 59 20  
hamburg@avnet-abacus.eu

Im Technologiepark 2-8  
DE-85586 Poing  
Phone: +49 (0) 8121 775 400  
bayern@avnet.eu

Lina-Ammon-Str. 19 b  
DE-90471 Nuernberg  
Phone: +49 (0) 911 244 250  
Fax: +49 (0) 911 244 25 25  
bayern@avnet.eu

Neue Ramtelstr. 4  
DE-71229 Leonberg  
Phone: +49 (0) 7152 3009 70  
Fax: +49 (0) 7152 3009 96  
stuttgart@avnet-abacus.eu

Rotenburger Str. 20  
D-30659 Hannover  
Phone: +49 (0) 511 336517 10  
hannover@avnet-abacus.eu

## GREECE

c/o Abacus Avnet Serbia  
Milentija Popovića 5B,  
Floors 6-8  
Belgrade RS-11070  
Phone: +381 11 4022302  
Fax: +381 11 4049900  
belgrade@avnet-abacus.eu

## HUNGARY

c/o Avnet Abacus Slovakia  
GreenPoint Offices,  
Blok F Turcianska 2  
SK-82109 Bratislava  
Phone: +421 232 242 608  
Fax: +421 2 32 1111 40  
budapest@avnet-abacus.eu

## IRELAND

c/o Avnet Abacus Bolton  
Deakins Business Park  
Blackburn Road, Egerton  
Bolton BL7 9RP  
+44 (0)1204 936400  
abacus.bolton@avnet-abacus.eu

## ISRAEL

1 Habrosh Street  
Bney Dror IL-4581500  
Phone: +972 9 778 0280  
Fax: +972 3 760 0794  
israel@avnet-abacus.eu

## ITALY

Via Manzoni 44  
IT-20095 Cusano Milanino/Milano  
Phone: +39 02 660 921  
Fax: +39 02 66092 332  
milano@avnet-abacus.eu

Viale dell'industria 23  
IT-35129 Padova  
Phone: +39 049 7800 381  
Fax: +39 049 7730 36  
padova@avnet-abacus.eu

Via Scaglia Est. 31/33  
IT-41126 Modena  
Phone: +39 059 34891  
Fax: +39 059 344 993  
modena@avnet-abacus.eu

Via Panciatichi 40/11  
IT-50127 Firenze  
Phone: +39 055 436 1928  
Fax: +39 055 428 8810  
firenze@avnet-abacus.eu

Via Tiburtina, 652/A  
C/O Urban Places  
IT-00159 Roma  
Phone: +39 02 660 921  
rome@avnet-abacus.eu

## LATVIA

c/o Avnet Abacus Poland  
Plac Solny 16  
PL-50-062 Wroclaw  
Phone: +48 71 34 205 99  
Fax: +48 71 34 229 10  
latvia@avnet-abacus.eu

## LITHUANIA

c/o Avnet Abacus Poland  
Plac Solny 16  
PL-50-062 Wroclaw  
Phone: +48 71 34 205 99  
Fax: +48 71 34 229 10  
lithuania@avnet-abacus.eu

## NETHERLANDS

Stadionstraat 2, 6th floor  
NL-4815 NG Breda  
Phone: +31 (0) 76 57 22 300  
Fax: +31 (0) 76 57 22 303  
breda@avnet-abacus.eu

## NORWAY

Olaf Helsetsvet 6,  
NO-0694 Oslo  
Phone: +47 (0) 94 89 53 73  
oslo@avnet-abacus.eu

## POLAND

Plac Solny 16  
PL-50-062 Wroclaw  
Phone: +48 71 34 205 99  
Fax: +48 71 34 229 10  
wroclaw@avnet-abacus.eu

## PORTUGAL

Tower Plaza, Rot. Eng. Edgar  
Cardoso, 23,Piso 14, Sala E  
PT-4400-676 Vila Nova de Gaia  
Phone: +351 223 779502  
Fax: +351 223 779503  
portugal@avnet-abacus.eu

## ROMANIA

SkyTower Building, 12th floor,  
Calea Floreasca 246C,  
RO-014476 Bucharest  
Phone: +4021 528 16 90  
romania@avnet-abacus.eu

## SERBIA

Milentija Popovića 5B, Floors 6-8  
Belgrade RS-11070  
Phone: +381 11 4022302  
Fax: +381 11 4049900  
belgrade@avnet-abacus.eu

## SLOVAKIA

GreenPoint Offices,  
Blok F Turcianska 2  
SK-82109, Bratislava  
Phone: +421 232 242 608  
Fax: +421 2 32 1111 40  
slovakia@avnet-abacus.eu

## SLOVENIA

Dunajska Cesta 167  
SI-1000 Ljubljana  
Phone: +386 (0)1 560 97 60  
Fax: +386 (0)1 560 98 78  
ljubljana@avnet-abacus.eu

## SOUTH AFRICA

Block 13, Pinewood Office Park  
33 Riley Road Woodmead,  
ZA-2191 Sandton, Johannesburg  
Phone: +27 (0)10 447 0180  
avnet-abacus-sales-southafrica@avnet.eu

## SPAIN

NyN Tower, C/Tarragona  
149-157, Floor 19  
ES-08014 Barcelona  
Phone: +34 (0) 93 327 85 50  
Fax: +34 (0) 93 425 05 44  
barcelona@avnet-abacus.eu

Avenida Madariaga 1  
Floor 3  
ES-48014 Bilbao  
Phone: +34 (0) 94 457 00 44  
Fax: +34 (0) 94 456 88 55  
bilbao@avnet-abacus.eu

Ronda de Poniente  
(pq Empresarial Euronova),  
4 - 2ª PLANTA, tres Cantos,  
28760, Madrid  
madrid@avnet-abacus.eu

## SWEDEN

Avnet Nortec AB  
Hemvärmsgatan 9  
SE-171 54 Solna  
Phone: +46 (0)8587 462 00  
Fax: +46 (0)8587 460 01  
stockholm@avnet-abacus.eu

Smörhålevägen 3  
SE-43442 Kungsbacka  
Phone: +46 (0)8 58746 200  
Fax: +46 (0)300 140 15  
gothenburg@avnet-abacus.eu

## SWITZERLAND

Bernstrasse 394  
CH-8953 Dietikon  
Phone: +41 (0)43 322 49 90  
Fax: +41 (0)43 322 49 99  
zurich@avnet-abacus.eu

## TURKEY

Tatlısu Mahallesi Pakdil  
Sokak No: 7 Kat: 2  
TR-34774 Umraniye Istanbul Turkiye  
Phone: +90 216 52 88 370  
Fax: +90 216 52 88 377  
istanbul@avnet-abacus.eu

## UK

Building 5, Waltham Park  
White Waltham  
Maidenhead Berkshire SL6 3TN  
Phone: +44 (0)1628 512900  
Fax: +44 (0)1628 512999  
abacus.maidenhead@avnet-abacus.eu

Deakins Business Park  
Blackburn Road, Egerton  
Bolton BL7 9RP  
+44 (0)1204 936400  
abacus.bolton@avnet-abacus.eu

## UKRAINE

c/o Avnet Abacus Poland  
Plac Solny 16  
PL-50-062 Wroclaw  
Phone: +48 71 34 205 99  
Fax: +48 71 34 229 10  
ukraine@avnet-abacus.eu