























PCB & Chassis Mount

3W to 5W	10W to 15W	20W to 25W	30W	40W	60W	75W to 80W	100W to 130W	150W to 160W	180W to 265W	350W to 500W	500W to 650W
<p>VCE03</p> <ul style="list-style-type: none"> • 3W • 40.6 x 19.1 x 19.1mm • PCB mount • 85-305VAC input • Class II 	<p>ECE10</p> <ul style="list-style-type: none"> • 10W • 38.1 x 25.4 x 15.2mm • PCB mount • <0.3W standby power • Class II 	<p>ECE20</p> <ul style="list-style-type: none"> • 20W • 52.4 x 27.2 x 23.0mm • PCB mount • Encapsulated • Class II 	<p>ECL30</p> <ul style="list-style-type: none"> • 30W • 75.2 x 34.6 x 26.7mm • PCB & chassis mount • Single & multi outputs • Class II 	<p>ECF40</p> <ul style="list-style-type: none"> • 40W • 76.2 x 38.1 x 28.0mm • Low profile • <0.15W no load power • Class I & II 	<p>ECE60</p> <ul style="list-style-type: none"> • 60W • 91.4 x 38.1 x 28.0mm • PCB & chassis mount • <0.3W no load power • Class II 	<p>ASB75</p> <ul style="list-style-type: none"> • 75W • Half brick package • Baseplate cooled • No external components • Optional heatsink 	<p>FCB100</p> <ul style="list-style-type: none"> • 100W • 85W convection cooled • 101.6 x 50.8 x 31.8mm • Med/ITE/household • Class I & II 	<p>EPL150</p> <ul style="list-style-type: none"> • 150W • 100W convection cooled • 101.6 x 50.8 x 25.1mm • Medical BF compliant • Class I & II 	<p>ECP180</p> <ul style="list-style-type: none"> • 180W • 120W convection cooled • 101.6 x 50.8 x 25.4mm • Up to 95% efficiency • Class I & II 	<p>GCS350</p> <ul style="list-style-type: none"> • 350W • 200W convection cooled • 127.0 x 76.2 x 36.3mm • Fan cover options • Remote On/Off 	<p>PBL500</p> <ul style="list-style-type: none"> • 500W • 250W convection cooled • 180.3 x 101.6 x 39.6mm • Medical BF compliant • Class II
<p>MCE03</p> <ul style="list-style-type: none"> • 3W • 40.6 x 19.1 x 19.1mm • PCB mount • Medical 2 x MOPP • Class II 	<p>ECL10</p> <ul style="list-style-type: none"> • 10W • 49.5 x 25.4 x 22.9mm • PCB & chassis mount • Peak load capability • Class II 	<p>MCE20</p> <ul style="list-style-type: none"> • 20W • 66.0 x 33.0 x 23.4mm • PCB mount • Medical 2 x MOPP • Class II 	<p>EML30</p> <ul style="list-style-type: none"> • 30W • 75.2 x 34.6 x 26.7mm • PCB & chassis mount • Peak load capability • Class II 	<p>ECE40</p> <ul style="list-style-type: none"> • 40W • 78.7 x 38.1 x 27.9mm • PCB & chassis mount • <0.3W no load power • Class II 	<p>FCS60</p> <ul style="list-style-type: none"> • 60W • 101.6 x 50.8 x 26.4mm • 2 x MOPP • <0.15W no load power • Class I & II 	<p>ECE80</p> <ul style="list-style-type: none"> • 80W • 91.4 x 45.7 x 28.0mm • PCB & chassis mount • <0.3W no load power • Class II 	<p>ASB110</p> <ul style="list-style-type: none"> • 110W • Full brick package • Baseplate cooled • No external components • Optional heatsink 	<p>VFB150</p> <ul style="list-style-type: none"> • 150W • 100W convection cooled • 127.0 x 76.2 x 39.0mm • 0.15W no load power • 12V/0.3A fan supply 	<p>GCS180</p> <ul style="list-style-type: none"> • 180W • 150W convection cooled • 127.0 x 76.2 x 36.3mm • Fan cover options • Class I & II 	<p>SMP350</p> <ul style="list-style-type: none"> • 350W • 177.8 x 91.4 x 43.1mm • Integral fan • No leakage current • Remote On/Off 	<p>CCP550</p> <ul style="list-style-type: none"> • 550W • 400W conduction cooled • 127.0 x 76.2 x 37.6mm • Medical BF compliant • STBY or fan output
<p>ECE05</p> <ul style="list-style-type: none"> • 5W • 25.4 x 25.4 x 15.2mm • PCB mount • <0.3W standby power • Class II 	<p>MCE10</p> <ul style="list-style-type: none"> • 10W • 50.8 x 29.2 x 23.1mm • PCB mount • Medical 2 x MOPP • Class II 	<p>VCE20</p> <ul style="list-style-type: none"> • 20W • 66.0 x 33.0 x 23.4mm • PCB mount • 85-305VAC input • Class II 		<p>MCE40</p> <ul style="list-style-type: none"> • 40W • 87.9 x 38.9 x 28.5mm • PCB mount • Medical 2 x MOPP • Class II 	<p>VCB60</p> <ul style="list-style-type: none"> • 60W • 101.6 x 50.8 x 25.6mm • Low profile • 90-305VAC input • Low cost 	<p>LCE80</p> <ul style="list-style-type: none"> • 80W • 101.6 x 50.8 x 27.9mm • Constant V & I modes • Harmonics class C >50W • Class I & II 	<p>ECP130</p> <ul style="list-style-type: none"> • 130W • 100W convection cooled • 76.2 x 50.8 x 28.0mm • Low profile • Up to 95% efficiency 	<p>GCS150</p> <ul style="list-style-type: none"> • 150W • 110W convection cooled • 127.0 x 76.2 x 36.3mm • Fan cover options • Class I & II 	<p>EPL225</p> <ul style="list-style-type: none"> • 225W • 150W convection cooled • 101.6 x 50.8 x 32.3mm • Medical BF compliant • Class I & II 	<p>ECH450</p> <ul style="list-style-type: none"> • 450W • 250W convection cooled • 127.0 x 76.2 x 36.1mm • Medical BF compliant • Remote On/Off 	<p>UCH600</p> <ul style="list-style-type: none"> • 600W • 203.2 x 127.0 x 40.0mm • Medical BF compliant • Convection cooled • Fanless operation
<p>VCE05</p> <ul style="list-style-type: none"> • 5W • 33.0 x 27.9 x 19.1mm • PCB mount • Low cost • Class II 	<p>VCE10</p> <ul style="list-style-type: none"> • 10W • 50.8 x 29.2 x 23.1mm • PCB mount • 85-305VAC input • Class II 	<p>EHL20</p> <ul style="list-style-type: none"> • 20W • 69.9 x 47.0 x 29.2mm • PCB mount • 85-528VAC input • Class II 		<p>FCS40</p> <ul style="list-style-type: none"> • 40W • 76.2 x 50.8 x 26.4mm • 2 x MOPP • <0.3W no load power • Class I & II 			<p>ECS130</p> <ul style="list-style-type: none"> • 130W • 100W convection cooled • 101.6 x 50.8 x 32.5mm • <0.5W no load power • Class I & II 	<p>ASB160</p> <ul style="list-style-type: none"> • 160W • Full brick package • Baseplate cooled • No external components • Optional heatsink 	<p>ECP225-A</p> <ul style="list-style-type: none"> • 225W • 150W convection cooled • 127.0 x 76.2 x 25.4mm • Low profile • 5V/2A standby 	<p>GCU500</p> <ul style="list-style-type: none"> • 500W • 250W convection cooled • 165.1 x 83.8 x 39.3mm • Class B emissions • Low leakage current 	<p>CCH600</p> <ul style="list-style-type: none"> • 600W • 177.8 x 101.6 x 44.5mm • Industrial & MIL-STD • Baseplate cooled • Fanless operation
<p>EME05</p> <ul style="list-style-type: none"> • 5W • 36.1 x 25.4 x 15.2mm • PCB mount • Encapsulated/open-frame • Class II 	<p>ECL15</p> <ul style="list-style-type: none"> • 15W • 62.0 x 30.7 x 20.0mm • PCB & chassis mount • Single & multi outputs • Class II 	<p>ECL25</p> <ul style="list-style-type: none"> • 25W • 75.2 x 34.6 x 22.3mm • PCB & chassis mount • Single & multi outputs • Class II 		<p>VCE40</p> <ul style="list-style-type: none"> • 40W • 87.9 x 38.1 x 28.5mm • PCB mount • 85-305VAC input • Class II 					<p>GCS250</p> <ul style="list-style-type: none"> • 250W • 180W convection cooled • 127.0 x 76.2 x 36.3mm • Fan cover options • Class I & II 	<p>GSP500</p> <ul style="list-style-type: none"> • 500W • 650W peak for 100ms • 180W convection cooled • 152.4 x 101.6 x 41.9mm • <0.5W standby power 	<p>PBR650</p> <ul style="list-style-type: none"> • 650W • 203.2 x 101.6 x 65.5mm • Medical BF compliant • Remote On/Off • 5V/0.5A standby
<p>ECL05</p> <ul style="list-style-type: none"> • 5W • 49.5 x 25.4 x 22.9mm • PCB & chassis mount • Peak load capability • Class II 	<p>EML15</p> <ul style="list-style-type: none"> • 15W • 62.0 x 30.7 x 24.1mm • PCB & chassis mount • Peak load capability • Class II 								<p>GCS265</p> <ul style="list-style-type: none"> • 265W • 180W convection cooled • 127.0 x 88.8 x 36.3mm • 5V/3A standby • Class I & II 	<p>PBR500</p> <ul style="list-style-type: none"> • 500W • 400W convection cooled • 177.8 x 101.6 x 44.5mm • Medical BF compliant • Remote On/Off 	<p>MHP650</p> <ul style="list-style-type: none"> • 650W • 233.2 x 101.6 x 63.5mm • Mechanical options • Low leakage current • Remote On/Off
<p>EHL05</p> <ul style="list-style-type: none"> • 5W • 52.4 x 27.2 x 23.0mm • PCB mount • 85-528VAC input • Class II 											<p>SHP650</p> <ul style="list-style-type: none"> • 650W • 177.8 x 101.6 x 44.5mm • Mechanical options • Low leakage current • Remote On/Off

Chassis Mount

750W to 800W	1kW to 1.5kW	3kW	5kW
 <p>GSP750</p> <ul style="list-style-type: none"> 750W 900W peak for 100ms 254.0 x 101.6 x 41.9mm 2 x MOPP Remote On/Off 	 <p>MHP1000</p> <ul style="list-style-type: none"> 1kW 1.2kW high line 242.6 x 149.8 x 61.0mm Single output Remote On/Off 	 <p>HPF3K0</p> <ul style="list-style-type: none"> 3kW 279.4 x 177.8 x 63.5mm Programmable V & I Analog & digital interfaces Outputs: 24-60VDC 	 <p>HPL5K0</p> <ul style="list-style-type: none"> 5kW 330.2 x 127.0 x 127.0mm Programmable V & I Analog & digital interfaces 3 Phase 180-264VAC
 <p>HDS800</p> <ul style="list-style-type: none"> 800W 248.9 x 127.0 x 40.6mm Programmable V & I Analog & digital interfaces Graphical User Interface 	 <p>SHP1000</p> <ul style="list-style-type: none"> 1kW 1.2kW high line 241.0 x 150.0 x 61.0mm Single output Remote On/Off 	 <p>HDL3000</p> <ul style="list-style-type: none"> 3kW 317.0 x 170.0 x 64.0mm Programmable V & I Analog & digital interfaces Outputs: 12-60VDC 	 <p>HPT5K0</p> <ul style="list-style-type: none"> 5kW 330.2 x 127.0 x 127.0mm Programmable V & I Analog & digital interfaces 3 Phase 342-528VAC
 <p>HPA1K5</p> <ul style="list-style-type: none"> 1.5kW 279.4 x 106.6 x 41.6mm Programmable V & I Analog & digital interfaces Graphical User Interface 	 <p>HDL3000HV</p> <ul style="list-style-type: none"> 3kW 301.5 x 170.0 x 64.0mm Programmable V & I Analog & digital interfaces Outputs: 150-400VDC 	 <p>HPT5K0-L</p> <ul style="list-style-type: none"> 5kW 336.5 x 254.0 x 63.5mm Programmable V & I Analog & digital interfaces 3 Phase 342-528VAC 	
 <p>GFR1K5</p> <ul style="list-style-type: none"> 1.5kW 299.7 x 101.6 x 43.3mm 1U hot swap PC interface Current share & signals 	 <p>HDS3000</p> <ul style="list-style-type: none"> 3kW 366.0 x 127.0 x 127.0mm Programmable V & I Analog & digital interfaces Graphical User Interface 		
 <p>HDS1500</p> <ul style="list-style-type: none"> 1.5kW 294.5 x 127.0 x 63.5mm Programmable V & I Analog & digital interfaces Graphical User Interface 			

Configurable

400W to 900W	850W to 1.2kW	900W to 1.1kW	1kW to 2.5kW	3kW
 <p>fleXPower X4</p> <ul style="list-style-type: none"> 400W to 900W 254.0 x 127.0 x 63.5mm 1 to 10 outputs SEMI F47 compliant Fan control option 	 <p>nanofleX</p> <ul style="list-style-type: none"> 850W to 1.2kW Low 1U profile 1 to 4 outputs Programmable V & I Analog & digital interfaces 	 <p>fleXPower X9</p> <ul style="list-style-type: none"> 900W to 1.1kW 254.0 x 152.4 x 63.5mm 1 to 12 outputs SEMI F47 compliant Fan control option 	 <p>fleXPower X10</p> <ul style="list-style-type: none"> 1kW to 1.2kW 254.0 x 177.8 x 63.5mm 1 to 14 outputs SEMI F47 compliant Fan control option 	 <p>fleXPower XTL30</p> <ul style="list-style-type: none"> 3kW 317.5 x 127.0 x 127.0mm 1 to 10 outputs 3 Phase 180-264VAC
 <p>fleXPower XM4</p> <ul style="list-style-type: none"> 400W to 900W 254.0 x 127.0 x 63.5mm 1 to 10 outputs SEMI F47 compliant Fan control option 		 <p>fleXPower XM9</p> <ul style="list-style-type: none"> 900W to 1.1kW 254.0 x 152.4 x 63.5mm 1 to 12 outputs SEMI F47 compliant Fan control option 	 <p>fleXPower XM10</p> <ul style="list-style-type: none"> 1kW to 1.2kW 254.0 x 177.8 x 63.5mm 1 to 14 outputs SEMI F47 compliant Fan control option 	
 <p>fleXPower X5</p> <ul style="list-style-type: none"> 400W to 900W 254.0 x 127.0 x 63.5mm 1 to 10 outputs SEMI F47 compliant Fan control option 			 <p>fleXPower XTL15</p> <ul style="list-style-type: none"> 1.5kW 279.4 x 177.8 x 63.5mm 1 to 10 outputs 3 Phase 180-264VAC 	
 <p>fleXPower XM5</p> <ul style="list-style-type: none"> 400W to 900W 254.0 x 127.0 x 63.5mm 1 to 10 outputs SEMI F47 compliant Fan control option 			 <p>fleXPower XT16</p> <ul style="list-style-type: none"> 1.6kW 279.4 x 177.8 x 63.5mm 1 to 14 outputs 3 Phase 342-528VAC Fan speed control 	
 <p>fleXPower X7</p> <ul style="list-style-type: none"> 400W to 900W 254.0 x 127.0 x 63.5mm 1 to 10 outputs SEMI F47 compliant Fan control option 			 <p>fleXPower X15</p> <ul style="list-style-type: none"> 1.5kW to 2.5kW 279.4 x 127.0 x 127.0mm 1 to 20 outputs SEMI F47 compliant Fan control option 	
 <p>fleXPower XM7</p> <ul style="list-style-type: none"> 400W to 900W 254.0 x 127.0 x 63.5mm 1 to 10 outputs SEMI F47 compliant Fan control option 			 <p>fleXPower XM15</p> <ul style="list-style-type: none"> 1.5kW to 2.5kW 279.4 x 127.0 x 127.0mm 1 to 20 outputs SEMI F47 compliant Fan control option 	

DIN Rail Mount

40W to 60W	80W
 <p>ECE40/60</p> <ul style="list-style-type: none"> 40/60W DIN rail version Peak load capability <0.3W no load power Class II 	 <p>ECE80</p> <ul style="list-style-type: none"> 80W DIN rail option Peak load capability <0.3W no load power Class II