



Smart Technology. Delivered.™

Industrial Wireless-M2M Antenna Solutions

Laird designs and manufactures customized, performance-critical products for wireless and other advanced electronics applications.





Smart Technology. Delivered.™

About Laird

Laird provides systems, components and solutions that protect electronics from electromagnetic interference and heat, which enables connectivity in mission critical systems through wireless applications and antenna systems. We are a leader in the design, development and delivery of innovative technologies that enable people, organisations and applications to connect efficiently and effectively. Our reputation has been built on three guiding principles:

- Innovation- putting our in-depth knowledge of the latest materials and processes to work in creating outstanding products for our customers.
- Reliable fulfillment- delivering what our customers need to their exact specifications, on time and on budget, and in the quantities required.
- Speed- rationalizing the design and delivery cycle to minimize the time from initial concept to final implementation.

A Brief Introduction to Industrial Wireless-M2M

Industrial Wireless-M2M antennas eliminate the “last wire” going from the device to the data collection point. This reduces or eliminates cabling, eliminates the need to deploy an expensive network infrastructure by utilizing existing WWAN networks and increases user mobility throughout the facility. Industrial Wireless-M2M antennas also eliminate signal dead spots or shadows, allowing users to be reached anywhere inside or outside a building.

Depend on Laird

Laird Industrial Wireless-M2M antennas are particularly applicable for environments where aesthetics and wide-angle coverage are necessary for successful wireless deployment. Their surprisingly small size allows the antennas to be hidden almost anywhere, providing an invisible solution for most applications.

Benefits of Industrial Wireless-M2M Technology

Some benefits of using Laird’s Industrial Wireless-M2M antennas include:

- Tight antenna pattern control
- Uniformity of wireless signal
- Multi-band operation
- Narrow or wide band per port
- Small, aesthetic packaging

Industrial Wireless-M2M Antennas

Revie Series

Print circuit board (PCB) antennas that are embedded inside devices for aesthetically pleasing integration with high durability. The products feature:

- Wide bandwidth
- Ground plane independence
- Omnidirectional Vertically Polarized radiators
- RoHS compliant

MODEL	PART NUMBER	FREQUENCY (MHz)	VSWR	GAIN (dBi)	DIMENSIONS (mm)		
					L	W	H
Revie	AAF95003/ AAF95004	900/1800/1900	2.5	1.0	80	30	15
Revie Pro	MAF95256	868/900/1800/1900	2.5		80	30	15
Revie Prime	EPR9221A1	824-960/1710-2170	3.0/2.5		70	20	0.8



1. Other part numbers available based on connector and cable configuration, call for details.
2. Connector/cable configurations can be customized to meet requirements.

Heptaband-Dipole Series

Portable wireless antennas that provide excellent radio transmission characteristics while offering the ultra flexibility of seven bands in one profile. The products feature:

- Wide bandwidth: 824-960/1575/1710-2170/2400-2500
- Gain of 1-3 dBi with max VSWR of 2.5:1
- Low profile blade style
- Available in black or gray
- Snap in or connectorized

MODEL	PART NUMBER	DIMENSIONS (mm)		CONNECTOR TYPE
		LENGTH	WIDTH	
HEPTA-FL04 ²	MAF94306	161	9.3	Snapin/Captive w/Flying lead (no connector)
HEPTA-IP04 ²	MAF94304	161	9.3	Snappin/Captive w/IPEX MHF
HEPTA-xx ¹	MAF94300	161	9.3	RP-SMA, SMA, RP-TNC, TNC
HEPTA90-TN	MAF94309	161	9.3	TNC, Blade Angle-90 degree



1. Other part numbers available based on connector and cable configuration, call for details.
2. Connector/cable configurations can be customized to meet requirements.

Rubber Duck Series

Portable wireless antennas that provide excellent radio transmission characteristics while offering a robust mechanical design capable of surviving the harshest environments. The product features:

- Omnidirectional vertically polarized dipole design
- Maximum VSWR of 1.5
- RoHS compliant

MODEL	PART NUMBER	FREQUENCY (MHz)	GAIN (dBi)	LENGTH (mm)	CONNECTOR TYPE
CXE-821	CXE-821-TN/ CAF28266	824-896	2.5	179.3	TNC
CXF-821	CXF821TN/ CAF28569	824-896	2.2	218.4	TNC
WXR-1850	CAF28793	1850-1990	1.0	177.8	TNC (m)




Directional Base Station

Antennas suited for long-range applications that provide directional pattern coverage. The products feature:

- Vertically polarized radiators with a maximum VSWR < 1.5
- UV Stable housing
- One-piece brass radiator
- Advance microwave substrate
- Stainless steel hardware
- UltraLink pigtailed Type N (f) connector configured to application.
- PC series 200 watt power rating
- YA series 100 watt power rating
- DC ground for lightning protection

MODEL	PART NUMBER	BANDWIDTH (DEG)		GAIN	DIMENSIONS (mm)		
		EL	AZ		LENGTH	WIDTH	HEIGHT
PC804N	806-902	70	90	8.0	330	—	—
PC826N	821-896	55	65	10.7	629	—	—
PC8210N	824-896	40	45	13.0	1,169	—	—
YA9-9 ⁴	860-960	53	60	9.0	500	—	—
YA9-11 ⁴	860-960	50	50	11.0	900	—	—
YA9W-11 ^{2,4}	860-960	45	—	11.0	850	—	—
YA9-13 ⁴	860-960	30	38	13.0	1,450	—	—
YA9-W-13 ^{2,4}	860-960	35	—	13.0	1,200	—	—
PC884N	860-960	70	90	8.0	330	—	—
PC886N	860-960	55	65	10.0	629	—	—
PC17113N	1710-1880	35	35	13.0	673	95	38
PC18513N	1850-1990	35	35	13.0	673	95	38
LP800-2500-9 ^{3,4}	806-960/1710-2500	55	90/75	13.0	394	267	70



• YA9-9

1. Unless specified the antenna is a Yagi antenna
2. NLOS Aluminum Yagi
3. Log periodic antenna
4. Backhaul product

Directional Indoor/Outdoor Panels

Antennas that offer high gain in a thin low profile package, and provide directional pattern coverage in indoor or outdoor environments. The products feature:

- Integrated coaxial pigtailed can be customized in length and connector for the app
- Low profile designs
- UV stabilized radomes
- Vertically polarized design with VSWR <2:1

MODEL	PART NUMBER	BANDWIDTH (DEG)		GAIN	DIMENSIONS (mm)		
		EL	AZ		LENGTH	WIDTH	HEIGHT
S8248P ¹	824-896	65	70	8.0	305	203	51
S888P ¹	880-960	65	70	8.0	305	203	51
S1718P ¹	1710-1880	65	65	8.0	152	152	32
S17112 ¹	1710-1880	25	65	12.0	330	152	25
S1711290P ¹	1710-1880	10	90	12.0	864	76	30
S1858P ¹	1850-1990	62	65	8.0	152	152	32
S18512P ¹	1850-1990	25	65	12.0	330	152	25
S1851290P ¹	1850-1990	10	90	12.0	864	76	30



• S8248P-S9028P



• S1858PC

1. Part numbers above are completed with the addition of the cable length and connector (e.g. S8248P12NF implies 12" of cable terminated in a TypeN female connector)

2. Connector/cable configurations can be customized to meet requirements

3. Reference part numbers CAF95979 and CAF95996

4. Reference part number CAF94318 and CAF95993

5. Reference part number ID850 is CAF95978 and ID0850 is CAF94122

6. For Indoor applications

Industrial Wireless-M2M Antennas

DirectLink™ Series Indoor/Outdoor Panels

Antennas designed to meet the most demanding needs of the contemporary wireless environment, and are well suited for both indoor and outdoor wall or mast applications. The products feature:

- Low profile designs
- UV stabilized radomes
- Integrated coaxial pigtails that can be customized in length and connector for the app
- VSWR <2:1 with a 75 watt power rating

PART NUMBER	FREQUENCY (MHz)	BANDWIDTH (DEG)		GAIN	DIMENSIONS (mm)		
		EL	AZ		LENGTH	WIDTH	HEIGHT
S8242MP	824-896	120	110	2.0	101.6	76.2	38.1
S8802MP	880-960	120	110	2.0	101.6	76.2	38.1
S1718MP ³	1710-1880	60	85	7.5	144.8	96.8	15
S1857MP	1850-1990	50	80	7.5	144.8	96.8	15

1. Part numbers above are completed with the addition of the cable length and connector (e.g. S1857MP10SMF implies 10" of cable terminated in a TypeN female connector)
2. Connector/cable configurations can be customized to meet requirements
3. Antenna has option for articulating mount (e.g. S1718AMP)



• S8802MP

Directional Indoor/Outdoor Sectors

Antennas comprising of a directional antenna array with a radiation pattern that is shaped to cover a specified beamwidth. They are used when wide angle coverage is required, and concentrate applied power towards a specified area at the exclusion of other areas. The products feature:

- Low profile vertically polarized designs
- Integrated coaxial pigtails that can be customized in length and connector
- SR-series 25 watt power rating
- S-series 50 watt power rating

PART NUMBER	FREQUENCY (MHz)	PART NUMBER	BANDWIDTH (DEG)		GAIN	DIMENSIONS (mm)		
			EL	AZ		LENGTH	WIDTH	HEIGHT
S1711290P	1710-1880	90 deg Sector	10	90	12.0	864	76	30
SR1717140D	1710-1880	140 deg Sector	30	140	7.0	305	89	64
SR1716180D	1710-1880	180 deg Sector	30	180	6.0	305	89	64
S1851290P	1850-1990	90 deg Sector	10	90	12.0	864	76	30
SR1857140D	1850-1990	140 deg Sector	30	140	7.0	305	89	64
SR1856180D	1850-1990	180 deg Sector	30	180	6.0	305	89	64

1. Part numbers above are completed with the addition of the cable length and connector (e.g. SR1717140D12NF implies 12" of cable terminated in a TypeN female connector)
2. Connector/cable configurations can be customized to meet requirements
3. VSWR <2:1



• SR2405135D

Directional Indoor Multi-Polarity Panels

Directional dual port multi-polarization panel antennas that are well suited for indoor applications where multipath is a concern. The products feature:

- A minimum of 18 dB isolation and max VSWR of 1.5
- HVP & SLP models offer polarization diversity
- Low profile designs
- 25 watt power rating
- Integrated coaxial pigtails can be customized in length and connector for the app

PART NUMBER	FREQUENCY (MHz)	BANDWIDTH (DEG)		GAIN	DIMENSIONS (mm)		
		EL	AZ		LENGTH	WIDTH	HEIGHT
S828HVP/SLP ²	824-896	65	70	8.0	305/305	305/305	44/51
S888HVP/SLP ²	880-960	65	70	8.0	305/305	305/305	44/51
S9028PC ⁴	902-928	65	65	7.5	254	254	38
SS1717HVP/SLP ²	1710-1880	65	70	7.0	375/152	235/152	64/32
S1718PC ⁴	1710-1880	65	65	7.0	152	152	32
S1857HVP/SLP ²	1850-1990	65	70	7.0	375/152	235/152	64/32
S1857PC ⁴	1850-1990	65	65	7.0	152	152	32

1. Part numbers above are completed with the addition of the cable length and connector (e.g. S828HVP12NF implies 12" of cable terminated in a TypeN female connector)
2. Antenna can be configured in either dual H/V (e.g. S828HVP) or slant +/- 45 polarization (e.g. S828SLP)
3. Connector/cable configurations can be customized to meet requirements.
4. Circularly polarized antenna



• S9027PS

Squint™ Directional Indoor Panels

High-performance ceiling mount, low profile panel antennas that offer bi-directional radiation characteristics in a small package. The products feature:

- Ceiling mount vertical polarized antenna with a max VSWR of 1.5
- Mounting hardware adjusts height from ceiling
- High performance in a small package
- Excellent for hallways and tunnels
- 50 watt power rating

• SQ82243



PART NUMBER	FREQUENCY (MHz)	BANDWIDTH (DEG)		GAIN	DIMENSIONS (mm)			PATTERN TYPE
		EL	AZ		LENG	WID	HT	
SQ1715DD	1710-1880	65	70	5.0	152	152	32	Dual Directional
SQ1855DD	1850-1990	65	70	5.0	152	152	32	Dual Directional
S1857MD	1850-1990	68	69	7.0	184	95	51	Directional

1. Part numbers above are completed with the addition of the cable length and connector (e.g. SQ1715DD12NF implies 12" of cable terminated in a TypeN female connector)

2. Connector/cable configurations can be customized to meet requirements

Squint™ Omnidirectional Indoor Panels

Antennas that feature an omnidirectional pattern while focusing energy where it is most desired. Unique pattern characteristics mitigate multipath issues. The products feature:

- Omnidirectional while focusing energy where it is most desired
- Integrated coaxial pigtailed can be customized in length and connector for the app
- Unique pattern characteristics mitigate multi-path issues
- Single and multi-band models
- 50 watt power rating

• SQ2405DD12NF



PART NUMBER	FREQUENCY (MHz)	BANDWIDTH (DEG)		VSWR	GAIN	DIMENSIONS (mm)		
		EL	AZ			LENGTH	WIDTH	HEIGHT
SQ8243P	824-896	45.25	360	1.5	3.5	250	250	38
SQ8803P	880-960	45.25	360	1.5	3.5	250	250	38
SQ1713P	1710-1880	45	360	1.5	3.5	152	152	32
SQ1712PV ³	1710-1880	75	360	1.5	2.0	102	102	22
SQ1853P	1850-1990	45	360	1.5	3.5	152	152	32
SQ1852PG	1850-1990	50	360	1.5	2.5	102	102	22
SQ1852PV ³	1850-1990	75	360	1.5	2.0	102	102	22
SQ82183P	824-896/1850-1990	60	360	2.0	3.5	257	257	38
SQ87173P	870-896/1710-1880	60	360	2.0	3.0	257	257	38
SQ82243P	824-896/1850-1990/2400-2500	55	360	2.0	3.0	257	257	38

1. Part numbers above are completed with the addition of the cable length and connector (e.g. S828HVP12NF implies 12" of cable terminated in a TypeN female connector)

2. Antenna can be configured in either dual H/V (e.g. S828HVP) or slant +/- 45 polarization (e.g. S828SLP)

3. Connector/cable configurations can be customized to meet requirements

4. Circularly polarized antenna

Omnidirectional Indoor Panels

Antennas that feature an omnidirectional pattern while focusing energy where it is most desired. Unique pattern characteristics mitigate multipath issues. The products feature:

- Low profile designs
- Single and multi-band models
- Extremely uniform and symmetrical pattern characteristics
- Integrated coaxial pigtailed can be customized in length and connector for the app

• SL80173WP



PART NUMBER	FREQUENCY (MHz)	BANDWIDTH (DEG)		VSWR	GAIN	DIMENSIONS (mm)		
		EL	AZ			LENGTH	WIDTH	HEIGHT
SL8064P	806-866	100	360	2.0	4.0	155	155	32
SL8244P	824-896	100	360	2.0	4.0	152.4	152.4	31.75
SL8804P	880-960	100	360	2.0	4.0	152.4	152.4	31.75
SL1852P	1850-1990	100	360	1.7	2.0	63.5	63.5	20.32
SL82184P ³	824-896/1850-1990	—	360	2.0	4.0	152.4	152.4	31.75
SL88174P	880-960/1710-1880	—	360	2.0	4.0	152.4	152.4	31.75
SL80173WP	880-960/1710-1880/ 1920-2170	70/60/60	360	2.0	3.0	152.4	152.4	31.75
SL8025WP	806-960/1710-2170/ 2400-2500	55/50/60	360	2.0	3.0	152.4	152.4	31.75
SL17182P ³	1710-1755/1850-1990/2110-2155	65	360	2.0	2.0	152.4	152.4	31.75

1. Part numbers above are completed with the addition of the cable length and connector (e.g. SL80173WP105M implies 12" of cable terminated in a SMA male connector)

2. Connector/cable configurations can be customized to meet requirements

3. Dual port antenna designs

Industrial Wireless-M2M Antennas

Microsphere™

Antennas that feature an omnidirectional pattern, and suited to a variety of uses including handheld devices, in-building systems, or other applications where mobility is a factor. The products feature:

- Surprisingly small size allows for an invisible solution for most apps
- The field pattern is vertically polarized and toroidal, providing omnidirectional coverage in any plane around the long axis of the antenna
- 50-watt power rating



MODEL	PART NUMBER	FREQUENCY MHz	VSWR	GAIN dBi	DIMENSIONS (mm)		
					LENGTH	WIDTH	HT
IF850-SF00	CAF95952	806-960	2.0	3.0	114	86	2.5
IF8519-SF00	CAF94135	806-896/1850-1990	1.5	3.0	159	136	2.5
IF9018-SF00	CAF94126	880-960/1710-1880	1.5	3.0	129	156	2.5
IFMULT-SF002	CAF94362	806-960/1710-1990/ 1920-2170	2.0	3.0	112	138	2.5
IFULTRA-SF00	CAF94895	806-960/1710-1990/ 1920-2170/2400-2500	2.5	1.8 3.6 3.0 2.9	179	80	1.7
3G/4G MicroSphere	CFS69271-FNF	698-806/ 824-960/ 1710-1880/1850-1990/ 1920-2170/2100-2500/ 2500-2700	2.1	1.5 3.0 3.0 4.5	100	164	1.6
3G/4G MicroSphere	CFS69271-FSMAF	698-806/ 824-960/ 1710-1880/1850-1990/ 1920-2170/2100-2500/ 2500-2700	2.1	1.5 3.0 3.0 4.5	100	164	1.6

1. Part numbers above are completed with the addition of the cable length and connector (e.g. 5Q185PG12NF implies 12" of cable terminated in a TypeN female connector)
 2. Connector/cable configurations can be customized to meet requirements
 3. Vehicular application

Omnidirectional Fiberglass Sticks

Traditional antennas that provide a 360 degree transmission pattern, and are used when coverage in all directions is required. The products feature:

- Vertically polarized collinear design with a max VSWR of 2:1
- Protective UV inhibiting coating
- Radiating elements are made from high efficiency copper and are carefully phased to provide maximum gain in the horizontal plane
- 100-watt power rating

PART NUMBER	FREQUENCY (MHz)	BANDWIDTH (DEG)		GAIN	DIMENSIONS (mm)	
		EL	AZ		LENGTH	DIA
FG8063WP	806-896	—	360	5.0	737	33
FG8240	824-896	75	360	2.0	381	33
FG8243	824-896	33	360	5.0	625	33
FG8246	824-896	17	360	8.0	1651	33
FG821/18503	821-896/ 1850-1990	60/75	360	2.0/5.0	356	33
FGT880/21703	870-960/1710-1880/ 1900-2170	80/22/ 20	360	0.8/2.9/3.9	349	33
FG16397	806-896/890-960/ 1850-1990/ 2400-2500	110/90/ 60/70	360	2.0/1.0/3.3/ 2.0	356	33

1. See Fiberglass Base Antenna Accessories 2. Type N (f) connector



Omnidirectional Sticks

Traditional antennas that provide a 360 degree transmission pattern, and are used when coverage in all directions is required. The products feature:

- Vertically polarized collinear design
- Protective UV inhibiting coating
- Radiating elements are made from high efficiency copper and are carefully phased to provide maximum gain in the horizontal plane
- Type N(f) connector but other connectors available on selected models.
- VSWR <2:1 with 100-watt power rating

PART NUMBER	FREQUENCY (MHz)	BANDWIDTH (DEG)		GAIN	DIMENSIONS (mm)	
		EL	AZ		LENGTH	DIA
S8240B	824-896	75	360	2.0	445	25
S8243B	824-896	45	360	5.0	780	25
S8244B	824-896	25	360	6.0	1070	25
OD9-6 ⁴	860-960	16	360	6.0	1700	38
OD9-8 ⁴	860-960	10	360	8.0	2600	38
OD9-11 ⁴	860-960	7	360	11.0	3400	38
OD9-11D1 ^{2,4}	860-960	7	360	11.0	3400	38
S8800B	860-960	75	360	2.0	445	25
S8803B	880-896	45	360	5.0	780	25
S8804B	880-960	25	360	6.0	1070	25
S1713B ³	1710-1880	38	360	5.0	320	25
S1800B ³	1850-1990	—	360	2.0	203	25
S1803B ³	1850-1990	38	360	5.0	305	25

1. Unless specified antennas are designed for outdoor use
2. Built-in Electrical down tilt of 1 degree

3. Indoor Ceiling Grid Mount
4. Backhaul product

Phantom Antennas

Antennas that provide true field diversity design which ensures uninterrupted video and data transmissions in urban canyons and rural drop off areas.

The products feature:

- True field diversity performance
- 3.0 dBi gain with a VSWR <2.0
- Mechanically robust for both indoor and outdoor applications
- Ideal for both Industrial Wireless and M2M
- NMO mount standard
- 150-watt power rating

PART NUMBER	FREQUENCY (MHz)	BANDWIDTH (DEG)		LENGTH
		EL	AZ	
TRA8213 ^{2,3,4}	821-896	130	360	69
TRA8063 ^{2,3,4}	890-960	130	360	69
TRA8903 ^{2,4}	890-960	130	360	69
TRA9023 ^{2,3,4}	902-928	130	360	69
TRA16003 ²	1600-1850	130	360	69
TRA17753	1750-1825	130	360	69
TRA18503 ^{2,4}	1850-1990	130	360	69
TRA806/17103 ²	806-960/1710-2500	130	360	69
TRA821/18503 ²	821-896/1850-1990	130	360	69

Low Profile Antennas

Unique, patented low profile antennas that are ideal where space is a concern in both indoor and outdoor applications. The products feature:

- The Phantoms yield true field diversity performance
- 3.0 dBi gain with a VSWR < 2.0
- Mechanically robust for both indoor and outdoor applications
- Ideal for both Industrial Wireless and M2M
- Discadoo[®] antenna requires a ground plane
- 150 /100 watt power rating for the Phantoms/Discadoo[®] antennas

PART NUMBER	FREQUENCY (MHz)	DIMENSIONS		LENGTH
		LENG	DIA	
ETRA7603	760-870	69	—	Phantom Elite
ETRA7643	764-806	69	—	Phantom Elite
DISC806M5	806-866	19	121	Low Profile Discadoo
DTRA8063P ²	806-866	32	—	Low Profile Phantom
DTRA8213P ²	821-896	32	—	Low Profile Phantom
ETRA8063 ^{2,3}	821-896	69	—	Phantom Elite
ETRA8213 ^{2,4}	821-896	69	—	Phantom Elite
DISC824M ⁵	824-896	19	121	Low Profile Discadoo
DISC890M	890-960	19	121	Low Profile Discadoo
ETRA8903	890-960	69	—	Phantom Elite
DTRA9023P2	902-928	32	—	Low Profile Phantom
ETRA9023	902-928	69	—	Phantom Elite
DTRA821/18503P ²	821-896/1850-1990	32	—	Low Profile Phantom
ETRA821/18503 ²	821-896/1850-1990	69	—	Phantom Elite



Industrial Wireless-M2M Special Antennas

Healthcare

Low profile antennas that provide maximum performance for critical hospital monitoring, featuring single or dual ISM frequency bands along with both horizontal and vertical polarization components to improve overall signal integrity in RF cluttered environments. The products feature:

- The SL60144PF model offers both horizontal and vertical polarization components to improve overall signal integrity in RF cluttered environments
- Single or dual ISM frequency bands
- Maximum VSWR of 2.0
- Low profile ceiling mount designs

PART NUMBER	FREQUENCY (MHz)	GAIN	POLARIZATION	DIMENSIONS (mm)			CONNECTOR TYPE
				LENG	WID	HT	
SL6081PV	608-614	2.0	Vertical	155	155	32	SMA(m)
SL60144PF	608-614 / 1395-1432	2.0 / 3.0	Vert-Horiz	216	—	38	75 Ohm Fixed F(f)

LTE Devices

Products that provide broadband global and localized solutions for devices, In-building Wireless (IBW), and base station applications. The products cover:

- Broadband global solutions (698-2700 MHz)
- Localized solutions that operate in the 698-806 band
- Localized solutions that cover the 2500-2695 band

PART NUMBER	FREQUENCY (MHz)	ANTENNA TYPE	VSWR	GAIN	DIMENSIONS (mm)		CONNECTOR TYPE	POWER RATING
					LENG	WID		
IN7-3RD	680-800	Dipole-Rubber Duck	2.0	3.0	158	15.2	RSMA, RTNC, SMA(m)	10W
ETRA(B)6983	698-806	Phantom-Elite	2.0	2.9	87.4	3.6	NMO	100W
ETRA(B)6983P	698-806	Phantom-Elite	2.0	2.9	87.4	3.6	P-mount	100W
DBA69273	698-960/1710-2700	Dipole-Blade	2.5	0.7/2.1	29.8	29.8	TNC(m)	100W



LTE Base Station

Antennas that deliver broadband service through a wireless connection, and utilize an Industrial Wireless - M2M frequency that can be used in indoor and outdoor environments.



PART NUMBER	FREQUENCY (MHz)	ANTENNA TYPE	BEAMWIDTH (DEG)		VSWR	GAIN (dBi)	POLARIZATION	DIMENSIONS (mm)			POWER RATING
			EL	AZ				LENG	WID	HT	
J71014V00-70N ¹	710-790	60 deg Sector	14	60	1.5	16	Vertical	1600	335	297	50W ave, 600W pk
J23017V00-60N ¹	2300-2700	60 deg Sector	7	60	1.8	17.5	Vertical	1013	102	213	39W ave, 480W pk
J23018D00-60N ¹	2300-2700	60 deg Sector	7	60	1.8	18	Dual H/V	1011	381	267	40W ave, 480W pk
J23018D00-60N ¹	2300-2700	65 deg Sector	7	65	1.8	17	Slant +/- 45	1019	160	102	40W ave, 480W pk
J23016V00-90N ¹	2300-2700	90 deg Sector	7	90	1.8	16.5	Vertical	1013	102	213	40W ave, 480W pk
SA24-45-20-WB ²	2300-2700	45 deg Sector	7	45	1.5	20	Vertical	864	178	89	50W
SA24-60-17-WB ²	2300-2700	60 deg Sector	8	60	1.5	17	Vertical	851	165	64	50W
SA24-90-17-WB ²	2300-2700	90 deg Sector	7	90	1.5	17	Vertical	851	165	64	50W
SA24-120-16-WB ²	2300-2700	120 deg Sector	9	120	1.5	16	Vertical	851	165	64	50W

1. See accessories for Tilt Mount kit, J-series sector antennas
 2. Backhaul products

LTE In-Building Wireless

Antennas applicable for environments where aesthetics and wide angle coverage are necessary for successful wireless deployment. Their surprisingly small size allow the antennas to be hidden almost anywhere, providing an invisible solution for most applications. The products cover:

- Broadband global solutions (698-2700 MHz)
- Localized solutions that operate in the 698-806 band
- Localized solutions that cover the 2500-2695 band



MODEL	FREQUENCY (MHZ)	ANTENNA TYPE	PATTERN TYPE	BANDWIDTH		VSWR	GAIN dBi	POLARIZATION	DIMENSIONS (mm)			CONNECTOR TYPES	MOUNT STYLE	POWER RATING	PIM, 3RD ORDER 2X20 W, dBc	
				EL*	AZ*				LENG	WID	HT				TYPICAL (HIGH/LOW BAND)	MAX
IN800/2700-S	806-860 / 1710-2700	Panel	Omnidirectional	90	360	1.5	3.0	Vertical	186	87	—	Type N(f)	Ceiling	50W	—	—
CMD69273	698-960 / 1710-2700	2-port MIMO	Omnidirectional	—	360	2.0	3-4/ 5.0-5.6	Vertical	219	—	44	2-Type N(f)	Ceiling	10W	—	—
CMD69273P	698-960 / 1710-2700	2-port MIMO	Omnidirectional	—	360	2.0	3-4/ 5.0-6.9	Vertical	219	—	44	2-Type N(f)	Ceiling	50W	<-154dBc / <-155dBc	<-150 dBc
CMS69273	698-960 / 1575 / 1710-2700	Panel	Omnidirectional	90	360	2.0	1.0 / 3.0	Vertical	199	—	86	Type N(f)	Ceiling	25W	—	—
CMS69273S	698-960 / 1575 / 1710-2700	Panel	Omnidirectional	90	360	2.0	1.0 / 3.0	Vertical	199	—	86	Type N(f)	Ceiling w/ threaded stem	25W	—	—
CMS69273P	700/850/900/1800/1900/ 2300/2400/2500	Low PIM 2-port MIMO	Omnidirectional	—	360	2.0	3.1/3.1/2.8/ 5.9/4.5/4.3/ 5.9/6.9	Linear H/V	219	—	44	2-Type N(f)	Ceiling	50W	<-152 dBc / <-160 dBc	<-150 dBc
PAS69278P	698-960 / 1710-2700	Dual Port Panel	Directional	55/70	50/80	2.0	7.5-9.0 5.7-9.5	Slant ± 45°	295	295	82	2-Type N(f)	Wall / Mast	50W	<-151 dBc / <-153 dBc	<-150 dBc
PAV69278I	698-960 / 1710-2700	Panel	Directional	64/51	75/63	2.0	8.0	Vertical	249	249	61	Type N(f)	Wall	50W	—	—
PAV69278PI	698-960 / 1710-2700	Low PIM Panel	Directional	64/51	75/63	2.0	8.0	Vertical	249	249	61	Type N(f)	Wall	50W	<-150 dBc / <-155 dBc	<-150 dBc
SL69273PT	Port1: 698- 806/1710- 2170 Port2: 824- 894/1850-1990 Port3: 2500-2700	3-port Panel	Omnidirectional	—	360	2.0	3.0 / 2.0/2.0	Vertical	216	—	44	Type N(f)	Ceiling	5W	—	—
CMX69273P	698-960 / 1710-2700	2-Port MIMO	Omnidirectional	—	360	1.7:1	4.5/3.5	Linear	—	250	49	Model Specific	Ceiling	50W	<-154 dBc / <-153 dBc	<-150 dBc
CLS69273	698-960 / 1710-2700	Panel	Omnidirectional	—	360	<2.0:1	3.1/6.3	Vertical	250	—	47.5	Type N(f)	Ceiling	50W	—	—
CLS69273P	698-960 / 1710-2700	Panel	Omnidirectional	—	360	<2.0:1	3.1/6.3	Vertical	250	—	47.5	Type N(f)	Ceiling	50W	<-156 dBc	<-150 dBc
PAV69278O	698-960 / 1710-2700	Panel	Directional	64/51	75/63	2.0:1	7.6/8.1	Vertical	249.4	248.6	61.3	Pigatail w/ Type N(f) Fixed Type N(f)	Wall/Mast	50W	—	—

*Connector types available upon request.



Laird™

Smart Technology. Delivered.™

www.lairdtech.com

Americas: +1.847.839.6925

IAS-AmericasEastSales@lairdtech.com

Europe: +44.1628.858941

IAS-EUSales@lairdtech.com

Asia:

IAS-AsiaSales@lairdtech.com

Middle East and Africa: +44.1628.858941

IAS-MEASales@lairdtech.com

IAS-BRO-INDUSTRIAL M2M_0416

Any information furnished by Laird and its agents is believed to be accurate and reliable. All specifications are subject to change without notice. Responsibility for the use and application of Laird materials rests with the end user, since Laird and its agents cannot be aware of all potential uses. Laird makes no warranties as to the fitness, merchantability or suitability of any Laird materials or products for any specific or general uses. Laird, Laird Technologies, Inc or any of its affiliates or agents shall not be liable for incidental or consequential damages of any kind. All Laird products are sold pursuant to the Laird Technologies' Terms and Conditions of sale in effect from time to time, a copy of which will be furnished upon request. © Copyright 2016 Laird Technologies, Inc. All Rights Reserved. Laird, Laird Technologies, the Laird Logo, and other marks are trademarks or registered trademarks of Laird Technologies, Inc. or an affiliate company thereof. Other product or service names may be the property of third parties. Nothing herein provides a license under any Laird or any third party intellectual property rights.

