



Connected mobility
solutions

Engineering tomorrow's vehicles: the foundation for automotive OEMs in their drive towards the fully autonomous vehicle



REDEFINING THE CONNECTED CAR


Established in 1938, Molex is one of the world's largest manufacturers of interconnect products and system solutions for cables, connectors, media modules, Ethernet switches and gateways. Our expertise and deep experience in high-speed networking, datacom, rugged industrial and automotive solutions enable OEMs and Tier 1 manufacturers to incorporate next-generation vehicle architecture and develop the intelligent vehicles of the future

COMPLETE SOLUTIONS TO ACHIEVE YOUR VISION

Our capabilities are constantly evolving to meet the demanding requirements for autonomous driving, infotainment and connectivity. We take a holistic solutions mentality to achieve end-to-end connectivity and optimal performance.

End-to-end data connectivity

We believe that complete end-to-end signal integrity within a full-vehicle network architecture can be achieved. To accomplish this, we are developing groundbreaking solutions, establishing an ecosystem, investing in key technologies and working alongside industry-leading suppliers and collaborators who share our vision.



ADAS/AD (ADVANCED DRIVER ASSIST SYSTEMS/ AUTONOMOUS DRIVING)

Molex develops connectivity solutions that enable vehicle-to-vehicle and vehicle-to-infrastructure communication. The centre of our solutions is the Molex Gateway, a secure hub that gathers and processes data from all components and zones, then routes it to a functional domain. The Molex Gateway seamlessly integrates multiple hardware and software systems as well as legacy automotive protocols.



IN-VEHICLE INFOTAINMENT

Molex solutions provide the in-vehicle processing power and connectivity needed for effective communication within an intelligent vehicle network. Our cutting-edge connectivity solutions enable high-speed data and content transmission to vehicle displays and user interfaces, creating an optimal user experience.




CONNECTIVITY

With our expertise in high-speed data transmission, prioritisation, scalability and security, Molex is enabling faster, more streamlined vehicle connectivity than ever before. Our Ethernet Automotive Network delivers end-to-end data integration and prioritisation for a range of vehicle profiles. The network allows for OTA updates, diagnostics, telematics and analytic smart learning integration, with seamless communication between the vehicle and the cloud.

Ethernet-based vehicle architecture: approaching full vehicle autonomy

Molex's award-winning Automotive Ethernet Network Platform addresses the needs of automotive OEMs for a safe and safe-operational vehicle. We are translating automakers' needs for a secure, reliable and connected vehicle foundation into a high-performance computing network platform on wheels.

This future-ready, Ethernet-based vehicle architecture delivers seamless multi-zone integration across multiple hardware and software systems – with the flexibility to incorporate legacy automotive protocols. With the 10 Gbps automotive Ethernet platform from Molex, the fully autonomous vehicle is one step closer.



- Legacy Networks
- ... Legacy Network Redundancy
- 100 Mbps
- 1 Gbps
- ... 1 Gbps Redundancy
- 10 Gbps
- ... 10 Gbps Redundancy

ETHERNET GATEWAY AND SWITCH SOLUTIONS

Driving the transformation of in-vehicle networks.

MULTI-ZONE GATEWAY VEHICLE ARCHITECTURE

KEY CAPABILITIES

- Automotive Ethernet connectivity
- Legacy automotive connectivity
- PKI authentication certificate
- Multi-zone fail operational
- Machine learning integration
- Firewalls and VLAN routing
- Diagnostics: BiST, DIOP, Link QoS
- AUTOSAR classic
- Time Sensitive Network (TSN) - AVB

KEY INTERFACE

- 10 Gbps 10GBase-TX Ethernet ports
- 2.5 Gbps Base-TX Ethernet port
- 1 Gbps 1000Base-T1 Ethernet ports
- 100Mbps 100Base-T1 Ethernet ports
- USB 2.0 OTG
- CAN-FD ports
- LIN ports

NEXT GENERATION

- USB 3.1 Gen1 (5 Gbps)
- LVDS inputs
- HDBase-T port
- Most, FlexRay

High-speed networking solutions: best-in-class data speeds for seamless connectivity

Molex is a leading supplier of high-speed networking cables supporting OEMs in the development of in-vehicle networks that are secure, reliable and provide high bandwidth. We are addressing the increased demand for in-vehicle processing power by providing an end-to-end Ethernet-based solution that operates at high bandwidths across multiple hardware and software components. This allows us to seamlessly connect high-speed sensor, sensor clusters and Ethernet network platforms.

Molex high-speed networking cable solutions are offered at a variety of data rates to meet the needs of ADAS and AD, in-vehicle infotainment or connectivity applications while running at different protocols to transmit the data.

APPLICATION BASED ON DATA SPEED PERFORMANCE

Data Speed	Applications			Product
20 Gbps+	ADAS/AD sensor data	Camera	Internet	HSAutoGig
	Autonomous driving instrument cluster	Antenna	Navigation	
20 Gbps	ADAS Modules	GPS	NextGen wireless LAN	HFM Licensed by Rosenberger
		Gateway/switch	Sensors	
13 Gbps		4K displays	Surround view	HSAL2
	ADAS/AD sensor data	Controller	Telematics	
	Autonomous driving	Diagnostics/data upload	ADAS	
6 Gbps	Camera sensor based	Infotainment	4K screens	HSAL2 Hybrid
	Camera	Navigation		
	Connected vehicle services	Navigation	Controller	
2 Gbps	Diagnostics/data upload	Telematics	2K screens	HSAL1
	Infotainment	Camera		
		Display		
480 Mbps+	Connected vehicle services	Infotainment		Illuminated
	Diagnostics/data upload	Navigation		
		Telematics		
	In-vehicle networks			
	Charging			
	Media modules			

PROTOCOLS BY DATA SPEED PERFORMANCE


Data Speed	Protocols				Product
20 G					HSAutoGig
10 G	GMSL3	NGAUTO	FPD-Link-IV	10GBase-Tx	HSAL2
1 G	USB3.X	GMSL2	HDMI	DisplayPort	HSAL2 Hybrid
	MIPI?	Apix3	HD-Base-T		
100 M	Apix2	GMSL	FPD-LINK-III		HSAL2 Hybrid
	1000Base-T1		FPD-LINK-II		
10 M	USB2.0				HSAL1 Illuminated
	100Base-T1				
	A2B				

Automotive connectivity solutions


REFERENCE GUIDE

As a leading supplier of high-speed networking solutions, Molex is supporting OEMs in the development of in-vehicle networks that are secure, prioritized, reliable and high bandwidth. Building upon its strength in cables, connectors, media modules and signal integrity innovations, Molex is addressing the increased demand for in-vehicle processing power.


HSAUTOLINK I

	Speed	Protocol	Cable type	Application
	2 Gbps	Up to 100 Base, USB 2.0	UTP, STP	Connected vehicle services, Diagnostics/ Data upload, Infotainment, Navigation, Telematics, Display


HSAUTOLINK II

	Speed	Protocol	Cable type	Application
	13 Gbps	Up to 1000 Base, USB 2.0/ USB 3.0, DisplayPort, FTP	UTP, STP, TwinAx	Camera sensor based, camera, controller, diagnostics/data upload, infotainment, navigation, telematics, ADAS


HSAUTOLINK II HYBRID

	Speed	Protocol	Cable type	Application
	6 Gbps	Up to 1000 Base	UTP, STP, TwinAx	Camera sensor based, camera, controller, diagnostics/data upload, infotainment, navigation, telematics, ADAS



HIGH-SPEED FAKRA MINI

	Speed	Protocol	Cable type	Application
	20 Gbps	Up to MultiGig Ethernet	Coax	Instrument cluster, ADAS, Modules, Camera, Antenna, GPS, Gateway/Switch, 4K displays, Infotainment, Internet, Navigation, NextGen wireless LAN, Sensors, Surround view


HSAUTOGIG


	Speed	Protocol	Cable type	Application
	20 Gbps+	Up to MultiGig Ethernet	STP, TwinAx	Instrument cluster, ADAS, modules, camera, antenna, GPS, gateway/switch, 4K displays, infotainment, internet, navigation, NextGen wireless LAN, sensors, surround view. Buses, trucks, taxi, self driving


USB ILLUMINATED

	Speed	Protocol	Cable type	Application
 Type A	480 Mbps	USB 2.0	STP	Infotainment, navigation, media modules
 Type C	480+ Mbps	USB 2.0/USB 3.0	STP	


MEDIA MODULES & SMART CHARGER SOLUTIONS

	Smart Charger Solutions	Features & Benefits
	Dual and single port USB smart chargers	USB-A, Type C interfaces and BC 1.2, MFI and type C charging protocols, LED back lighting. Optional covers

	USB power delivery module	Features & benefits
	9-16V battery operating voltage, -40°C to 75°C operating temp	Supports up to: 60W charging on two USB-C devices, simultaneously at 75°C and 12V, Supports up to 45W charging on two USB-C devices, simultaneously at 75°C and 9V. Supports up to 60W charging on single USB-C Device at 55°C and 9V. Surface-mount solution with compact package size (75x65x28). Molex Mega-Fit power connector on the rear

	Media hub solutions	Features & benefits
	Multi port media hubs with smart charging support.	USB-A and Type C interface, USB 2.0 support, BC 1.2, MFI and type C charging protocols, Apple CarPlay, Android Auto and CarLife host sharing support, SD card and digital and analog Aux Jack support, LED back lighting

ETHERNET GATEWAY/SWITCH SOLUTIONS

	Gateway solutions	Features & benefits
	1G Ethernet Gateway	100 Base T1 Ethernet ports with PoDL, 1000 Base T1 ports, 1G Tx diagnostic port, CAN ports, USB ports, Power ports
	10G Ethernet Gateway	10G Ethernet ports, 2.5G Ethernet port, 100 Base T1 Ethernet ports with PoDL, 1000 Base T1 ports, 1G Tx diagnostic port, CAN ports, USB ports: Power ports, Software stack

Offices

AUSTRIA

Schönbrunner Str. 297-307
A-1120 Vienna
Phone: +43 1 86642 0
Fax: +43 1 86642 250
wien@avnet-abacus.eu

BELARUS

c/o Avnet Abacus Russia
Office 26, Building 2
10 Korovinskoye Shosse,
127486 Moscow
Phone: +7 (495) 737 3689
Fax: +7 (495) 737 3686
belarus@avnet-abacus.eu

BELGIUM

De Kleetlaan 3
1831 Diegem
Phone: +32 2 227 2000
diegem@avnet-abacus.eu

BULGARIA

c/o Avnet Abacus Austria
Schönbrunner Str. 297-307
A-1120 Vienna
Phone: +43 1 86642 0
Fax: +43 1 86642 250
bulgaria@avnet-abacus.eu

CROATIA

c/o Avnet Abacus Slovenia
Dunajska Cesta 167
1000 Ljubljana
Phone: +386 (0)1 560 97 54
Fax: +386 (0)1 560 98 78
croatia@avnet-abacus.eu

CZECH REPUBLIC

c/o Avnet Abacus Austria
Schönbrunner Str. 297-307
A-1120 Vienna
Phone: +43 1 86642-0
Fax: +43 1 86642 250
praha@avnet-abacus.eu

DENMARK

Knudlundvej 24
DK-8653 Them
Phone: +45 86 84 84 84
Fax: +45 86 84 82 44
them@avnet-abacus.eu

Lyskær 9, DK-2730 Herlev
Phone: +45 86 84 84 84
Fax: +45 43 29 37 00
herlev@avnet-abacus.eu

EGYPT

Canan Residence
Hendem Cad.
No:54 Ofis A2
Serifali Umraniye Istanbul
TR - 34775 Turkiye
Phone: +90 216 52 88 370
Fax: +90 216 52 88 377
egypt@avnet-abacus.eu

ESTONIA

Aida 5,
EE-80011 Pärnu
Phone: +372 56637737
paernu@avnet-abacus.eu

FINLAND

Pihatörmä 1 B
FI-02240 Espoo
Phone: +358 (0) 207 499 220
Fax: +358 (0) 207 499 240
espo@avnet-abacus.eu

FRANCE

Immeuble Carnot Plaza
14 Avenue Carnot
91349 Massy Cedex, Paris
Phone: +33 (0) 1 6447 2929
Fax: +33 (0) 1 6447 9150
paris@avnet-abacus.eu

8 chemin de la Terrasse
Bat D ter étage
31500 Toulouse
Phone: +33 (0) 5 6247 4787
Fax: +33 (0) 5 6247 4761
toulouse@avnet-abacus.eu

35 avenue des Peupliers
Les Peupliers2
35510 Cesson
Phone: +33 (0) 2 9983 7720
Fax: +33 (0) 2 9983 4829
rennes@avnet-abacus.eu

Parc Club du Moulin à Vent
Bât 10, 33 rue du Dr. G Lévy
F-69693 Vénissieux Cedex,
Lyon
Phone: +33 (0) 4 7877 1370
Fax: +33 (0) 4 7877 1391
lyon@avnet-abacus.eu

GERMANY

Englische Str. 27
D - 10587 Berlin
Phone: +49 (0) 30 790 997 0
Fax: +49 (0) 30 790 997 51
berlin@avnet-abacus.eu

Industriestr. 26
D-76297 Stutensee
Phone: +49 (0)7249 910 149
Fax: +49 (0)7249 910 177
stutensee@avnet-abacus.eu

Wilhelmstr. 1, D-59439
Holzwickede / Dortmund
Phone: +49 (0) 2301 2959 27
Fax: +49 (0) 2301 2959 29
dortmund@avnet-abacus.eu

Oehleckerring 9a - 13
22419 Hamburg
Phone: +49 (0) 40 608 23 59 0
Fax: +49 (0) 40 608 23 59 20
hamburg@avnet-abacus.eu

Gruber Str. 60c-60d
D-85586 Poing / Munich
Phone: +49 (0) 8121 777 03
Fax: +49 (0) 8121 777 531
muenchen@avnet-abacus.eu

Lina-Ammon-Str. 19 b
D-90471 Nürnberg
Phone: +49 (0) 911 244 250
Fax: +49 (0) 911 244 25 25
nuernberg@avnet-abacus.eu

Gutenbergstr. 15
D-70771 Leinfelden-
Echterdingen / Stuttgart
Phone: +49 (0) 711 78260 02
Fax: +49 (0) 711 78260 333
stuttgart@avnet-abacus.eu

Gaußstraße 10
D-31275 Lehrte
Phone: +49 (0) 5132 5099 0
Fax: +49 (0) 5132 5099 76
lehrte@avnet-abacus.eu

GREECE

c/o Abacus Avnet Austria
Schönbrunner Str. 297-307
A-1120 Vienna
Phone: +43 1 86642-0
Fax: +43 1 86642 250
greece@avnet-abacus.eu

HUNGARY

c/o Avnet Abacus Austria
Schönbrunner Str. 297-307
A-1120 Vienna
Phone: +43 1 86642-0
Fax: +43 1 86642 250
budapest@avnet-abacus.eu

IRELAND

c/o Avnet Abacus Bolton
Oceanic Building
Waters Meeting Road
Bolton BL1 8SW
Phone: +44 (0)1204 547170
Fax: +44 (0)1204 547171
bolton@avnet.eu

ISRAEL

Avnet Components Israel Ltd.
P.O. Box 48 Tel-Mond, 4065001
Phone: 972-9-7780280
Fax: 972-3-760-1115
avnet.israel@avnet.com

ITALY

Via Manzoni 44
I-20095 Cusano Milanino
(Milano)
Phone: +39 02 660 921
Fax: +39 02 66092 332
milano@avnet-abacus.eu

Viale dell'industria 23
I-35129 Padova
Phone: +39 049 7800 381
Fax: +39 049 7730 36
padova@avnet-abacus.eu

Via Zoe Fontana 220
I-00131 Roma
Phone: +39 06 4123 1952
Fax: +39 06 4192 618
roma@avnet-abacus.eu

Via Scaglia Est. 31/33
41126 Modena
Phone: +39 059 34891
Fax: +39 059 344993
modena@avnet-abacus.eu

Via Panciatchi 40/11
I-50127 Firenze
Phone: +39 055 436 1928
Fax: +39 055 428 8810
firenze@avnet-abacus.eu

LATVIA

c/o Avnet Abacus Poland
Plac Solny 16
PL-50-062 Wroclaw
Phone: +48 71 34 205 99
Fax: +48 71 34 229 10
latvia@avnet-abacus.eu

LITHUANIA

c/o Avnet Abacus Poland
Plac Solny 16
PL-50-062 Wroclaw
Phone: +48 71 34 205 99
Fax: +48 71 34 229 10
lithuania@avnet-abacus.eu

NETHERLANDS

Stadionstraat 2, 6th fl.
NL-4815 NG Breda
Phone: +31 (0) 76 57 22 300
Fax: +31 (0) 76 57 22 303
breda@avnet-abacus.eu

NORWAY

Ryensvingen 3 B
N-0680 Oslo
Phone: +47 (0) 22 70 76 60
Fax: +47 (0) 22 70 76 61
oslo@avnet-abacus.eu

POLAND

Plac Solny 16
PL-50-062 Wroclaw
Phone: +48 71 34 205 99
Fax: +48 71 34 229 10
wroclaw@avnet-abacus.eu

PORTUGAL

Tower Plaza, Rot. Eng. Edgar
Cardoso, 23, Pl. 14, Sala E
PT-4400-676 Vila Nova
de Gaia
Phone: +351 223 779502
Fax: +351 223 779503
portugal@avnet-abacus.eu

ROMANIA

c/o Avnet Abacus Slovenia
Dunajska Cesta 159
1000 Ljubljana
Phone: +386 (0)1 560 97 54
Fax: +386 (0)1 560 98 78
romania@avnet-abacus.eu

RUSSIA

Office 31, Building 2
10 Korovinskoye Shosse
127486 Moscow
Phone: +7 (495) 737 3689
Fax: +7 (495) 737 3686
Moscow@avnet-abacus.eu

SERBIA

c/o Avnet Abacus Slovenia
Dunajska Cesta 167
1000 Ljubljana
Phone: +386 (0)1 560 97 54
Fax: +386 (0)1 560 98 78
serbia@avnet-abacus.eu

SLOVAKIA

c/o Avnet Abacus Austria
Schönbrunner Str. 297-307
A-1120 Vienna
Phone: +43 1 86642-0
Fax: +43 1 86642 250
slovakia@avnet-abacus.eu

SLOVENIA

Dunajska Cesta 167
1000 Ljubljana
Phone: +386 (0)1 560 97 54
Fax: +386 (0)1 560 98 78
ljubljana@avnet-abacus.eu

SOUTH AFRICA

Ground Floor, Forrest House
Belmont Office Park
Belmont Road, Rondebosch
7700, Cape Town
Phone: +27 (0) 21 689 4141
Fax: +27 (0) 21 686 4709
sales@avnet.co.za

202 Chelmsford, 2nd Floor
Nelson Road, Essex Gardens,
Westville, 3629, Durban
Phone: +27 (0) 31 266 8104
Fax: +27 (0) 31 266 1891
sales@avnet.co.za

Block 3, Pinewood Office Park
33 Riley Road
Woodmead, 2191
Sandton, Johannesburg
Phone: +27 (0) 11 319 8600
Fax: +27 (0) 11 319 8650
sales@avnet.co.za

SPAIN

NyN Tower, C/ Tarragona,
151-157, Floor 19
ES-08014 Barcelona
Phone: +34 (0) 93 327 85 50
Fax: +34 (0) 93 425 05 44
barcelona@avnet-abacus.eu

Plaza Zabalgane
12 Bajo Izda,
Galdakao / Vizcaya
ES -48960 Bilbao
Phone: +34 (0) 94 457 0044
Fax: +34 (0) 94 456 8855
bilbao@avnet-abacus.eu

C/Chile, 10 2ª Plla.
Oficina 229
ES -28290 Las Matas / Madrid
Phone: +34 (0) 913 72 7200
Fax: +34 (0) 916 36 9788
madrid@avnet-abacus.eu

SWEDEN

Löfströms Allé 5,
Sundbyberg, Box 1830,
SE-171 27 Solna
Phone: +46 (0) 858 746200
Fax: +46 (0) 858 746 001
stockholm@avnet-abacus.eu

Smörhålevägen 3
SE-43442 Kungsbacka
Phone: +46 (0)8 58746 200
Fax: +46 (0)300 140 15
gothenburg@avnet-abacus.eu

SWITZERLAND

Bernstrasse 392
CH-8953 Dietikon
Phone: +41 (0) 43 322 49 90
Fax: +41 (0) 43 322 49 99
zurich@avnet-abacus.eu

TURKEY

Tatlisu Mahallesi,
Pakdil Sokak
No:5 B Blok Kat 2
34774 Umraniye
Istanbul Turbine
Phone: +90 216 52 88 370
Fax: +90 216 52 88 377
istanbul@avnet-abacus.eu

UK

First Floor, The Gatehouse
Gatehouse Road
Aylesbury, Bucks
HP19 8DB
Phone: +44 (0) 1296 678920
Fax: +44 (0) 1296 678939
Aylesbury@avnet.eu

Building 5
Waltham Park
White Waltham
Maidenhead
Berkshire SL6 3TN
Phone: +44 (0)1628 512900
Fax: +44 (0)1628 512999
maidenhead@avnet.eu

Avnet House
Rutherford Close
Meadway,
Stevenage
Hertfordshire SG1 2EF
Phone: +44 (0)1438 788 500
Fax: +44 (0)1438 788 250
stevenage@avnet.eu

Oceanic Building
Waters Meeting Road
Bolton
BL1 8SW
Phone: +44 (0)1204 547170
Fax: +44 (0)1204 547171
bolton@avnet.eu

UKRAINE

c/o Avnet Abacus Poland
Plac Solny 16
PL-50-062 Wroclaw
Phone: +48 71 34 205 99
Fax: +48 71 34 229 10
ukraine@avnet-abacus.eu

All trademarks and logos are the property of their respective owners. This document provides a brief overview only, no binding offers are intended. No guarantee as to the accuracy or completeness of any information. All information is subject to change, modifications and amendments without notice. Printed on FSC certified paper.