



life.augmented

Power management Guide



Contents

4	Introduction	
6	Applications	
6	Energy generation and distribution	
12	Power supplies	
33	Wearable devices - power management	
34	LED lighting and controls	
41	Electro-Mobility	
48	Industrial power & tools	
51	Major home appliances	
53	Software tools	
53	eDesignSuite	
54	Products	
54	AC-DC conversion ICs	
60	Battery management ICs	
62	DC-DC switching conversion ICs	
64	Digital power controllers and microcontrollers	
68	Diodes and rectifiers	
70	Hot-swap power management	
72	IGBTs	
74	Intelligent power module - SLLIMM™	
75	Intelligent power switches	
76	LED drivers	
81	Linear voltage regulators	
82	LNB supplies	
83	Photovoltaic ICs	
84	Power MOSFETs	
87	Power over ethernet ICs	
88	Protection devices	
90	STDRIVE MOSFET and IGBT gate drivers	
91	USB Type-C and power delivery controllers	

Introduction



More than 30 years of technology innovation in power management directly resulting in value creation for our customers, from products to system solutions

There is no secret when designing a power management system or sub-system: regardless of the final use, whether it is an energy generation or distribution system, a power supply or a LED driving circuit, an industrial SMPS or an electric vehicle power application, it must provide high efficiency and low standby power, as well as high power density, reliability and safety, while respecting specific cost constraints.

The key enablers for any such system with the above features are discrete and integrated power semiconductors, which play a crucial role in every step along the energy supply chain and, when applied in conjunction with advanced control technologies, can drive continuous improvement in energy savings for homeowners and communities, and ultimately for the entire planet.



The technological innovation that has been at the core of ST's strategy for more than 25 years is the reason why ST today can offer an extensive range of cutting-edge products for power and energy management. ST's portfolio includes higher-efficiency power technologies such as :

- Silicon carbide power discretes
- HV and LV power MOSFETs IGBTs
- Customized power modules
- Diodes
- Protection devices
- AC-DC converters and controllers
- DC-DC converters
- Linear voltage regulators
- Analog ICs
- Battery management ICs
- Digital controllers
- STM32 microcontrollers
- MOSFET and IGBT gate drivers

Moreover, ST offers a variety of high performance sensors as well as wireless and wired connectivity ICs to complement the latest smart power electronics applications with additional sensor-driven features and monitoring functions.

ST is also committed to the development of GaN power devices, which represent a major step forward in power electronics by providing high-frequency operation with increased efficiency and higher power density than silicon based transistors.

Additionally, we provide a comprehensive range of reference designs and hardware and software evaluation and development tools, including the eDesignSuite tool that can help engineers design and optimize their high efficiency power solutions.



Applications

ENERGY GENERATION AND DISTRIBUTION


Solar Centralized Generation - Solar Inverters (String and Central)

String and central inverters are the most common power conversion systems used for grid-connected solar applications. They comprise a DC-DC conversion stage, to adapt voltage levels and implement the Maximum Power Point tracking (MPPT) function to maximize energy transfer from the panel, and a DC-AC conversion stage to correctly shape current and voltage waveforms transferred to the AC grid. The inverter has an anti-islanding function that guarantees safety in case of AC disconnection. With power ranging from a few kilowatts for string and multi-string inverters to tens or hundreds of kilowatts for central inverter solutions, the trend is to use topologies with very high input voltages (up to 1500 V).


We offer a broad range of silicon-carbide (SiC) power MOSFETs - with the industry's highest operating junction temperature of 200 °C - and trench-gate field-stop IGBTs, that can be also combined into our high-efficiency ACEPACK power modules. Together with galvanically-isolated gate drivers and high-performance STM32 microcontrollers we enable engineers to design high-efficiency string and central inverters. In addition we have a range of wireless and wired connectivity solutions.



Typical Block Diagram for String Inverter



Typical Block Diagram for Central Inverter



ST'S product offering for String and Central Solar Inverter

	Power MOSFETs	IGBTs	Power Modules	Diodes & Discretes
Inverter Power Stage DC-DC and DC-AC	600 V-650 V MDmesh DM2 ST*60DM2, ST*65DM2 600 V-650 V MDmesh DM6 ST*60DM6, ST*65DM6 650 V MDmesh M5 ST*65M5 1200 V MDmesh K5 ST*N120K5 SiC MOSFETs SCT*N65G2, SCT*N120, SCT*N120G2	600 V V series STG*V60DF 650 V HB series STG*H65DFB 650 V HB2 series STG*H65DFB2 650 V M series STG*M65DF2 1200 V H series STG*H120DF2 1200 V M series STG*M120DF3	ACEPACK Power Modules A1P50S65M2 A1P25S12M3 A1P35S12M3 A2P75S12M3 A1P25M12W2-1' A1P18M65W2-1'	600 V Ultrafast STTH*06 STTH*R06 1200 V Ultrafast STTH*12 100 V Power Schottky STPS*100 SiC Diodes STPSC*065 STPSC*H12 TVS for Power MOSFET & IGBT Protection SMA4F, SMA6F, SMB15F series
Inverter Driving & Control stage	MCUs	MOSFET and IGBT Gate Drivers	Protections	Connectivity
Data Logger/Internet Gateway	MCUs	EEPROM	Protections	Connectivity
Solar Tracker	Motor CTRL	Motion Sensors	Environmental Sensors	Connectivity
	STM32F334 STM32G4 STM32H7 STM32F3 STM32F4 STM32F7	HV HB Gate Drivers L649* Isolated Gate Drivers STGAP* Multiple LS Gate Drivers PM8834 Single LS Gate Drivers PM88*1	TVS for Power Rail Surge Protection SMA4F, SMA6F, SMB15F, SMC30J series ESD and High Speed Port series for Ethernet and USB Protection	Bluetooth Low Energy BlueNRG, STM32WB Power Line Transceivers ST8500, ST7580 RS-422 and RS-485 ST3485*, STR485*
	STM32F0 STM32G0 STM32F1 STM32F3	Standard Serial EEPROM	ESD and High Speed Port series for Ethernet and USB Protection	RS-422 and RS-485 ST3485*, STR485*
	3-phase Field Oriented Control (FOC)	Accelerometer IIS3DHH, IIS2DH, IIS2ICLX Magnetometer-IIS2MDC eCompass-ISM303DAC 6 axis IMU-ISM330DL, ISM330DHCX	Pressure - LPS22HH Pressure water proof - LPS33W Temperature - STTS22H Humidity - HTS221	Bluetooth Low Energy BlueNRG, STM32WB

Note: * is used as a wildcard character for related part number

1 samples available in Q4 2020

Solar Distributed Generation - Microinverter

In residential photovoltaic systems Microinverters are often used as an alternative to string inverters to perform the DC to AC power conversion at panel level, helping maximize energy yield and mitigate problems related to partial shading, dirt or single panel failures. A microinverter consists of a DC-DC converter - implementing maximum power point tracking (MPPT) - and a DC-AC inverter to shape current and voltage for injection into the AC grid. Data - including voltage, current and power generated - from all the microinverters in the installation are collected by a concentrator and dispatched to a local or remote monitoring and control access point.


Our solution includes MDmesh and STripFET power MOSFETs, high-voltage, galvanically isolated gate drivers, high-voltage silicon-carbide (SiC) diodes together with high-performance STM32 microcontrollers - providing a set of dedicated peripherals to help implement complex power conversion control algorithms. A range of wireless and wired connectivity solutions including multi-standard power line modems complete the solution.

ST's product offering for Microinverter

	Power MOSFETs	Diodes	Protections	Signal Conditioning
Microinverter Power Stage	60 V-100 V STripFET F7 ST*N6F7, ST*N8F7, ST*N10F7 600 V-650 V MDmesh DM2 ST*60DM2, ST*65DM2 600 V-650 V MDmesh DM6 ST*60DM6, ST*65DM6 600 V MDmesh M6 ST*60M6 800 V-900 V MDmesh K5 ST*80K5, ST*90K5 SiC MOSFET SCT*N65G2	600 V Ultrafast STTH*R06 1200 V Ultrafast STTH*S12 100 V Power Schottky STPS*100 SiC Diodes STPSC*065 STPSC*H12	TVS for Power MOSFET and Power Rail Surge Protection SMA4F, SMA6F, SMB15F series	Precision Op Amps (<50 MHz) TSZ*, TSV*, TS9*, LMV* Current Sensing TSC*
	MCUs	MOSFET and IGBT Gate Drivers	Sensors	Connectivity
Microinverter Driving & Control stage	STM32F334 STM32G4 STM32H7 STM32F3 STM32F4 STM32F7	HV HB Gate Drivers L638*, L639*, L649* Isolated Gate Drivers STGAP* Multiple LS Gate Drivers PM8834 Single LS Gate Drivers PM88*1	Pressure - LPS22HH Pressure water proof - LPS33W Temperature - STTS22H Humidity - HTS221 Protections TVS for Power Rail Surge Protection SMA4F, SMA6F, SMB15F, SMC30J series	Bluetooth Low Energy BlueNRG, STM32WB Power Line Transceivers ST8500, ST7580 RS-485 and RS-232 STR485*, ST3232* EEPROM Standard Serial EEPROM
	MCUs	EEPROM	Protections	Connectivity
Data Logger/Internet Gateway	STM32F0 STM32G0	Standard Serial EEPROM	ESD and High Speed Port (HSP) series for Dataline ESD and EOS Protection	Bluetooth Low Energy BlueNRG, STM32WB Power Line Transceivers ST8500, ST7580 RS-422 and RS-485, and RS-232 ST3485*, STR485*, ST3232*

Note: * is used as a wildcard character for related part number

Typical Block Diagram



Solar Distributed Generation - Power Optimizer

In architectures based on the use of power optimizers, the maximum power point tracking (MPPT) function is performed at the level of photovoltaic panels, individually operating each one at its optimal I-V point which ensures maximum power generation. This results in an improved energy yield of the overall solar system compared to traditional string or central inverter based architectures.

Power optimizers can help minimize a system's design constraints as well as improve reliability and safety - by helping ensure compliance with the latest NEC 2017 regulations that require rapid shut-down in the event of grid disconnection, while at the same time reducing maintenance costs.


We provide high-performance STM32 microcontrollers as well as high-efficiency STripFET F7 LV Power MOSFETs, Diodes, SiC MOSFETs and trench-gate field-stop IGBTs, galvanically-isolated gate drivers and power line communication solutions to help achieve superior efficiency and reliability for power optimizer based architectures.

ST's product offering for Power Optimizer

	MCUs	Power MOSFETs	Gate Drivers	By Pass Diodes	Diodes	Protections	Connectivity
Power Optimizer	STM32F334 STM32F0 STM32G0 STM32F3 STM32G4	60 V to 100 V STripFET F7 ST*N6F7 ST*N8F7 ST*N10F7	HV HB Gate Drivers L649* Isolated Gate Drivers STGAP*	30 V to 45 V Power Schottky STPS*30 STPS*45 45 V FERD FERD*45	100 V to 200 V Power Schottky STPS*100, STPS*200 100 V FERD FERD*100	TVS for Power MOSFET & IGBT Protection SMA4F, SMA6F, SMB15F, SMC30J series	Bluetooth Low Energy BlueNRG, STM32WB Power Line Transceivers ST8500, ST7580 Signal Conditioning Precision Op Amps (<50 MHz) TSZ*, TSV*, TS9*, LMV* Connectivity
	MCUs	Power MOSFETs	Gate Drivers	IGBTs	Diodes	Protections	Connectivity
Inverter	STM32F334 STM32G4 STM32H7 STM32F3 STM32F4 STM32F7	SiC MOSFETs SCT*N120 SCT*N120G2	Multiple LS Gate Drivers PM8834 Single LS Gate Drivers PM88*1	600 V V series STG*V60DF 650 V HB series STG*H65DFB 650 V HB2 series STG*H65DFB2 650 V M series STG*M65DF2 1200 V H series STG*H120DF2 1200 V M series STG*M120DF3	600 V Ultrafast STTH*06 STTH*R06 SiC Diodes STPSC*065 STPSC*H12	Power Rail Surge Protection SMA4F, SMA6F, SMB15F, SMC30J series ESD Protection for I/O interfaces	Bluetooth Low Energy BlueNRG, STM32WB Power Line Transceivers ST8500, ST7580
	MCUs	EEPROM	Protections	Connectivity	Protections	Connectivity	Connectivity
Data Logger/Internet Gateway	STM32F0 STM32G0	Standard Serial EEPROM	ESD and High Speed Port series for Dataline ESD and EOS Protection	Bluetooth Low Energy BlueNRG, STM32WB Power Line Transceivers ST8500, ST7580	ESD and High Speed Port series for Dataline ESD and EOS Protection	Bluetooth Low Energy BlueNRG, STM32WB Power Line Transceivers ST8500, ST7580	Bluetooth Low Energy BlueNRG, STM32WB Power Line Transceivers ST8500, ST7580

Note: * is used as a wildcard character for related part number

Typical Block Diagram



Energy Distribution - Home & Commercial Battery Storage Systems

The adoption of energy storage devices, whose reserve capacity can be used for balancing purposes, peak-load shaving or to shift loads, is increasingly widespread in energy distribution networks.


Two use cases are particularly important: the use in residential or commercial building to help reduce consumers' electricity bills by reducing energy consumption from the grid during peak hours and to help avoid stability and voltage drop issues associated with the fast-charging schedules of the increasing number of electric vehicles (EV).

By interacting with the grid, batteries and potentially solar panels, power converters are at the heart of these systems and must operate with high-efficiency and superior reliability over time.


We can provide a range of power discretes including silicon-carbide (SiC) and silicon power transistors, ACEPACK power modules, silicon-carbide (SiC) and silicon diodes, isolated gate drivers and high-performance STM32 microcontrollers as well as energy metering ICs to help develop high-efficiency commercial battery storage systems.



Typical Block Diagram - Home Battery Storage System



Typical Block Diagram - Commercial Battery Storage System



ST's product offering for Home & Commercial Battery Storage Systems

	Power MOSFETs	IGBTs	Power Modules	MOSFET and IGBT Gate Drivers	Diodes & Discretes
DC-DC Converter & Bidirectional DC-DC Converter	40 V-100 V STripFET F7 ¹ ST*N4F7, ST*N6F7, ST*N8F7, ST*N10F7				600 V Ultrafast STTH*06 STTH*R06
Power Stage	600 V-650 V MDmesh M2 ST*60M2, ST*65M2		ACEPACK Power Modules	HV HB Gate Drivers L649*	800 V to 1200 V Ultrafast STTH*08 STTH*10 STTH*12
DC-AC Converter	600 V-650 V MDmesh DM2 ST*60DM2, ST*65DM2	600 V V series STG*V60DF	A1P50S65M2 A1P25S12M3 A1P35S12M3 A2P75S12M3	Isolated Gate Drivers STGAP*	SiC Diodes STPSC*065 STPSC*H12
Power Stage	600 V-650 V MDmesh DM6 ST*60DM6, ST*65DM6	650 V HB series STG*H65DFB	A1P25M12W2-1 ³ A1P18M65W2-1 ³	Multiple LS Gate Drivers PM8834	TVS for Power MOSFET & IGBT Protection and for Power Rail Surge Protection SMA4F, SMA6F, SMB15F, series
	800 V to 1200 V MDmesh K5 ST*80K5, ST*9*K5 ST*105K5, ST*120K5	650 V M series STG*M65DF2		Single LS Gate Drivers PM88*1	
	SiC MOSFETs SCT*N65G2 SCT*N120 SCT*N120G2	1200 V H series STG*H120DF2			
		1200 V M series STG*M120DF3			
System Control Stage	MCUs STM32F334 STM32G4 STM32H7 STM32F3 STM32F4 STM32F7	Signal Conditioning Precision Op Amps (<50 MHz) TSZ*, TSV*, TS9*, LMV* Current Sensing TSC*	EEPROM Standard Serial EEPROM Protections TVS for Power Rail Surge Protection SMA4F, SMA6F, SMB1F and ESD series	Sensors Pressure - LPS22HH Pressure water proof - LPS33W Temperature - STTS22H Humidity - HTS221	Connectivity Power Line Transceivers ST8500, ST7580 RS-485 and RS-232 STR485*, ST3232*
Data Logger / Internet Gateway	MCUs STM32F0 STM32G0 STM32F1 STM32F3	Protections ESD and High Speed Port series for Dataline ESD and EOS Protection	EEPROM Standard Serial EEPROM	Connectivity Power Line Transceivers ST8500, ST7580 Bluetooth Low Energy BlueNRG, STM32WB RS-485 and RS-232 STR485*, ST3232* Sub-1GHz RF Transceivers ² S2-LP, SPIRIT1 Sub-1GHz Wireless MCU ² STM32WL	

Note: * is used as a wildcard character for related part number 1 only for bidirectional dc-dc converter 2 only for commercial battery storage systems 3 samples available in Q4 2020

POWER SUPPLIES

Auxiliary SMPS

Many appliances and equipment require the availability of a switch-mode power supply (SMPS) that works separately from the main power supply to support, for instance, stand-by operation. Power ratings can vary from a few watts to tens of watts for these auxiliary supplies, which can be either isolated or non-isolated. To ensure good performance, engineers must choose the power topology – including fixed frequency or quasiresonant flyback – that best meets the efficiency, size, safety and cost requirements.

ST offers a wide portfolio of highly-integrated high voltage converters for applications up to 20 W, with an extremely low total stand-by consumption – down to less than 4 mW – and breakdown voltages as high as 1050 V. In addition to PWM switching controllers, power MOSFETs and diodes, we offer an extensive set of evaluation and development tools as well as reference designs to help engineers develop high-efficiency and compact auxiliary power supply solutions.

Isolated Auxiliary SMPS

In the power range up to 20 W, ST helps the designers of high-power-density and cost-effective isolated auxiliary power supplies with higher switching frequencies solutions to minimize transformer and output capacitor size. The power stage is managed by a high voltage converter.


In the 20 to 75 W power range, the need to meet increasingly tight efficiency and stand-by requirements for auxiliary power supplies has pushed the use of quasi-resonant topologies replacing more mainstream fixed frequency based designs. The power stage is managed by an off-line controller coupled with HV power MOSFETs.

ST's recommended products for Isolated Auxiliary SMPS

Isolated flyback	PSR-CV	HV converters		Offline controllers	HV Power MOSFETs	MOSFET Protection	Voltage Ref CC/CV Ctrl	Output diodes	Synch Rect	LDO
		Regulation with optocoupler	VIPer*5 VIPer*6 VIPer*7 VIPer*8	VIPer0P VIPer*1 VIPer*6 VIPer122 VIPer222 ALTAIR*	HVLED001*	STCH03 L6566B L6566BH L6565	800 V to 1700 V MDmesh K5 ST*80K5, ST*9*K5, ST*105K5, ST*120K5, ST*150K5, ST*12N170K5 600 V-650 V MDmesh M6 ST*60M6, ST*65M6 SiC MOSFET SCT*N65G2	Power MOSFET Protection: SMA4F, SMA6F, SMB15F series Reverse blocking diodes 600 V Ultrafast STTH*06 800 V to 1200 V Ultrafast STTH*08 STTH*10 STTH*12	Voltage Reference T*431 T*432 Voltage and Current Ctrl TSM*, SEA05*	Schottky, FERG STPS* FERD*45, FERG*50, FERD*60, FER*100

Note: * is used as a wildcard character for related part number

Typical configuration for Isolated Auxiliary Power Supply up to 20 W based on VIPerPlus or 75W and more based on PWM Controllers



MAIN EVALUATION BOARDS AND REFERENCE DESIGNS

STEVAL-VP26K01F

Three outputs, isolated SSR flyback converter with extended input voltage range for Smart Meter and Power Line Communication



STEVAL-ISA181V1

12 V / 600 mA isolated SSR flyback converter with Zero Power remote control



STEVAL-VP26K03F

Double output isolated PSR flyback converter with extended input voltage range



EVAL-STCH03-45W

45 W / 12 V QR flyback with adaptive synchronous rectification



Non Isolated Auxiliary SMPS

In a number of applications the reference of the secondary circuit is connected to the same reference as the primary – the AC mains. In such cases, an off-line non-isolated auxiliary power supply can be used to provide a regulated DC voltage using an inductor or low-cost transformer – with simplified isolation – as an energy transfer element by modulating the power supply's duty-cycle.


A buck – step-down – topology can be used to generate a positive output with respect to the common terminal and a buck-boost when the output voltage needs to be negative. A non-isolated flyback converter is the alternative when a higher output power is required.

ST's recommended products for Non-Isolated Auxiliary SMPS

	HV converters	VIPer Protection	Reverse blocking diodes	Output diodes	LDO
Buck				600 V Ultrafast STTH*06	Low Dropout (LDO) Linear Regulators LDF, LDFM, LDK220, LDK320, LDL212
Buck-boost	VIPer0P VIPer*1 VIPer*6 VIPer122 VIPer222			800 V to 1200 V Ultrafast STTH*08 STTH*10	
Non-isolated flyback		SMA4F, SMA6F, SMB15F series	600 V Ultrafast STTH*06 800 V to 1200 V Ultrafast STTH*08 STTH*10 STTH*12	Schottky, FERG STPS* FERD*45, FERG*50, FERD*60, FER*100	

Note: * is used as a wildcard character for related part number

Typical configurations for Non-Isolated Auxiliary Power Supply



MAIN EVALUATION BOARDS



STEVAL-VP12201B
15 V / 200 mA buck converter



STEVAL-ISA178V1
5 V / 0.2 A buck converter



STEVAL-VP22201B
5 V / 0.36 A
buck converter



STEVAL-ISA196V1
5 V / 1.2 A non-isolated flyback converter

Smart Chargers and Adapters

Today, many device charging technologies and standards designed to ensure interoperability and improve convenience and ease of use are available, including wireless charging, quick charge and USB Type-C and Power Delivery.

ST can help engineers design charging solutions that meet requirements set by the mainstream standards – as well as proprietary charging protocols – with innovative converter architectures enabling best-in-class energy efficiency and power density as well as ensuring the lowest possible stand-by power.

USB Type-C™ PD Adapters and Quick Chargers


The new slim and reversible USB Type-C™ connector with USB Power Delivery (PD) feature provides up to 100 W (20 V, 5 A) enabling a faster and more efficient charging solution. Having considerably expanded the capability of USB devices, these connectors are now widely found in wall chargers and adapters.

Designers of USB Type-C™ and Power Delivery compliant adapters and wall chargers can benefit from stand-alone controllers, from STM32 microcontrollers and their associated protocol stack, our STSAFE secure element as well as a specifically developed range of protection and filtering devices.

ST's recommended products for USB Type-C Power Delivery Subsystem

Type-C and USB-PD Controllers			Authenticaiton & Secure MCUs	V _{rm}	Protections			LDO
MCUs	Type-C Controller/ interface	Standalone Solutions			High surge current compact protection (V _{BUS})	Single and multi lines protection for MCUs Communication Channel (CC) and Side Band Use (SBU)	Type C Port protection Over voltage protection for USB-C and PD 3.0 controllers	
STM32G0, STM32G4, STM32L5		STUSB1600 STUSB1700 STUSB4500L STUSB4500 STUSB4700 STUSB4710 STUSB4761	STSAFE-A	20 V	ESDA25P35-1U1M ESDA24P140-1U3M	ESDL20-1BF4 ESDA25W	TCPP01-M12	ST715 LDK320
STM32F0 STM32F3	STUSB1602A			15 V	ESDA17P100-1U2M ESDA15P50-1U1M	ESDA17P20-1U1M		Load Switch STELPD01
				9 V	ESDA13P70-1U1M			
				5 V	ESDA7P120-1U1M	ESDA6V1L ESD051-1F4		

Typical configuration



MAIN EVALUATION BOARDS AND REFERENCE DESIGNS

STEVAL-USBP45C

45 W USB Type-C™ Power Delivery 3.0 adapter reference design with programmable controller (MCU)



Note: 1 available in Q4 2020

EVLSTCH03-45WPD

45 W USB Type-C™ Power Delivery 3.0 adapter reference design with certified standalone controller



STEVAL-USBP27S

27 W USB Type-C™ Power Delivery 3.0 adapter with PPS fetature




X-NUCLEO-SRC1M1¹

USB Type-C Power Delivery Source expansion board based on TCPP02-M18¹



Typical block diagram with Certified Source and Sink Standalone Controllers



MAIN EVALUATION BOARDS AND REFERENCE DESIGNS

STEVAL-ISC004V1

STUSB4710A USB Power Delivery evaluation board (with on-board DC-DC)



STEVAL-ISC005V1

STUSB4500 USB Power Delivery evaluation board



EVAL-SCS001V1

5V-20V SINK USB-PD reference design (migration from DC barrel)



EVAL-SCS002V1

5V SINK USB-C reference design (migration from USB micro-B)



X-NUCLEO-USBPDM1

USB Type-C™ Power Delivery SINK expansion board based on TCPP01-M12




X-NUCLEO-DRP1M1¹

USB Type-C Power Delivery Dual Role Power expansion board based on TCPP03-M20¹



Note: 1 available in Q4 2020




Automotive-grade USB Type-C and Power Delivery solution


The USB Type-C and USB Power Delivery specifications allow smarter connectivity with fewer cables, less connectors and universal chargers.

The Type-C connector supports all the features of previous standards, and ports can be configured to only supply power in a Provider role, only sink power in a Consumer role, or be able to switch between both in a Dual role. Both data and power roles can be independently and dynamically swapped using the USB Power Delivery protocol. Most of the automotive applications require support for the Provider role only. When a USB device is connected, the Provider and the device (Consumer) negotiate a contract for the power objects through configuration channels.

Typical Block Diagram for Automotive grade USB Power Delivery



Complete USB Power Delivery version 2.0 including software stack available in AutoDevKit.



Digitally controlled dual-channel DC-DC suitable for USB Power Delivery 3.0

KEY FEATURES

- Dual independent channel up to 3A each
 - Compatible with both 12V and 24V input
 - Combined channels for up to 100W
 - Digitally selectable fixed output voltages: 3.3 - 5 - 9 - 15 - 20 V
 - PPS-V: PWM programmable output voltages with 20 mV steps
 - PPS-I: PWM programmable output current with 50 mA steps
- More details available on AN5362

Adapters for Tablets, Notebook and All-in-One (AIO) Computers

Power AC-DC adapters for notebooks, tablets and AIO need to be small, thin, lightweight and provide excellent EMI performance as well as ultra-low, highly efficient standby power, regardless of the load conditions.

A typical high-efficiency design includes a flyback stage with synchronous rectification and for higher power, a Power Factor Corrector (PFC) working in Transition Mode (TM) followed by a flyback, forward or half-bridge LLC resonant stage with synchronous rectification.


ST offers a broad range of high-voltage MDmesh™ and low-voltage STripFET power MOSFETs as well as standard and field-effect rectifiers (FERD). Our offering also includes a range of PFC, PWM primary controllers, synchronous rectification controllers, and single-chip analog and digital combo controllers.

ST's recommended products for Tablets, Notebook and AIO Adapters

	Controllers	Power MOSFETs	Diodes	
PFC Block	TM Analog Controllers L6562A*, L6563*, L6564*	600 V-650 V MDmesh M2 ST*60M2, ST*65M2, ST*60M2-EP	600 V Ultrafast for TM STTH*L06, STTH*06, STTH15AC06*	
	CCM Analog Controllers L4981*, L4984D	600 V-650 V MDmesh M6 ST*60M6, ST*65M6	600 V Ultrafast for CCM STTH*R06, STTH*T06	
Isolation Stage	Converters & Controllers	Power MOSFETs	Diodes & Discretes	Voltage Reference, CC/CV Ctrl
	HV Converters for Flyback SSR: VIPer*5, VIPer*7, VIPer*8 PSR: VIPer0P, VIPer*1, VIPer122, VIPer222, VIPer*6, ALTAIR*	800 V to 950 V MDmesh K5 ST*80K5, ST*9*K5	Output Diodes for Flyback Schottky, FERD, STPS*, FERD*45, FERD*50, FERD*60, FERD*100	Voltage Reference T*431, T*432
	Flyback Controllers STCH03, L6566A, L6566B, L6565	600 V-650 V MDmesh M2 ST*60M2, ST*65M2, ST*60M2-EP	Clamping Diodes for Flyback 600 V to 1000 V Ultrafast STTH*06, STTH*08, STTH*10	Voltage and Current Ctrl TSM*, SEA05*
	PFC & LLC Combo Controllers STCMB1, STNRG011	600 V-650 V MDmesh M6 ST*60M6, ST*65M6	Output Diodes for LLC Schottky, FERD STPS*	Post Regulation
	LLC Analog Controllers L6599*, L6699	600 V MDmesh DM6 ST*60DM6	MOSFET protection for Flyback SMA6F, SMB15F series	DC-DC Converters ST1S*, ST1S40, ST1S50
	SR Analog Controllers SRK1000, SRK1001 for Flyback SRK2000A, SRK2001, SRK2001A for LLC	40 V-100 V STripFET F7 ST*N4F7, ST*N6F7, ST*N8F7, ST*N10F7		Low Dropout (LDO) Linear Regulators ST715 LDK320

Note: * is used as a wildcard character for related part number

Typical Block Diagram with PFC Front-End



MAIN EVALUATION BOARDS AND REFERENCE DESIGNS

EVLSTCH03-36W-SR

36W USB charger with selectable output voltage (5-9-12 V @3A) based on QR flyback with adaptive synchronous rectification



EVL CMB1-90WADP

19 V - 90 W adapter based on TM PFC and HB LLC analog combo controller



EVLSTNRG011-150

12 V - 150 W power supply based on TM PFC and HB LLC digital combo controller



EVL400W-EUPL7

12 V - 400 W adapter based on CCM PFC and HB LLC analog controller



Note: EU CoC ver. 5 Tier 2 and EuP lot 6 Tier 2 compliance ensured

Wireless Charging

Wireless chargers are expected to become ubiquitous in hotels, airports, cafes and other public places as they enable topping off the batteries of portable and wearable devices, letting the user forget about cables.

In a wireless battery charging system, power is transferred by electromagnetic induction (inductive power transfer) between a transmitting pad - or dongle (TX) - and the battery-powered device (RX), such as a smartphone, smartwatch or sports gear. The power transmitter unit controls the current in the transmitting coil to transfer the correct amount of power as required by the receiver unit that continuously provides this information to the transmitter by modulating the transmitter carrier frequency through controlled resistive or capacitive load insertion. Generating the correct amount of power guarantees the highest level of end-to-end energy efficiency and helps limit the device's operating temperature.


We have a range of wireless battery charging solutions including transmitters and receivers providing low stand-by power and foreign objects detection (FOD) feature. In order to prevent unwanted damage to any NFC Cards that might be close to the wireless charging source during operation, it is recommended to add an NFC Reader. The NFC Reader is able to detect the presence of the NFC Card or Tag (ST Reader ICs can detect Type A, B, F, or V NFC Cards), and therefore instruct the operating system to stop transmitting power. ST also offers evaluation and development tools and reference designs to help develop high-efficiency and compact wireless chargers that are Qi compliant.

ST's recommended products for Wireless Charging

	Wireless charging controllers, MCUs	Gate drivers	Power MOSFETs	Protections	Diodes	NFC reader
Transmitter	STWBC, STWBC-EP, STWBC-MC, STWBC-WA, STM32F0, STM32F334, STM32G4	L6743B	STL10N3LLH5, STL8DN6LF3, ST*N2VH5, STL8DN10LF3, STL6N3LLH6, STL10N3LLH5	TVS SMA4F, SMA6F, SMB15F series	STPS*L30 STPS*45/60/100 FERD*45/60/100	ST25R3911B ST25R3912 ST25R3916
Receiver	STWLC68, STM32F0			ESDALC14V2-1U2	BAT30F4, BAR46	

Note: * is used as a wildcard character for related part number

Typical Block Diagram



MAIN EVALUATION BOARDS AND REFERENCE DESIGNS

Transmitters

STEVAL-ISB045V1

2.5 W wireless charger transmitter



STEVAL-ISB047V1

Qi 3-coil 15 W wireless charger transmitter



EVALSTWBC-EP

Qi MP-A15 15W wireless charger transmitter



STEVAL-QiNFCAU1

Qi 3-coil 15 W wireless charger TX with NFC and Secure Authentication



STEVAL-ISB044V1

Qi MP-A10 15 W wireless charger transmitter



Receivers

STEVAL-ISB68WA

Qi-based wireless power receiver reference design for wearable applications up to 2.5 W



STEVAL-ISB68RX

Qi wireless power receiver for Baseline Power Profile (BPP) applications up to 5 W



NFC Readers

ST25R3911B-DISCO

ST25R3911B based NFC Reader Discovery Board



ST25R3916-DISCO

ST25R3916 based NFC Universal Device Discovery Board



Desktop PCs Power Supply

The requirements for the standard ATX PC power market are a small form factor with better performance.


An intelligent control scheme that enables the adaption of load variation to minimize power consumption, together with optimized power semiconductors, is the key in meeting market demands. The smart analog and digital controllers, such as the STCMB1 and the STNRG011, the high-voltage MDmesh™ Power MOSFETs used for the PFC and DC-DC stages, the low-voltage STripFET Power MOSFETs for synchronous rectification, and SiC diodes (STPSC*) help designers develop the best PC power supply solutions to improve efficiency. ST's DC-DC converters guarantee high power density for the post-regulation.

ST's recommended products for Desktop PC's Power Supply

	Controllers	Power MOSFETs	Diodes & Discretes	Opamp V/I Sensing
PFC Block	TM Analog Controllers L6562A*, L6563*, L6564* CCM Analog Controllers L4981*, L4984D MCUs & Digital Controllers STM32F0, STM32G0, STM32F301, STM32F334, STM32G4, STNRG388A, STNRGPF01, STNRGPF02, STNRGPF12	600 V-650 V MDmesh M2 ST*60M2, ST*65M2, ST*60M2-EP 600 V-650 V MDmesh M6 ST*60M6, ST*65M6 650 V MDmesh M5 ST*65M5	600 V Ultrafast for TM STTH*L06, STTH*06, STTH15AC06* 600 V Ultrafast for CCM STTH*R06, STTH*T06 SiC Diodes STPSC*065 TVS for Power Rail Surge Protection SMAJ40CA-TR	Precision Op Amps (<50 MHz) TSZ*, TSV*, TS9*, LMV* MOSFET and IGBT Gate Drivers Multiple LS Gate Drivers PM8834 Single LS Gate Drivers PM88*1
	Isolation DC-DC Stage	PFC & LLC Combo Controllers STCMB1, STNRG011 LLC Analog Controllers L6599*, L6699 Asymmetrical HB Controllers L6591 MCUs & Digital Controllers STM32F0, STM32G0, STM32F301, STM32F334, STM32G4, STNRG388A SR Analog Controllers SRK2000A, SRK2001, SRK2001A for LLC	600 V-650 V MDmesh M2 ST*60M2, ST*65M2, ST*60M2-EP 600 V-650 V MDmesh M6 ST*60M6, ST*65M6 600 V-650 V MDmesh DM2 ST*60DM2, ST*65DM2 600 V-650 V MDmesh DM6 ST*60DM6, ST*65DM6 40 V-100 V STripFET F7 ST*N4F7, ST*N6F7, ST*N8F7, ST*N10F7	Output Diodes Schottky, FERD STPS*, FERD*45, FERD*50, FERD*60, FERD*100 Protections TVS for Power MOSFET and Power Rail Surge Protection SMA4F, SMA6F, SMB15F series LDO Low Dropout (LDO) Linear Regulators LDF, LDFM, LDK320, LDL212
Post Regulation		L6726A, L673*, PM6680	STL90N3LLH6	T*431, T*432

Note: * is used as a wildcard character for related part number

Typical configuration



MAIN EVALUATION BOARDS AND REFERENCE DESIGNS

EVL6563S-250W

250 W transition-mode PFC pre-regulator



EVL400W-EUPL7

12 V - 400 W SMPS for adapters and ATX power supplies



Server & Telecom Power

AC-DC PSU & DC-DC power distribution


Data centers house thousands of servers, usually built in very dense network farms. Data center power requirements are constantly increasing and traditional power systems are no longer sufficient to meet this growing demand. The power distribution chain, from the front-end AC-DC stage to the back-end DC-DC power distribution, needs to deliver the best performance in terms of efficiency, power density and ability to interface with the digital world.

In telecom system power, the use of complex digital ASICs for managing growing data traffic is pushing further the power envelope. Telecom power management systems have to be highly energy-efficient and very dense to deliver the required high levels of power, while maintaining reasonable power consumption.

ST offers an extensive product and solution coverage to ensure the most optimized power design across the entire distribution chain. Our digital and analog controllers combined with MOSFETs and drivers are key ingredients for implementing the most efficient and most dense AC-DC power delivery. On the backend DC-DC power distribution, ST offers advanced solutions for the Point-of-Load conversion and a recently developed innovative DC-DC conversion from the 48 V DC supply.



Typical Block Diagram for Server PSU



ST'S product offering for Server and Telecom AC-DC PSU

		SCRs	Diodes	
Input Stage (Rect. & inrush current limiter)			Bridge Rectifier Diodes STBR*08, STBR*12	
	Controllers	High Temp. SCR TN*015H-6, TN*050H-8, TN*050H-12W	Diodes & Discretes	MOSFET and IGBT Gate Drivers
PFC Block	CCM Analog Controllers L4981*, L4984D	Power MOSFETs	600 V Ultrafast for CCM STTH*R06 STTH*T06	HV HB Gate Drivers L649*
	MCUs & Digital Controllers STM32F0, STM32G0, STM32F301, STM32F334, STM32G4, STNRG388A, STNRGPF01, STNRGPF12		600 V-650 V MDmesh M2 ST*60M2, ST*65M2	Isolated Gate Drivers STGAP*
		600 V-650 V MDmesh M6 ST*60M6, ST*65M6	SiC Diodes STPSC*065	Multiple LS Gate Drivers PM8834
		650 V MDmesh M5 ST*65M5	TVS for Power MOSFET and Power Rail Surge Protection SMA4F, SMA6F, SMB15, series	Single LS Gate Drivers PM88*1
		SiC MOSFETs SCT*N65G2	Opamp V/I Sensing	eFuses
			Precision Op Amps (<50 MHz) TSZ*, TSV*, TS9*, LMV*	
	Controllers	Power MOSFETs	Diodes	STEF01 STEF05-STEF05S STEF12-STEF12S STEF12H60
Isolation DC-DC Stage	LLC Analog Controllers L6599A, L6699	600 V-650 V MDmesh M2 ST*60M2, ST*65M2, ST*60M2-EP	Output Diodes for LLC Schottky, FERD STPS*	
	Asym. HB Analog Controllers L6591	600 V-650 V MDmesh M6 ST*60M6, ST*65M6	FERD*45, FERD*50, FERD*60	
	MCUs & Digital Controllers STM32F334, STM32G4, STNRG388A	600 V-650 V MDmesh DM2 ST*60DM2, ST*65DM2	TVS for Power MOSFET and Power Rail Surge Protection SMA4F, SMA6F, SMB15, series	MOSFET and IGBT Gate Drivers
	SR Analog Controllers SRK2000A, SRK2001, SRK2001A	600 V-650 V MDmesh DM6 ST*60DM6, ST*65DM6	LDO	HV HB Gate Drivers L649*
		SR 60 V-100 V StripFET F7 ST*N6F7 ST*N8F7 ST*N10F7	Low Dropout (LDO) Linear Regulators LDF, LDFM, LD39050, LD39100, LD39200, LDL112, LDL212, LD59100	Isolated Gate Drivers STGAP*
				SR Multiple LS Gate Drivers PM8834
				SR HV HB Gate Drivers L649*

Note: * is used as a wildcard character for related part number

MAIN EVALUATION BOARDS AND REFERENCE DESIGNS

STEVAL-ISA147V3

500 W fully digital AC-DC power supply (D-SMPS)



STEVAL-ISA172V2

2 kW fully digital AC-DC power supply (D-SMPS)



STEVAL-DPSLLCK1

3 kW Full Bridge LLC resonant digital power supply



EVLSTNRG-1kW

1 kW SMPS digitally controlled multi-phase interleaved converter



STEVAL-IPFC01V1

3 kW three-channel digitally controlled interleaved PFC



STEVAL-IPFC02V1

2 kW two-channel digitally controlled interleaved PFC



STEVAL-IPFC12V1

2 kW two-channel digitally controlled interleaved PFC with digital inrush current limiter



STEVAL-DPSTPFC1*

3.6 kW PFC totem pole with digital inrush current limiter



Note: *available in Q4 2020

Power Distribution for Modern Data Center

To support the evolution and expansion of cloud services, the internet of things, mobile apps and new generation of telecommunication infrastructure, the demand for data centers performance is growing exponentially with more powerful CPUs, and this segment is expanding in artificial intelligence and machine learning.

In the newest architecture a 48 V DC rail is generated from the AC-DC power supply unit that will then be converted to provide the number of DC rails needed to supply the variety of loads and circuits in the server. This conversion must meet stringent efficiency targets requiring innovative architectures like those developed by ST.


We offer a wide range of high-efficiency regulated and unregulated DC-DC conversion solutions including STB, STC, HSTC for 48 V to 12V intermediate bus conversion.

Moreover we offer 12V to Point of Load conversion including multi-phase digital controller and Smart Power Stages (SPS) to support the most recent INTEL and AMD CPU specifications.


Finally, ST offers direct conversion solutions, from 48V to the point of load, based on the Power Stamp Alliance (PSA) products.




Power Delivery for Modern Data Center



Typical Configuration for Switched-Tank Converter (STC) System - 48 V to 12 V non isolated unregulated IBC





Typical Configuration for STBUCK - 48 V to 12 V non isolated regulated IBC



Note: * is used as a wildcard character for related part number

Typical Configuration for 48 V Isolated Direct Conversion



SSD Power Management

Solid State Drives (SSD) serve the same function as Hard Disk Drives, but they have a different set of internal components; they have no moving parts and data is stored in flash memory. SSDs can access data faster than HDDs and have several other advantages such as better performance and robustness and lower power consumption. SSDs are widely used in desktop and notebook computers as well as for storage in data centers.


ST offers state-of-the-art products for SSD system architecture including Power Management ICs featuring protections and communication bus. Our portfolio of high-quality components allows the design of solutions meeting the most demanding requirements of both consumer SSD and enterprise-grade SSDs.

ST device family is ideal to design advanced power management solutions for microcontroller, DDR, Flash memory, on SSD server and consumer applications.


The IC series features multiple Buck and LDOs with programmable outputs and supports conversions from a wide range of input voltage buses as 12V, 5V and 3.3V.

High switching frequency eases the design of compact application while specific control techniques ensures best in class efficiency at heavy and light load operation.

Full programmability via high speed serial interfaces as I2C and PMBus® allows configurability to fit different application requirements.




Typical Block Diagram for SSD Power Management




Note: * is used as a wildcard character for related part number




STPMIC06



STPMIC07M



L7292




Power over Ethernet (PoE)

Power over Ethernet (PoE) is a widely adopted technology used to transfer power and supply the powered device (PD) including wireless access points, VoIP phones over an RJ-45 cable also carrying data as described in the IEEE 802.3 standard and its evolutions including IEEE 802.3bt, IEEE 802.3at and IEEE 802.3af.

We offer a range of products providing a complete interface with all the functions required by the communication standard, including detection and classification as well as protection features such as under-voltage lockout (UVLO) and in-rush current limitation. In addition, these products can control hot-swap power MOSFETs that can greatly simplify the development of IEEE 802.3 compliant solutions for powered devices (PD).




Typical block diagram for PoE Power Management



MAIN EVALUATION BOARDS AND REFERENCE DESIGNS

STEVAL-POE001V1

Power Over Ethernet (PoE) - IEEE 802.3bt compliant interface



STEVAL-POE002V1

5 V/8 A, synchronous flyback converter, Power over Ethernet (PoE) IEEE 802.3bt compliant reference design



STEVAL-POE003V1

5 V/20 A, active clamp forward converter, Power Over Ethernet (PoE) - IEEE 802.3bt compliant reference design



STEVAL-POE005V1

12 V/8 A, active clamp forward converter, Power Over Ethernet (PoE) IEEE 802.3bt compliant reference design



STEVAL-POE006V1

3.3 V/20 A, active clamp forward converter, Power Over Ethernet (PoE) IEEE 802.3bt compliant reference design



Note: * is used as a wildcard character for related part number

LED TV Power Supply

Beyond their outstanding image quality, new-generation televisions have a very thin design, are highly power-efficient and feature a stand-by power mode. Power Supply Units (PSUs) play a key role in ensuring TVs meet market requirements and have an elegant form factor.

To achieve these stringent requirements, PSUs typically have a Power Factor Corrector (PFC) stage and use advanced topologies, like half-bridge LLC (HB-LLC) resonant.

ST offers a broad portfolio of high-voltage MDmesh™ and low-voltage STripFET™ power MOSFETs, field-effect rectifier diodes (FERD), Schottky and Ultrafast diodes, a full range of protection ICs as well as dedicated analog and digital switching controllers which negate the necessity of auxiliary power by consuming very low power at no load. In addition, STM32 microcontrollers enable developers to exploit the full potential of digital PSU implementations.




ST's recommended products for LED TV Power Supply


	Controllers	Power MOSFETs	Diodes	Opamp V/I Sensing
PFC Block	TM Analog Controllers L6562A*, L6563*, L6564*	600 V-650 V MDmesh M2 ST*60M2, ST*65M2, ST*60M2-EP	600 V Ultrafast for TM STTH*L06 STTH*06 STTH15AC06*	Precision Op Amps (<50 MHz) TSZ*, TSV*, TS9*, LMV*
	CCM Analog Controllers L4981*, L4984D	600 V-650 V MDmesh M6 ST*60M6, ST*65M6	600 V Ultrafast for CCM STTH*R06 STTH*T06	MOSFET and IGBT Gate Drivers
	MCUs & Digital Controllers STM32F0, STM32G0, STM32F301, STM32F334, STM32G4, STNRG388A, STNRGPF01, STNRGPF02, STNRGPF12	650 V MDmesh M5 ST*65M5	SiC Diodes STPSC*065	Multiple LS Gate Drivers PM8834 Single LS Gate Drivers PM88*1
Isolation Stage	Flyback Controllers L6566A, L6566B, L6565, L6668, STCH03	600 V-650 V MDmesh M2 ST*60M2, ST*65M2, ST*60M2-EP	Output Diodes for Flyback Schottky, FERD, Ultrafast STPS*, FERD*, STTH*	MOSFET and IGBT Gate Drivers
	PFC & LLC Combo Controllers STCMB1, STNRG011	600 V-650 V MDmesh M6 ST*60M6, ST*65M6	Clamping Diodes for Flyback 600 V to 1000 V Ultrafast STTH*06, STTH*08, STTH*10	HV HB Gate Drivers L649*
	LLC Analog Controllers L6599*, L6699	600 V-650 V MDmesh DM2 ST*60DM2, ST*65DM2	Output Diodes for LLC Schottky, FERD STPS*	Isolated Gate Drivers STGAP*
	Asymmetrical HB Controllers L6591	600 V MDmesh DM6 ST*60DM6	FERD*45, FERD*50, FERD*60, FERD*100	SR Multiple LS Gate Drivers PM8834 SR HV HB Gate Drivers L649*
	MCUs & Digital Controllers STM32F0, STM32G0, STM32F301, STM32F334, STM32G4, STNRG388A	60 V-100 V STripFET F7 ST*N6F7 ST*N8F7 ST*N10F7	MOSFET Protection for Flyback SMA4F, SMA6F, SMB15F series	DC-DC Conversion
	SR Analog Controllers SRK1000, SRK1001 for Flyback SRK2000A, SRK2001, SRK2001A for LLC		Voltage Reference T*431, T*432	ST1S12, ST1S3*, ST1S4*, ST1S50

Note: * is used as a wildcard character for related part number


Typical Block Diagram for Analog Control Solutions for Small Panel Size



Typical Block Diagram: Analog Control Solutions with no Aux supply, for Small/Medium Panel Size



Typical Block Diagram for Digital Control Solutions for Medium/Large Panel Size



MAIN EVALUATION BOARDS AND REFERENCE DESIGNS

STEVAL-IPFC02V1

2 kW two-channel digitally controlled interleaved PFC



STEVAL-IPFC12V1

2 kW two-channel digitally controlled interleaved PFC with digital inrush current limiter



STEVAL-DPSTPFC1*

3.6 kW PFC totem pole with digital inrush current limiter



EVLCMB1-90WADP

19 V - 90 W adapter based on TM PFC and HB LLC analog combo controller



EVLSTNRG011-150

12 V - 150 W power supply based on TM PFC and HB LLC digital combo controller



EVLCMB1-AIO210W

12 V - 210 W adapter based on TM PFC and HB LLC analog combo controller




Note: * available in Q4 2020

DC-DC Conversion


A DC-DC switching converter is used to locally supply any component or part of a system with the desired DC voltage and current. Depending on the application's relationship between the input and output voltage, engineers have to choose the best power topology – buck, boost, buck-boost or inverting, with or without synchronous rectification. In addition, they can decide to use an implementation based on monolithic ICs or with discrete power switches and controllers – or even an advanced digital implementation. Whatever the choice, the right semiconductor products are key to meet the specific efficiency and size design targets.

ST's broad product portfolio includes highly-integrated DC-DC converters and PWM controllers, power MOSFETs and rectifiers, protection ICs, linear voltage regulators, to address a wide range of topologies and power requirements. We also provide a comprehensive range of hardware and software evaluation and development tools including our eDesignSuite that helps engineers design high-efficiency DC-DC converters.


Typical buck configuration: up to 61 Vin/3 A Iout



Typical multi-phase configuration: up to 12 Vin, very high output current



Typical single phase discrete configuration: up to 18 Vin, high output current



MAIN EVALUATION BOARDS AND REFERENCE DESIGNS

STEVAL-ISA152V1

Asynch. buck up to 60 Vin, 3.3 Vout - 3 A Iout



STEVAL-ISA208V1

Synch. Buck 38 Vin, 5 Vout-3 A Iout



STEVAL-1PS02B

Synch. Buck with Aux Switch, 5.5 Vin, Dynamic Voltage Selection up to 2.5V - 400 mA







STEVAL-ISA205V1

Synch. Buck 12 Vin, 3.3 Vout-2 A Iout, Auto. Grade




ST's product offering for Switching Converters (DC-DC)




■ Asynchronous ■ Automotive ■ Synchronous ■ Compact BOM
Note: * dual, parallel up to 7A

Note: * is used as a wildcard character for related part number

Typical 48 Vin, up to 65 W Pout, Synchronous Flyback configuration



Typical 48 Vin, > 65 W Pout, Active Clamp Forward configuration



MAIN EVALUATION BOARDS

STEVAL-ISA203V1

- Input Voltage range: 42 - 56 V DC
- Switching Frequency - 250 kHz
- Output:
 - Power - 60 W
 - Voltage - 12 V DC
 - Current - 5A
- Peak Efficiency > 94%



STEVAL-ISA204V1

- Input Voltage range: 42 - 56 V DC
- Switching Frequency - 250 kHz
- Output:
 - Power - 100 W
 - Voltage - 5 V DC
 - Current - up to 20 A
- Peak Efficiency > 94%




Note: * is used as a wildcard character for related part number

WEARABLE DEVICES - POWER MANAGEMENT

Wearable devices, by their very nature, must be compact and comfortable for the user. They need to deliver precise information about the user states and conditions, have low power consumption and the right level of performance to make them convenient and easy to use. ST's products for wearable devices are designed to meet the needs of the most demanding systems with a portfolio covering smart watches, fitness trackers, heart-rate monitors, sports equipment and a variety of other wearable devices. Our portfolio includes digital processing, sensors, connectivity, security and power management solutions that can make the difference in a challenging and competitive market.

Specifically for power management, ST provides a range of solutions to match the needs of very small form factor with outstanding efficiency performance and longer battery life.

Typical Block Diagram of Smart Watch



MAIN EVALUATION BOARDS AND REFERENCE DESIGNS

STEVAL-1PS01AJR/1PS01DJR/1PS01EJR

Evaluation board based on the ST1PS01 400 mA nano-quiescent synchronous step-down converter with digital voltage selection



STEVAL-1PS02B

Evaluation board based on the ST1PS2 400 mA nano-quiescent synchronous step-down converter with digital voltage selection and AUX switch



STEVAL-LD0001V1

Quad high performance LDO evaluation board based on LDBL20, LDLN025, LD39130S and STLQ020



LED LIGHTING AND CONTROLS



LED General Illumination

LED lamps and bulbs can have a number of different form-factors depending on the specific use, size and dimension of the application, including retrofit bulbs, high-bay lights, low-bay lights, emergency lights. Driving a string of LEDs involves AC-DC and DC-DC conversion – designed using non-isolated, isolated, single stage or multi-stage topologies – which must ensure high efficiency and reliability at a competitive cost point.

Modern applications include a range of connectivity features to implement remote monitoring and control, making LED lighting a pillar of the smart home, smart building and smart city environment. ST's portfolio includes a variety of RF transceivers, wireless MCUs, network processor ICs and fully certified modules for key wireless connectivity technologies. Our embedded software for BLE Mesh enables mesh networking of connected smart lighting end products.

For the LED driving stage we have a range of pulse-width modulation (PWM) and power factor correction (PFC) controllers, power MOSFETs and diodes as well as a comprehensive set of hardware evaluation and development tools including reference designs to help developers design high-efficiency LED lighting solutions.

Typical Block Diagram



ST'S product offering for LED General Illumination

	Controllers	Power MOSFETs	Diodes	MOSFET and IGBT Gate Drivers
PFC Block	TM Analog Controllers L6562*, L6563*, L6564* CCM Analog Controllers L4981*, L4984D MCUs & Digital Controllers STM32F0, STM32G0, STM32F301, STM32F334, STM32G4, STLUX, STNRG388A, STNRGPF*2	800 V to 1200 V MDmesh K5 ST*80K5, ST*9*K5, ST*105K5, ST*120K5 600 V-650 V MDmesh M2 ST*60M2, ST*65M2, ST*60M2- EP 600 V-650 V MDmesh M6 ST*60M6, ST*65M6 SiC MOSFET SCT*N65G2	600 V Ultrafast for TM STTH*L06, STTH*06, STTH15AC06* 600 V Ultrafast for CCM STTH*R06, STTH*T06 SiC Diodes STPSC*065	Single LS Gate Drivers PM88*1
	Controllers & Converters	Power MOSFETs	Diodes & Discretes	Voltage Reference, CC/CV Ctrl
Isolation Stage	Offline LED Drivers HVLED001B, HVLED001A, HVLED007, HVLED8* HV Converters VIPer0P, VIPer*1, VIPer*6, VIPer122, VIPer222, VIPer*5, VIPer*7, VIPer*8 LLC Analog Controllers L6599*, L6699 PFC & LLC/LCC Combo Controllers STCMB1, STNRG011, STNRG012* MCUs & Digital Controllers STM32F0, STM32G0, STM32F301, STM32F334, STM32G4, STM8S, STLUX, STNRG388A SR Analog Controllers SRK1000, SRK1001 for Flyback SRK2000A, SRK2001, SRK2001A for LLC	800 V to 950 V MDmesh K5 ST*80K5, ST*9*K5 950V MDmesh DK5 ST*95DK5 600 V-650 V MDmesh M2 ST*60M2, ST*65M2, ST*60M2-EP 600 V-650 V MDmesh M6 ST*60M6, ST*65M6 600 V-650 V MDmesh DM2 ST*60DM2, ST*65DM2 600 V MDmesh DM6 ST*60DM6 60 V-100 V StripFET F7 ST*N6F7, ST*N8F7, ST*N10F7	Clamping Diodes for Flyback 600 V to 1000 V Ultrafast STTH*06, STTH*08, STTH*10 Output Diodes for Flyback Schottky, FERD, Ultrafast STPS*, FERD*, STTH* Output Diodes for LLC/LCC Schottky, FERD STPS* FERD*45, FERD*50, FERD*60, FERD*100 MOSFET Protection for Flyback SMA4F, SMA6F, SMB15F series	Voltage Reference T*431, T*432 Voltage and Current Ctrl TSM*, SEA05* MOSFET and IGBT Gate Drivers HV HB Gate Drivers L649* Isolated Gate Drivers STGAP* Multiple LS Gate Drivers PM8834
Multiple strings management	Offline LED Drivers HVLED002 MCUs & Digital Controllers STM32F0, STM32G0, STM32F334, STM32G4, STM8S, STLUX, STNRG388A	600 V-650 V MDmesh M2 ST*60M2, ST*65M2, ST*60M2-EP 600 V-650 V MDmesh M6 ST*60M6, ST*65M6 STripFET F7 ST*N6F7, ST*N8F7, ST*N10F7	Schottky Diodes STPS* FERD Diodes FERD* ≥ 200 V Ultrafast Diodes STTH* DC-DC LED Drivers LED5000, LED600, ST1CC40, LED2000, LED2001	HV HB Gate Drivers L649*, L6395 Single LS Gate Drivers PM88*1 Multiple LS Gate Drivers PM8834
	Bluetooth Low Energy (BLE MESH)		2.4 GHz Multi Standard (ZigBee, Thread, 802.15.4)	Sub-1GHz
Wireless Connectivity	BLE 5.0 SoC BlueNRG-1, BlueNRG-2 BLE 4.2 SoC BlueNRG-MS Baluns BALF-NRG-0*D3, BALF-NRG-02J5 Dual core MCUs BLE 5.0 STM32WB IPD (Integrated Passive Device) MLPF-WB55-01E3, MLPF-WB55-02E3	BlueNRG Modules BlueNRG-M0, BlueNRG-M2 STM32 Wireless Module STM32WB5MMG1	2.4 GHz Dual Core Wireless MCUs STM32WB STM32 Wireless Module STM32WB5MMG1	Sub-1GHz Wireless MCU STM32WL Sub-1GHz Transceivers S2-LP, SPIRIT1 Sub-1GHz Transmitters STS1TX, S2-LPTX MCUs STM32F0, STM32G0, STM32L0 Baluns BALF-SPI-0*D3, BALF-SPI2-0*D3

Note: 1 available in Q4 2020

MAIN EVALUATION BOARDS

EVLHVLED007W35F

35 W LED driver with very low THD, based on Transition Mode Flyback converter (CVout)



STEVAL-ILL070V4

35 W LED Driver with very high efficiency based on CC QR flyback converter



EVAL-PSR01B-35W

35 W LED Driver with very high efficiency based on QR flyback converter with PSR (CVout)



STEVAL-LLL004V1

75 W AC-DC digitally controlled non isolated constant current LED driver



EVAL-IBD002-35W

35 W Inverse buck with LED current control and with Analog/PWM dimming



STEVAL-ILL078V1

1A, up to 60 V Vin, buck LED driver with digital dimming




LED Street Lighting

Street lighting installations have evolved from basic energy-hungry illumination spots to central devices enabling a set of services, such as presence and traffic level monitoring and incident detection surveillance, while optimizing illumination levels to specific road and weather conditions to support administrations transforming cities in Smart Cities.

We have a broad range of wired and wireless connectivity, power management and LED driving solutions. A range of high-performance and low-power STM32 microcontrollers together with presence, proximity, camera and environmental sensors as well as MEMS microphones enable design of advanced street lighting systems.

Typical Block Diagram



MAIN EVALUATION BOARDS

STEVAL-LLL008V1

100 W - 1.4 A constant current LED Driver with Sub-1GHz connectivity based on QR Flyback and inverse buck converters.



STEVAL-LLL006V1

75 W LED driver (CC/CV) with Sub-1GHz connectivity



STEVAL-LLL004V1

75 W AC-DC digitally controlled non isolated constant current LED driver



EVL80WLED-STCH03

80 W - 1 A primary side current loop control LED driver based on QR flyback converter



EVL150W-HVSL

150 V - 1 A LED driver featuring TM PFC and LCC resonant converter with STCMB1 combo controller



EVL6699-HVSL

150 V - 1 A LED driver featuring TM PFC and LCC resonant converter with L6699



STEVAL-ILL066V2

100 W LED street lighting with DALI2.0 communication interface using the STLUX385A digital controller



STEVAL-ILL053V2

48 V - 130 W high efficiency converter with PFC for LED street lighting



ST'S product offering for LED Street Lighting

	Controllers	Power MOSFETs	Diodes & Discretes	MOSFET and IGBT Gate Drivers
Power Supply	TM PFC Analog Controllers L6562*, L6563*, L6564*	800 V to 1050 V MDmesh K5 ST*80K5, ST*9*K5, ST*105K5	600 V Ultrafast for TM PFC STTH*L06, STTH*06, STTH15AC06*	Single LS Gate Drivers PM88*1
	CCM PFC Analog Controllers L4981*, L4984D	950V MDmesh DK5 ST*95DK5	600 V Ultrafast for CCM PFC STTH*R06, STTH*T06	Multiple LS Gate Drivers PM8834
LED Driver	Offline LED drivers HVLED001B, HVLED001A, HVLED007	600 V-650 V MDmesh M2 ST*60M2, ST*65M2, ST*60M2-EP	SiC Diodes STPSC*065	HV HB Gate Drivers L649*
	PFC & LLC/LCC Combo Controllers STCMB1, STNRG011, STNRG012*	600 V-650 V MDmesh M6 ST*60M6, ST*65M6	Output Diodes for Flyback Schottky, FERD, Ultrafast STPS*, FERD*, STTH*	Isolated Gate Drivers STGAP*
Sensing, Processing, Control, LED Bypass	LLC/LCC Controllers L6599A*, L6699	600 V-650 V MDmesh DM2 ST*60DM2, ST*65DM2	Clamping Diodes for Flyback 600 V to 1000 V Ultrafast STTH*06, STTH*08, STTH*10	Voltage Reference, CC/CV Ctrl
	MCUs & Digital Controllers STM32F0, STM32G0, STM32F301*, STM32F334, STM32G4, STLUX, STNRG388A	600 V MDmesh DM6 ST*60DM6	Output Diodes for LLC/LCC Schottky, FERD STPS*, FERD*45, FERD*50, FERD*60, FERD*100	Voltage Reference T*431, T*432
Connectivity	SR Analog Controllers SRK1000, SRK1001 for Flyback SRK2000A, SRK2001, SRK2001A for LLC	SiC MOSFET SCT*N65G2	MOSFET Protection for Flyback SMA4F, SMA6F, SMB15F series	Voltage and Current Ctrl TSM*, SEA05*
		60 V-100 V STripFET F7 ST*N6F7, ST*N8F7, ST*N10F7		
	Controllers	DC-DC Buck LED Drivers	DC-DC Boost LED Drivers	LED Array Drivers
	Offline LED drivers HVLED002	LED5000, LED6000, ST1CC40, LED2000, LED2001	LED6001, LED7707, LED7708	STP04/08/16/24, STCS*, LED8102S
	Temperature Sensors	Control Unit	Protection Switch	Diodes & Discretes
	STLM20 STTS751 LM135Z	MCUs STM32F0, STM32G0	60 V-100 V STripFET F7 ST*N6F7, ST*N8F7, ST*N10F7	LBP01
	Wired - Power Line Communication	Wireless - Sub-1GHz	Wireless - Sigfox	Wireless - LoRa
	Power Line Transceivers ST7570, ST7580, ST7590	Sub-1GHz Wireless MCU STM32WL Sub-1GHz Transceivers S2-LP, SPIRIT1 Sub-1GHz Transmitters STS1TX, S2-LPTX Sub-1GHz Wireless MCU STM32WL MCUs STM32F0, STM32G0, STM32L0 Balun BALF-SPI-0*D3, BALF-SPI2-0*D3 Certified Modules SPSGRF (868 and 915 MHz) SPSGRFC (433, 868 and 915 MHz)	Sub-1GHz Wireless MCU STM32WL Sub-1GHz Transceivers S2-LP Sub-1GHz Transmitters S2-LPTX Sub-1GHz Wireless MCU STM32WL MCUs STM32L0, STM32L4 Baluns BALF-SPI2-01D3 Secure MCUs STSAFE-A100	LoRa Wireless MCU STM32WL MCUs STM32L0, STM32L1, STM32L4 Embedded Software I-CUBE-LRWAN Secure MCUs STSAFE-A100

Note: * is used as a wildcard character for related part number

1 available in Q4 2020




LED POE Lighting

Power over Ethernet (PoE) is a widely adopted technology used to supply a powered device (PD) over an RJ-45 cable while carrying data. Described in the IEEE 802.3 standard and its enhancements including IEEE 802.3bt, IEEE 802.3at and IEEE 802.3af, this technology is becoming attractive for LED lighting.

We have a range of products providing a complete interface with all the functions required by the communication standard including detection and classification, protection features such as under-voltage lockout (UVLO) and in-rush current limitation as well as the control of the hot-swap power MOSFETs that can greatly simplify the development of IEEE 802.3 compliant solutions for powered devices (PD). We also have high-efficiency, optimized DC-DC conversion solutions for supplying the LEDs.



Typical Block Diagram



ST'S product offering for LED PoE Lighting

PoE Interface	Protections	Auxiliary Power Supply	LED Driver
IEEE 802.3bt PM8805	TVS for Power Rail Surge Protection SMA4F, SMB15F	Buck L7987L	Buck LED6000
IEEE 802.3at PM8803, PM8801			Inverse Buck HVLED002
IEEE 802.3af PM8800A			60 V-100 V STripFET F7 ST*N6F7, ST*N8F7, ST*N10F7
			Schottky Diodes STPS*

Note: * is used as a wildcard character for related part number

MAIN EVALUATION BOARDS

STEVAL-POEL45W1

45 W PoE powered LED lighting with BLE control



STEVAL-ILL078V1

1 A, up to 60V Vin, buck LED driver board based on the LED6000



Lighting Controls

Lighting controls have evolved from simple triac dimmers to more sophisticated architectures including light sensors, digital and PWM dimmers, DALI network-based systems and wireless programming solutions.


ST's long-term partnerships with major lighting suppliers combined with our leadership in discrete and integrated power devices enable us to offer high efficiency and cost-optimized solutions for all types of lighting applications and their control – both wired (e.g. Powerline) or wireless (RF) – for industrial, residential, commercial, and architectural lighting applications.

DALI Lighting Solution

Digital Addressable Lighting Interface (DALI) is a trademark for a network-based technology used to effectively control lighting in building automation. Originally defined in IEC 60929 standards, it's updated in IEC 62386 which includes LED device types.

We provide a range of analog and digital controllers including the STLUX family and the STM32 microcontrollers to implement the AC-DC and DC-DC power converter and run the DALI protocol.

Typical Block Diagram for DALI Lighting System




ST'S product offering for Lighting Controls

LED Driver	MCUs	Power Management	KNX Transceiver
Digital Controllers STLUX	STM32F1, STM32L1, STM8	Refer to LED General Illumination section	TVS Protection on KNX Bus SMAJ40CA-TR
Development Tools STSW-STLUXLIB02, STSW-STLUXSMED02	Embedded Software STSW-DALI002, STSW-DALI001, STSW-STM8025		STKNX

MAIN EVALUATION BOARDS

STEVAL-ILL066V2

100 W LED street lighting evaluation board with DALI2.0 communication interface using the STLUX385A digital controller



STEVAL-ILM001V1

Plug-in hardware module for the STM8S-DISCOVERY interface for DALI communication




LED Wireless Programming

Today's smart LED bulbs let users control features including brightness and color. These properties are controlled through the driver and can be programmed and modified at any time during manufacturing, distribution, installation or maintenance.

The use of NFC technology enables wireless programming using a smartphone, tablet or portable RFID/NFC reader, without having to power up the LED driver, and brings enhanced flexibility and energy-savings in addition to reducing development time and cost.

STMicroelectronics offers optimized and complete LED driver programming solutions with its comprehensive NFC portfolio, fully addressing the lighting market and featuring all the functions needed for wireless LED programming.

Typical Block Diagram of LED Wireless Programming



ST'S product offering for LED Wireless Programming

	NFC/RFID Reader IC	Protections	Microcontrollers
NFC Reader + MCU	ST25R	Antenna Protection Reader: ESDZV18-1BF4 Tag: USBLC6-2M6	STM8S STM32F0, STM32G0
	Dynamic NFC Tag		MCUs and Digital Controllers
LED Driver for high-end market	ST25DV-I2C Series		STM8S STM32F0, STM32G0 STM32F3, STM32F334, STM32G4 STLUX
	Dynamic NFC Tag with PWM Output		LED Driver
LED Driver for entry-level market	ST25DV-PWM Series		HVLED001*, HVLED002 LED600*, LED5000, LED2000 STP04/08/16/24, LED12/16/24*, LED8102S

Note: * is used as a wildcard character for related part number

MAIN EVALUATION BOARDS

ST25R3911B-DISCO

Discovery kit for ST25R3911B high performance HF reader/NFC



ST25DV-PWM-eSET

Discovery kit for the ST25DV-PWM NFC/RFID tag IC




ST25DV-DISCOVERY

Discovery kit for ST25DV04 Dynamic NFC/RFID tag IC



ELECTRO-MOBILITY

Key applications



Solutions

ST's key products and solutions for Electro-Mobility applications include:



FIND OUT MORE

www.st.com/electro-mobility

Battery Management System (BMS)
Charging Station
DC-DC Converter
Small Electric Vehicles
Electric Traction (Main Inverter)
Mild Hybrid 48 V Systems

On Board Charger (OBC)
Acoustic Vehicle Alerting System (AVAS)
HV Battery Disconnect & Fire-off System
Vehicle Control Unit (VCU)



Main Traction Inverter


The traction inverter converts energy from the vehicle's battery to drive the electrical engine. This key component has a direct impact on a vehicle's road performance, driving range and reliability, which also depends on the inverter's weight and size.

Subject to all the possible stress found in a road vehicle from heat and vibrations, these converters must be able to handle high power and currents along with the associated Electro Magnetic Compatibility (EMC) challenges as well as provide fail-safe operation to ensure dependability and safety for the driver and passengers.

To help developers increase the inverter's power efficiency and reduce size and weight, ST has a wide portfolio of discrete semiconductors including AEC-Q101 qualified silicon and silicon-carbide (SiC) MOSFETs and diodes as well as IGBTs. These are complemented by AEC-Q100 qualified galvanically isolated IGBT and MOSFET gate drivers and SPC5 32-bit automotive microcontrollers for implementing scalable, cost-effective and energy-efficient solutions.



Main Inverter



Note: * is used as a wildcard character for related part number

FIND OUT MORE

www.st.com/main-inverter-electric-traction




Bidirectional DC/DC Converter

Electric vehicles (EV) use two different power systems; a high-voltage battery (200 to 800 V_{DC}) for traction and a low-voltage (12/48V) one for supplying all the electric appliances in the vehicle. Traditionally, the low-voltage battery was charged from the alternator, but in today's vehicles it gets its power from the high-voltage battery pack. However, in specific electric car architectures, this low voltage battery should be ready to help recharge the high-voltage battery pack in order to provide energy for cranking the car. This means that the on-board DC-DC converter must be bi-directional and very efficient as well as highly reliable in order to run the complex control algorithms needed to ensure an energy-efficient solution.

ST has a wide offer of discrete semiconductors including AEC-Q101 qualified silicon and silicon-carbide (SiC) MOSFETs and diodes as well as IGBTs. These are complemented by AEC-Q100 qualified galvanically isolated IGBT and MOSFET gate drivers and SPC5 32-bit automotive microcontrollers to enable scalable, cost-effective and energy-efficient solutions for implementing these challenging converters.



Bidirectional DC/DC Converter



Note: * is used as a wildcard character for related part number

FIND OUT MORE

www.st.com/bidirectional-dc/dc-converter



48 V Start-Stop System


A start-stop system aims at reducing the amount of engine idle time, by shutting down and restarting the internal combustion engine automatically when the vehicle stops. Thus, it contributes to improving fuel economy and reducing CO2 emissions. This is especially useful in urban environments where vehicles can spend significant amounts of time in traffic.

Start-stop operations require power electronics that can handle high current during cranking and ensure reliability during start stop cycles, operating on/off at high temperatures

ST's solutions include silicon power MOSFETs, protections, gate drivers and microcontrollers which are in accordance to AEC-Q100 and AEC-Q101 standards.



Start-Stop system



Note: * is used as a wildcard character for related part number

FIND OUT MORE

www.st.com/48v-start-stop-system



On-Board Charger (OBC)


At the heart of any electric (EV) or plug-in hybrid (HEV) vehicle lies the high-voltage (200 to 800 Vdc) battery and its associated charging system. The on-board charger (OBC) provides the means to recharge the battery from the AC mains either at home or from outlets found in private or public charging stations.

From a 3.6 kW single-phase to a 22 kW three-phase high-power converter, today's OBCs must have the highest possible efficiency and reliability to ensure rapid charging times as well as meet the limited space and weight requirements.

ST has a wide offer of discrete semiconductors including AEC-Q101 qualified silicon and silicon-carbide (SiC) MOSFETs and diodes as well as IGBTs. These are complemented by AEC-Q100 qualified galvanically isolated IGBT and MOSFET gate drivers and SPC5 32-bit automotive microcontrollers for implementing these challenging converters.



OBC



Note: * is used as a wildcard character for related part number

FIND OUT MORE

www.st.com/on-board-charger



DC Fast Charging Station


The number of full electric vehicles (EVs) is rapidly growing and, as a result, the charging infrastructure is also expanding, including DC fast charging stations, which have the attractive capability of providing the vehicle with a 100 km driving range in just 10-12 minutes.

While architectures based on renewable sources and battery storage technologies – to take charging stations off-grid are emerging, mainstream solutions are fed from the grid and a converter – in the range of 120 kW or more - has a 3-phase input Power Factor Correction (PFC) stage and an isolated DC-DC converter. DC Charging stations also provide secure connectivity and authentication with the vehicle.

We can provide a range of power discretes including silicon-carbide (SiC) and silicon power MOSFETs and diodes, isolated gate drivers as well as high-performance STM32 microcontrollers to help develop high-efficiency, high-power density DC charging stations.



Typical Block Diagram



MAIN EVALUATION BOARDS AND REFERENCE DESIGNS

STDES-PFCBIDIR

15 kW, three-phase, three-level Active Front End (AFE) bidirectional converter



STDES-VIENNARECT

15 kW, three-phase Vienna rectifier with low cost mixed-signal control for power factor correction



STEVAL-DPSTPFC1*

3.6 kW PFC totem pole with digital inrush current limiter



Note: * available in Q4 2020

ST'S product offering for DC Fast Charging Station

	Input stage	3ph PFC	DC/DC		Control units		Driving stage	Current sensing & signal conditioning	Aux SMPS	HMI	Metering	Connectivity	
			1^ side	2^ side	1^ side	2^ side						1^ side	2^ side
Rectifiers	SiC series - 650 V	•	•										
	SiC series - 1200 V	•	•										
	Ultrafast RQ series - 600 V	•	•	•									
	Ultrafast R series - 600 V	•	•						•				
	STBR series - 800V/1200V	•	•										
Thyristors	Schottky series - 40/45/60/100 V								•				
	TN series - 1200 V	•											
	TYN series - 1200 V	•											
	TM8050H series - 800 V	•											
TVS protections	TN3050H, TN5050H series -1200 V	•											
	SM4TY, SM6TY, SM15TY, SM30TY		•	•	•				•				
HMI ESD protections	ESDAxxY series, EMIF06-1005MX12Y									•			
Power MOSFETs	SiC series - 650/1200 V	•	•										
	M5 series - 650 V	•											
	M6 series - 600/650 V	•	•										
	DM6 series - 600/650 V		•										
	DM2 series - 600/650 V		•										
IGBTs	K5 series - 1200 V	•							•				
	H series - 1200 V	•											
	HB series - 650 V	•	•										
	HB2 series - 650 V	•	•										
ACEPACK Power Modules	V series - 600V	•	•										
	Customized modules	•	•										
MCUs (32bit)	STM32F334, STM32G4, STM32F3	•	•		•								
	STM32F0, STM32F1, STM32G0			•		•							
Gate drivers	L6491						•						
	STGAP1AS						•						
Memories (EEPROM)	M24**, M95**				•								
	Customized modules												
Current sense amplifiers	TSC102, TSC2010, TSC2011, TSC2012	•						•					
	Customized modules												
HV converters	VIPer*7, VIPer*6, VIPer26K								•				
	Customized modules												
Offline controllers	L6566BH, STCH03								•				
	Customized modules												
Voltage regulators	L5963, L5964, L798*, L698*								•				
	Customized modules												
CAN transceivers	L9616												•
	Customized modules												
CAN ESD protections	ESDCAN*Y Series						•					•	•
	Customized modules												
Power line transceivers	ST2100											•	•
	ST7540, ST7580, ST8500											•	
Bluetooth Low Energy Transceiver	SoC and Wireless MCUs												•
	Modules												•
NFC/RFID	Dynamic tags												•
	Readers												•
Metering ICs	M24SR, ST25DV-I2C												•
	ST25R												•
LED array drivers	STPM32, STPM33, STPM34										•		
	LED1642, STP08, STP16, LED77*, LED8102S									•			

Note: * is used as a wildcard character for related part number

INDUSTRIAL POWER & TOOLS

Industrial Welding

Arc welding is an assembling process that joins metal parts by causing their fusion through high-current flowing through the electrode and the base material. The current, either DC or AC, is generated by a specifically designed high-frequency inverter switched mode power supply (SMPS) usually based on half-bridge, full-bridge, and two-transistor forward topologies.

The main requirements in an SMPS for welding are high efficiency and reliability as well as power density to enable lighter and more compact designs.

We have a range of power MOSFETS and diodes – both Si and SiC based for higher efficiency – and IGBTs as well as galvanically isolated gate drivers and high-performance 32-bit STM32 microcontrollers to enable compact designs with higher efficiency.




ST'S product offering for Industrial Welding


	MCUs & Digital Controllers	MOSFET/IGBT Gate Drivers	IGBTs & Power Modules	Power MOSFETs	Diodes & Discretes
PFC	MCUs STM32F0 STM32G0 STM32F301 STM32F334 STM32G4 Digital Controllers STNRGPF01, STNRGPF02, STNRGPF12	Single LS Gate Drivers PM88*1, TD35* Multiple LS Gate Drivers PM8834 Isolated Gate Drivers STGAP* HV HB Gate Drivers L649*	600 V V series STG*V60F 650 V HB series STG*HP65FB 650 V HB2 series STG*HP65FB2 1200 V H series STG*H120F2	600 V-650 V MDmesh M2 ST*60M2, ST*65M2, ST*60M2-EP 600 V-650 V MDmesh M6 ST*60M6, ST*65M6 650V MDmesh M5 ST*65M5 650 V-1200 V SiC MOSFETs SCT*N65G2, SCT*N120	600 V Ultrafast STTH*W06, STTH*R06, STTH*T06 1200 V Ultrafast STTH*S12 SiC Diodes STPSC*065, STPSC*H12 TVS for Power Rail Surge Protection SM*T, SM*F, SMC30J series
DC-DC TTF			600 V V series STG*V60DF 650 V HB series STG*H65DFB 650 V HB2 series STG*H65DFB2 1200 V H series STG*H120DF2	650 V MDmesh M5 ST*65M5 600 V-650 V MDmesh M2 ST*60M2, ST*65M2, ST*60M2-EP 600 V-650 V MDmesh DM2 ST*60DM2, ST*65DM2 600 V-650 V MDmesh M6 ST*60M6, ST*65M6 600 V-650 V MDmesh DM6 ST*60DM6, ST*65DM6 800 V to 1200 V MDmesh K5 ST*80K5, ST*9*K5, ST*105K5, ST*120K5 950 V to 1050 V MDmesh DK5 ST*95DK5, ST*105DK5 650 V-1200 V SiC MOSFETs SCT*N65G2, SCT*N120	600 V Ultrafast STTH*R06, STTH*06 1000-1200 V Ultrafast STTH*10, STTH*12 TVS for Power Rail Surge Protection SM*T, SM*F, SMC30J series
DC-DC PS-FB	STM32F334 STM32G4 STM32F301 STM32F1 STM32F3	Isolated Gate Drivers STGAP* HV HB Gate Drivers L649*	ACEPACK Power Modules Customized Modules		TVS for Power Rail Surge Protection SM*T, SM*F, SMC30J series
Secondary Inverter		600 V V series STG*V60DF 650 V HB series STG*H65DFB 650 V HB2 series STG*H65DFB2	600 V V series STG*V60DF 600 V-650 V MDmesh DM2 ST*60DM2, ST*65DM2 600 V-650 V MDmesh M6 ST*60M6, ST*65M6 600 V MDmesh DM6 ST*60DM6	600 V-650 V MDmesh M2 ST*60M2, ST*65M2, ST*60M2-EP 600 V-650 V MDmesh DM2 ST*60DM2, ST*65DM2 600 V-650 V MDmesh M6 ST*60M6, ST*65M6 600 V MDmesh DM6 ST*60DM6	200 V to 400 V Ultrafast STTH*W02, STTH*W03, STTH*W04, STTH240F0 Power Schottky High Temperature STTH*10, STTH*12 TVS for Power Rail Surge Protection SM*T, SM*F, SMC30J series

Note: * is used as a wildcard character for related part number

Typical configuration for Single-Phase Architecture for Low/Medium Power Welding



Typical configuration for Single and Three-Phase Architectures for Medium/High Power Welding



Uninterruptable Power Supplies (UPS)

Uninterruptable Power Supplies (UPS) ensure continuity of supply by converting the DC voltage from a battery or battery bank to an AC voltage with the requested amplitude and frequency in case of power outages.


Depending on application requirements, an UPS can be built with a simple off-line configuration or with a double conversion online method for high-end, medium- or high-power UPSs. This also improves the quality of the power supplied to sensitive loads including computers, servers, smart industry machines, instrumentation and telecommunication equipment. We offer high-performance discrete devices including high- and low-voltage power MOSFETs, IGBTs, thyristors and silicon-carbide (SiC) diodes and power MOSFETs as well as galvanically-isolated and high-voltage gate drivers, PFC controllers and high-performance STM32 microcontrollers to enable high-efficiency, high-reliability UPS designs.

ST's product offering for Uninterruptable Power Supplies (UPS)

	SCRs & TRIACs	Diodes		SCRs & TRIACs
Rect. & inrush current limiter	High Temp. SCR TN*015H-6, TN*050H-8, TN*050H-12W High Temp. Triacs T1635T	Bridge Rectifier Diodes STBR*08, STBR*12	Bypass	Standard SCR TYN6*, TYN8*, TYN10*, TYN12* High Temp. SCR TN5050H-12WY Standard and Snubberless Triacs T2550-12, TPDV*
	MCUs & Digital Controllers	Power MOSFETs	IGBTs	Diodes
	MCUs STM32F0, STM32G0, STM32F301, STM32F334, STM32G4 Digital Controllers STNRG388A, STNRGPF01, STNRGPF02, STNRGPF12	600 V-650 V MDmesh M2 ST*60M2, ST*65M2 600 V-650 V MDmesh M6 ST*60M6, ST*65M6 650 V MDmesh M5 ST*65M5 SiC MOSFET SCT*N65G2	600 V V series STG*V60F 650 V HB series STG*HP65FB 650 V HB2 series STG*HP65FB2 1200 V H series STG*H120F2	600 V Ultrafast for CCM STTH*R06 STTH*T06 SiC Diodes STPSC*065 STPSC*H12
PFC Block				Opamp V/I Sensing
				Precision Op Amps (<50 MHz) TSZ*, TSV*, TS9*, LMV* MOSFET and IGBT Gate Drivers Multiple LS Gate Drivers PM8834 Single LS Gate Drivers PM88*1 HV HB Gate Drivers L649* Isolated Gate Drivers STGAP*
				Protections
				TVS for Power MOSFET Protection SMA4F, SMA6F, SMB15F series
	MCUs	Power MOSFETs	Diodes	MOSFET and IGBT Gate Drivers
Charge Controller		600 V-650 V MDmesh M2 ST*60M2, ST*65M2 600 V-650 V MDmesh M6 ST*60M6, ST*65M6 600 V-650 V MDmesh DM2 ST*60DM2, ST*65DM2 600 V-650 V MDmesh DM6 ST*60DM6, ST*65DM6		HV HB Gate Drivers L649* Isolated Gate Drivers STGAP*
			600 V Ultrafast STTH*06	
				Post Regulation
DC-AC Stage	STM32F334 STM32G4 STM32F4 STM32F7	SiC MOSFET SCT*N65G2	600 V V series STG*V60DF 650 V HB series STG*H65DFB 650 V HB2 series STG*H65DFB2 1200 V H series STG*H120DF2	1200 V Ultrafast STTH*12 SiC Diodes STPSC*065 STPSC*H12
				Multiple LS Gate Drivers PM8834 Single LS Gate Drivers PM88*1 HV HB Gate Drivers L649* Isolated Gate Drivers STGAP*
DC-DC Stage		60 V-100 V STripFET F7 ST*N6F7, ST*N8F7, ST*N10F7		DC-DC Converters L698*, ST1S14, L7985, L7986, L7987* Low Dropout (LDO) Linear Regulators LDF, LDFM, LDK220, LDK320, LDK715, LDL212

Note: * is used as a wildcard character for related part number

Typical block diagram for Online UPS with double conversion stage



MAJOR HOME APPLIANCES

Refrigeration, Washing, Drying and Miscellaneous Equipment


The white goods market requires low-cost and high-energy-efficiency solutions. The refrigeration, washing, drying and the miscellaneous (Air conditioner, water heater) equipment are some of the major home appliance applications that ST, thanks to its wide product portfolio, is able to satisfy with suitable and dedicated power products and high-performing STM32 microcontrollers combined with complementary gate drivers (L638* and L649*). Using SiC diodes (STPSC*), new high-voltage MDmesh MOSFETs or suitable field-stop trench-gate IGBTs, high-efficiency PFC is guaranteed. To reduce the 3-phase inverter design effort, ST offers the SLLIMM™ family (small low-loss intelligent molded module) of highly-integrated, high-efficiency intelligent power modules (IPM) integrating the power stage (both on IGBT and Mosfet discretes), driving network and protections. Another approach for designing a 3-phase inverter is based on the use of six discrete IGBTs/MOSFETs with the new 3-phase gate drivers STDRIVE601. High reliability against the inrush current is ensured by new SCRs in the front-end stage. STPW programmable electronic power breaker family provides a convenient, integrated solution for quickly and safely disconnecting a faulty load from a 12 V bus.

ST's product offering for Refrigeration, Washing, Drying and Miscellaneous Equipment

	SCRs & TRIACs	Diodes		LED Drivers		HV Converters
Rect. & inrush current limiter	High Temp. SCR TN*015H-6, TN1610H-6, TN*050H-12W Standard SCR: TN815, TN*15-600B High Temp. Triacs: T1635T	Bridge Rectifier Diodes STBR*08, STBR*12	User Interface	LED Array Drivers STP04/08/16/24 LED12/16/24* STCS*, LED8102S	AUX SMPS	ViPerPlus
	MCUs & Digital Controllers	IGBTs	Diodes	Opamp V/I Sensing	Power MOSFETs	Power Breakers
PFC Block	MCUs STM32F0, STM32G0, STM32F103, STM32F301, STM32F334, STM32G4, STM32F4 Digital Controllers STNRG388A, STNRGPF01, STNRGPF02, STNRGPF12	600 V V series STG*V60F 650 V HB series STG*HP65FB 650 V HB2 series STG*HP65FB2	STTH*AC06 STTH*R06 STPSC*065 DLF	Precision Op Amps (<50 MHz) TSZ*, TSV*, TS9*, LMV* MOSFET and IGBT Gate Drivers Multiple LS Gate Drivers PM8834 Single LS Gate Drivers PM88*1	600 V-650 V MDmesh M2 ST*60M2, ST*65M2 600 V-650 V MDmesh M6 ST*60M6, ST*65M6 650 V MDmesh M5 ST*65M5 SiC MOSFET SCT*N65G2	STPW12 Protections TVS for Power Rail SMA4F, SMA6F, SMB15F, SMC30J series
	MCUs	IGBTs	IPM	MOSFET and IGBT Gate Drivers	Power MOSFETs	Post Regulation
3Ph Inverter Compressor, Drum Motor, Fan, Pumps	STM32F0, STM32G0, STM32F103, STM32F301, STM32F334, STM32G4, STM32F4	600 V H series STG*H60DF 650 V M series STG*M65DF2	IPM for compressor and drum motor STGIPQ*60T-H STIPQ*M60T-H STGIF*CH60(T)S-L(E) STGIB*CH60(T)S-L(E) STGIB*M60(T)S-L(E) STIB*60DM2-L IPM for fan and pumps STIPNS*M50T-H STGIPNS*H60T-H STIPQ*M60 STGIPQ*60T-H	3-Phase HV Gate Driver STDRIVE601 HV HB Gate Drivers L638*, L649* Isolated Gate Drivers STGAP* Protections TVS for Power Rail Surge Protection SMA4F, SMA6F, SMB15F, SMC30J series	600 V-650 V MDmesh DM2 ST*60DM2, ST*65DM2 600 V-650 V MDmesh DM6 ST*60DM6, ST*65DM6 SiC MOSFET SCT*N65G2	DC-DC Converters L698*, ST1S14, L7985, L7986, ST1S4*, ST1S50 Low Dropout (LDO) Linear Regulators LDF, LDFM, LDK220, LDK320, LDK715, LDL212

Note: * is used as a wildcard character for related part number

Typical configuration



MAIN EVALUATION BOARDS

STEVAL-IHT008V1

1 kW, digital inrush current limiter based on Triac



STEVAL-IPM*

300 W to 3 kW Power board based on SLLIMM™



Software tools

Induction Cooking

Induction cooking ranges must be efficient, safe and provide friendly user interfaces. Resonant-switching topologies are typically used for the power converter in these appliances, as they also help achieve lower levels of electro-magnetic interferences (EMI).

We have specifically developed trench-gate field-stop IGBTs and diodes that, together with a selection of high-voltage gate drivers and high-performance STM32 microcontrollers, are ideal for high-efficiency converters. ST also offers environmental sensors and the LED and LCD display drivers, touchscreen controllers and proximity and sensors required for touch or touch-less user interfaces.




ST's product offering for Induction Cooking

	MCUs	IGBTs	MOSFET and IGBT Gate Drivers	Sensors			
Single-switch quasi-resonant (voltage resonance)	STM8* STM32F100	1250 V IH series STG*IH125DF	Multiple LS Gate Drivers PM8834 Single LS Gate Drivers PM88*1	Environmental Sensors Humidity - HTS221 Temperature - STLM20 Temperature - STTS751			
HB series resonant (current resonance)	STM32F0, STM32G0 STM32F100	600 V HB series STG*H60DLFB 650 V IH series STG*IH65DF	HV HB Gate Drivers L649* Isolated Gate Drivers STGAP*	Motion Sensors Accelerometer - IIS3DHHC Proximity Sensors ToF - VL53L*, VL6180*			
User interface (front panel)	MCUs	LED Drivers	AC-DC	DC-DC	LDO	Power Breakers	
	STM8, STM32F0, STM32G0, STM32F4*9, STM32F7*	LED Array Drivers STP04/08/16/24, LED1642GW, LED8102S, LED12/16/24*	Power Management VIPerPlus	L698*, ST1S14, L7985, L7986, L7987*	LDF, LDFM, LDK220, LDK320, LDK715, LDL212	STPW12	

Note: * is used as a wildcard character for related part number

Topology example



eDesignSuite

eDesignSuite is a comprehensive and flexible suite of design aid utilities and engineering tools, that streamlines development of winning solutions with a wide range of ST products meeting user's application requirements.

Explore the advanced features of our Power Management Design Center, an on-line design tool that smartly helps designers of power management systems and subsystems accelerating the engineering development process - select-evaluate-refine and prototyping - for a large and growing number of ICs and Discrete in our broad portfolio.

The software tool supports a variety of switching power converters, in power supply, LED lighting and battery charger applications, making easy the design path from user's specification to circuit's analysis and customization.

The main features of the tool are: automatic proposal for complete solution or fully customizable design, fully annotated and interactive schematics, complete and interactive bill of materials, main current and voltage simulations, efficiency curves, Bode stability and power-loss data, and fully interactive transformer design.

<https://eds.st.com/>



SMART SIMULATOR AND SYSTEM DESIGN ENGINE

Power conversion and LED lighting

- Automatic proposal for complete solution or fully customizable design
- Fully annotated and interactive schematics
- Complete and interactive bill of materials
- Set of analysis diagrams (main current and voltage simulations, efficiency curves, Bode stability and power-loss data)
- Fully interactive transformer design
- IPFC design based on STNRGPF digital controllers including c code generation

SIMULATORS AND SMART SELECTORS

Power MOSFETs, Diodes, AC Switches

- Part numbers proposed based on application electrical specifications
- I-V curves comparison among several part numbers
- Power losses calculated based on voltage/current target application waveforms



Smart simulator and system design engine view

CONFIGURATORS

STLUX & STNRG SMEDs configurator

- SMED configurator schemes
- Input configuration
- Clock, comparators and ADC settings
- FSM (finite state machine) configuration
- C code generation
- Load register setting on board in a click

Products

AC-DC CONVERSION ICs

High-voltage converters

ST's **high-voltage AC-DC converters** combine an advanced pulse width modulation (PWM) controller with a high-voltage power MOSFET in a single package. This makes them ideally suited for offline switch mode power supplies (SMPS) with output power spanning from a few to a few tens of watts.

The **VIPerPlus series** (VIPer0P, VIPer122, VIPer222 and VIPer*1, VIPer*5, VIPer*6, VIPer*7, VIPer*8 families) features an 800 V avalanche-rugged power MOSFET and leading-edge PWM controller and consumes less than 4 mW for VIPer0P, 10 mW for VIPer*1 and 30 mW in standby for the others. It also comes with the largest choice of protection schemes and supports different topologies.

The VIPer26K belongs to VIPer*6 family and integrates a 1050 V avalanche-rugged power MOSFET, suitable for cost effective 1-phase/3-phases smart meters, industrial systems and lighting power supplies.

The Altair series has a built-in 800/900 V avalanche-rugged power MOSFET and a PWM controller specifically designed to work in constant-current/constant-voltage primary-side regulation (PSR-CC/CV). It means opto-less implementation, thus significantly reducing component count.

1050 V	10W	VIPer26K		Very High Voltage SMPS Embedded E/A for direct output regulation / fly-back or buck converter
900V	7W	Altair04		Accurate Primary Side Regulation Constant current/constant voltage
800V	Up to 18W	VIPer01-11-31		Logic Level MOSFET - 5V supply voltage Embedded E/A, Very low standby consumption, 18VDC start-up voltage
	6W	VIPer0P		Zero Power Mode Smart standby management through buttons or MCU
	Up to 15W	VIPer06-16-26		Embedded E/A Direct output regulation / settable current limit / fly-back or buck converter
		VIPer17-27-37		Brown-out Output OVP, current limit, fly-back with optocoupler
		VIPer28-38		Peak Power Output OVP, current limit, fly-back with optocoupler
		VIPer25-35		Quasi Resonant Output OVP, current limit, fly-back with optocoupler
730	Up to 8W	VIPer122-222		Embedded E/A, 730V BV Optimized for low power

Flyback Primary side regulation

VIPer01-11-31	VIPer122-222
VIPer26K	VIPer06-16-26
Altair04	VIPer0P

Flyback Secondary side regulation

VIPer01-11-31	VIPer122-222	VIPer28-38
VIPer26K	VIPer06-16-26	VIPer25-35
Altair04	VIPer0P	VIPer122-222

Buck Converter Up to 500mA Output Current

VIPer01-11-31	VIPer122-222
VIPer26K	VIPer06-16-26
	VIPer0P

MAIN APPLICATIONS




PFC controllers

ST **power factor correction (PFC) controllers** operate in transition mode (TM, suitable for $P \leq 250$ W) and continuous current mode (CCM, suitable for $P > 250$ W), and are suitable for a wide-range-mains operation.


These devices embed advanced protection features, which make SMPS more robust and compact, requiring fewer external components. These features include output overvoltage, brown-out, feedback disconnection and boost inductor saturation protection. The high-voltage start-up capability, present in the L6564H and L6563H, helps improve the SMPS standby efficiency in systems that do not include an auxiliary power supply.

TM PFC controllers



	Basic features	Advanced protections	Remote on/off control	Tracking boost function	Interface for cascaded converter
L6562A*	●				
L6564*	●	●	●		
L6563*	●	●	●	●	●

CCM PFC controllers



L4984D	Line-modulated, fixed-off-time (LM-FOT) control
L4981A	Fixed frequency, average-current mode
L4981B	Line modulated frequency, average-current mode

MAIN APPLICATIONS



Note: * is used as a wildcard character for related part number

www.st.com/ac-dc-converters
www.st.com/pfc-controllers

PWM and resonant controllers

ST's portfolio of advanced controllers includes a variety of **primary controllers** intended to fit high-performance applications. Very high efficiency is achieved with single-ended topologies at a fixed switching frequency or with quasi-resonant operation; the new STCH03 offline constant-current primary-side regulation controller (PSR-CC) guarantees very low power consumption at no load condition. For high-power, high-current applications, ST offers controllers for half-bridge resonant and asymmetrical half-bridge topologies. The STCMB1 and STNRG011 combo controllers including high-voltage start-up, Xcap discharge circuit, PFC and resonant driving stages, guarantee high performance and high integration with a smaller pinout. The new STNRG012¹ is specifically designed to support LED lighting and industrial applications requiring DC source management, with additional THD optimizer function.

Flyback controllers

STCH03

- Offline quasi-resonant controller in SO-8 package
- Constant-current primary-side regulation mode (PSR-CC) or constant-voltage regulation with optocoupler
- Advanced burst mode operation (< 10 mW consumption @ no load)
- UVP, autorestart/latched OVP and internal OTP
- 650 V HV start up


L6566*

- Offline fixed-frequency or quasi-resonant controllers
- Suited for SMPS with PFC front-end (A version)
- Suited for SMPS with 3-phase mains (BH version)
- 700 V start up (A/B version), 840 V start up (BH version)
- Brownout protection

L6565

- Offline quasi-resonant controller
- Constant power vs mains change
- Ultra-low start-up current

HB-LLC resonant controllers



Analog combo controller (PFC+LLC/LCC)

STCMB1

- 800 V start-up voltage
- Embedded X-cap discharge circuit
- Transition Mode (TM) PFC control method
- Self-adjusting dead-time and anticapacitive mode for LLC

Multi-mode digital combo controller (PFC+LLC/LCC)

STNRG011

STNRG012¹

- Onboard 800 V startup circuit, line sense and X-cap discharge compliant with IEC 62368-1, for reduced standby power (STNRG011 only)
- DC source management with no X-cap discharge (STNRG012 only)
- THD optimizer for LED Lighting applications (STNRG012 only)
- Enhanced fixed on time multi-mode TM PFC controller
- Time-shift control of resonant half-bridge
- ROM memory for SW digital algorithms
- NVM memory for programmable key application parameters

Asymmetrical half-bridge controller

L6591

- PFC interface
- Brown out
- 700 V start-up voltage

MAIN APPLICATIONS



Tablets and smartphones
L6565, L6566*, STCH03



Laptops
L6565, L6566*, STCH03, STCMB1, STNRG011



High-power adapters and TVs
L6565, L6566*; L6599A*, L6699, STCMB1, STNRG011



Desktop PCs, commercial and street lighting
L6599A*, L6699, STCMB1, STNRG011, STNRG012¹

www.st.com/ac-dc-converters
www.st.com/pwm-controllers
www.st.com/resonant-controllers

Note: * is used as a wildcard character for related part number


¹available in Q4 2020

Synchronous rectification controllers

Synchronous rectifiers are used to drive power MOSFETs that replace the rectification diodes in the secondary side of SMPS, thus providing high efficiency especially in low-output-voltage, high-current power supplies.

The product portfolio supports the most common flyback and LLC resonant topologies. The main benefits include high efficiency, space saving, cost reduction and high reliability.

SR Controllers for Flyback




**Three options available: SRK1000 (0.5 μs), SRK1000A (2 μs), SRK1000B (3 μs)

SYNCHRONOUS RECTIFICATION BENEFITS

- Improved efficiency
- Better thermal performance
- High power density
- Increased reliability

SR controllers for LLC resonant



MAIN APPLICATIONS



High-power adapters and TVs
SRK1000, SRK1001



Desktop PCs and Server/Telecoms
SRK2000A, SRK2001, SRK2001A


www.st.com/ac-dc-converters
www.st.com/synchronous-rectification-controllers

Note: * is used as a wildcard character for related part number

Voltage and current controllers

ST offers a wide range of highly-integrated **voltage controllers** for constant-voltage (CV), constant-current (CC) SMPS applications, such as adapters, battery chargers and LED pilot lamps. They enable a more robust design, safer SMPS, very low power dissipation and low stress for secondary-side components.

SEA05 internal block diagram



CC/CV controllers for chargers, adapters and others

- | SEA05 | SEA05L | TSM10* |
|--|---|--------|
| <ul style="list-style-type: none"> Advanced CC/CV controller (SEA05) Advanced CC/CV controller with efficient LED pilot lamp driver (SEA05L) 0.5% voltage reference precision up to 36 Vcc Low quiescent current: 200 μA (SEA05), 250 μA (SEA05L) Current sense threshold 50 mV (SEA05) 4% current loop precision (SEA05L) | <ul style="list-style-type: none"> Compact solution Easy compensation 0.5 and 1% voltage reference precision | |

MAIN APPLICATIONS



Adapters



Battery chargers



Residential, commercial and street lighting

www.st.com/ac-dc-converters
www.st.com/voltage-and-current-controllers

Signal conditioning

Signal conditioning devices include **Operational Amplifiers** and **Current Sensing amplifiers**. These devices enable accurate and fast current measurement in power supplies. **Comparators** are also very powerful allies of the power supply designer to implement protection features such as over-temperature, over-current, and over/under voltage.

Operational Amplifiers


TSZ181, TSZ182

- 5 V zero-drift amplifier
- Input offset voltage 25 μ V max
- Gain bandwidth 3 MHz

TSB712, TSB7192

- 36 V amplifier
- Input offset voltage 300 μ V max
- Gain bandwidth 6 MHz (unity gain stable) or 22 MHz

Typical application schematic for low-side current measurement in a PFC



Current Sensing Amplifiers

TSC103

- Operating voltage 2.9 to 70 V
- Surviving voltage on shunt -16 to 75 V
- Amplification gain x50 x100
- Package TSSOP8, SO8

TSC101

- Operating voltage 2.8 to 30 V
- Surviving voltage on shunt -0.3 to 60 V
- Amplification gain x20 x50 x100
- Package SOT23-5


TSC2010

- Operating voltage: -20 to 70 V
- Amplification gain x20 x60 x100
- Offset voltage: \pm 200 μ V max
- 2.7 to 5.5 V supply voltage
- Gain error: 0.3% max
- Packages MiniSO8 SO8

TSC210

- Operating voltage: -0.3 to 26 V
- Amplification gain x50 x200 x1000
- Offset voltage: \pm 35 μ V max
- Gain error: 1% max
- Package QFN10 SC70-6

Typical application schematic for high-side current measurement



Comparators


TS3021, TS3022

- Propagation delay: 38 ns
- Low current consumption: 73 μ A
- Rail-to-rail inputs
- Push-pull outputs
- Supply operation from 1.8 to 5 V

TS3011

- Propagation delay: 8 ns
- Low current consumption: 470 μ A
- Rail-to-rail inputs
- Push-pull outputs
- Supply operation from 2.2 to 5 V

Typical application schematic for fault detection using a non-inverting comparator, with hysteresis



MAIN APPLICATIONS



Wireless battery charger transmitters



Server/Telecom



Solar



UPS



Lighting




Factory automation

BATTERY MANAGEMENT ICs

Battery chargers and battery monitoring ICs

ST's **battery chargers** are specifically designed for the portable and mobile markets, and add value to new designs by minimizing power consumption and reducing the space on the PCB. These products offer charge currents from as little as 40 mA up to 1.2 A and can be used for any rechargeable lithium-ion and Li-Polymer battery. Using very simple topologies, some of these devices also feature a power-path function offering instant-on operation and thermal regulation according to the JEITA international standard.

Battery chargers



- STBC02/STBC03**
- Embed a linear battery charger, a 150 mA LDO, 2 SPDT load switches and a protection circuit module
 - STBC02 embeds a smart reset/watchdog and a single wire interface for IC control
 - Use a CC/CV algorithm with programmable (only STBC02) fast charge, precharge and termination current

- STBC15**
- Microbatteries charging and monitoring circuit
 - Charging current up to 40 mA (set by dedicated pin)
 - 150 nA quiescent current

ST's **battery fuel gauge ICs** can be located in the battery pack or in the handheld device and integrate functions to monitor the battery voltage, current and temperature. Using a built-in Coulomb counter, these fuel gauge ICs calculate battery charge and store the data in 16-bit register resolution for retrieval by the system controller. Access is via an industry-standard I2C interface, enabling the controller to create an accurate graphical representation of the remaining battery-operating time.

- STC3115**
- OptimGauge™ algorithm for STC3115
 - OptimGauge+™ algorithm for SCT3117
- STC3117**
- Coulomb counter and voltage gas gauge operations
 - Programmable low battery alarm
 - Internal temperature sensor

FUEL GAUGE ICs MAIN BENEFITS

- 3 % accuracy of battery state of charge no need for shunt resistor
- Accurate estimation of battery state of charge at power-up
- Reliable battery swap detection
- SoH and impedance tracking with OptimGauge+ algorithm (ST IP)
- Charger enable and system reset control for accurate OCV reading

MAIN APPLICATIONS



Bluetooth accessories
STC4054



USB
L6924U, STC4054,
STBCFG01



Fitness
STNS01, STBC02, sSTBC03



Smartphones
STBCFG01, STC3115,
SCT3117

Wireless charging ICs

ST fully covers wireless charging applications with **dedicated ICs for both transmitter and receiver**. The STWBC, STWBC-EP and STWBC-MC, compatible with Qi standard, and the STWBC-WA, dedicated to wearable applications, make-up ST's wireless power transmitters (Tx) family. The receiver family (Rx) consists of the STWLC68 dedicated to Qi compliant consumer applications.

Wireless power transmitters



STWBC

- Supports applications up to 5 W
- Qi A11 certified

STWBC-WA

- Supports applications up to 2.5 W
- Wireless power transmitter dedicated to wearables

STWBC-EP

- Supports application up to 15 W
- Qi extended power certified

STWBC-MC

- Support multi-coil applications up to 15 W
- Qi extended power certified

Common features


- Digital feedback with foreign object detection (FOD)
- Smart standby (best in class consumption)
- GUI for configuration and run-time analysis
- Firmware customization via API

Wireless power receivers

STWLC68

STWLC68

- Qi 1.2.4 compliant
- Supports 20 W Rx in proprietary mode
- Supports up to 7.5W Tx (dependant on coil)
- Industry leading efficiency
- Accurate voltage and current measurements for FOD
- Robust device protection from over-voltage events



MAIN APPLICATIONS



Wireless battery charger transmitters
STWBC, STWBC-EP, STWBC-MC



Tablets and smartphones
STWLC68




Wearables
STWBC-WA

DC-DC SWITCHING CONVERSION ICS


DC-DC converters

ST offers a wide portfolio of monolithic **DC-DC switching converters** (i.e. controller and MOSFET in the same package). This broad portfolio of ICs is composed of highly-specialized products to meet every market requirement. High reliability and robustness for industrial (factory automation, UPS, solar, home appliances, lighting, etc.) and other high-voltage applications. High efficiency at any load and a high level of performance for consumer (smartphones, digital cameras, portable fitness devices, LED TVs, set top boxes, Blue-ray players, computer & storage, etc) and server/telecom applications.




DC-DC CONVERTERS MAIN FEATURES

- Up to 61 VIN/3 A
- Synchronization capability
- Internal compensation
- Low consumption
- Adjustable fsw
- Internal soft start
- Low quiescent current



MAIN APPLICATIONS



www.st.com/dc-dc-switching-converters


Note: * is used as a wildcard character for related part number

DC-DC controllers

ST offers a wide portfolio of **DC-DC switching controllers** for server and telecom applications according to market requirements: single-phase controllers with embedded drivers, advanced single-phase controllers with embedded non-volatile memory (NVM), and our newest controllers with or without SPS (Smart Power Stage) compatibility as well as multiphase digital controllers for CPU & DDR memory power supplies.


Single-phase Buck controllers

- L672*** Single-phase cost effective PWM controller
- L673*** Single-phase PWM controller with embedded driver and light load efficiency optimization
- PM6697** Analog single-phase controller with SVID with embedded gate driver
- PM6680** Dual-output PWM controller up to 36Vin



Multi-phase Buck controllers

- PM676*** Fully digital buck controller with PMBus for CPU/DDR
- PM677*** Fully digital buck controller with PMBus for advanced CPU/DDR



MAIN APPLICATIONS



www.st.com/dc-dc-switching-converters
www.st.com/single-phase-controllers
www.st.com/multi-phase-controllers

Note: * is used as a wildcard character for related part number

DIGITAL POWER CONTROLLERS AND MICROCONTROLLERS

Digital power controllers

ST offers a number of advanced digital controllers, featuring innovative solutions to optimize converter efficiency in a wide range of load conditions (especially at light loads) and to have more flexibility. ST offers two main digital controller families tailored for specific applications: **STLUX** for lighting and **STNRG** for power conversion. In STLUX and STNRG families, the innovative SMED (state machine, event-driven) digital technology and the integrated microcontroller make STLUX and STNRG easily programmable and versatile. SMED is a hardware state machine triggered by internal or external events.

Digital controllers tailored for power conversion and lighting applications

STNRG*

- Common features
- Innovative digital control technique based on 6 programmable SMEDs with max PWM resolution of 1.3 ns
- Customizable algorithm for higher conversion efficiency
- Internal 96 MHz PLL
- Operating temperature -40 to 105°C
- Serial, I2C and GPIO interfaces

STNRG*

- Digital controller tailored for power conversion
- Up to 4 comparators with external reference


STLUX*

- Digital controller tailored for lighting applications
- Suitable for primary-side regulation and multi-strings lighting applications
- DALI 2.0 for remote control and connectivity

Digital controller for interleaved CCM boost PFC

STNRGPF01 STNRGPF02 STNRGPF12

- Digital controller fully configurable through GUI for fast and easy design, does not require writing any firmware
- Mixed signal architecture
- 3-channel interleaved boost PFC (STNRGPF01)
- 2-channel interleaved boost PFC (STNRGPF02 and STNRGPF12)
- Inrush current limiter (digital with STNRGPF12, mechanical with STNRGPF02)
- Ideal for wide power range above 500 W
- Reduced EMI filter and inductor volume
- Reduced output capacitor RMS current
- Flexible working frequency up to 300 kHz to drive both MOSFETs and IGBTs
- Configurable phase shedding for wide load range high efficiency conversion
- Programmable fast overcurrent and thermal protection (STNRGPF02 and STNRGPF12)
- On-chip UART/I2C digital interfaces for convenient connectivity
- Ideal for outdoor applications with -40 to +105 °C operating range



STNRG* internal block diagram

MAIN APPLICATIONS



www.st.com/stlux
www.st.com/stnrg

Note: * is used as a wildcard character for related part number

Microcontrollers for digital power

The **32-bit microcontrollers** most suitable for power management applications are the STM32F334 and the STM32G474 MCU from the mixed-signal **STM32F3 series** and **STM32G4 series**, the STM32H743 MCU from the high performance **STM32H7 series** and those of the entry-level **STM32G0 series**.

The STM32G0 series has a 32-bit ARM® Cortex®-M0+ core (with MPU) running at 64 MHz and is particularly well suited for cost-sensitive applications. STM32G0 MCUs combine real-time performance, low-power operation, and the advanced architecture and peripherals of the STM32 platform.

The STM32F3 series MCU combines a 32-bit ARM® Cortex®-M4 core (with FPU and DSP instructions) running at 72 MHz with a high-resolution timer and complex waveform builder plus event handler.

The STM32G4 series and his 32-bit ARM® Cortex®-M4+ core running at 170 MHz is in the continuity of STM32F3 series, keeping leadership in analogue leading to cost reduction at the application level and a simplification of the application design, he explores new segments and applications.

Finally, the STM32H7 series has a 32-bit ARM® Cortex®-M7 running at 480 Mhz with precision FPU, DSP and advanced MPU.

These MCU specifically address digital power conversion applications such as digital switched-mode power supplies, lighting, welding, solar, wireless charging, motor control and way more.

STM32G0

- Cortex®-M0 core
- Very low power consumption
- Timer frequency up to 128 Mhz resolution (8ns)
- High-speed ADCs for precise and accurate control
- More RAM for Flash: up to 36 KB SRAM for 128 KB and 64 KB Flash memory

STM32F334

- Cortex®-M4 core
- High resolution timer V1 (217ps resolution) with waveform builder and event handler
- 12-bit ADCs up 2.5 Msps conversion time
- Built-in analog peripherals for signal conditioning and protection (25ns from fault input to PWM stop)

STM32G474

- Cortex®-M4+ core
- High resolution timer V2 (184ps resolution) with waveform builder and event handler
- Mathematical accelerator, digital smps and power factor correction
- High-speed ADCs for precise and accurate control (4Msps)
- Dual bank flash for live upgrade

STM32H743

- Cortex®-M7 core
- High performance up to 480 MHz
- High resolution timer V1 (2.1ns resolution) for real time control
- High-speed ADCs for precise and accurate control (3.6 Msps)


STM32G474 block diagram

Connectivity 4x SPI, 4x I ² C, 6x UxART 1x USB 2.0 FS, 1x USB-C PD3.0 (+PHY) 3x CAN-FD 2x I ² S half duplex, SAI	Arm® Cortex®-M4 Up to 170 MHz 213 DMIPS	Timers 5x 16-bit timers 2x 16-bit basic timers 3x 16-bit advanced motor control timers 2x 32-bit timers 1x 16-bit LP timer 1x HR timer (D-Power) 12-channel w/ 184ps (A. delay line)
External interface FSMC 8-/16-bit (TFT-LCD, SRAM, NOR, NAND) Quad SPI	Floating Point Unit Memory Protection Unit Embedded Trace Macrocell	Analog 5x 12-bit ADC w/ HW overspl 7x Comparators 7x DAC (3x buff + 4x non-buff) 6x op-amps (PGA) 1x temperature sensor Internal voltage reference
Accelerators ART Accelerator™ 32-Kbyte CCM-SRAM	16-channel DMA + MUX Up to 2x 256-Kbyte Flash memory / ECC Dual Bank 96-Kbyte SRAM	
Math Accelerators Cordic (trigo...) Filtering		

Digital Power Supply and PFC Design Workshop with STM32 MCUs in collaboration with the company partner Biricha



MAIN APPLICATIONS



www.st.com/stm32

Automotive microcontrollers for in-car digital power


SPC5 automotive microcontrollers family are suited for in-car digital power applications such as traction inverters, on-board chargers, bidirectional DC/DC as well as Battery Management Systems.

SPC58 E-line combines real-time behavior with ISO26262 ASIL-D safety.


The embedded hardware security module (HSM) ensures protection against cyber security attacks.

The Generic Time Module (GTM) completes the peripheral set by delivering a high-performance timer, synchronization units, embedded hardware DPLL and micro-cores.








SPC58 Chorus family provides a connected, secure and scalable platform delivering a wide range of communication interfaces and low-power capabilities to complete the in-car connectivity needs.

 SPC5	SPC58 E Line
Core	Triple 3x e200z4d @ 180 MHz
eFlash Code	4 MB to 6 MB
Timers	GTM3
Safety	ASIL-D
Advanced Networking	8x CAN-FD FlexRay 2x Ethernet
Security	HSM medium
ADC	5x 12 bit (SAR) 3x 10 bit (SAR) 6x 16 bit (SigmaDelta)
High Temperature support (165 Tj)	Qualified

ST offers a complete ecosystem rich of partners, discovery tools, and the free to download SPC5-Studio IDE containing all peripherals drivers and graphical interface for configuration.




MAIN APPLICATIONS


-  Vehicle Security
-  Software over-the-air
-  Parking Services
-  Remote Assistance
-  Maintenance free
-  Safety
-  HEV

www.st.com/spc5

Package Options




eTQFP 64-176
(exposed pad)




QFN 48
(exposed pad)


Networking




ETHERNET



lin
LOCAL INTERCONNECT NETWORK



CAN^{FD}




FlexRayTM


Scalability

Up to:
3 cores, 200 MHz, 10 MB flash


Secure & Safety




ASIL
D



Evita
Medium/Full



HIS
Hardware/Software




ISO 26262

DIODES AND RECTIFIERS

ST's **Schottky** and **Ultrafast** diode portfolio includes 650 to 1200 V SiC and 45 to 100 V field-effect rectifier diodes (**FERD**) ensuring that designers can take advantage of the very latest technologies to develop cost-efficient, high-efficiency converter/inverter solutions. Depending on the targeted application and its voltage, developers can choose from a wide range of devices to ensure the best compromise in terms of forward voltage drop (VF) and leakage current (IR) as well as other characteristics.

 **AEC-Q101 automotive-grade qualified diodes and rectifiers** >



Field-effect rectifiers (FERD)

FERD*

Low voltage diodes, for high efficiency and high power density applications

Power Schottky diodes

STPS*


Power Schottky diodes for low voltage general purpose applications

Ultrafast rectifiers

STTH*

Ultrafast high voltage diodes for general purpose application

MAIN APPLICATIONS



www.st.com/schottky
www.st.com/ultrafast-rectifiers
www.st.com/field-effect-rectifier-diodes


Note: * is used as a wildcard character for related part number

SiC diodes

In addition to ensuring compliance with today's most stringent energy efficiency regulations (Energy Star, 80Plus, and European Efficiency), ST's **silicon-carbide** diodes show four times better dynamic characteristics with 15% less forward voltage (VF) than standard silicon diodes. Silicon-carbide diodes belong to our STPOWER™ family.

The efficiency and robustness of solar inverters, motor drives, uninterruptible power supplies and circuits in electrical vehicles are therefore greatly improved by the use of silicon-carbide (SiC) diodes.

ST proposes a 600 to 1200 V range with single and dual diodes encapsulated in package sizes from DPAK to TO-247, including the ceramic insulated TO-220 as well as the slim and compact PowerFLAT™ 8x8 featuring an excellent thermal performance, the new standard for high-voltage (HV) surface-mount (SMD) packages and available for 650 V SiC Diodes from 4 A to 10 A.



SiC diodes provide zero recovery time with negligible switching losses

SIC DIODES BENEFITS

- High efficiency adding value to the power converter
- Reduced size and cost of the power converter
- Low EMC impact, simplifying certification and speeding time to market
- High robustness ensuring high reliability of the power converter
- Gain on PCB and mounting cost with the dual diodes

650 V SiC diodes in insulated TO-220 packages: the solution to speed production

STPSC*065

STPSC*H12

- 650V (STPSCx065)
- 1200V (STPSC*H12)
- 2 available trade-offs, low VF and High surge

MAIN APPLICATIONS



www.st.com/sic-diodes


Note: * is used as a wildcard character for related part number

HOT-SWAP POWER MANAGEMENT

eFuses

eFuses are electronic fuses that can replace larger conventional fuses or other protection, reducing ownership costs in production and in the field.


Unlike fuses, they offer complete and flexible management of the fault (overcurrent/overvoltage), without requiring replacement after actuation. They thus help to improve equipment uptime and availability and also reduce maintenance costs and false returns. Compared to traditional protection devices, these new electronic fuses enable versatile and simple programming of protection parameters, such as overcurrent threshold and start-up time.



eFuse MAIN FEATURES

- Do not degrade or require replacement after a trip event
- Programmable over-current protection and turn-on time
- Latched or autoretry function
- Overvoltage clamp
- Over-temperature protection
- Integrated power device
- Internal undervoltage lockout

eFuses, a smart offer for a lots applications



MAIN APPLICATIONS



Home appliances
STEF05, STEF01,
STEF12, STEF12S




Server and Data Storage
STEF033, STEF05,
STEF05L, STEF4S,
STEF12, STEF05S,
STEF12S, STEF12H60



USB connections
STEF05, STEF05L,
STEF05S



Factory automation
STEF01,
STEF12, STEF12S



Set-top boxes
STEF12,
STEF12S

www.st.com/efuse

Power breakers

Connected in series to the power rail, ST's **power breakers** are able to disconnect the electronic circuitry if power consumption exceeds the programmed limit. When this happens, the device automatically opens the integrated power switch, disconnecting the load, and notifies the remote monitoring feature.

STMicroelectronics' STPW programmable electronic power breaker family provides a convenient, integrated solution for quickly and safely disconnecting a faulty load from a 12 V bus.


Inserted between the power rail and the load, the STPW power breakers contain a low-resistance (50 mΩ) power switch and precision circuitry for sensing the load power. If the user-programmed limit is exceeded, the switch turns off and a signal on the dedicated monitor/fault pin informs the host system. In normal operation, this output presents an analog voltage proportional to the load power to permit continuous monitoring.

Also featuring built-in auto-restart after a user-adjustable delay, and programmable PWM masking time to prevent protection triggering by inrush current, the STPW family simplifies design for safety and eases certification to standards such as the UL 60730 specifications for abnormal operation. This integrated solution effectively replaces discrete circuitry or a combination of ICs such as a current-sense amplifier or a hot-swap controller plus MOSFET switches, by offering improved accuracy and saving board space and bill of materials for each load protected.


Power breakers

STPW12

- Auto-retry function with programmable delay
- Adjustable precise power limitation from 11 to 16 W
- 12 V rails
- Programmable power limit masking time
- Over-temperature protection
- Integrated N-channel power MOSFET
- Internal undervoltage lockout



Typical home appliance block diagram for STPW12



MAIN APPLICATIONS



Home appliances
STPW12



Air conditioning
STPW12



Factory automation
STPW12

IGBTs

ST offers a comprehensive portfolio of **IGBTs (Insulated Gate Bipolar Transistors)** ranging from 600 to 1250 V in trench-gate field-stop (TFS) technologies.

Featuring an optimal trade-off between switching performance and on-state behavior (variant), ST's IGBTs are suitable for industrial and automotive segments in applications such as general-purpose inverters, motor control, home appliances, HVAC, UPS/SMPS, welding equipment, induction heating, solar inverters, traction inverters, on-board chargers & fast chargers.

Breakdown Voltage									
600 V		650 V				1200 V		1250 V	
Current									
5 to 20 A	20 to 80 A	4 to 200 A	20 to 80 A	15 to 100 A	20 to 50 A	15 to 75 A	8 to 75 A	15 to 40 A	20 A, 30 A
Switching frequency									
8 to 30 kHz	50 to 100 kHz	2 to 20 kHz	16 to 60 kHz			Up to 8 kHz	2 to 20 kHz	20 to 100 kHz	16 to 60 kHz
IGBT Series									
H	V	M	HB	HB2	IH	S	M	H	IH
Focus Applications									
Home appliances (fans, pumps, washing machines and dryers)	Welding, high frequency converters PFC, solar, UPS, charger	Industrial motor control, automotive traction inverter, GPI, Air-Con	High frequency converters, PFC, solar, UPS, charger, welding, induction heating and soft switching	Induction heating and soft switching	Industrial motor control, GPI, Air-Con	PFC, welding, high frequency converters, solar, UPS, charger	Induction heating, microwave and soft switching		

H series

STG*H*

600 V family

- 3 μ s of short-circuit capability
- Low saturation voltage
- Minimal collector turn-off
- Series optimized for home appliance applications

1200 V family

- 5 μ s of short-circuit capability @ starting $T_J = 150^\circ\text{C}$
- Low turn-off losses
- Up to 100 kHz as switching frequency

V series

STG*V60*F

High fsw series

- Negligible current tail at turn-off
- Very low turn-off switching losses
- Soft and very fast recovery antiparallel diode
- Up to 100 kHz in hard switching topologies
- AEC-Q101 qualified device

M series

STG*M*

650 V family

- 6 μ s of min short-circuit capability @ starting $T_J = 150^\circ\text{C}$
- Wide safe operating area (SOA)
- Very soft and fast recovery antiparallel diode
- Suitable for any inverter system up to 20 kHz
- AEC-Q101 qualified devices

1200 V family

- 10 μ s of min short-circuit capability @ starting $T_J = 150^\circ\text{C}$
- Freewheeling diode tailored for target application
- Suitable for any inverter system up to 20 kHz

HB series

STG*H*B

- Low saturation voltage
- Minimal tail current turn-off
- Different diode option
- Optimum trade-off between conduction and switching losses
- Low thermal resistance
- 4 leads package available
- Very high robustness in final application
- Automotive eligible

HB2 series

STG*H*FB2

- Very low saturation voltage
- Reduced gate charge
- Different diode option
- Optimum trade-off between conduction and switching losses
- Low thermal resistance
- 4 leads package available
- High efficiency in final application
- Automotive eligible

IH series

STG*IH*

650 V family

- Very low VCE(sat): 1.5 V @ ICN
- Very low Eoff
- Low drop forward voltage diode
- Designed for soft commutation application only

1250 V family

- Minimized tail current
- Very low drop freewheeling diode
- Tailored for single-switch topology

S series

STG*S120DF3

- 10 μ s of short-circuit capability @ starting $T_J = 150^\circ\text{C}$
- Wide safe operating area (SOA)
- Soft and fast recovery antiparallel diode
- Low drop series: very low VCE(sat)
- Suitable for very low frequency application, up to 8 kHz

MAIN APPLICATIONS



Welding



Solar



UPS



Home appliances



Air conditioning



Motor control



Induction heating

Note: * is used as a wildcard character for related part number

www.st.com/igbt

INTELLIGENT POWER MODULE - SLLIMM™




The **SLLIMM**, small low-loss intelligent molded module, is the ST's family of compact, high efficiency, dual-in-line **intelligent power modules (IPM)**, with optional extra features. This family includes different solutions in terms of package (SMD, through hole, full molded and DBC) and silicon technology (IGBT, MOSFET and Super Junction MOSFET). Optimally balancing conduction and switching energy with an outstanding robustness and EMI behavior makes the new products ideal to enhance the efficiency of compressors, pumps, fans and any motor drives working up to 20 kHz in hard switching circuitries and for an application power range from 10 W to 3 KW.

KEY FEATURES


- 600 V, IGBT based from 3 A to 35 A DC rating at 25 °C
- 600 V, Super Junction Mosfet based from 3 A to 15 A DC rating at 25 °C
- 500 V, MOSFET based, 1 A and 2 A DC rating at 25 °C
- Low VCE(sat), Low RDS(on)
- Optimize driver and silicon for low EMI
- Lowest Rth value on the market for the DBC package versions
- Internal bootstrap diode
- Maximum junction temperature: 175 °C for IGBT and 150 °C for SJ-MOSFET
- Separate open emitter outputs
- NTC on board
- Integrated temperature sensor
- Comparator for fault protection
- Shutdown input/fault output
- Isolation rating of 1500 Vrms/min

KEY BENEFITS

- Easy to drive through microcontroller
- Higher robustness and reliability
- Plug'n Play solution

SLLIMM nano series	SLLIMM nano 2 nd series	SLLIMM 2 nd series
600 V IGBT 500 V MOSFET 1 up to 3 A	600 V IGBT 600 V SJ-MOSFET 3 up to 8 A	600 V IGBT 600 V SJ-MOSFET 8 up to 35 A
		
NDIP (TH) NSDIP (SMD) 12.45 x 29.15 x 3.10 mm	N2DIP (TH) 12.45 x 32.15 x 4.10 mm	SDIP2F-26L SDIP2B-26L 24 x 38 x 3.5 mm
10 W	100 W	500 W 3000 W Power


MAIN APPLICATIONS



www.st.com/igbt

INTELLIGENT POWER SWITCHES


STMicroelectronics offers **intelligent power switches (IPS)** for low- and high-side configurations. ST's IPS feature a supply voltage range from 6 to 60 V, overload and short-circuit protection, current limitation set for industrial applications, different diagnostic types, high-burst, surge and ESD immunity, very low power dissipation and fast demagnetization of inductive loads. Devices are designed using ST's latest technologies, thus offering state-of-the-art solutions in any application field.



IPS MAIN FEATURES

- Logic
- Driving
- Protections
- Diagnostic
- Power stage
- ...all on a single chip

Output Current/Channel (A)



Note 1: low side switch 2: isolated

MAIN APPLICATIONS




www.st.com/ips

LED DRIVERS

Offline LED drivers

Dedicated **LED drivers** operating from the AC mains ensure highly-accurate LEDs control to provide a high level of light quality and avoid flickering. By combining a state-of-the-art low-voltage technology for the controller and an extremely robust 800 V technology for the power MOSFET in the same package, HVLED8* converters (i.e controller + MOSFET in the same package) feature an efficient, compact and cost-effective solution to drive LEDs directly from the rectified mains. This family of converters works in constant-current / constant-voltage primary-side regulation (PSR-CC/CV). HVLED001A and HVLED001B controllers are also available for high power needs working in constant-voltage (PSR-CV) primary-side regulation; a dimming function is also available. For both families (HVLED converters and controllers), the primary-side regulation cuts bill-of-material costs, while also simplifying design and reducing the space occupied by LED control circuitry.

Offline LED converters with PSR




Offline LED controllers with PSR



Offline LED controllers



Topology example



MAIN APPLICATIONS

Residential lighting
HVLED815PF

Commercial and street lighting
HVLED001A, HVLED001B, HVLED007

Note: * output power for european input voltage 230 Vac

www.st.com/led


DC-DC LED drivers

ST's monolithic buck switching regulators offer input voltage capability up to 61 V and deliver output currents up to 4 A with high switching frequency. They enable simple, efficient and cost-effective solutions for driving high-brightness LEDs. They also feature dedicated circuitry for dimming. Boost regulators provide the necessary high voltages to drive multiple LEDs in series, guaranteeing accurate LED current matching.


DC-DC LED drivers converters



DC-DC LED drivers controllers



Topology examples



MAIN APPLICATIONS

Halogen bulbs replacements and home appliances
LED5000, LED6000

Traffic signals
LED2000, LED2001, ST1CC40, LED5000, LED6000

Street lighting
LED5000, LED6000, HVLED002


Emergency lighting
LED6001, ST1CC40

Commercial and architectural lighting
LED5000, LED6000, LED6001, HVLED002

www.st.com/led

LED array drivers

ST's **LED array drivers** fully integrate all functions required to drive high-brightness LEDs. These devices allow constant-current control in a single-chip solution. The external parts are reduced to only one resistor that sets the preferred maximum current for all outputs. Devices also come with additional features such as high current, high precision, local and global LED brightness adjustment, thermal shutdown, error detection and auto power-saving functionalities.



24 channel RGB (8x3) drivers

- Current gain control (LED2472G), constant current (STP24DP05)
- Error detection
- Autopower saving (LED2472G)

12/16 channel drivers

- Current gain control (LED1642GW), constant current (STP16C*/D*)
- Error detection (STP16C*/D*)
- Dot correction (LED1202)
- Autopower saving
- Local dimming (LED1642GW, LED1202), global dimming (STP16C*/D*)

4/8 channel drivers

- Constant current
- Direct I/O (LED8102S)
- Error detection (STP08)
- Global dimming

MAIN APPLICATIONS



Traffic signals

LED8102S, LED2472G, STP24DP05, STP04



Large panel signs

LED1642GW, LED2472G, STP24DP05, STP16, STP08



Home appliances

LED8102S, STP16, STP08, LED1642GW, STP4CMP



Special lighting

STP04, LED1642GW, LED2472G, LED8102S



Wearable/
High End consumer
LED1202

LED row drivers


LED row drivers are essentially boost regulators that provide the necessary high voltages to drive multiple LEDs in series, guaranteeing accurate LED current matching.

ST offers both single- and multi-channel high-efficiency boost LED drivers featuring a wide dimming range, low noise and small footprint. They also embed protection functions such as overvoltage and overcurrent protection, thermal shutdown and LED-array protection.

LED row driver converters


Rows	Model	Current
6 rows	LED7707	• 85 mA/row
	LED7706	• 30 mA/row
1 row	STLA02*	• 20 mA/row
	STLD40D	• 0.5 A/1.5 A/2 A/row
	STCS*	• 0.5 A/1.5 A/2 A/row

Global dimming




LED row driver controllers

Rows	Model	Current	Feature
16 rows	LED7708	• 85 mA/row	• Grouped or independent row dimming



LED matrix driver

Matrix	Model	Current	Feature
5 x 24	STLED524	• 20 mA/dot	• Adjustable luminance for each LED (dot)



MAIN APPLICATIONS



Smartphones
STLED25, STLD40D



Keyboard and accessories
STLA02*



Home appliances and ATMs
LED7706, LED7707, LED7708, STCS*




Wearables
STLED524

Note: * is used as a wildcard character for related part number

Note: * is used as a wildcard character for related part number

LED bypass protection


The **LBP01 series** of LED bypass protection devices are bypass switches that can be connected in parallel with 1 or 2 LEDs. In the event of a LED failure, this device shunts the current through other LEDs. It also provides overvoltage protection against surges as defined in IEC 61000-4-2 and IEC 61000-4-5



LBP01 get reliable your led application

LBP01


- Keep LED strings on in case of LED open mode failure
- Reduced maintenance cost
- Increase lifetime of the lighting system



MAIN APPLICATIONS



Display panels



Residential, commercial, architectural and street lighting



Emergency lighting



Traffic signals

LINEAR VOLTAGE REGULATORS

ST offers a complete portfolio of industry-standard **high-performance regulators** for both positive and negative outputs. Among our products, you can find the optimal combination of ultra-low dropout voltage (from 50 to 220 mV for 100 mA to 3 A load current) and low quiescent current - for the highest efficiency design - (from 0.3 to 20 μ A for 50 mA to 2 A) or dynamic performance for the best transient response, power supply ripple rejection (up to 92 dB at 1 kHz) and low noise (as low as 6.3 μ Vrms). All this coupled with a choice of the smallest form factor packages for size-conscious applications such as a 0.47 x 0.47 mm STSTAMP™ package.

			Ultra-low dropout	Low Iq	Low noise, high PSRR
STLQ015	LDK120/130	LD39015	●	●	●
STLQ50	LD040L	LD59030	●	●	●
ST/LDK715	LDK220	LD39020/30	●	●	●
ST1L08	LDK320	ST730/2	●	●	●
LD56100	LD56050	LD39050/100	●	●	●
LDBL20	LDCL015	LD57100	●	●	●
LDFM/LDF	LDLN015	LD39115J	●	●	●
LD59100	LDL112	LD39130S	●	●	●
STLQ020	LDL212	LD39200	●	●	●
LDLN025/30	LD59015	LD59150	●	●	●
L5050S	L5150BN	L5300GJ	●	●	●

Ultra-low dropout

- High efficiency in low-/medium-power applications
- Best cost/performance trade-off
- Large offer for lout capability and packaging

Low quiescent current Iq

- Extending battery life
- Suitable for space-constrained battery-powered applications

Low noise, high PSRR

- High signal fidelity
- Reduced size of external filter components

MAIN APPLICATIONS



Tablets, smartphones, and wearables
LD39115, LD39130, LD39020/30, ST1L08, LDBL20, LD59015, LDLN025/30, STLQ020, LD56030, LD56050, LD56100, LD57100



Healthcare
STLQ015, STLQ020, ST715, LD39130



Home appliances
LDK220/320, LDF, LDFM, LDL212, ST730/2



Automotive ADAS, ECU
LDK130, LD39100, LD59150, LD040L

LNB SUPPLIES

LNB supplies ICs

ST's **LNB (low-noise block) supply ICs** are intended for analog and digital satellite receivers, satellite TVs, satellite PC cards. These devices are monolithic voltage regulator and interface ICs specifically designed to provide the 13/18 V power supply and the 22 kHz tone signaling to the LNB downconverter in antenna dishes or to the multi-switch box.



Single tuner ICs

LNBH25S

LNBH29

LNBH30

Dual-tuner IC

LNBH26S

Main common features

- Complete interface between LNB and I2C bus
- 15 output voltage levels
- Output surge robustness up to 40 V
- P2P compatibility between single- and dual-tuner versions
- Stable with ceramic and electrolytic capacitors
- Built-in high-efficiency 12 V DC-DC converter
- Selectable output current limit by external resistor
- Compliant with main satellite-receiver output-voltage specifications
- Accurate built-in 22 kHz tone generator suits widely accepted standards
- Internal overload and over-temperature protection

MAIN APPLICATIONS



Set-top boxes and PC card satellite receiver

www.st.com/lnb-supplies


PHOTOVOLTAIC ICs

DC-DC converters with embedded MPPT algorithm


The maximum power point tracking (MPPT) algorithm maximizes the power output by photovoltaic panels according to temperature and solar irradiation conditions.

The SPV1040 is a monolithic DC-DC synchronous boost converter able to harvest the energy generated by even a single solar cell characterized by a very low output voltage. It is especially designed to work in outdoor environments with loads up to about 3 W.


The SPV1050 is an ultra-low-power battery charger and energy harvester (from photovoltaic cells or a thermo-electric generators) that guarantees a very fast charge of supercapacitors and any type of battery including thin-film solid-state batteries. It is specifically designed to work in indoor environments or with very small thermal gradients with loads up to about 350 mW.



Solar curves



Thermo-electric generator (TEG)



MAIN APPLICATIONS



Smartphones, digital cameras, and camcorders
SPV1040



Fitness, climate, home and factory automation monitoring
SPV1050


www.st.com/photovoltaic-ics
www.st.com/mppt-dcdc-converters

Note: * A CC-CV battery charger is needed to apply lithium batteries charging profile

POWER MOSFETs

High-voltage power MOSFETs

ST's **HV Power MOSFET** portfolio offers a broad range of breakdown voltages from 400 to 1500 V, with low gate charge and low on-resistance, combined with state-of-the-art packaging. ST's **MDmesh™** high-voltage MOSFETs technology has enhanced power-handling capability, resulting in high-efficiency solutions. Supporting applications for a wide voltage range such as switch mode power supplies, lighting, DC-DC converters, motor control and automotive applications, ST has the right Power MOSFET for your design.



K5 series

ST*N*K5

- Very low RDS(on)
- Small Qg and capacitance
- Small packages
- Suited for hard switching topologies

M5 series

ST*N*M5

- Extremely low RDS(on)
- High switching speed
- Suited for hard switching topologies

M2/M2-EP series

ST*N*M2

ST*N*M2-EP

- Extremely low Qg
- Optimized for light load conditions
- Tailored for high-frequency applications (M2-EP)
- Suited for hard switching & ZVS/LLC topologies

DK5 Series

ST*N*DK5

- Lowest trr @ Very High Voltage BVDSS
- High dV/dt capability
- Targeting high power 3-phases industrial equipment

M6 series

ST*N*M6

- Lower RDS(on) x area vs previous generation
- Extremely low gate charge (Qg)
- Optimized capacitances profile for better efficiency @ light load
- Optimized threshold voltage (VTH) and gate resistance (RG) values for soft switching


DM2 & DM6 series

ST*N*DM2

ST*N*DM6

- Improved trr of intrinsic diode
- High dV/dt capability
- Suited for ZVS/LLC topologies

MAIN APPLICATIONS




www.st.com/mosfet

Note: * is used as a wildcard character for related part number

Low-voltage power MOSFETs

ST's **LV Power MOSFET** portfolio offers a broad range of breakdown voltages from -100 V to 100 V, with low gate charge and low on-resistance, combined with state-of-the-art packaging.

ST's **STripFET™** low-voltage MOSFETs support a wide voltage range for synchronous rectification, UPS, motor control, SMPS, power-over-Ethernet (PoE), inverter, automotive and other applications in a wide range of miniature and high-power packages: DPAK, D2PAK, SOT-223, TO-220, TO-220FP, TO-247, PowerFLAT (5 x 6)/(3.3 x 3.3)/(2 x 2), SO-8 and SOT23-6L.



H6 series

ST*N*H6

- Very good RDS(on)
- Soft diode recovery
- Suited for OR-ing, square-wave HB, battery mgmt topologies

F6 series

ST*N*F6


- Wide voltage range
- Soft diode recovery
- Very good RDS(on)
- Suited for load-safety switch, buck and sync rectification

F7 series

ST*N*F7

- Extremely low RDS(on)
- Optimized body diode (low Qrr) and intrinsic capacitance for an excellent switching performance
- Proper Crss/Ciss ratio for best-in-class EMI performance
- Suited for flyback and sync rectification

MAIN APPLICATIONS



www.st.com/mosfet

Note: * is used as a wildcard character for related part number


SiC MOSFETs

Based on the advanced and innovative properties of wide bandgap materials, ST's **silicon carbide (SiC) MOSFETs** feature very low RDS(on) per area for the new 650 V/1200 V Gen2 product families, combined with excellent switching performance, translating into more efficient and compact designs.

ST is among the first companies to produce high-voltage SiC MOSFETs. These new families feature the industry's highest temperature rating of 200 °C for improved thermal design of power electronics systems.

Compared to silicon MOSFETs, SiC MOSFETs also feature significantly reduced switching losses with minimal variation versus the temperature. These features render the device perfectly suitable for high-efficiency and high power density applications.

ST's SiC Mosfet 650 V - Normalized $R_{DS(on)}$ vs Temperature




SIC MOSFETS MAIN BENEFITS

- Smaller form factor and higher power density
- Reduced size/cost of passive components
- Higher system efficiency
- Reduced cooling requirements and heatsink size

THROUGH-HOLE EXTENDED PACKAGE RANGE



SURFACE MOUNT EXTENDED PACKAGE RANGE



Sic mosfets, the real breakthrough in high voltage switching

SCT*N120G2*

- VBR = 1200 V (SCT*N120G2), 650 V (SCT*N65G2)
- Low power losses at high temperature
- High operating temperature capability (200 °C)

- Body diode with no recovery losses
- Low power losses at high temperatures
- Easy to drive
- Low gate charge (SCT*N65G2)




MAIN APPLICATIONS



Note 1: coming soon * is used as a wildcard character for related part number

POWER OVER ETHERNET ICs

Power over Ethernet (PoE) is a widely adopted technology used to transfer both data and electrical power over an RJ-45 cable. ST offers solutions for PoE applications on the powered devices (PD) side that integrate a standard power over Ethernet (PoE) interface and a current mode PWM controller to simplify the design of the power supply sections of all powered devices. ST's **PoE-PD ICs** are compliant with both the more recent IEEE 802.3bt specification.



PoE-PD devices

PM8803

- IEEE 802.3at PD interface
- PWM current mode controller with double gate driver
- Integrated 100 V, 0.45 W, 1 A hot-swap MOSFET
- Supports flyback, forward active clamp, and flyback with synchronous rectification topologies

PM8801

- Sleep mode with LED indicator and Maintain Power Signature
- IEEE 802.3at PD interface + PWM current mode ctrl with double gate driver
- Integrated 100 V, 0.45 W, 640 mA hot-swap MOSFET
- Supports flyback, forward active clamp, and flyback with synchronous rectification topologies

PM8800A

- IEEE 802.3af PD interface
- PWM current mode controller
- Integrated 100 V, 0.5 W, 800 mA hot-swap MOSFET
- Supports both isolated and non-isolated topologies


PM8804

- PWM current mode controller
- Double Gate Driver
- Support Isolated Active Forward Converter
- Input voltage up to 75 VDC
- Embedded start-up (20 mA)
- Slope compensation
- Programmable fixed frequency (up to 1 MHz)

PM8805

- IEEE 802.3bt PoE-PD interface
- System in Package
- Dual Active bridges
- HotSwap MOSFET
- Compact package (10 times smaller than discrete BOM) with high thermal performances
- 100 W capability

Main standards



Power over Ethernet power supply protection

PEP01-5841


- Power supply protection compliant with IEC61000-4-5 Level 2 : 1 kV
- Allow to use 100 V power Mosfet
- Stand off voltage: 58 V
- Surface mount SO-8 package

PROTECTION DEVICES

TVS

The **TVS Transient Voltage Suppressor** is an avalanche diode specially designed to clamp over voltages and dissipate high transient energy. TVS are power devices to protect applications against Electrical Over-Stress (EOS), specifically against surge events as defined by IEC 61000-4-5.


A large choice of package is available to meet application requirements.




TVS Transil series against repetitive overvoltage in high temperature conditions

TVS

- Clamping voltage characteristics defined at 25 °C, 85 °C and 125 °C
- Stand-off voltage range: from 85 V to 188 V
- Low leakage current: 0.2 µA at 25 °C
- Maximum operating junction temperatures:
 - SMB and SMC: 150 °C
 - DO-15 and DO-201: 175 °C



MOSFET Protection with TVS



MAIN APPLICATIONS




www.st.com/eos8-20-protection

ESD protection

Driven by market needs, ST's **ESD protection** devices are available as single line devices for flexibility and multi-line arrays for integration in compact application. All this devices are rated according to IEC 61000-4-2 and specific requirements, such as low capacitance and bandwidth for high speed lines.

A large choice of packages is available to meet application requirements.



Power delivery Protections

Ultimate TVS protection for USB fast-charging ports


ESDAxxP

Strong and thin protection, the ESDAxxP-1U1M series helps to stop damages due to the surge events

KEY FEATURES & BENEFITS

- Complete voltage range 5 V, 9 V, 12 V, 15 V and 20 V.
- A unique small and thin package for all the voltages (1.0 mm x 1.6 mm x 0.55 mm) minimizing the PCB area consumption.
- Highest housed 8/20µs IPP in the market, from 35 A to 120 A.

Peak pulse current performances



Stand-off voltage (V _{RM})	Protection	
	High surge current compact protection (V _{BUS})	Single and multi lines protection for MCUs Communication Channel (CC) and Side Band Use (SBU)
20 V	ESDA25P35-1U1M ESDA24P140-1U3M	ESDL20-1BF4 ESDA25W
15 V	ESDA17P100-1U2M ESDA15P50-1U1M	ESDA17P20-1U1M
9 V	ESDA13P70-1U1M	ESDL121-1BU2 ESDZV053-1BU2 ESD051-1F4
5 V	ESDA7P120-1U1M	

MAIN APPLICATIONS





Note: * is used as a wildcard character for related part number

www.st.com/esd-protection

STDRIVE MOSFET AND IGBT GATE DRIVERS

ST's **power MOSFET and IGBT gate drivers** include integrated high-voltage half-bridge, single and multiple low-voltage gate drivers. Robustness and reliability, system integration and flexibility: that's ST's gate driver offer to you. In particular the STDRIVE families L639*, L649* and STGAP series offer smart functionalities to protect and simplify application implementation and usage.



600 V gate drivers

- Half bridge
- 4 A source/sink driver high current capability (L6491)
- Integrated bootstrap diode
- Adjustable deadtime (L6494L)
- Comparator, op amp integrated, smart SD, interlocking and program. DT (L6390)
- Extended temperature range (A version)

3-Phase

- Best In Class for propagation delay 85 ns
- 200 mA/350 mA sink / source driver current capability
- Integrated bootstrap diode

Low side gate drivers

- 2 level turn-off (TD35*)
- Miller clamp (TD35*)
- Pulse trans / opto input (TD35*)
- Dual independent low side driver (PM8834)
- 4 A source/sink driver high current capability (PM8834)




Galvanically-isolated single and dual gate drivers

- Up to 6 kV isolation (STGAP2HS)
- High voltage rail up to 1.7 kV
- Up to 5 A source/sink driver current capability
- 2 Level turn-off (STGAP1AS)
- Miller clamp, negative gate supply
- Optimized for SiC MOSFET driving (STGAP2SiCS)

L6743B- 12V Half bridge gate driver

- Integrated bootstrap diode
- High frequency operation
- Enable pin
- Adaptive dead-time management
- Flexible gate-drive: 5 V to 12 V compatible
- High-impedance (HiZ) management for output stage shutdown
- Preliminary OV protection
- VFD8FN8 3 x 3 mm package

MAIN APPLICATIONS



www.st.com/stdrive

USB TYPE-C™ AND POWER DELIVERY CONTROLLERS

With an extensive technology and IPs portfolio, ST provide a range of **USB-IF certified solutions for USB type-C and Power Delivery** to support implementations in a variety of sink, source and dual role devices. From USB-Type-C interfaces and PD Controllers to Authentication, ST complements the portfolio with Power Management ICs, full range of **protection** for data and power lines protection. ST's solutions cover from **Type-C port interface ICs** to **USB PD controllers**, and offer, a wide flexibility with hard wired and MCU to fit different use cases and every power ratings.

Standalone solutions

STUSB Controllers cover power path applications with optimized partitioning from USB Type-C™ Interface for 15 W device to Power delivery PHY and BMC Driver ICs companion chip of STM32 based solution to standalone Full Hardware USB PD Controller optimized for AC adapters up to 100 W.


MCU based solutions

Our STM32 solutions will help you to manage the complexity of implementing USB Type-C™ and Power Delivery technology ensuring that your embedded application supports the latest use cases. ST ecosystem for USB Type-C™ reduces the acquisition cost of a technology that requires expertise in different areas such as connectivity, power management, data communication and authentication.

Combining middleware, configuration and debugging tools, as well as hardware development platforms, our MCU-based solutions are specifically designed to address this challenge and offer great flexibility to implement USB Type-C™ and Power Delivery (PD).

A companion Type-C Port Protection device **TCP01-M12** is proposed for advanced protection of the USB-C connector line in sink applications, such as CC and Vbus line. For source applications like power adapters, TCP02-M18 is recommended (mass-production Q4-2020). For Dual Role Port applications (DRP), TCP03-M20 is recommended (mass-production Q4-2020).

MCD Solutions Overview & Partitioning



STM32 USB PD3.0 controllers


Introduced in December 2017, **STM32G0** is the world's 1st standard USB PD 3.0 microcontroller with a UCPD interface (UCPD stands for USB-Type-C and Power Delivery).

This new IP, available in **STM32G0/G4/L5 series**, allows to develop USB-C sink, source and dual role devices in a wide range of embedded applications.

UCPD enabled STM32G0/G4/L5 provides a high flexibility to migrate embedded applications to USB-C and Power Delivery technology while managing other application environment thanks to the versatile feature set and peripherals available in a traditional MCU. UCPD is certified PD3.0 and support all new features such as C-Authentication and Programming Power Supply (PPS).

https://www.st.com/content/st_com/en/stm32-usb-c.html

STM32G081 block diagram



UCPD is a new interface that supports:

- USB Type-C connector management
- USB Power Delivery 3.0 communication protocol including C-authentication and Programming Power Supply




STM32G0 USB-C Ecosystem: for short time-to-market

Our STM32G071B-DISCO kit allows to discover and display USB-C power and feature capabilities of any USB-C compliant host.

Associated with our professional-grade STM32CubeMonitor-UCPD software GUI, the kit acts as a USB PD analyzer and allows customer to debug, configure and inject in one click USB PD3.0 packets while monitoring Vbus voltage and Ibus current between two USB-C devices.

Our well-known STM32 configurator STM32CubeMx supports easy setting of UCPD.

An evaluation board STM32G081B-eval is proposed with two USB-C ports offering 45 W of power with different profiles.

Discover and learn  STM32G071B-DISCO	Develop  NUCLEO-G071RB STM32G081B-EVAL	Configure & Debug  STM32CubeMX STM32CubeMonitor-UCPD
--	---	---


Type-C Port Protection

TCPPO1-M12

The **TCPPO1-M12** (type-C port protection) is a single chip solution for USB type-C port protection that facilitates the migration from USB legacy connectors type-A or type-B to USB type-C connectors. The TCPPO1-M12 features 22 V tolerant ESD protection as per IEC61000-4-2 Level 4 on USB type-C connector communication channel (CC) and VBUS lines. To allow fast certification for USB power delivery, the TCPPO1-M12 provides overvoltage protection on CC1 and CC2 pins when these pins are subjected to short circuit with the VBUS pin that may happen when removing the USB type-C cable from its receptacle. For sink applications, TCPPO1-M12 triggers an externally programmable N-MOSFET overvoltage protection on VBUS pin when a defective power source applies a voltage higher than selected OVP threshold. Also, the TCPPO1-M12 integrates a “dead battery” management logic that is compliant with the USB power delivery specification. The VBUS N-MOSFET load driver can also be used in source applications.

KEY FEATURES

- ESD protection for CC1, CC2 and VBUS
- Compliant with IEC 61000-4-2 Level 4 (± 8 kV contact discharge, ± 15 kV air discharge)
- Over Voltage Protection on CC lines against short-to-VBUS overvoltage
- Externally programmable Over Voltage Protection on VBUS line
- Integrated VBUS gate driver for external N-MOSFET
- Over Temperature Protection
- Integrated “Dead Battery” management
- Open-drain fault reporting
- Operating junction temperature from -40 °C to 85 °C
- ECOPACK®2 compliant




TCPPO1-M12: Protecting USB Type-C Against Damages and Serving Engineers with Efficiency



STUSB family of standalone (auto-run) USB-C and Power Delivery controllers

Being designed with ST's 20 V process technology, STUSB family is natively compliant with USB PD electrical requirements. STUSB controller ICs are certified and integrate the mandatory protection and application features for autonomous port management, without the need for external circuitry. STUSB controllers are optimized for power path applications ranging from 15W to 100W, on both SINK and SOURCE sides. Being hardwired, STUSB controllers are fast and predictive to guarantee safety and interoperability while increasing port robustness and minimizing power consumption. Implementation is fast and easy and requires no deep know how of the USB PD standard or advanced software skills. Standalone controllers are powered from VBUS to minimize BOM cost and can fully operate without external MCU support. For more flexibility, an MCU can optionally change main power parameters or read port status, with light software layer.



STUSB controllers: Main common functions

- Manage the type-C port connection
- Enable the power path (VBUS)
- Negotiate power capabilities
- Interact with the power management unit
- Monitor the power path
- Protect the port and manage re-start on fault
- Report majors events to the MCU (optional)

STUSB1600

- USB-C SOURCE / SINK / DUAL ROLE
- High Voltage protections
- Integrated VBUS discharge
- Dead battery support
- Optional interface to MCU through I2C + IRQ

STUSB1700

- USB-C SOURCE
- High Voltage protections
- GPIO-controlled current profile (Power sharing, Thermal protection)
- VBUS powered (no LDO needed)
- AEC-Q100 available

STUSB4500L

- USB-C 5V SINK
- Dead battery support
- VBUS powered (ZERO power on VBAT)
- Input Over Voltage protection
- SOURCE power budget reporting
- QFN and CSP package available

STUSB1602

- STUSB1602: SOURCE / SINK / DUAL ROLE
- STUSB1702: SOURCE – Auto Grade
- Integrated Type-C PHY + BMC coding
- Perfect MCU companion chip ensuring port protection, power path monitoring and management, role advertisement and detection, PD PHY communication

- Integrated 600 mA VCONN switch with integrated protection
- Integrated VBUS and VCONN discharge path
- I2C, SPI+ IRQ MCU interface – Dual I2C address support
- Accessory & dead battery support
- STSW-STUSB010: ready-to-use software frameworks for fast prototyping of most common application scenario such as: basic source, sink and DRP but also more complex use cases, which include optional features of PD3.0, for example VDM, extended messages.

STUSB1702

STUSB47

- USB PD SOURCE
- Offers up to 5 programmable PDOs
- Full hardware solution - no software
- Internal and/or external VBUS discharge path
- Very low power consumption
- E-marked cable identification (for >3A support)
- Over-temperature protection

STUSB4500

- Role: USB PD SINK
- Dead Battery support
- VBUS powered (ZERO power on VBAT)
- Input Over Voltage protection
- QFN and CSP package available
- SOURCE power profile reporting
- STSW-STUSB003: open source software drivers for dynamic power management

At STMicroelectronics we create technology that starts with You



life.augmented



Order code: BRPMGUIDE0720

For more information on ST products and solutions, visit www.st.com

© STMicroelectronics - July 2020 - Printed in the United Kingdom - All rights reserved
ST and the ST logo are registered and/or unregistered trademarks of STMicroelectronics International NV or its affiliates in the EU and/or elsewhere. In particular, ST and the ST logo are Registered in the US Patent and Trademark Office. For additional information about ST trademarks, please refer to www.st.com/trademarks.
All other product or service names are the property of their respective owners.



life.augmented