

# OPTIGA™ Connect IoT OC2321

## Datasheet

### Infineon eSIM IoT Solution

## Description

OPTIGA™ Connect IoT is an embedded SIM (eUICC) turnkey solution that enables cellular connectivity at scale for IoT devices.

OPTIGA™ Connect IoT consists of an eUICC including GSMA compliant eSIM operating system and pre-loaded bootstrap connectivity.



## Key Features

- Remote SIM provisioning compliant with GSMA SGP.02 V3.2
- Compliant with 2G, 3G, 4G (LTE), CDMA, NB-IoT, CAT-M networks
- Tata [1] connectivity bootstrap - worldwide coverage
- Allows to accommodate multiple MNO profiles
- OTA capable
- 32-bit architecture based on Arm® SecurCore® SC300 enhanced by Infineon Technologies' cache and security technology
- ISO/IEC 7816 UART interface
- Power Supply 1.8/3/5 Volts
- Common Criteria EAL5+ certified hardware
- VQFN-8 package (MFF2)
- Removable SIM and other packages on request

## Application

- IoT end nodes and edge gateways
- Smart Home (security, alarm, light-HVAC-Energy control)
- iHealth monitoring
- Smart City (security, lighting, parking sensor)
- Industry Automation (smart machines, security camera, factory automation, asset tracking)
- Smart Energy (metering, storage, distribution)
- Commercial telematics
- GPS Tracker

**Table of contents**

**Table of contents**

	<b>Description</b> .....	1
	<b>Key Features</b> .....	1
	<b>Application</b> .....	1
	<b>Table of contents</b> .....	2
<b>1</b>	<b>General Description</b> .....	4
1.1	Operating system features .....	4
1.1.1	Hardware features .....	4
1.1.2	Software features .....	4
1.1.3	Communications .....	5
1.2	Authentication algorithms .....	5
1.3	Remote SIM provisioning (RSP) .....	5
1.4	Over The Air (OTA) functionality .....	6
1.5	Memory Management .....	6
1.6	Countries .....	7
<b>2</b>	<b>System integration</b> .....	8
2.1	General requirements for Cellular Modem .....	8
2.1.1	Supported network access technologies .....	8
2.1.2	Support TCP/UDP and BIP (Bearer Independent Protocol) .....	8
2.1.3	Network connection control modem requirements .....	9
2.1.4	SMS support .....	9
2.1.5	Additional modem requirements .....	9
2.2	Device IMEI .....	9
2.3	OPTIGA™ Connect IoT pin code .....	10
2.4	How to retrieve the OPTIGA™ Connect IoT identifier using AT commands .....	10
2.5	APN configuration .....	10
2.6	VPN .....	10
<b>3</b>	<b>Design-in</b> .....	11
3.1	Power supply schematic .....	11
3.2	Interface ISO/IEC 7816-3 .....	11
<b>4</b>	<b>Electrical Characteristics</b> .....	12
4.1	Absolute maximum ratings .....	12
4.2	Operational characteristics .....	13
4.2.1	DC electrical characteristics .....	13
4.2.2	AC electrical characteristics .....	13
4.2.2.1	Power-Up Considerations .....	14
4.3	Interface Characteristics .....	15
4.3.1	Interface characteristics (compliant to ETSI TS 102 221) .....	15

---

**Table of contents**

<b>5</b>	<b>Description of delivery forms</b> .....	17
5.1	External connectivity .....	17
5.2	SMD package .....	19
5.2.1	PG-VQFN-8-4 (MFF2) .....	19
<b>6</b>	<b>Ordering information</b> .....	22
	<b>Terminology</b> .....	23
	<b>References</b> .....	25
	<b>Revision history</b> .....	26
	<b>RoHS compliance</b> .....	27
	<b>Disclaimer</b> .....	28

**1 General Description**

**1 General Description**

The product described along this document, contains some solutions and applications developed in response to the mobile network operator needs and the different market requirements.

**1.1 Operating system features**

**1.1.1 Hardware features**

**Table 1 Hardware features**

<b>Device</b>	<b>SLM97CNFX1M00PE</b>
FLASH	1024 K
RAM	32 K
Voltage	1.8V, 3V, 5V
32-bit CPU	based on ARM SecurCore SC300
Internal clock	up to 44 MHz
External clock	from 1 MHz to 10 MHz
Operating supply voltage	1.62V – 5.5V
Operating temperature range	- 40°C to + 105°C
Data retention	Min. 10 years
Erase/Write cycles	Min. 500.000
I/O	ISO 7816-3 (T=0)
I/O speed	8, 16, 31, 32, 64, 186, 372 clocks per ETU

**1.1.2 Software features**

According to GSMA SGP.02: Remote Provisioning Architecture for embedded UICC. Technical Specification, Version 3.2.

- Java Card (TM) V3.0.5, Global Platform V2.3
- SIM Alliance Interoperable format V2.0; V2.1
- Compliant with 2G, 3G, 4G (LTE), CDMA, - NB-IoT, CAT-M networks
- ETSI, 3GPP rel 12 compliant
- Pre-enabled Bootstrap connectivity profile
- Fall back as an option
- Storage of up to 10 eSIM profiles
- SIM, UICC, USIM, ISIM functionality
- Support of CAT, SAT, USAT, OTA, CAT-TP, EAP
- DNS resolver, TLS key derivation
- Supported Crypto algorithms SHA, DES, AES, ECC, RSA

---

## **1 General Description**

### **1.1.3 Communications**

- 11h (D=1, F=372)
- 12h (D=2, F=372)
- 18h (D=12, F=372)
- 94h (D=8, F=512)
- 95h (D=16, F=512)
- 96h (D=32, F=512)
- 97h (D=64, F=512)

### **1.2 Authentication algorithms**

- COMP128\_2
- COMP128\_3
- MILENAGE
- TUAK
- CAVE

### **1.3 Remote SIM provisioning (RSP)**

OPTIGA™ Connect IoT features a standard mechanism for remote profile provisioning and management, meaning you can remotely provision a SIM in form of an electrical profile, and subsequently change the subscription remotely from one operator (MNO) to another. Such an eSIM needs to be connected to an initial operator with a minimal initial profile installed during manufacturing process. This first profile is denominated Provisioning Profile or Bootstrap.

The Embedded SIMs and Remote SIM Provisioning (RSP) cannot be considered to be “Soft SIMs”. The physical hardware element is always present and adds an indispensable layer of security. A ‘Soft SIM’ would be a solution with no SIM hardware where all SIM functionality is carried out by a software layer.

Although the general perception might be that all eUICCs are MFF2-packaged and soldered onto PCBs, it is important to understand that an eUICC is neither a form factor nor a hardware concept. It’s a feature concept for the way SIM profiles are managed. All functionalities of a SIM/(U)SIM are available within an eUICC, but an eUICC is capable to host multiple profiles, one active at a time.

However, it is important to note that electrical profiles stored in an eUICC are different from each other, meaning that Applets on one profile are not available on another. The profiles are entirely independent and no data can be shared between them.

eUICCs can be deployed once, and modified indefinitely without any compromise on security.

A SM-DP (Subscription Manager Data Preparation) server manages the profile creation, storage, personalization and download and a SM-SR (Subscription Manager Secure Routing) server manages the secure routing for the profile download and activation.

There is a theoretical maximum of 10 Profiles that can be stored on an OPTIGA™ Connect IoT eUICC, practically depending on the available memory and the size of the Profiles.

OPTIGA™ Connect IoT is fully compliant to

- GSMA SGP.02: Remote Provisioning Architecture for Embedded UICC. Technical Specification, Version 3.2.
- SIMalliance: eUICC Profile Package – Interoperable Format. Technical Specification, Version 2.1.

---

## **1 General Description**

### **1.4 Over The Air (OTA) functionality**

OTA configuration has become increasingly important as new updates and services come to stream. OTA via SMS optimizes the configuration data updates in eSIMs and enables the distribution of new software updates to IoT devices with the necessary settings to access services.

OTA messaging provides remote control of IoT devices for service and subscription activation, personalization and programming of a new service for mobile operators.

- Over The Air (OTA) protocol according to ETSI 102 225 and 3GPP 31.115
- OTA mechanism supports all the UICC administrative commands as specified by ETSI TS 102 222

OPTIGA™ Connect IoT fully supports the standards for Remote Application Management (RAM) and Remote File Management (RFM).

- RFM applications compliant to ETSI 102 226 and 3GPP 31.116
- RAM conformous to ETSI 102 226 and GlobalPlatform – UICC Configuration

### **1.5 Memory Management**

The Dynamic Memory Management implemented in OPTIGA™ Connect IoT features the possibility to create and delete files avoiding any memory loss after file deletion. In the same way, the Dynamic Memory Management enables load and install of new applications onto the eSIM avoiding memory loss after deletion of applets.

The free memory in the eSIM always can be used by files, packages, applets or objects, all of them coexist in the same memory portion; and also the free memory always can be recovered on deletion operations.

As previously indicated, the operating system is Java Card based; consequently it features a garbage collector which reflects this dynamical object memory recovery mechanism.

The memory management mechanism is designed for best performance and optimum safety of the end user data

---

## **1 General Description**

### **1.6 Countries**

Tata Communications [1] powered connectivity operates in the following countries:

Afghanistan, Albania, Algeria, Andorra, Angola, Anguilla, Antigua and Barbuda, Argentina, Armenia, Aruba, Australia, Austria, Azerbaijan, Bahamas, Bahrain, Bangladesh, Barbados, Belarus, Belgium, Belize, Benin, Bermuda, Bhutan, Bolivia, Bosnia and Herzegovina, Botswana, Brazil, Brunei, Darussalam, Bulgaria, Burkina Faso, Burundi, Cambodia, Cameroon, Canada, Cape Verde, Cayman Islands, Central African Republic, Chad, Chile, China, Colombia, Congo, Democratic Republic of the Congo, Cook Islands, Costa Rica, Cote d'Ivoire, Croatia, Cuba, Cyprus, Czech Republic, Denmark, Djibouti, Dominica, Dominican Republic, East Timor, Ecuador, Egypt, El Salvador, Equatorial Guinea, Estonia, Ethiopia, Falkland Islands (Malvinas), Faroe Islands, Fiji, Finland, France, French Polynesia, Gabon, Gambia, Georgia, Germany, Ghana, Gibraltar, Greece, Greenland, Grenada, Guadeloupe, Guam, Guatemala, Guinea, Guinea-Bissau, Guyana, Haiti, Honduras, Hong Kong, Hungary, Iceland, India, Indonesia, Islamic Republic of Iran, Iraq, Ireland, Israel, Italy, Jamaica, Japan, Jordan, Kazakhstan, Kenya, Republic of Korea, Kosovo, Kuwait, Kyrgyzstan, Lao People's Democratic Republic, Latvia, Lebanon, Lesotho, Liberia, Libyan Arab Jamahiriya, Liechtenstein, Lithuania, Luxembourg, Macao, The former Yugoslav Republic of Macedonia, Madagascar, Malawi, Malaysia, Maldives, Mali, Malta, Mauritania, Mauritius, Mexico, Moldova, Monaco, Mongolia, Montenegro, Montserrat, Morocco, Mozambique, Myanmar, Namibia, Nepal, Netherlands, Netherlands Antilles, New Caledonia, New Zealand, Nicaragua, Niger, Nigeria, Non Terrestrial, Norway, Oman, Pakistan, Occupied Palestinian Territory, Panama, Papua New Guinea, Paraguay, Peru, Philippines, Poland, Portugal, Puerto Rico, Qatar, Romania, Russian Federation, Rwanda, Saint Kitts and Nevis, Saint Lucia, Saint Vincent and the Grenadines, Sao Tome and Principe, Saudi Arabia, Senegal, Serbia, Seychelles, Sierra Leone, Singapore, Slovakia, Slovenia, South Africa, South Sudan, Spain, Sri Lanka, Sudan, Sudan, Suriname, Swaziland, Sweden, Switzerland, Syrian Arab Republic, Taiwan - Province of China, Tajikistan, United Republic of Tanzania, Thailand, Togo, Trinidad and Tobago, Tunisia, Turkey, Turkmenistan, Turks and Caicos Islands, Uganda, Ukraine, United Arab Emirates, United Kingdom, United Kingdom - Channel Islands, United States of America, Uruguay, Uzbekistan, Vanuatu, Venezuela, Vietnam, Virgin Islands, British, Yemen, Zambia, Zimbabwe

**2 System integration**

**2 System integration**

**2.1 General requirements for Cellular Modem**

The eSIM remote profile management functionality uses some specific functions which need to be supported by the cellular modem. Below you'll find some guidance on the support of the different network access technologies as well as the required modem features.

**2.1.1 Supported network access technologies**

In order for our connectivity partner to administrate the OPTIGA™ Connect IoT eSIM, the modem shall support at least one of the following network access technologies: 2G, 3G, LTE/4G, 5G.

Only after a corresponding profile has been successfully loaded into the eSIM and activated, the modem device may use LTE-M or NB-IOT radio technologies if supported by the carrier.


**Attention:** *The use of LTE CAT-M and NB-IOT may prevent further remote management since SMS are usually not supported. The subscription management server may then not be able to reach the device to administrate the eSIM. Please contact our connectivity partner Tata Communications [1] for further information.*

**2.1.2 Support TCP/UDP and BIP (Bearer Independent Protocol)**

The subscription management server can use SMS, CAT\_TP and HTTPS for remote OTA communication with the eSIM.

The Bearer Independent Protocol (BIP) is a mechanism used to enable the internet protocol connectivity between the remote subscription manager server and the OPTIGA™ Connect IoT eSIM through the modem. Over that data link, two layers of bi-directional secure channels (CAT-TP and HTTPS) are established so the exchange of critical information is protected end-to-end.

In both cases, TCP and/or UDP protocols are the underlying layers between the subscription management platform and the modem but a bearer independent protocol is used for the data exchange between the modem and the eSIM as illustrated here below.



**Figure 1 Data exchange between the modem and the eSIM**

*Note:* Please note that 2 independent data channels are needed. One data channel is dedicated to the user data operation to the active MNO profile and one admin channel for the subscription management operation. The admin channel is using specific APN, IP and secure access.

In order to ensure that the OPTIGA™ Connect IoT can be remotely managed using our partner platform, please check with your modem provider how to enable BIP and that the following BIP commands are supported:

- OPEN CHANNEL (UDP and TCP over IP)



---

## **2 System integration**

- CLOSE CHANNEL
- RECEIVE DATA
- SEND DATA
- GET CHANNEL STATUS
- ENVELOPE (EVENT DOWNLOAD - Data available)
- ENVELOPE (EVENT DOWNLOAD – Channel status)

The modem may have to be reset in order for the new settings to be active.

### **2.1.3 Network connection control modem requirements**

For network connection control the modem shall also support:

- RPLMN details (LAC/TAC, NMR) to identify the most recently wireless network to which the device was successfully connected.
- Quality of service (failures, duration, power, location).
- New network selection after SIM/USIM update.

### **2.1.4 SMS support**

Because SMS are used for triggering the opening of a CAT\_TP or HTTPS session to the eSIM, the modem shall support:

- Point-to-point MO and MT SMS
- SMS cell broadcast
- Text and PDU mode

### **2.1.5 Additional modem requirements**

To guarantee a good service operation, the modem shall also support the following features:

- Basic SAT commands (TERMINAL PROFILE, FETCH, TERMINAL RESPONSE)
  - PROVIDE LOCAL INFORMATION (location information, IMEI, Network Measurement Results (NMR), date and time, access technology, at least)
  - POLL INTERVAL, POLLING OFF, TIMER MANAGEMENT [at least one timer], ENVELOPE (TIMER EXPIRATION)
  - SET UP EVENT LIST and ENVELOPE (EVENT DOWNLOAD – location status, call connected, call disconnected, Access Technology Changed, Network Rejection)
  - ENVELOPE (SMS-PP DOWNLOAD)

The modem shall support the following commands from the 3GPP TS 27.007 (Technical Specification Group Core Network and Terminals-AT command set for User Equipment (UE)- Release 9) for all generic purposes:

- AT+CRSM (Restricted SIM access)

## **2.2 Device IMEI**

The device shall contain a unique IMEI (International Mobile Equipment Identity) value compliant with the format defined in ETSI TS 123 003.

The value of IMEI shall be directly copied from TERMINAL RESPONSE of the Provide Local Information command (see ETSI TS 102 223 and ETSI TS 124 008).

---

## 2 System integration

### 2.3 OPTIGA™ Connect IoT pin code

The PIN code is disabled by default in the eSIM. It can be enabled if needed; contact Tata Communications [\[1\]](#) support for more information.

### 2.4 How to retrieve the OPTIGA™ Connect IoT identifier using AT commands

This unique identifier may be required by the connectivity provider partner to enable the eSIM on its subscription and connectivity management platform.

The device may retrieve the EID stored in the OPTIGA™ Connect IoT IC and shall then support the following commands:

- *AT+CCHO (Open Logical Channel)*
- *AT+CCHC (Close Logical Channel)*
- *AT+CGLA (Generic UICC Logical Channel Access)*

Please note that the EID number is also printed on the chip package (See [Figure 9](#))

### 2.5 APN configuration

The Access Point Name needs to be configured in the device to enable the connectivity to the internet.

Make sure that the following APN URL is properly configured in the modem:

- `move.dataxs.mobi`

Private, customized APN are available upon request. Please contact Tata Communications [\[1\]](#).

### 2.6 VPN

When enabled, the Virtual Private Network (VPN) ensures the confidentiality of the data exchanges via encryption and decryption mechanisms when connected to the internet through a public network. Please contact our partner Tata Communications [\[1\]](#) to learn more about the possible options.


**3 Design-in**

**3 Design-in**

This chapter explains the schematics of the product and gives some recommendations as to how the controller can be externally connected.


**3.1 Power supply schematic**

The following figure illustrates how the security controller is to be supplied.



**Figure 2 Power supply diagram**

**3.2 Interface ISO/IEC 7816-3**



**Figure 3 ISO/IEC 7816-3 interface schematic diagram**

The figure illustrates how the ISO/IEC 7816-3 modem is to be connected to the security controller.

**4 Electrical Characteristics**

**4 Electrical Characteristics**

This section summarizes certain electrical characteristics of the controllers. It provides operational characteristics as well as electrical DC and AC characteristics and particular interface characteristics.

Notes:

1.  $T_A$  as given for the operating temperature range of the controller unless otherwise stated.
2. All currents flowing into the controller are considered positive.

**4.1 Absolute maximum ratings**

**Table 2 Absolute maximum ratings**

Parameter	Symbol	Values			Unit	Note or test condition
		Min.	Typ.	Max.		
Supply voltage	$V_{CC}$	- 0.3	–	7.0	V	–
Input voltage	$V_{IN}$	- 0.3	–	$V_{CC} + 0.3$	V	–
Operating temperature (ambient)	$T_A$	- 40	–	105	°C	$T_J$ must be kept.
Junction temperature	$T_J$	- 40	–	110	°C	
Storage temperature	$T_S$	- 40	–	125	°C	–
Pulse voltage ESD protection of ISO pad group	$V_{ESD}$	4000	–	–	V	ISO 7816-1

Notes:

1. The values stated in the table may be further restricted for particular products (i.e. sales codes).
2. All voltages are referenced to the power supply ground in the corresponding package, unless otherwise specified.
3. Stresses exceeding the values listed under 'Absolute maximum ratings' may cause permanent damage to the device. This is a stress rating only and functional operation of the device at these or at any other conditions whose values exceed those indicated in the operational sections of this document is not implied. Exposure to absolute maximum rating conditions for extended periods may affect device reliability, including NVM data retention and write/erase endurance.

## 4 Electrical Characteristics

### 4.2 Operational characteristics

This section specifies the AC and DC characteristics of the controller, along with details relating to the specific interfaces provided by the controller.

#### 4.2.1 DC electrical characteristics

**Table 3** DC characteristics

Parameter	Symbol	Values			Unit	Note or test condition
		Min.	Typ.	Max.		
Supply voltage	$V_{CC}$	1.62	–	5.5	V	Overall functional voltage range
		4.5	5.0	5.5	V	ISO/IEC 7816-3 Class A
		2.7	3.0	3.3	V	ISO/IEC 7816-3 Class B
		1.62	1.8	1.98	V	ISO/IEC 7816-3 Class C ETSI TS 102613
		1.65	1.8	1.95	V	ISO Class C*
Supply current	$I_{CC}$	–	tbd	21	mA	$f_{SYS} = 44$ MHz
Supply current in sleep mode	$I_{CCS1}$	–	–	200	$\mu$ A	$T_A = 25^\circ\text{C}$ , $f_{UART\_CLK} = 1$ MHz; All inputs at $V_{CC}$ , No peripheral active
	$I_{CCS2}$	–	–	100	$\mu$ A	Class B / Class C $T_A = 25^\circ\text{C}$ , CLK off RNG oscillators and DCO off RST and IO at $V_{CC}$
	$I_{CCS3}$	–	–	200	$\mu$ A	$T_A = 25^\circ\text{C}$ , RNG oscillators and DCO off All inputs at $V_{CC}$ After I <sup>2</sup> C mode start-up

#### 4.2.2 AC electrical characteristics

**Table 4** AC characteristics


Parameter	Symbol	Values			Unit	Note or test condition
		Min.	Typ.	Max.		
Supply ramp-up time	$t_{VCCR}$	1 <sup>1)</sup>	-	$10^7$	$\mu$ s	0 to 100% of target supply voltage
Internal frequency	$f_{SYS}$	-	-	44 (typical)	MHz	Programmable down to 1/32. Maximum frequency is product specific

<sup>1</sup> At faster supply ramp times chip internal ESD elements temporary causing a cross current between VCC and GND larger than allowed ( $I_{CC}$ ).

**4 Electrical Characteristics**

**4.2.2.1 Power-Up Considerations**

The rampup times given in [AC electrical characteristics](#) apply under the assumption of a linear rise in voltage from 0% to 100% of the target voltage level. However, owing to possible current spike effects, it is recommended to follow the voltage characteristics shown in the figure below.



**Figure 4 Recommended power-up behavior**

## 4 Electrical Characteristics

### 4.3 Interface Characteristics

This chapter provides electrical characteristics with respect to operation of particular interfaces of the controller.

*Note: Unless otherwise stated, all values in this section are measured at the pins of the used package, i.e., the resistance, capacitance and inductance, for example, of the package and the bond wires are already included in these values!*

#### 4.3.1 Interface characteristics (compliant to ETSI TS 102 221)

The electrical characteristics of the pad described below comply with the standard ETSI TS 102 221.

Notes:

1. All currents flowing out of the pad are considered to be positive.
2. Symbol  $T_A$  describes the ambient temperature range.

**Table 5 Maximum ratings**

Parameter	Symbol	Values			Unit	Note or test condition
		Min.	Typ.	Max.		
Pad input voltage	$V_I$	-0.3		$V_{CC} + 0.3$	V	

**Table 6 DC electrical characteristics**

Parameter	Symbol	Values			Unit	Note or test condition
		Min.	Typ.	Max.		
I/O, bidirectional port	$V_{IH}$	$0.7 * V_{CC}$	-	$V_{CC} + 0.3$	V	$I_{IH} = - 20 \mu A \dots + 20 \mu A$
	$V_{IL}$	- 0.3	-	$0.2 * V_{CC}$	V	$I_{IL} = - 1 \text{ mA} \dots + 20 \mu A$
	$V_{OH}$	$0.7 * V_{CC}$	-	$V_{CC} + 0.3$	V	$I_{OH} = - 20 \mu A \dots + 20 \mu A$
I/O, bidirectional port	$V_{OL}$	0	-	0.4	V	$I_{OL} = 1 \text{ mA}$ Class A
		-	-	$0.15 * V_{CC}$	V	$I_{OL} = 1 \text{ mA}$ Class B
		-	-	$0.15 * V_{CC}$	V	$I_{OL} = 0.5 \text{ mA}$ Class C
I/O, bidirectional port	$V_{OL}$	-	-	0.4	V	$I_{OL} = -1 \text{ mA}$ Class A & B
		-	-	0.3	V	$I_{OL} = -1 \text{ mA}$ Class C
RST	$V_{IH}$	$0.8 * V_{CC}$	-	$V_{CC} + 0.3$	V	$I_{IH} = - 20 \mu A \dots + 20 \mu A$
	$V_{IL}$	- 0.3	-	$0.2 * V_{CC}$	V	$I_{IL} = - 50 \mu A \dots + 20 \mu A$
CLK	$V_{IH}$	$0.7 * V_{CC}$	-	$V_{CC} + 0.3$	V	$I_{IH} = - 20 \mu A \dots + 20 \mu A$
	$V_{IL}$	- 0.3	-	$0.2 * V_{CC}$	V	$I_{IL} = - 20 \mu A \dots + 20 \mu A$

**4 Electrical Characteristics**

**Table 7 AC electrical characteristics**

Parameter	Symbol	Values			Unit	Note or test condition
		Min.	Typ.	Max.		
<b>I/O</b>						
Rise/fall time	$t_R, t_F$	–	–	1	$\mu\text{s}$	30 pF external
Pad input capacitance	$C_{IN}$			5	pF	Bare die (no package considered)
<b>RST</b>						
Rise/fall time	$t_R, t_F$	–	–	1	$\mu\text{s}$	30 pF external
Hold time low	$t_{HR}$	80	–	–	$\mu\text{s}$	Both conditions have to be kept. External clock pulses
		400	–	–	clk	
Pad input capacitance	$C_{IN}$			2	pF	Bare die (no package considered)
<b>CLK</b>						
External frequency	$f_{CLK}$	1	–	10	MHz	@ specified duty cycle
Rise/fall time	$t_R, t_F$	–	–	$0.1 \cdot 1/f_{CLK}$	ns	$0.1 V_{CC}$ to $0.9 V_{CC} = V_T$ $0.5 V_{CC}$
Duty cycle		40	–	60	%	
Pad input capacitance	$C_{IN}$			2	pF	Bare die (no package considered)



**5 Description of delivery forms**

**5 Description of delivery forms**

This chapter provides information about available delivery forms and how the product's interfaces are assigned to the package pins.

For further information on compliance of the packages with European Parliament Directives, see [RoHS compliance](#).

For details and recommendations on the assembly of packages on PCBs, please see:

<http://www.infineon.com/cms/en/product/technology/packages>

**5.1 External connectivity**

Package pins are usually connected to a product pad and are used as inputs, outputs, or bi-directionally, depending on the available input and output stages. The abbreviations listed here are used in the package description to classify each pin.

**Table 8 Abbreviations for pin type**


Abbreviation	Description
I	Input. Digital levels
O	Output. Digital levels
I/O	I/O is a bi-directional signal
PWR	Power
GND	Ground
NC	Not connected (JEDEC Standard). May be connected externally

**Table 9 Abbreviations for buffer type**

Abbreviation	Description
ISO_I_CLK	Input pad
ISO_I	Input pad
ISO_IO	Input/output pad

**5 Description of delivery forms**

**Package layout**



**Figure 5 PG-VQFN-8-4 package layout**

**Pad-to-signal reference**

The contacts and their functionality are given in the table below.

**Table 10 Pad-to-signal reference for PG-USON-8-4**

Pin	Symbol	Pin type	Buffer type	Signal function / remarks
1	GND	(n.a.)	-	Common ground reference. All GND pins must be tied together externally
2	NC		-	
3	ISO_0	I/O	ISO_IO	ISO/IEC 7816-3: UART_IO
4	NC	-	-	
5	NC	-	-	
6	ISO_1	I	ISO_I_CLK	ISO/IEC 7816-3: UART_CLK
7	ISO_2	I	ISO_I	ISO/IEC 7816-3: UART_RST
8	V <sub>CC</sub>	(n.a.)	-	Power and pad supply (V <sub>CC</sub> )

**5 Description of delivery forms**

**5.2 SMD package**

The figures in the sections below show the following aspects of the package:


- Package outline: shows the package dimensions of the controller in the individual packages
- Package footprint: shows footprint recommendations
- Tape and reel packing
- Sample marking pattern: describes the productive sample marking pattern on the package
- Package layout: shows a simple layout with the pin numbers described in the pin reference

*Note: Unless specified otherwise, all figure dimensions are given in mm.*

*Note: The drawings are for information only and not drawn to scale. More detailed information about package characteristics and assembly instructions is available on request.*

**5.2.1 PG-VQFN-8-4 (MFF2)**


**Package outline**



**Figure 6 PG-VQFN-8-4 package outline**


**5 Description of delivery forms**

**Package footprint**



**Figure 7 PG-VQFN-8-4 package footprint**


**Tape & reel packing**



**Figure 8 PG-VQFN-8-4 tape & reel packing**

**5 Description of delivery forms**

**Production sample marking pattern**



**Figure 9 PG-VQFN-8-4 sample marking pattern**

The dot indicates pin 01 for the chip. The “lot code” and “serial number” are defined and inserted during fabrication.

The following table describes the sample marking pattern:

**Table 11 Marking table for PG-VQFN-8-4 packages**

Indicator	Description
Line 1	EID [31 .. 24]
Line 2	EID [23 .. 16]
Line 3	EID [15 .. 8]
Line 4	EID [7 .. 0]

---

**6 Ordering information**

**6 Ordering information**

**Table 12**      **Ordering information**

<b>Salescode</b>	<b>Package</b>	
	<b>Name</b>	<b>Description</b>
OC2321	PG-VQFN-8-4 (MFF2)	OPTIGA™ Connect IoT eUICC M2M

**Terminology**

**Terminology**

**Table 13 Description of terminology**

<b>Terminology</b>	<b>Description</b>
3GPP	3rd generation partnership project
AES	Advanced encryption standard
CAT-M	LTE card application toolkit (CAT) M
CAT-TP	Card application toolkit transport protocol
CAVE	Cellular authentication and voice encryption
CDMA	Code Division Multiple Access
CLK	Clock
DES	Data encryption standard
DNS	Domain name server
EID	eUICC/UICC hardware unique Identifier
eSIM	Embedded Subscriber Identity Module
ETSI	European telecommunications standards institute
eUICC	Embedded Universal Integrated Circuit Card
GP	GlobalPlatform
ICC	Integrated Circuit Card
ISIM	IP multimedia services identity module
ISO/IEC	International organization for standardization
GSMA	Global System for Mobile Communications Association
LTE	Long-term evolution (telecommunication)
M2M	Machine to Machine
MNO	Mobile network operator
NB-IoT	NarrowBand-Internet of Things
OTA	Over the Air
PIN	Personal identification number
RAM	Random Access Memory
RAM	Remote Application Management
RFM	Remote File Management
RSA	Public-key cryptosystem (Ron Rivest, Adi Shamir and Leonard Adleman)
RSP	Remote Sim Provisioning
SGP.02	M2M specification eSIM GSMA
SIM	Subscriber Identity Module / Subscriber Identification Module

---

**Terminology**

**Table 13**            **Description of terminology (continued)**

<b>Terminology</b>	<b>Description</b>
SM-DP	Subscription Manager - Data Preparation = MNO platform connecting into the SM-SR to securely and remotely deliver profiles into eUICCs in the field
SMS	Short message service
SM-SR	Subscription Manager Secure Routing = TATA's eUICC life-cycle management platform
TLS	Transport layer security
UART	Universal Asynchronous Receiver Transmitter
UICC	Universal Integrated Circuit Card
USIM	Universal subscriber identity module



## References

### Partnership

1. **Tata Communications:** see <https://www.tatacommunications.com/solutions/mobility-iot/internet-of-things/esim/infineon-partnership/>

### Java Card Functionality

2. **Sun Microsystems Java Card™ Specification:** Virtual Machine Specification; Java Card™ Platform, Version 3.0.5.

### GlobalPlatform Functionality

3. GlobalPlatform Card Specification, Version 2.3.

### UICC Functionality

4. **ETSI TS 102 221:** Smart cards; UICC-Terminal interface; Physical and logical characteristics (Release 12).
5. **ETSI TS 102 222:** Integrated Circuit Cards (ICC); Administrative commands for telecommunications applications (Release 7).
6. **3GPP TS 31.101:** 3rd Generation Partnership Project; Technical Specification Group Core Network and Terminals; UICC-terminal interface; Physical and logical characteristics (Release 12).

### SIM Functionality

7. **3GPP TS 51.011:** 3rd Generation Partnership Project; Technical Specification Group Core Network and Terminals; Specification of the Subscriber Identity Module-Mobile Equipment (SIM-ME) interface (Release 4).
8. **3GPP TS 11.17:** 3rd Generation Partnership Project; Technical Specification Group Core Network and Terminals; Subscriber Identity Module (SIM) conformance test specification (Release 1999).

### M2M Functionality

9. **ETSI TS 102 671:** Smart Cards; Machine to Machine UICC; Physical and logical characteristics (Release 9).

### eUICC Functionality

10. **GSMA SGP.02:** Remote Provisioning Architecture for Embedded UICC. Technical Specification, Version 3.2.

---

Revision history

## Revision history

Reference	Description
<b>Revision 2.0, 2020-09-11</b>	
all chapters	Changed product name to OPTIGA™ Connect IoT
<a href="#">External connectivity</a>	Enhanced chapter external connectivity
<a href="#">Terminology</a>	Added chapter terminology
<b>Revision 1.0, 2020-04-27</b>	
	First edition

**RoHS compliance**

**RoHS compliance**

On January 27, 2003 the European Parliament and the council adopted the directives:

- 2002/95/EC on the Restriction of the use of certain Hazardous Substances in electrical and electronic equipment ("RoHS")
- 2002/96/EC on Waste Electrical and Electrical and Electronic Equipment ("WEEE")

Some of these restricted (lead) or recycling-relevant (brominated flame retardants) substances are currently found in the terminations (e.g. lead finish, bumps, balls) and substrate materials or mold compounds.

The European Union has finalized the Directives. It is the member states' task to convert these Directives into national laws. Most national laws are available, some member states have extended timelines for implementation. The laws arising from these Directives have come into force in 2006 or 2007.

The electro and electronic industry has to eliminate lead and other hazardous materials from their products. In addition, discussions are on-going with regard to the separate recycling of certain materials, e.g. plastic containing brominated flame retardants.

Infineon is fully committed to giving its customers maximum support in their efforts to convert to lead-free and halogen-free<sup>2)</sup> products. For this reason, Infineon's "Green Products" are ROHS-compliant.

Since all hazardous substances have been removed, Infineon calls its lead-free and halogen-free semiconductor packages "green." Details on Infineon's definition and upper limits for the restricted materials can be found here.

The assembly process of our high-technology semiconductor chips is an integral part of our quality strategy. Accordingly, we will accurately evaluate and test alternative materials in order to replace lead and halogen so that we end up with the same or higher quality standards for our products.

The use of lead-free solders for board assembly results in higher process temperatures and increased requirements for the heat resistivity of semiconductor packages. This issue is addressed by Infineon by a new classification of the Moisture Sensitivity Level (MSL). In a first step the existing products have been classified according to the new requirements.



<sup>2</sup> Any material used by Infineon is PBB and PBDE-free. Plastic containing brominated flame retardants, as mentioned in the WEEE directive, will be replaced if technically/economically beneficial.

## Trademarks

All referenced product or service names and trademarks are the property of their respective owners.

**Edition 2020-09-11**

**Published by**

**Infineon Technologies AG**

**81726 Munich, Germany**

**© 2020 Infineon Technologies AG**

**All Rights Reserved.**

**Do you have a question about any aspect of this document?**

**Email:**

**[CSSCustomerService@infineon.com](mailto:CSSCustomerService@infineon.com)**

**Document reference**

**IFX-gkz1572784616133**

## IMPORTANT NOTICE

The information given in this document shall in no event be regarded as a guarantee of conditions or characteristics ("Beschaffheitsgarantie").

With respect to any examples, hints or any typical values stated herein and/or any information regarding the application of the product, Infineon Technologies hereby disclaims any and all warranties and liabilities of any kind, including without limitation warranties of non-infringement of intellectual property rights of any third party.

In addition, any information given in this document is subject to customer's compliance with its obligations stated in this document and any applicable legal requirements, norms and standards concerning customer's products and any use of the product of Infineon Technologies in customer's applications.

The data contained in this document is exclusively intended for technically trained staff. It is the responsibility of customer's technical departments to evaluate the suitability of the product for the intended application and the completeness of the product information given in this document with respect to such application.

## WARNINGS

Due to technical requirements products may contain dangerous substances. For information on the types in question please contact your nearest Infineon Technologies office.

Except as otherwise explicitly approved by Infineon Technologies in a written document signed by authorized representatives of Infineon Technologies, Infineon Technologies' products may not be used in any applications where a failure of the product or any consequences of the use thereof can reasonably be expected to result in personal injury.