

Designing with pressure sensors

Solutions and technology from TE Connectivity



AUTHORIZED DISTRIBUTOR

AVNET[®] ABACUS



'Designing with pressure sensors' webinar

Thank you for joining this webinar presented by Luke Smith, Senior Product Manager, Avnet Abacus and Nicholas Argyle, Applications Engineer at TE Connectivity.

- Short introduction to Avnet Abacus and TE Connectivity
- 40 minute technical presentation
- 10 minute Q&A session



AUTHORIZED DISTRIBUTOR

03.10.2017

AVNET[®] ABACUS

Avnet Abacus and TE Connectivity partnership

Avnet Abacus is part of Avnet, a leading global distributor of electronic components.

We specialise in interconnect, sensors, wireless, passive, power supplies and battery products.

Our extensive team of technical specialists offers design and solution support to engineers across Europe.

TE Connectivity (TE) is a global technology leader, providing connectivity and sensor solutions.

With the acquisition of Measurement Specialties (MEAS), a global designer and manufacturer of sensors and sensor-based systems, TE is one of the largest sensor companies in the world.

Together we bring you a portfolio of high-performing Sensor solutions and associated technologies that enable you to transform concepts into smart connected designs across a wide range of applications



AUTHORIZED DISTRIBUTOR

AVNET[®] ABACUS

Designing with pressure sensors

The key themes we will cover in this webinar are:

- Pressure sensor base technologies – an in depth look at the products, how they are constructed, their parameters and example products
- Choosing the right pressure sensor for your application – key points for consideration
- Configuring a sensor from the datasheet
- Customisation options, when an off the shelf solution will not suffice




AUTHORIZED DISTRIBUTOR

03.10.2017

AVNET[®] ABACUS

Agenda

- 03 TESS Introduction
- 08 Pressure sensing
- 10 TE base technologies
- 12 MEMS (Micro-Electro-Mechanical Systems)
Piezo-resistive pressure sensing
- 50 Microfused – silicon strain gauge
- 54 Bonded foil strain gauge (BFSG)



03.10.2017

AUTHORIZED DISTRIBUTOR

TE Sensor Solutions (TESS) overview

PRODUCT PORTFOLIO KEY FACTS

- Portfolio includes technologies capable of measuring most physical characteristics
- Sensors used in virtually all end markets
- Specialises in custom sensing solutions
- Focus on highly engineered, application-specific solutions

KEY FACTS ABOUT SENSOR MARKET

- Global sensor market expected to grow from \$80B in 2014 to \$116B in 2019
- Sensors and connectors have common end market segments and customer base
- Sensor market is highly fragmented with few large incumbents
- Global trends of green, safe, connected and reliable systems are driving sensor and connector content growth

With a position in both sensors and connectors, TE will be able to lead in providing system-level solutions



AUTHORIZED DISTRIBUTOR

03.10.2017

AVNET[®] ABACUS

TE Sensor Solutions worldwide resources



AUTHORIZED DISTRIBUTOR

03.10.2017

AVNET[®] ABACUS

TE Sensor Solutions – Industries & Technologies

Industries Served

- Aerospace and defence
- Appliances
- Automation and control
- Consumer
- Industrial
- Intelligent buildings
- Medical
- Oil and gas
- Test and measurement

Sensor types

- Digital component
- Flow, force, humidity
- Liquid level
- Photo optic
- Piezo film
- Position, pressure, temperature
- Rate and inertial
- Scanners and systems
- Torque, ultrasonic, vibration
- Water level



TE acquired brands

MEASUREMENT SPECIALTIES

INTERSEMA

PIEZOFILM SENSORS

YSI TEMPERATURE

IC SENSORS

ENTRAN

SCHAEVITZ SENSORS

RTD COMPANY

ELEKON

MACRO SENSORS

GENTECH

ATEXIS

ENCODER DEVICES

SENTELLIGENCE

FGP SENSORS

API TECHNOLOGIES CORP

HUMIREL

WEMA

VISYX

BETATHERM SENSORS

AST

PRESSURE SYSTEMS

HL PLANER TECHNIK

SENSOTHERM

CELESCO



AUTHORIZED DISTRIBUTOR


03.10.2017

AVNET[®] ABACUS

TE sensor portfolio overview


PRESSURE SENSORS & LOAD CELLS

- MEMS Die and Oil filled
- MEMS Si Strain Gauge
- Altimeters & Barometers
- BFSG Technology




TEMPERATURE, HUMIDITY, & HEATERS

- NTC Thermistor
- Platinum & Nickel RTD
- Thermocouple
- Non-contact IR
- PTC Heaters



POSITION, ROTARY, & TILT

- LVDT/RVDT
- M-R Rotary
- Inclinometers
- AMR Magnetics
- Precision Resistive



VIBRATION & OPTICAL

- Accelerometer
- Vibration
- Rate Gyros
- Tilt
- Visible & IR





PIEZOELECTRIC SENSORS

- Piezo Polymer Film
- Liquid Level Sensors
- Air Bubble Detectors
- Contact Microphones



Pressure sensing

TE pressure sensor overview



AUTHORIZED DISTRIBUTOR

03.10.2017

AVNET ABACUS

Pressure sensing TE base technologies

Base technologies

1. MEMS Piezo-Resistive


- “Ultrastable™”
- “Harsh Media” (media isolated)

2. MEMS Silicon strain gauge

- “Microfused™” technology

3. Bonded foil strain gauge (BFSG)



- Robust applications




MEMS (Micro-Electro-Mechanical Systems)

Piezo-Resistive pressure sensing

Piezo-resistive sensor cross-section




TOP VIEW OF DIE



Wheatstone Bridge Circuit

Resistors




AUTHORIZED DISTRIBUTOR

03.10.2017

AVNET ABACUS

Principle of measurement



mV pressure die have “ratio-metric” outputs



AUTHORIZED DISTRIBUTOR

03.10.2017

Resistance measurement

- The resistors are arranged in a Wheatstone bridge

Bending of membrane

- Pressure difference between the top side and the vacuum reference (under side for differential sensors) will lead to displacement of membrane of typically 1.5 μm

Change of resistance


- The resistance of the Piezo resistors will change
- Typically 150mV full scale signal at 5V (1 bar / 14.5 PSI sensor)

Temperature Dependency

- The change in resistance is depending on the temperature \rightarrow temperature calibration is needed
- Temperature information can be taken from sensor directly

AVNET[®] ABACUS

Sensors measure extremely small stress!




0.1 mbar is equivalent to 0.1 nanometer of membrane deflection !

Pressure at sea level = 1013.25 mbar = 101.325 KPa


At sea level the atmospheric pressure decreases approx 0.1 mbar per 1 meter of altitude.

Types of sensors – uncompensated (mV)




- Do NOT have temperature compensation and do not have a calibrated zero offset
- Ratio-metric output
- Wide zero offset tolerance (i.e -5 to 20mV) @ 5V
- Wide Span tolerance (i.e 50 to 200mV) @ 5V
- Low cost option
- Requires more external circuitry and set up

Types of sensors – compensated and calibrated (mV)




- External compensation resistors to stabilise the output characteristics with variations in temperature
- Resistors mounted on ceramic hybrid (thermally stable) and laser trimmed
- Zero offset calibrated again via laser trimmed resistors. Small offset (i.e 0mV +/-2mV)
- Span adjusted for a tight tolerance. (i.e 100mV +/-2mV)

Laser Trimmed resistors




Types of sensors – amplified and digital





- Instrumentation Micro Controller / Asic is used to convert the mV signal into an Digital (I2C / SPI) signal.
- All compensation/Calibration is programmed in the Micro/Asic.
- Amplified can be Active output or D-A conversion.

Pressure sensing fundamentals

GAUGE





DIFFERENTIAL





Pressure sensing fundamentals


ABSOLUTE



SEALED GAGE



Board-mount pressure sensors



Pressure range

- 2 InH₂O to 300 psi
- Gauge, Absolute, Differential, Compound Pressures

Packages

- Ceramic and plastic SMD
- Ceramic Leaded
- TO Cans

Outputs

- mV Output.
- mV Output, Temperature Compensated.
- Amplified. 0.5 to 4.5V.
- Digital Output.

Board-mount pressure sensors

mV Uncompensated & Uncalibrated Sensors:


- MS1451

mV Compensated & Calibrated Sensors:

- 1210, 1220, 1230 & 1240
- 13, 23, 33, 43, 17, 27, 37 & 47
(TO8 package)
- MS4425 & 4426
- MS1471
- MS52xx & MS54xx.

Amplified Sensors:

- MS4515 & MS4525
- MS5525ASO (moulded package –
High quantity).



Board-mount pressure sensors

Digital Sensors (not including calibrated altimeters/barometers):

- MS4515DO & MS4525DO.
- MS5525DSO (moulded package – high quantity)
- MS5803 (abs and gel fill).
- MS5837 (abs).



Board-mount pressure sensors applications

PCB MOUNT



ALTIMETER




PNEUMATIC CONTROL



MEDICAL



HVAC AIRFLOW



AIRSPEED



AUTHORIZED DISTRIBUTOR

03.10.2017

AVNET[®] ABACUS

Altimeters and barometers



Pressure range

- 10 mbar to 2000 mbar
- Absolute

Packages

- Ceramic SMD
- DFN
- QFN

Outputs

- mV Output, Uncompensated
- Digital Output, Calibrated and Temperature Compensated

Resolution

- 14 or 24 bits



Temperature Sensor

- Digital output
- -40 to +85°C

Altimeters and barometers

- MS5607
- MS5611
- MS5637 (inc temp in device)
- MS5805 (Gel fill)
- MS8607 (inc humidity and temp in device)

NOTE: you can use ANY 1bar absolute sensor and calibrate into a altimeter/barometer



Altimeters and barometer applications


GPS NAVIGATION



HOBBY DRONE



MOBILE PHONE




WEATHER STATION



WEARABLES




SPORT WATCH



Ultra stable pressure capsules

MEMS Die – Media isolated stainless pressure cell
70 mbar (1 psi) to 666 Bar (10K psi)



AUTHORIZED DISTRIBUTOR

03.10.2017

AVNET ABACUS

Ultra stable pressure capsules



Model 82

- 19mm dia
- Low Pressure (down to 1psi)

Model 85

- 13mm dia
- Medium Pressure – High Accuracy

Model 86

- O-ring Mount
- Millivolt, Amplified or Digital outputs

Model 89

- 8mm dia
- High Pressure (up to 5000psi)

Model 154N

- 19mm dia
- O-ring Mount

Model 86D

- O-ring Mount or w/fittings
- Differential Pressure



AUTHORIZED DISTRIBUTOR

03.10.2017

AVNET[®] ABACUS

Medical applications

- Ventilators
- Oxygen concentrator
- Vaporisers
- Gas delivery (oxygen)
- Gas blenders
- CPAP
- Digital flow meters
- Nitric oxide therapy
- Drug delivery
- Inhalers (intelligent)
- Pressure therapy mattresses
- Wound therapy / drainage
- Blood pressure
- Altitude correction for gas flow



Industrial and HVAC applications

- Ink printing
- Data loggers
 - Water utility
 - Gas utility
- Gas sampling (inc portable)
- Air/Gas pressure control
- Filter / flow monitoring
- Pressure controllers
- Compressors
- Steel mills (roller pressure)
- Cryo systems
- Lab water level monitoring
- Diesel tank level monitoring
- Burner control
- Gas pressure leakage



03.10.2017

AUTHORIZED DISTRIBUTOR

AVNET ABACUS

Ultra stable pressure transmitters



Model US300

- Low cost
- Survive hostile media

Model U7100

- Small size
- Low pressure ranges available

Model U5200

- Excellent performance
- Large number of std configurations

Model U5300

- Best performance
- Rugged housing

Model D5100

- True differential measurement
- High level output

Ultra-stable pressure tx'er and capsule applications

PNEUMATIC/HYDRAULIC CONTROL



MEDICAL




AUTOMOTIVE



SENSOR BUILDING BLOCK



MANIFOLD



AUTHORIZED DISTRIBUTOR

03.10.2017

AVNET[®] ABACUS

Submersible pressure / liquid level transducer



Packaging

- Designed for hostile environments
- 316 stainless steel or titanium
- Waterproof construction
- Moisture barrier in vent tube

Performance

- Up to $\pm 0.25\%$ accuracy
- Vented gauge or sealed gauge
- 5 to 50 psi ranges
- Available with nose cone
- Available with anti-fouling front end

Applications

- Liquid level in storage tanks
- Water level in reservoirs and lakes
- Sewage treatment
- Salt water and brine depth

Submersible pressure / liquid level transducer applications

IRRIGATION WATER LEVEL



SEWAGE TREATMENT



STORAGE TANK LEVEL



WATER QUALITY MONITORING



Microfused Silicon strain gauge


Microfused™ silicon strain gauge pressure sensor

3.5 BAR (50 PSI) TO 1K BAR (15K PSI)




Model MSP-300

Wheatstone Bridge




Front end is machined from a single piece of stainless steel very high reliability



2 Thin area flexes in reaction to the pressure

1 Pressure applied to sensor port

3 Piezo resistive strain gauges change value in reaction to the flex



Microfused pressure sensors



MSP-100



MSP-300



MSP-340



M5100



M7100

Pressure range

- 15 psi to 30,000 psi
- Gauge, absolute

Packages

- Threaded port (male & female)
- Hermetic front end
- Compensation and gain in package

Outputs

- mV Output, uncompensated
- 0.5V to 4.5V compensated
- 1.0V to 5.0V compensated
- 4 to 20 mA compensated
- Cable or connector interface

Microfused pressure sensor applications

REFRIGERATION



MEDICAL GAS



HYDRAULIC SYSTEMS



PAINT SPRAYER



PNEUMATIC CONTROLS



INDUSTRIAL PROCESS




COMPRESSOR





Bonded foil strain gauge (BFSG)

Bonded foil strain gauge (BFSG)



RANGES FROM 0 TO 5BAR, UP TO 7KBAR.
VERY HIGH OVERPRESSURE.



- The principle of the transducer is a force-summing diaphragm coupled via a force rod (pushrod) to a strain-gauged double cantilever beam with integral isolation, forming a four-arm Wheatstone bridge in a very symmetrical manner.
- This sensor assembly transduces the force applied to the sensor diaphragm into a millivolt output.
- This construction has very high over pressure capabilities!

BFSG PRODUCTS

ANALOGUE SINGLE END MEASUREMENT:

- P700 (amplified, 4-20mA)
- P900 (amplified, 4-20mA)
- P981 (amplified, 4-20mA)
- P1200 (amplified, 4-20mA)
- P9000 (amplified, 4-20mA)
- P101 (mV, amplified)
- P105 (mV, amplified)
- P125 (mV, amplified)



AUTHORIZED DISTRIBUTOR

03.10.2017

AVNET[®] ABACUS

Determining what pressure sensor to use

- What is the application?
- What is the media (dry gas / air or liquid)?
 - If liquid – media isolated cells or transmitters (exception – if moist liquid and for short duration, you can look at gel filled board mount sensor)
 - If Air/Dry Gas – any sensor
- What is the pressure range?
- Do you want to measure gage, absolute, differential or sealed gage?
- What is the required output (mV, amplified, digital or other)?
- Do you require board mount, media isolated cell or transmitter?
- What is the process connection (cells / transmitters – i.e ¼” BSP thread)?
- What electrical interface on the rear (cable, M10, other etc)?
- What is the required temp range (operating and compensated range)?
- Any IP rating (IP65, IP67 etc)?
- Quantity?



Configuring a sensor from the datasheet

ORDERING INFORMATION

4525DO	-	DS	3	A	I	004	G	P	
Model	-	Package Style	Supply Voltage	Output Type	Interface Type	Pressure Range (psi)	Pressure Type	Pin Style	Option Type
MS4525DO	-	SS = Single Sideport DS = Dual Sideport TP = Top Port MM = Manifold Mount	3 = 3.3 Vdc 5 = 5.0 Vdc	A = 10% to 90% B = 5% to 95%	I = I ² C (Addr.0x28H) J = I ² C (Addr.0x36H) K = I ² C (Addr.0x46H) S = SPI (not available for 'L' pin style) 0 = I ² C (Addr.0x48H) : : 9 = I ² C (Addr.0x51H)	001 002 005 015 030 050 100 150	A = Absolute D = Differential G = Gage C = Compound V = Vacuum	P = Thru Hole S = J Lead L = In Line	Blank = No Option F = Gel Coating L = Low Power M = Gel Coating and Low Power

Example: 4525DO-DS3AI005DPL

Model 4525DO, Dual Sideport, 3.3V, 10-90%, I2C addr 0x28H, 5psi, Differential, Thru hole, Low power.



AUTHORIZED DISTRIBUTOR

03.10.2017

AVNET[®] ABACUS

Value add – customisation

Board mount sensors:

- Special calibrations (i.e -30 to 200mBar) – easier with Asic based sensors
- Different Ports – mould tools required
- Gel coatings for media resistance

Media isolated sensors:

- Special threads. (quick connect etc)
- Potted rear electronics
- Cable length / type
- Connectors

Transmitters:

- Threads
- Cables
- Housing



Q&A and further resources

There will now be a 10-minute Q&A

Further resources – [click here to:](#)

- speak to one of our technical specialists in your local language
- download the Avnet Abacus white paper *Pressure sensors, design considerations and technology options*
- read the TE sensor overview
- view TE sensor products highlights and order a sensor tag demo kit
- download Avnet Abacus' sensor solutions brochure
- Listen to a recording of this webinar (available 48 hours after the webinar)
- share the on-demand version with your colleagues
- Download the full slide deck, along with additional information we didn't have time to include



AUTHORIZED DISTRIBUTOR

03.10.2017

AVNET[®] ABACUS



Thank you!

TE Connectivity and the TE connectivity (logo) are trademarks of the TE Connectivity Ltd. family of companies. Other logos, product and/or company names might be trademarks of their respective owners.



AUTHORIZED DISTRIBUTOR

03.10.2017

AVNET[®] ABACUS