



life.augmented



STM32MP1 microprocessor broadening STM32 MPU family

Press Presentation





life.augmented

**“ If only
I could make
a Smart Home Gateway
with advanced HMI and HD video**

Advanced HMI with graphics and video on top of real time applications



HD video decode
with Dual Arm Cortex-A7 @ 800 MHz

Better user experience
powered by advanced 3D GPU

Wide range of partners ready to support
you on many topics:
Graphics, HW & SW Services...

Seamless and flexible combination of
audio and real time processing
with Cortex-A + Cortex-M architecture





life.augmented

“ If only
I could find
an Industrial grade processor
for my applications

Industrial grade microprocessor for demanding applications



Industrial qualification combining both:
100% operating time during 10 years
Junction temperature: - 40°C to 125°C

10 years longevity commitment
renewed every year

Industrial connectivity, advanced analog
Cortex-M4 for real time processing

Advanced security for Industry 4.0

4 packages available in pitch 0.5 & 0.8mm



life.augmented

“If only
I could easily
improve my applications
with Artificial Intelligence

Embedding various Neural Networks for cutting-edge applications



TensorFlow Lite native support running on Cortex-A7 / Linux



STM32Cube.AI tool for machine learning running on Cortex-M4



Camera and audio interfaces to simplify input devices' integration




STM32MP1 - Constantly Improving



Boosting performances
with Dual Cortex-A7 @ 800MHz



A broader STM32 MPU ecosystem
to reduce development time & cost




Boosting performances with Dual Cortex-A7 @ 800MHz




Boosting performances Broadening possibilities

Pin to pin compatibility across all part numbers
Full HW compatibility with STPMIC1

SW compatibility
across the family



@ 650 MHz



@ 800 MHz




A Scalable Solution to best meet customers' needs

Boosting application possibilities

Graphic and communication
High Performance processing
up to 3040 DMIPS

Real-time & Low Power applications
260 DMIPS



Secure architecture for trusted devices



ENCRYPTION DECRYPTION AUTHENTICATION

- Duplicated resources on Cortex-A7 and Cortex-M4
 - Crypto and Hash Hardware Engines
 - TRNG
- Secure boot (ROM)
- Unique ID



CONFIDENTIALITY ANTI-TAMPERING

- TrustZone
- Secure RAMs and Peripherals
- Secure RTC with Active Tamper
- T°, V and 32KHz sensor monitoring
- Cortex-M4 resources HW isolation
- Secure OS support: OP-TEE



SECURE MANUFACTURING

- Paired Keys Tools Generator
- Signing Tools for boot
- Development and production programmers with provisioning and authentication

Some of the above features are optional and require to procure dedicated part numbers. Please refer to product specification

A broader STM32 MPU ecosystem to reduce development time & cost



Enhance your added value by relying on ST and authorized Partners' solutions



Solutions for EDGE computing & IoT
from sensors up to the Cloud

Simplifying Android™ development

A growing base of ST Authorized Partners

ST continuous investment into the most
recognized Open Source standards

Android is a trademark of Google LLC.

Create cloud based applications with STM32MP1 solutions

Complete support of main cloud provider





qualified device



Microsoft Azure IoT Platform

IBM Watson support soon



Example of STM32MP1 Discovery board used for EDGE processing

Simplifying Android™ development



Reduce development time & cost with pre-build Solutions provided by ST:

- Free of charge AOSP enablement
- Various Android™ packages


Extra headroom (up to 800MHz Cortex-A) for better user experience

Exclusive plug-in to bridge real-time Cortex-M and Android environments provided in the SDK

Android is a trademark of Google LLC.

Continuous investment in Linux to make customers' design simpler and more efficient

ST is continuously upstreaming Linux drivers to the Linux community





A growing base of partners addressing customers' challenges

Embedded Software

CRANK SOFTWARE

Embedded Wizard
GUI Solutions by TARA Systems

ENEAA

Prevas

Linaro

PHYTEC

Qt

PROVE & RUN

timesys®

Witekio
EMBEDDING SUCCESS

Software Development Tools

ac6

arm KEIL

CRANK SOFTWARE

Linaro

IAR SYSTEMS

Qt

timesys®

Training

ac6

bootlin

DOULOS

DK electronics

ENEAA

INNOWave
Inspire the next

HO
HandsOnTraining

IAR SYSTEMS

PHYTEC

timesys®

Witekio
EMBEDDING SUCCESS

Components and Modules

bytesatwork

DK electronics

EmCraft systems

emtrion
embedded systems

ENGICAM®
Custom Electronic Solutions

KARO electronics

kontron

oO OCTAVO SYSTEMS

PHYTEC

SoMLabs

Engineering Services

ac6

bootlin

CRANK SOFTWARE

DK electronics

EmCraft systems

emtrion
embedded systems

INNOWave
Inspire the next

KARO electronics

Prevas

Linaro

PROVE & RUN

Pengutronix.

timesys®

Qt

Witekio
EMBEDDING SUCCESS

STM32MP1 Line-up





Expanding the STM32MP1 portfolio now 48 part numbers

NEW



MPU
@ 800 MHz

STM32 MP151D	MP151F
1520 + 260 DMIPS	-
800 MHz Cortex-A7	-
209 MHz Cortex-M4	-
	Security

STM32 MP153D	MP153F
3040 + 260 DMIPS	-
800 MHz 2x Cortex A7	-
209 MHz Cortex-M4	-
CAN FD	Security

STM32 MP157D	MP157F
3040 + 260 DMIPS	-
800 MHz 2x Cortex-A7	-
209 MHz Cortex -M4	-
CAN FD - 3D GPU - DSI	Security



MPU
@ 650 MHz

STM32 MP151A	MP151C
1235 + 260 DMIPS	-
650 MHz Cortex-A7	-
209 MHz Cortex-M4	-
	Security


STM32 MP153A	MP153C
2470 + 260 DMIPS	-
650 MHz 2x Cortex-A7	-
209 MHz Cortex-M4	-
CAN FD	Security

STM32 MP157A	MP157C
2470 + 260 DMIPS	-
650 MHz 2x Cortex-A7	-
209 MHz Cortex-M4	-
CAN FD - 3D GPU - DSI	Security



All references are available in 4 Packages

- TFBGA257 10x10mm p0.5 (4 layers PTH PCB) - smallest package for dual Cortex-A GP MPU
- TFBGA361 12x12mm p0.5 (4 layers PTH + Laser via PCB)
- LFBGA354 16x16mm p0.8 (4 layers PTH PCB)
- LFBGA448 18x18mm p0.8 (6 layers PTH PCB)



All parts are software and pin to pin compatible

Arm® Cortex® core

Cortex-A7 + Cortex-M4


Dual Cortex-A7 + Cortex-M4



life.augmented



Building the future STM32 MPU portfolio expansion





STM32MP1 - your new companion for advanced applications



Boosting performances
with Dual Cortex-A7 @ 800MHz



A broader STM32 MPU ecosystem
to reduce development time & cost

Releasing your creativity



[/STM32](#)



[@ST_World](#)



[community.st.com/stm32mpu](#)



[www.st.com/STM32MP1](#)




STM32MP157 block diagram



*available for STM32MP157C and STM32MP157F only

Flexible architecture for power efficiency


Power figures at 650MHz



Typ @ VDDCORE = 1.2V, VDD = 3.3V @ 25 °C, Peripherals OFF

Flexible architecture for power efficiency


Power figures at 800MHz



Typ @ VDDCORE = 1.2V, VDD = 3.3V @ 25 °C, Peripherals OFF

STPMIC1 power management IC dedicated to STM32MP1 MPU

Simplify your design and optimize power consumption



DC/DCs & LDOs for

- STM32MP1
- Memories
- External devices

Optimized power consumption

BOM savings for typical applications

Small PCB footprint vs. full discrete solution

Thank you

© STMicroelectronics - All rights reserved.

The STMicroelectronics corporate logo is a registered trademark of the STMicroelectronics group of companies. All other names are the property of their respective owners.



life.augmented