



ON Semiconductor®

www.onsemi.com

Color Correction Matrix Usage in Sensor Studio

Overview

This document provides an overview of the color correction matrix that is used in the SensorStudio evaluation software. The document is not intended to be a tutorial for deriving a color correction matrix. The document will provide information to convert the supplied color correction matrix into a device-independent color space (CIE XYZ).

Color Correction Matrix

The purpose of the color correction matrix in SensorStudio is to transform camera RGB values into RGB values suitable for viewing on a display. The camera RGB data is expected to vary linearly with exposure. The camera RGB data is also normalized. This includes white balance and black level correction.

The color correction matrix can be expressed as a 3x3 matrix as shown in Equation 1 below. The 'cc' is used to denote the color corrected RGB values.

$$\begin{pmatrix} R_{CC} \\ G_{CC} \\ B_{CC} \end{pmatrix} = \begin{pmatrix} a_{11} & a_{12} & a_{13} \\ a_{21} & a_{22} & a_{23} \\ a_{31} & a_{32} & a_{33} \end{pmatrix} \begin{pmatrix} R_{CAMERA} \\ G_{CAMERA} \\ B_{CAMERA} \end{pmatrix} \quad (\text{eq. 1})$$

The relationship between linear RGB values and the XYZ values for a display may be expressed by a 3x3 matrix as shown in Equation 2 below. Equation 2 is computed such that RGB values of 100 will produce XYZ values corresponding to Illuminant D65. (RGB values equal to 100 correspond to those values which would be obtained for a perfectly reflecting, spectrally non-selective object located in the scene and illuminated by daylight at a correlated color temperature of 5,500 Kelvin.) The matrix given in Equation 2 is based on the CCIR Rec. 709 (HDTV).

$$\begin{pmatrix} X \\ Y \\ Z \end{pmatrix} = \begin{pmatrix} 0.41214 & 0.35768 & 0.18036 \\ 0.21251 & 0.71535 & 0.07214 \\ 0.01932 & 0.11923 & 0.94988 \end{pmatrix} \begin{pmatrix} R_{CC} \\ G_{CC} \\ B_{CC} \end{pmatrix} \quad (\text{eq. 2})$$

To compute a color correction matrix for the camera whose output is directly compatible with a device-independent color space such as CIE XYZ, cascade the results of Equations 1 and 2.

Example Color Correction Matrix

The following sets of color correction matrix coefficients were computed for CMOS and Interline Transfer CCD products and are implemented in SensorStudio. The example sets of color correction matrix coefficients correspond to the 3x3 matrix in Equation 1. The matrix converts camera RGB values (D50) into RGB values based on the CCIR Rec. 709 (HDTV). The coefficients are also dependent upon the IR-cut filter transmission data that was used in the calculation. Cascading an example matrix with

APPLICATION NOTE

Equation 2 will produce a color correction matrix with output in CIE XYZ.

The following sets of color correction matrix coefficients apply to both the Bayer color filter pattern and the Sparse color filter pattern. There are two sets of color filter array (CFA) – Gen1 CFA and Gen2 CFA.

Gen1 CFA Devices

- KAI-01050 (–CBA)
- KAI-01150 (–CBA or –PBA)
- KAI-02050 (–CBA)
- KAI-02150 (–CBA or –PBA)
- KAI-04050 (–CBA or –PBA)
- KAI-08050 (–CBA or –PBA)

1.75815	-0.49027	-0.26788
-0.19781	1.36582	-0.16800
0.21167	-0.84224	1.63057

Gen2 CFA Devices

- KAI-01050 (–FBA)
- KAI-01150 (–FBA or –QBA)
- KAI-02050 (–FBA)
- KAI-02150 (–FBA or –QBA)
- KAI-04050 (–FBA or –QBA)
- KAE-02150 (–FXA)

1.609774	-0.486341	-0.123434
-0.212176	1.532584	-0.320408
0.077655	-0.768204	1.690549

Gen2 CFA Devices

- KAI-08051 (–FBA, –FXA, –QBA or –QXA)
- KAE-08151 (–FXA)

1.595753	-0.476962	-0.118791
-0.201963	1.511913	-0.309950
0.078553	-0.729681	1.651128

AND9334/D

Gen1 CFA Devices

- KAI-16050 (-CXA or -PXA)
- KAI-29050 (-CXA or -PXA)

1.61673	-0.40321	-0.21351
-0.17718	1.36415	-0.18697
0.17376	-0.445	1.60167

Gen2 CFA Devices

- KAI-16050 (-FXA or -QXA)
- KAI-29050 (-FXA or -QXA)

1.59327	-0.40003	-0.19324
-0.20214	1.45308	-0.25094
0.10820	-0.76306	1.65487

Gen1 CFA Devices

- KAI-02170 (-CBA or -PBA)
- KAI-04070 (-CBA or -PBA)

1.58947	-0.39252	-0.19696
-0.13829	1.29576	-0.15747
0.13161	-0.64129	1.50968

Gen2 CFA Devices

- KAI-02170 (-FBA or -QBA)
- KAI-04070 (-FBA or -QBA)
- KAE-04471 (-FXA)

1.508631	-0.386366	-0.122265
-0.136752	1.352568	-0.215816
0.050764	-0.599392	1.548628

Gen1 CFA Devices

- KAI-16070 (-CXA or -PXA)

1.55429	-0.35465	-0.19964
-0.11303	1.27316	-0.16013
0.11427	-0.58609	1.47182

Gen2 CFA Devices

- KAI-16070 (-FXA or -QXA)

1.447288	-0.311429	-0.135859
-0.145714	1.334572	-0.188858
0.061099	-0.528920	1.467821

Gen1 CFA Devices

- KAC-06040-CBA
- KAC-12040-CBA
- NOIPxSEyyy (PYTHON Family Bayer Color)

1.528800	-0.418920	-0.109880
-0.274660	1.527000	-0.252340
0.002970	-0.731280	1.728310

Gen2 CFA Devices

- KLI-2113 (-RAA)

1.53236	-0.38047	-0.15188
-0.14424	1.32805	-0.18381
0.00883	-0.66326	1.65443

Gen2 CFA Devices

- KAI_11002 (-FBA or -QBA)

1.54624	-0.42947	-0.11677
-0.16610	1.43593	-0.26982
0.04549	-0.63964	1.59415

Gen2 CFA Devices

- KLI-4104 (-RAA)

1.49837	-0.35122	-0.14715
-0.12511	1.27902	-0.15391
0.00596	-0.60056	1.59460

Gen2 CFA Devices

- KLI-8023 (-RAA)

1.52057	-0.36110	-0.15947
-0.13315	1.31159	-0.17843
-0.00772	-0.64123	1.64895

Gen2 CFA Devices

- KAE-02152 (-FXA)
- KAI-08052 (-FXA, -QXA)

1.60391	-0.47296	-0.13095
-0.23423	1.50472	-0.27050
0.06969	-0.88184	1.81215

Gen2 CFA Devices

- KAI-29052 (-FXA)

1.52858	-0.36103	-0.16756
-0.26707	1.53551	-0.26844
0.03732	-0.88273	1.84542

ON Semiconductor and  are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of ON Semiconductor's product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using ON Semiconductor products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by ON Semiconductor. "Typical" parameters which may be provided in ON Semiconductor data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. ON Semiconductor does not convey any license under its patent rights nor the rights of others. ON Semiconductor products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use ON Semiconductor products for any such unintended or unauthorized application, Buyer shall indemnify and hold ON Semiconductor and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that ON Semiconductor was negligent regarding the design or manufacture of the part. ON Semiconductor is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

PUBLICATION ORDERING INFORMATION

LITERATURE FULFILLMENT:

Literature Distribution Center for ON Semiconductor
19521 E. 32nd Pkwy, Aurora, Colorado 80011 USA
Phone: 303-675-2175 or 800-344-3860 Toll Free USA/Canada
Fax: 303-675-2176 or 800-344-3867 Toll Free USA/Canada
Email: orderlit@onsemi.com

N. American Technical Support: 800-282-9855 Toll Free
USA/Canada
Europe, Middle East and Africa Technical Support:
Phone: 421 33 790 2910

ON Semiconductor Website: www.onsemi.com
Order Literature: <http://www.onsemi.com/orderlit>

For additional information, please contact your local Sales Representative